



A TIME AND PLACE *for everything™*

TW3070 Permanent Mount GPS L1 Antenna


The TW3070 by Tallysman Wireless is a professional grade, permanent mount GPS L1 antenna, specially designed for professional precision timing applications.

The TW3070 features a custom high performance, wide band patch element, a 40dB gain LNA stage and a high rejection out-of-band SAW filter. It provides ± 10 MHz bandwidth centred on 1575.42 MHz and covers the GPS L1, Galileo E1 and SBAS (WAAS/EGNOS/MSAS) signals, and it provides great axial ratio, excellent circular polarized signal reception, great multipath rejection and great out-of-band signal rejection.

The TW3070 is housed in a compact, industrial-grade weather-proof, domed shaped enclosure. Its radome is available in dark gray or white, it comes with a TNC female connector, and a L-bracket for mast mount is available (P/N#23-0040-0).



TW3070 Dimensions (mm)



Applications

- High Accuracy, Mission Critical GPS Timing
- Military & Security
- Network Timing and Synchronisation

Features

- Great axial ratio
- Low noise LNA: 1 dB
- High rejection SAW filter
- High gain: 40 dB typ.
- Low current: 15 mA typ.
- ESD circuit protection: 15 KV
- Wide voltage input range: +3.0 to 10 VDC
- Weather proof housing: IP67

Benefits

- Excellent multipath rejection
- Increase system accuracy
- Excellent signal to noise ratio
- Great out of band signal rejection
- Ideal for harsh environments
- RoHS compliant



A TIME AND PLACE *for everything™*

TW3070 Permanent Mount GPS L1 Antenna

Specifications

Vcc = 3V, over full bandwidth, T=25°C

Antenna

Antenna Element Gain (100mm ground plane)
Axial Ratio (over full bandwidth)

4 dBic at 90°
4 dB at 90°

Electrical

Architecture

3 stage LNA circuit + a mid section SAW filter.
(Pre-filter option available)

Frequency Bandwidth

1575 MHz ± 10 MHz

Polarization

RHCP

Gain

40 dB min. (at 1575.42 MHz)

Out-of-Band Rejection

<1560 MHz

>42 dB

>1600 MHz

>31 dB

>1620 MHz

>45 dB

VSWR (at LNA input)

<1.5:1

Noise Figure

1 dB typ.

Supply Voltage Range

+3.0 to 10 VDC nominal

Supply Current

15 mA typ.

ESD Circuit Protection

15 KV air discharge

Mechanicals & Environmental

Mechanical Size

66.5 mm dia. x 47.5 mm H

Connector / Cable

TNC female bulkhead / Custom cable assembly available

Operating Temp. Range

-40 to +85 °C

Enclosure

Radome: Dark Gray or White ASA Plastic

Base: Zamak White Metal

Weight

150 g

Attachment Method

L-Bracket option: P/N# 23-0040-0

Environmental

IP67 and RoHS compliant

Shock

Vertical axis: 50 G, other axes: 30 G

Vibration

3 axis, sweep = 15 min, 10 to 200 Hz sweep: 3 G

Warranty

One year – parts and labour

Ordering Information

TW3070 – GPS L1 antenna, dark gray, TNC connector

32-3070-0-00

TW3070 – GPS L1 antenna, white, TNC connector

32-3070-0-01

Please contact Tallysman Wireless additional information

Tallysman Wireless Inc

106 Schneider Road, Unit 3

Ottawa ON K2K 1Y2 Canada

Tel 613 591 3131

Fax 613 591 3121

sales@tallysman.com

The information provided herein is intended as a guide only and is subject to change without notice. This document is not to be regarded as a guarantee of performance. Tallysman Wireless Inc. hereby disclaims any or all warranties and liabilities of any kind. © 2011 Tallysman Wireless Inc. All rights reserved.

Doc # 60-0075-0

Rev 1.0