

Straight Blade Devices

TVSS Straight Blade Receptacles

15 & 20A, 125VAC

Pass & Seymour



Specifications


- UL1449 (latest revision). (1.2 x 50μs 6000V, 8 x 20μs 3000A).
- 1 filtering capacitor for 7 to 1 average noise reduction.
- Nominal let-through (suppressed) voltage in all 3 modes, 500V.
- Response time less than 1 nanosecond for unmounted MOV.
- Overcurrent protection in all 3 modes.
- Electronic components potted for electrical, mechanical and thermal stability.
- Thermal protection in all 3 modes.
- Leakage current: 0.5mA at 25°C/120VAC.
- 3 18mm dual pack MOVs to suppress transients in all modes – equally.
- Common mode noise attenuation: 500 KHz to 30 MHz; up to 35dB (50 ohm source impedance)
- Varistor voltage: 150V RMS.
- Back and side wire capability including ground terminal.
- Operating temperature: -40°C to 85°C (-40°F to 185°F)
- Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.

Specification, Hospital and Isolated Ground Receptacles


- Audible alarm able to be turned on/off.
- LED indicator light.
- 210 joules of energy absorption in each of the three modes.
- 13,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.
- Isolated Ground version complies with NEC 410-56 (C) and 250-74 exception 4.

Commercial Receptacles

- LED indicator light.
- 130 joules of energy absorption in each of the three modes.
- 9,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.




8200-ISP



IG8300-ISP

2 Pole, 3 Wire




All devices listed on this page conform to NEMA WD-1 and WD-6.


Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE587), ANSI/IEEE C62.45.

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance			


Pass & Seymour



5262-ISP



IG5362-ISP



5252-ISP

2 Pole, 3 Wire

NEMA
5-15RNEMA
5-20R

Straight Blade Devices TVSS Straight Blade Receptacles

15 & 20A, 125VAC

Catalog Number	Rating A. VAC		Color	NEMA Config. No.	3rd Party Compliance			
					UL1449	UL498	FSUL WC596	cUL/CSA
Extra Heavy-Duty Spec. Grade Duplex Receptacles Back & Side Wire*								
5262-ISP	15	125	Ivory	5-15R	•	•	•	•
5262-WSP	15	125	White	5-15R	•	•	•	•
5262-SP	15	125	Brown	5-15R	•	•	•	•
5262-GRYSP	15	125	Gray	5-15R	•	•	•	•
5262-REDSP	15	125	Red	5-15R	•	•	•	•
5262-LASP	15	125	Light Almond	5-15R	•	•	•	•
5262-BLSP	15	125	Blue	5-15R	•	•	•	•
5362-ISP	20	125	Ivory	5-20R	•	•	•	•
5362-WSP	20	125	White	5-20R	•	•	•	•
5362-SP	20	125	Brown	5-20R	•	•	•	•
5362-GRYSP	20	125	Gray	5-20R	•	•	•	•
53								