


PART NUMBER	C THREAD CLASS 2B	E DIA ±.005	K DIA MAX	R +.000 -.010	T THREAD CLASS 2A	RELEASE	MADE FROM
10-123011-6	.3125-32 UNEF	.190	.469	.215	.3750-32 UNEF	31508-287	10-123011- 6B
- 8	.4375-28 UNEF	.312	.594		.5000-28 UNEF		- 8B
-10	.5625-24 UNEF	.436	.719		.6250-24 UNEF		-10B
-12	.6875-24 UNEF	.561	.844		.7500-20 UNEF		-12B
-14	.8125-20 UNEF	.678	.969		.8750-20 UNEF		-14B
-16	.9375-20 UNEF	.802	1.094		1.0000-20 UNEF		-16B
-18	1.0625-18 UNEF	.894	1.219		1.1875-18 UNEF		-18B
-20	1.1875-18 UNEF	1.029	1.312	.312	1.1875-18 UNEF		-20B
-22	1.3125-18 UNEF	1.150	1.469		1.4375-18 UNEF		-22B
-24	1.4375-18 UNEF	1.274	1.594		1.4375-18 UNEF	33524-599	-24B

REL NO. 31508-287		REVISIONS			
CHG NO.	SYM	DESCRIPTION	DATE	APPROVED	
43525-746	A1	REDRAWN, WAS SIZE "B" TYPE WRITTEN; PROVIDED ENVELOPE DWG	11-21-64 W. GAY	[Signature]	
47524-170	A2	ADD & REL -XX9 FINISH	11-1-65 [Signature]	[Signature]	
55524-58	A3	ADD & REL -XXG FINISH	11-1-67 DEMATTIO	[Signature]	
72028-54	B	(CL II) ADD & REL -XX7 FINISH	5/12/81 [Signature]	[Signature]	
76484-1	C	(CL II) ADDED MADE FROM COLUMN	11-2-81 [Signature]	[Signature]	
80-44-1	D	(CL II) ADDED 9-3 SPEC TO NOTE 1	9-1-88 [Signature]	[Signature]	
82906	E	(CL II) ADD & REL -XXY FINISH	3-5-97 JED	[Signature]	
85035	F	ADD AND RELEASE -XXY FINISH & DATA	4-1-93 [Signature]	[Signature]	
85448	G	(CL II) SEE ECU: 85448	4-27-99 JED	[Signature]	
86546	H	(CL II) ADD & RELEASE -XXU FINISH & DATA	4-28-99 JED	[Signature]	



3. REF SYMBOL

2. THREADS ARE IN ACCORDANCE WITH
FEDERAL HANDBOOK H-28.

1. TO COMPLETE PART NO., ADD APPLICABLE LAST
DIGIT TO SUFFIX FOR DESIRED FINISH.

CHROMATE TREAT	SUFFIX - XX0
CADMIUM PLATE	SUFFIX - XX1
BLACK ANODIZE	SUFFIX - XX2
CADMIUM PLATE OLIVE DRAB	SUFFIX - XX3
GREY ANODIZE	SUFFIX - XX4
ANODIC COATING	SUFFIX - XX5
BRIGHT CADMIUM PLATE, NICKEL BASE	SUFFIX - XX7
NICKEL ALLOY PLATE	SUFFIX - XXG
CAD PLATE, O.D., NICKEL BASE	SUFFIX - XX9
BRIGHT NICKEL	SUFFIX - XX8
BLACK ZINC ALLOY PLATE	SUFFIX - XXY
BLACK ZINC CONDUCTIVE	SUFFIX - XXX

RELEASE NO.	
38524-872	9-3350 GREEN ZINC
35524-218	9-2158 ALLOY PLATE
35524-218	9-3487 SUFFIX -XXU 9-9263
32525-260	9-3047
31508-287	9-3487
35508-72	9-3290
55524-58	9-4332
47524-170	9-6914
42524-249	9-4960
	9-3435
	9-9181
	9-9181-1

ITEM NO.	QTY REQD	DESCRIPTION	PART NUMBER	CODE IDENT	ZONE
PARTS LIST					
UNLESS OTHERWISE SPECIFIED		DRAWN: HAYES	DATE: 7-12-56	NEXT ASSEMBLY	
LINEAR DIMENSIONS ARE IN INCHES. TOLERANCES: 3 PLACES ±.010; 2 PLACES ±.03; 1 PLACE ±.1; ANGLES ±2°. OTHER STANDARDS PER SCINTILLA SPEC 9-3800 AND MIL-STD 8.		CHECKED: Teelon	DATE: 4-7-65		
MATERIAL SPEC ALUMINUM ALLOY		MATERIAL:	STANDARDS: J. Balantieri 4-7-65	TITLE: ADAPTER, ELECTRICAL CONNECTOR, TYPE PB(), (ENVELOPE DRAWING)	
PROCESS SPEC		DRAFTING: D Sweet 4-7-65	ENGINEERING: W. J. Harrison 4-7-65	CODE IDENT NO. 77820	
		DEVELOPMENT:		SIZE C	10-123011
				SCALE NONE	WT
				REF	SHEET

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[10-123011-183](#) [10-123011-08G](#) [10-123011-18G](#) [10-123011-20G](#) [10-123011-081](#) [10-123011-083](#) [10-123011-103](#)
[10-123011-105](#) [10-123011-10G](#) [10-123011-123](#) [10-123011-125](#) [10-123011-12G](#) [10-123011-143](#) [10-123011-14G](#)
[10-123011-163](#) [10-123011-16G](#) [10-123011-203](#) [10-123011-223](#) [10-123011-22G](#) [10-123011-145](#) [10-123011-16Y](#)
[10-123011-122](#) [10-123011-165](#) [10-123011-085](#) [10-123011-243](#) [10-123011-20X](#) [10-123011-10X](#) [10-123011-185](#) [10-](#)
[123011-225](#) [10-123011-20Y](#) [10-123011-141](#) [10-123011-181](#) [10-123011-16X](#) [10-123011-12X](#) [10-123011-12Y](#) [10-](#)
[123011-08X](#) [10-123011-14X](#) [10-123011-18X](#) [10-123011-22X](#) [10-123011-14Y](#) [10-123011-10Y](#) [10-123011-121](#)