

10072353-X01-XXXLF

S = 0.38 μ m GOLD/GXT DN CONTACT AREA
2.0 μ m MIN MATTE TIN DN TAIL

ROHS COMPATIBLE
NOTE 6

G = 0.76μm GOLD/GXT ON CONTACT AREA
2.0μm MIN MATTE TIN ON TAIL

PACKAGING NOTE 5

F = GOLD FLASH ON CONTACT AREA
2.0μm MIN MATTE TIN ON TAIL

NB OF POSITIONS PER ROW
02 TO 25 PDS

1.27 μm MIN NICKEL UNDERPLATING

1. MATERIAL HOUSING: HIGH TEMP. THERMOPLASTIC
UL 94V-0, COLOR BLACK

2. MATERIAL TERMINAL: COPPER ALLOY

2. MATERIAL TERMINAL: COPPER ALLOY

3. TO DETERMINE DIMENSIONS:

N = NUMBER OF POSITIONS PER ROW.

4. 7N MIN PIN RETENTION IN EITHER DIRECTION.

5. PACKAGING :

= PLASTIC BOX

U = TUBE AVAILABLE FROM 06 TO 50 PDS
6. ROHS COMPATIBLE PRODUCT SPECIFICATIONS

α - PLATING

= "LF" MEANS THE PRODUCT IS LEAD-FREE

2 μ m MINIMUM MATTE TIN OVER 1.27 μ m
MINIMUM NICKEL UNDERPLATE.



b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDS MAX IN A CONVECTION, INRA-RED DR VAPOR PHASE OR REFLOW OVEN.

C - LABELLING:

- MEETS PACKAGING SPECS AS PER GS-14-920.

d - THIS PRODUCT MEETS EUROPEAN DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DISCRIBED
IN GS-47-0004



Copyright FCI.

[illegible]