



## PNP Silicon AF Transistor Array

- For AF input stages and driver applications
- High current gain
- Low collector-emitter saturation voltage
- Two ( galvanic) internal isolated Transistors with good matching in one package



| Type   | Marking | Pin Configuration |      |      |      |      |      | Package |
|--------|---------|-------------------|------|------|------|------|------|---------|
| BC857S | 3Cs     | 1=E1              | 2=B1 | 3=C2 | 4=E2 | 5=B2 | 6=C1 | SOT363  |

### Maximum Ratings

| Parameter                                      | Symbol    | Value       | Unit |
|------------------------------------------------|-----------|-------------|------|
| Collector-emitter voltage                      | $V_{CEO}$ | 45          | V    |
| Collector-base voltage                         | $V_{CBO}$ | 50          |      |
| Collector-emitter voltage                      | $V_{CES}$ | 50          |      |
| Emitter-base voltage                           | $V_{EBO}$ | 5           |      |
| DC collector current                           | $I_C$     | 100         | mA   |
| Peak collector current                         | $I_{CM}$  | 200         |      |
| Total power dissipation, $T_S = 115\text{ °C}$ | $P_{tot}$ | 250         | mW   |
| Junction temperature                           | $T_j$     | 150         | °C   |
| Storage temperature                            | $T_{stg}$ | -65 ... 150 |      |

### Thermal Resistance

|                                          |            |      |     |
|------------------------------------------|------------|------|-----|
| Junction - soldering point <sup>1)</sup> | $R_{thJS}$ | ≤140 | K/W |
|------------------------------------------|------------|------|-----|

<sup>1)</sup>For calculation of  $R_{thJA}$  please refer to Application Note Thermal Resistance

**Electrical Characteristics** at  $T_A=25^{\circ}\text{C}$ , unless otherwise specified


| Parameter                                                                                                                             | Symbol        | Values   |            |            | Unit          |
|---------------------------------------------------------------------------------------------------------------------------------------|---------------|----------|------------|------------|---------------|
|                                                                                                                                       |               | min.     | typ.       | max.       |               |
| DC Characteristics per Transistor                                                                                                     |               |          |            |            |               |
| Collector-emitter breakdown voltage<br>$I_C = 10\text{ mA}$ , $I_B = 0$                                                               | $V_{(BR)CEO}$ | 45       | -          | -          | V             |
| Collector-base breakdown voltage<br>$I_C = 10\text{ }\mu\text{A}$ , $I_E = 0$                                                         | $V_{(BR)CBO}$ | 50       | -          | -          |               |
| Collector-emitter breakdown voltage<br>$I_C = 10\text{ }\mu\text{A}$ , $V_{BE} = 0$                                                   | $V_{(BR)CES}$ | 50       | -          | -          |               |
| Emitter-base breakdown voltage<br>$I_E = 10\text{ }\mu\text{A}$ , $I_C = 0$                                                           | $V_{(BR)EBO}$ | 5        | -          | -          |               |
| Collector cutoff current<br>$V_{CB} = 30\text{ V}$ , $I_E = 0$                                                                        | $I_{CBO}$     | -        | -          | 15         | nA            |
| Collector cutoff current<br>$V_{CB} = 30\text{ V}$ , $I_E = 0$ , $T_A = 150\text{ }^{\circ}\text{C}$                                  | $I_{CBO}$     | -        | -          | 5          | $\mu\text{A}$ |
| DC current gain 1)<br>$I_C = 10\text{ }\mu\text{A}$ , $V_{CE} = 5\text{ V}$<br>$I_C = 2\text{ mA}$ , $V_{CE} = 5\text{ V}$            | $h_{FE}$      | -<br>200 | 250<br>290 | -<br>630   | -             |
| Collector-emitter saturation voltage1)<br>$I_C = 10\text{ mA}$ , $I_B = 0.5\text{ mA}$<br>$I_C = 100\text{ mA}$ , $I_B = 5\text{ mA}$ | $V_{CEsat}$   | -<br>-   | 75<br>250  | 300<br>650 | mV            |
| Base-emitter saturation voltage 1)<br>$I_C = 10\text{ mA}$ , $I_B = 0.5\text{ mA}$<br>$I_C = 100\text{ mA}$ , $I_B = 5\text{ mA}$     | $V_{BEsat}$   | -<br>-   | 700<br>850 | -<br>-     |               |
| Base-emitter voltage 1)<br>$I_C = 2\text{ mA}$ , $V_{CE} = 5\text{ V}$<br>$I_C = 10\text{ mA}$ , $V_{CE} = 5\text{ V}$                | $V_{BE(ON)}$  | 600<br>- | 650<br>-   | 750<br>820 | V             |

1) Pulse test:  $t < 300\mu\text{s}$ ;  $D < 2\%$


**Electrical Characteristics** at  $T_A = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified.

| Parameter                                                                                                                 | Symbol    | Values |      |      | Unit             |
|---------------------------------------------------------------------------------------------------------------------------|-----------|--------|------|------|------------------|
|                                                                                                                           |           | min.   | typ. | max. |                  |
| AC characteristics                                                                                                        |           |        |      |      |                  |
| Transition frequency<br>$I_C = 20\text{ mA}$ , $V_{CE} = 5\text{ V}$ , $f = 100\text{ MHz}$                               | $f_T$     | -      | 250  | -    | MHz              |
| Collector-base capacitance<br>$V_{CB} = 10\text{ V}$ , $f = 1\text{ MHz}$                                                 | $C_{cb}$  | -      | 3    | -    | pF               |
| Emitter-base capacitance<br>$V_{EB} = 0.5\text{ V}$ , $f = 1\text{ MHz}$                                                  | $C_{eb}$  | -      | 10   | -    |                  |
| Short-circuit input impedance<br>$I_C = 2\text{ mA}$ , $V_{CE} = 5\text{ V}$ , $f = 1\text{ kHz}$                         | $h_{11e}$ | -      | 4.5  | -    | kΩ               |
| Open-circuit reverse voltage transf.ratio<br>$I_C = 2\text{ mA}$ , $V_{CE} = 5\text{ V}$ , $f = 1\text{ kHz}$             | $h_{12e}$ | -      | 2    | -    | 10 <sup>-4</sup> |
| Short-circuit forward current transf.ratio<br>$I_C = 2\text{ mA}$ , $V_{CE} = 5\text{ V}$ , $f = 1\text{ kHz}$            | $h_{21e}$ | -      | 330  | -    | -                |
| Open-circuit output admittance<br>$I_C = 2\text{ mA}$ , $V_{CE} = 5\text{ V}$ , $f = 1\text{ kHz}$                        | $h_{22e}$ | -      | 30   | -    | μS               |
| Noise figure<br>$I_C = 200\text{ μA}$ , $V_{CE} = 5\text{ V}$ , $R_S = 2\text{ kΩ}$ ,<br>$f = 1\text{ kHz}$ , Δf = 200 Hz | F         | -      | -    | 10   | dB               |

**Total power dissipation  $P_{\text{tot}} = f(T_S)$**




**Permissible Pulse Load  $R_{\text{thJS}} = f(t_p)$**




**Permissible Pulse Load**

$$P_{\text{totmax}} / P_{\text{totDC}} = f(t_p)$$




**Transition frequency  $f_T = f(I_C)$**

$V_{CE} = 5V$




**Collector-base capacitance  $C_{CB} = f(V_{CBO})$**

**Emitter-base capacitance  $C_{EB} = f(V_{EBO})$**




**Collector cutoff current  $I_{CBO} = f(T_A)$**

$V_{CB} = 30V$




**Collector-emitter saturation voltage**

$I_C = f(V_{CEsat}), h_{FE} = 20$



### DC current gain $h_{FE} = f(I_C)$

$V_{CE} = 5V$



### Base-emitter saturation voltage

$I_C = f(V_{BEsat}), h_{FE} = 20$

