






DO NOT SCALE

DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	ECO-09-025699	05FEB10	KK	HMR



NOTES: 1 FOR USE ON STANDARD AND MINIATURE APPLICATION

2 REELED WITH PAPER COVER

3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

3 OBSOLETE	1	PRE-TIN PLATED	PHOSPHOR BRONZE	6-160870-8
------------	---	----------------	-----------------	-----------------------

GENERAL TOLERANCES ± 0.3

3 OBSOLETE	1	PRE-TIN PLATED	BRASS	6-160870-7
	1	TINPLATED	PHOSPHOR BRONZE	160870-4
	1	UNPLATED	PHOSPHOR BRONZE	-3
3 OBSOLETE	1	TINPLATED	BRASS	-2
	1	UNPLATED	BRASS	160870-1

NOTES

FINISH

MATERIAL

PART NUMBER

CUSTOMER
DRAWINGFOR REFERENCE ONLY
WILL NOT BE UPDATED

AMP

Tyco Electronics AMP
Barcelona, Spain

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

19

COPYRIGHT 1984

BY AMP-HOLLAND B.V.

ALL INTERNATIONAL RIGHTS RESERVED

AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING

DR
L.V.D.HEYDEN 17.12.'84WIRE RANGE
0.5-1.0 mm²

NAME

REV DATE
D M YCHK
20/12.84INSUL RANGE
2.0-3.3 DIA.

63 SERIES FASTIN-FASTON RECEPTACLE

17 01 03

APP
24.1.85

SIZE

A4

SHEET

1 OF 1

DRAWING NO

C-160870

REV LTR

D1