


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	47		J1	REVISED PER ECO-14-001124	24JAN2014	NK	MZ



- 1 0.76µm [0.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [0.200] MIN WITH 1.27µm [0.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76µm [0.000030] MIN NICKEL PER QQ-N-290.
- 2 1.27µm [0.000050] MIN TIN-LEAD PER MIL-T-10727 OVER 0.76µm [0.000030] MIN NICKEL PER QQ-N-290.
- 3 0.76µm [0.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [0.200] MIN WITH A UNIFORM GRADIENT TO 0.25µm [0.000010] MIN GOLD PER MIL-G-45204 ON THE REMAINDER OVER 0.76µm [0.000030] NICKEL PER QQ-N-290.
- 4 0.38µm [0.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [0.200] MIN WITH 1.27µm [0.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76µm [0.000030] MIN NICKEL PER QQ-N-290.
- 5 1.27µm [0.000050] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [0.200] MIN WITH GOLD FLASH ON REMAINDER OVER 1.90µm [0.000075] MIN NICKEL PER QQ-N-290.
- 6 GOLD PLATING NOT REQUIRED IN THIS AREA
- 7 WIRE RANGE 24-20 AWG. INSULATION RANGE 1.02[0.040]-2.03[0.080].
- 8 0.38µm [0.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [0.200] MIN, 1.27µm [0.000050] MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 5.69 [0.224] MIN ON OPPOSITE END, BOTH OVER 1.27µm [0.000050] MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT.
- 9 1.27µm [0.000050] MIN TIN PER MIL-T-10727 OVER 0.76µm [0.000030] MIN NICKEL PER QQ-N-290.
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

10	OBSOLETE	SMALL PACK	9	BRASS	2-66104-9 OR 3-66104-0	2-66105-0
		STANDARD	9	BRASS	2-66104-9 OR 3-66104-0	1-66105-9
		SMALL PACK	1	BRASS	66104-4	1-66105-8
		SMALL PACK	4	BRASS	66104-3	1-66105-7
		SMALL PACK	2	BRASS	66104-2	1-66105-6
		SMALL PACK	3	BRASS	66104-1	1-66105-5
	OBSOLETE	STANDARD	8	BRASS	2-66104-6	1-66105-4
	OBSOLETE	STANDARD	1	PHOSPHOR BRONZE	2-66104-3	1-66105-3
	OBSOLETE	STANDARD	2	PHOSPHOR BRONZE	2-66104-2	1-66105-2
	OBSOLETE	STANDARD	5	BRASS	1-66104-6	1-66105-0
		STANDARD	1	BRASS	66104-4	66105-4
		STANDARD	4	BRASS	66104-3	66105-3
		STANDARD	2	BRASS	66104-2	66105-2
		STANDARD	3	BRASS	66104-1	66105-1
		PACKAGING TYPE	BODY FINISH	MATERIAL	STRIP P/N REF	PART NO
		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 06/01/92	TE Connectivity	
		DIMENSIONS: mm [INCHES]		CHK W.LENKER 6-11-92		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G.STEINHAUER 7-8-92	NAME	
		0 PLC ± -		PRODUCT SPEC		
		1 PLC ± -		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
		2 PLC ± 0.13 [0.005]		—		
		3 PLC ± -		—	A2 00779 C=66105	
		4 PLC ± -		—		
		ANGLES ± -		—	SCALE 8:1 SHEET 1 OF 1 REV J1	
		FINISH		WEIGHT -		
		SEE CALLOUTS		CUSTOMER DRAWING		