

REFERENCE SPECIFICATIONS

-NFC 93425 (in compliance with HE 507)

PHYSICAL CHARACTERISTICS

- INSULATOR MATERIAL: THERMOPLASTIC UL94V0
- CONTACT MATERIAL: BRASS (SIGNAL CONTACT)
- BRASS (POWERS CONTACT)
- ACCESSORIES: BRASS
- SHELLS: STEEL

ELECTRICAL CHARACTERISTICS

- NOMINAL CURRENT: 7.5A (SIGNAL CONTACT)
- 30A or 40A (POWER CONTACT)
- CONTACT RESISTANCE: <=7.3 m Ohms(SIGNAL and POWER)
- CONTACT/CONTACT : >=1000 V
- CONTACT/GROUND : >=1200 V
- INSULATION RESISTANCE: >=5000 MOhms

ENVIRONMENTAL CHARACTERISTICS

- CLIMATIC CATEGORY: 55/125/21
- TEMPERATURE RANGE -55°C TO +125°C
- DAMP HEAT STEADY STATE 21 DAYS
- SALT SPRAY 24 HOURS

MECHANICAL CHARACTERISTICS

- RETENTION AGAINST TORQUE: - Threaded insert: 0.7 N.m maximum
- Female screw : 0.5 N.m maximum

NOTE RoHS INFORMATION

- The "LF" products meet european union Directives and other country regulations as described in GS-47-0004.
- The housing will withstand exposure to 260°C peak temperature for 3.5 seconds in a wave solder application with a 1.6mm minimum thick circuit board. See application notes/procedures if they are available.
- Termination plating spec:
 - Signal contacts: Ni + Gold/GxT
 - Power contacts: Ni 1.27µmi+Sn 2.5 to 7.5µ,pure bright
- Active area plating spec:
 - Signal and power contacts: Ni + Gold/GxT
- Shell plating :2 to 4µm Cu + Ni + 3 to 10µmm Sn,pure bright
- Accessories: Sn pure bright + nickel
- Packaging spec: See GS-14-920

Series

Shell size: **E A B C**
(see sheet 3)

Front accessory definition
(see sheet 2)

- blank**:without accessory
- L** :threaded insert M3
- O** :threaded insert UNC 4-40
- V** :female screw UNC 4-40

Layout of contacts (see sheet 3)

Contacts
P Pin

Termination type
5 Right angle/Europe standard

Plating
00 200 matings/unmatings
43 500 matings/unmatings

PCB accessories definition(see sheet 2)
A :without accessory
H :Metal brackets+harpoons for PCB 2.40mm
G :Metal brackets+harpoons for PCB 1.60mm
M :Metal brackets


Power contacts
30 :Fitted with power contacts 30 Amp.
40 :Fitted with power contacts 40 Amp.

DBL13W3P500G30LF

See note RoHS

TABLE 1:PCB HOLE DIAMETERS

POWER CONTACTS			ACCESSORIES	SIGNAL CONTACT
30 A	2.00	Ø2.40	Ø3.10	Ø1.00
40 A	2.80	Ø3.10		
Max current Power	ØA±0.10	PCB HOLE ±0.10	PCB HOLE ±0.10	PCB HOLE ±0.10




spec ref		dr		1, Product Eng	2015/06/16	projection 	mm 	size	A2	scale	1:1	
tolerance std		eng		Gregar Mathew	2019/11/11			ecn no	ELX-1-33009-1			
ISO 1101 ISO 406		chr		-	-				- rel level Released			
		appr		Varma Sudhir	2019/11/12	product family						
surface		linear	0.X		±0.3	Amphenol FCI	SUB MALE DW EUROPE FOOT PRINT			dwg no	C01-8639-2304c	rev E
			0.XX		±0.10.10		MIXED POWER RIGHT ANGL SOLDER					
ISO 1302			0.XXX		±0.05							
		angular	0°		±2°	cat. no.		-		Product - Customer Drw		sheet 1 of 7

Amphenol
FCi

© 2016 AFCI

C	FRONT ACCESSORY	Blank Without	L insert M3 O insert UNC 4.40	V insert UNC 4.40	Blank Without	L insert M3 O insert UNC 4.40	V insert UNC 4.40
	PCB ACCESSORIES	A Without	A Without	A Without	M Metal brackets	M Metal brackets	M Metal bracket




F	FRONT ACCESSORY	Blank Without	L insert M3 O insert UNC 4.40	V insert UNC 4.40	Blank Without	L insert M3 O insert UNC 4.40	V insert UNC 4.40
	PCB ACCESSORIES	G Metal brackets + harpoons for PCB 1.60mm	G Metal brackets + harpoons for PCB 1.60mm	G Metal brackets + harpoons for PCB 1.60mm	H Metal brackets + harpoons for PCB 2.40mm	H Metal brackets + harpoons for PCB 2.40mm	H Metal brackets + harpoons for PCB 2.40mm

spec ref				dr	1, Product Eng		2015/06/16		projection 	mm 	size	A2	scale	3:1		
tolerance std				eng	Gregar Mathew		2019/11/11				ecn no	ELX-133009-1				
ISO 1101				chr	-		-									
ISO 1101				appr	Varma Sudhir		2019/11/12				product family		-	rel level	Released	
ISO 406																
surface	linear	0.X	±0.30	Amphenol FCi	title	SUB MALE DW EUROPE FOOT PRINT					dwg no	C01-8639-2304c		rev	E	
		0.XX	±0.10													
		0.XXX	±0.05			MIXED POWER RIGHT ANGL SOLDER										
		ISO 1302	angular													0°

5W1

LAYOUT AND CONNECTOR DIMENSIONS

For PCB hole diameters see table I sheet I






Floating signal contacts

11W1

LAYOUT AND CONNECTOR DIMENSIONS




For PCB hole diameters see table I sheet I





7W2

LAYOUT AND CONNECTOR DIMENSIONS

For PCB hole diameters see table I sheet I







SIDE VIEW FOR ALL LAYOUTS



spec ref		dr		1, Product Eng		2015/06/16		projection		mm		size		scale			
tolerance std		eng		Gregar Mathew		2019/11/11						A2		2:1			
ISO 1101		chr		-		-						ecn no		ELX-133009-1			
ISO 406		appr		Varma Sudhir		2019/11/12		product family		D SUB -		rel level		Released			
surface		linear		Amphenol FCi		title		SUB MALE DW EUROPE FOOT PRINT				dwg no		C01-8639-2304c		rev	
ISO 1302		0.X				±0.30		cat. no.		-				Product - Customer Drw		sheet 4 of 7	
		0.XX				±0.10		MIXED POWER RIGHT ANGL SOLDER									
		0.XXX		±0.05												E	
		angular		0°		±0.2											





13W3

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



9W4





LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I




Floating signal contacts

17W2

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I






spec ref				dr1, Product Eng2015/06/16		projection		mm		sizeA2		scale2:1	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		engGregar Mathew2019/11/11						ecn noELX-133009-1		rel levelReleased	
ISO 1101				chr-2019/11/12									
ISO 406				apprVarma Sudhir2019/11/12		product family		D SUB -					
surface		linear		0.x±0.300.xx±0.100.xxx±0.005		AmphenolFCi		titleSUB MALE DW EUROPE FOOT PRINT		dwg noC01-8639-2304c		revE	
ISO 1302		angular		0°±2°		cat. no.-		Product - Customer Drw		sheet 5 of 7			

21W1

LAYOUT AND CONNECTOR DIMENSIONS




For PCB hole diameters see table I sheet I



27W2

LAYOUT AND CONNECTOR DIMENSIONS


For PCB hole diameters see table I sheet I



spec ref				dr		1, Product Eng		2015/06/16		projection		mm		size		A2		scale		2:1																			
tolerance std		TOLERANCES OTHERWISE SPECIFIED		eng		Gregar Mathew		2019/11/11						ecn no		ELX-133009-1		rel level		Released																			
ISO 1101		UNLESS SPECIFIED		chr		-																																	
ISO 406				appr		Varma Sudhir		2019/11/12																															
										product family										D SUB-																			
surface		linear		0.X		±0.30		Amphenol FCi		title		SUB MALE DW EUROPE FOOT PRINT MIXED POWER RIGHT ANGL SOLDER										dwg no		C01-8639-2304c		rev		E											
																														0.XX		±0.10							
																																		0.XXX		±0.005			
																																						angular	
ISO 1302																																							
cat. no.										-										Product - Customer Drw										sheet 6 of 7									


21WA4

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



25W3

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



spec ref		dr		1, Product Eng		2015/06/16		projection		size		scale					
tolerance std		eng		Gregar Mathew		2019/11/11				A2		2:1					
ISO 1101		chr		-		-				ech no		ELX-133009-1					
ISO 406		appr		Varma Sudhir		2019/11/12		product family		-		rel level		Released			
surface		linear		Amphenol FCi		title		SUB MALE DW EUROPE FOOT PRINT				dwg no		C01-8639-2304c		rev	
ISO 1302						cat. no.		-		Product - Customer Drw				sheet 7 of 7			
		angular															
		0°															
		±0.30															
		±0.10															
		±0.05															
		±2°															