


## IRG4BC30U-S

INSULATED GATE BIPOLAR TRANSISTOR

UltraFast Speed IGBT

### Features

- UltraFast: Optimized for high operating frequencies 8-40 kHz in hard switching, >200 kHz in resonant mode
- Generation 4 IGBT design provides tighter parameter distribution and higher efficiency than Generation 3
- Industry standard D<sup>2</sup>Pak package




$$V_{CES} = 600V$$

$$V_{CE(on)} \text{ typ.} = 1.95V$$

$$@V_{GE} = 15V, I_C = 12A$$

### Benefits

- Generation 4 IGBT's offer highest efficiency available
- IGBT's optimized for specified application conditions
- Designed to be a "drop-in" replacement for equivalent industry-standard Generation 3 IR IGBT's



### Absolute Maximum Ratings

|                           | Parameter                                           | Max.         | Units |
|---------------------------|-----------------------------------------------------|--------------|-------|
| $V_{CES}$                 | Collector-to-Emitter Breakdown Voltage              | 600          | V     |
| $I_C @ T_C = 25^\circ C$  | Continuous Collector Current                        | 23           | A     |
| $I_C @ T_C = 100^\circ C$ | Continuous Collector Current                        | 12           |       |
| $I_{CM}$                  | Pulsed Collector Current ①                          | 92           |       |
| $I_{LM}$                  | Clamped Inductive Load Current ②                    | 92           |       |
| $V_{GE}$                  | Gate-to-Emitter Voltage                             | $\pm 20$     | V     |
| $E_{ARV}$                 | Reverse Voltage Avalanche Energy ③                  | 10           | mJ    |
| $P_D @ T_C = 25^\circ C$  | Maximum Power Dissipation                           | 100          | W     |
| $P_D @ T_C = 100^\circ C$ | Maximum Power Dissipation                           | 42           |       |
| $T_J$<br>$T_{STG}$        | Operating Junction and<br>Storage Temperature Range | -55 to + 150 |       |

### Thermal Resistance

|                 | Parameter                                         | Typ. | Max. | Units        |
|-----------------|---------------------------------------------------|------|------|--------------|
| $R_{\theta JC}$ | Junction-to-Case                                  | —    | 1.2  | $^\circ C/W$ |
| $R_{\theta JA}$ | Junction-to-Ambient, ( PCB Mounted,steady-state)* | —    | 40   |              |

\* When mounted on 1" square PCB (FR-4 or G-10 Material ). For recommended footprint and soldering techniques refer to application note #AN-994.

**Electrical Characteristics @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)**


|                     | Parameter                                | Min. | Typ. | Max.      | Units                | Conditions                                            |
|---------------------|------------------------------------------|------|------|-----------|----------------------|-------------------------------------------------------|
| $V_{(BR)CES}$       | Collector-to-Emitter Breakdown Voltage   | 600  | —    | —         | V                    | $V_{GE} = 0V, I_C = 250\mu A$                         |
| $V_{(BR)ECS}$       | Emitter-to-Collector Breakdown Voltage ④ | 18   | —    | —         | V                    | $V_{GE} = 0V, I_C = 1.0A$                             |
| $DV_{(BR)CES}/DT_J$ | Temperature Coeff. of Breakdown Voltage  | —    | 0.63 | —         | V/ $^\circ\text{C}$  | $V_{GE} = 0V, I_C = 1.0mA$                            |
| $V_{CE(ON)}$        | Collector-to-Emitter Saturation Voltage  | —    | 1.95 | 2.1       | V                    | $I_C = 12A, V_{GE} = 15V$                             |
|                     |                                          | —    | 2.52 | —         |                      | $I_C = 23A$ See Fig.2, 5                              |
|                     |                                          | —    | 2.09 | —         |                      | $I_C = 12A, T_J = 150^\circ\text{C}$                  |
| $V_{GE(th)}$        | Gate Threshold Voltage                   | 3.0  | —    | 6.0       |                      | $V_{CE} = V_{GE}, I_C = 250\mu A$                     |
| $DV_{GE(th)}/DT_J$  | Temperature Coeff. of Threshold Voltage  | —    | -13  | —         | mV/ $^\circ\text{C}$ | $V_{CE} = V_{GE}, I_C = 250\mu A$                     |
| $g_{fe}$            | Forward Transconductance ⑤               | 3.1  | 8.6  | —         | S                    | $V_{CE} = 100V, I_C = 12A$                            |
| $I_{CES}$           | Zero Gate Voltage Collector Current      | —    | —    | 250       | $\mu A$              | $V_{GE} = 0V, V_{CE} = 600V$                          |
|                     |                                          | —    | —    | 2.0       |                      | $V_{GE} = 0V, V_{CE} = 10V, T_J = 25^\circ\text{C}$   |
|                     |                                          | —    | —    | 1000      |                      | $V_{GE} = 0V, V_{CE} = 600V, T_J = 150^\circ\text{C}$ |
| $I_{GES}$           | Gate-to-Emitter Leakage Current          | —    | —    | $\pm 100$ | nA                   | $V_{GE} = \pm 20V$                                    |

**Switching Characteristics @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)**


|              | Parameter                         | Min. | Typ. | Max. | Units | Conditions                                                                                                                                          |
|--------------|-----------------------------------|------|------|------|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| $Q_g$        | Total Gate Charge (turn-on)       | —    | 50   | 75   | nC    | $I_C = 12A$                                                                                                                                         |
| $Q_{ge}$     | Gate - Emitter Charge (turn-on)   | —    | 8.1  | 12   |       | $V_{CC} = 400V$ See Fig.8                                                                                                                           |
| $Q_{gc}$     | Gate - Collector Charge (turn-on) | —    | 18   | 27   |       | $V_{GE} = 15V$                                                                                                                                      |
| $t_{d(on)}$  | Turn-On Delay Time                | —    | 17   | —    | ns    | $T_J = 25^\circ\text{C}$<br>$I_C = 12A, V_{CC} = 480V$<br>$V_{GE} = 15V, R_G = 23\Omega$<br>Energy losses include "tail"<br>See Fig. 10, 11, 13, 14 |
| $t_r$        | Rise Time                         | —    | 9.6  | —    |       |                                                                                                                                                     |
| $t_{d(off)}$ | Turn-Off Delay Time               | —    | 78   | 120  |       |                                                                                                                                                     |
| $t_f$        | Fall Time                         | —    | 97   | 150  | mJ    | $T_J = 150^\circ\text{C}$ ,<br>$I_C = 12A, V_{CC} = 480V$<br>$V_{GE} = 15V, R_G = 23\Omega$<br>Energy losses include "tail"<br>See Fig. 13, 14      |
| $E_{on}$     | Turn-On Switching Loss            | —    | 0.16 | —    |       |                                                                                                                                                     |
| $E_{off}$    | Turn-Off Switching Loss           | —    | 0.20 | —    |       |                                                                                                                                                     |
| $E_{ts}$     | Total Switching Loss              | —    | 0.36 | 0.50 | nH    | Measured 5mm from package                                                                                                                           |
| $t_{d(on)}$  | Turn-On Delay Time                | —    | 20   | —    |       |                                                                                                                                                     |
| $t_r$        | Rise Time                         | —    | 13   | —    |       |                                                                                                                                                     |
| $t_{d(off)}$ | Turn-Off Delay Time               | —    | 180  | —    | pF    | $V_{GE} = 0V$<br>$V_{CC} = 30V$ See Fig.7<br>$f = 1.0MHz$                                                                                           |
| $t_f$        | Fall Time                         | —    | 140  | —    |       |                                                                                                                                                     |
| $E_{ts}$     | Total Switching Loss              | —    | 0.73 | —    |       |                                                                                                                                                     |
| $L_E$        | Internal Source Inductance        | —    | 7.5  | —    |       |                                                                                                                                                     |
| $C_{ies}$    | Input Capacitance                 | —    | 1100 | —    |       |                                                                                                                                                     |
| $C_{oes}$    | Output Capacitance                | —    | 73   | —    |       |                                                                                                                                                     |
| $C_{res}$    | Reverse Transfer Capacitance      | —    | 14   | —    |       |                                                                                                                                                     |

**Notes:**


- ① Repetitive rating;  $V_{GE} = 20V$ , pulse width limited by max. junction temperature. ( See fig. 13b )
- ②  $V_{CC} = 80\%(V_{CES})$ ,  $V_{GE} = 20V$ ,  $L = 10\mu H$ ,  $R_G = 23\Omega$ , (See fig. 13a)
- ③ Repetitive rating; pulse width limited by maximum junction temperature.
- ④ Pulse width  $\leq 80\mu s$ ; duty factor  $\leq 0.1\%$ .
- ⑤ Pulse width  $5.0\mu s$ , single shot.




**Fig. 1** - Typical Load Current vs. Frequency  
(For square wave,  $I = I_{\text{RMS}}$  of fundamental; for triangular wave,  $I = I_{\text{PK}}$ )




**Fig. 2** - Typical Output Characteristics




**Fig. 3** - Typical Transfer Characteristics




**Fig. 4** - Maximum Collector Current vs. Case Temperature




**Fig. 5** - Collector-to-Emitter Voltage vs. Junction Temperature




**Fig. 6** - Maximum Effective Transient Thermal Impedance, Junction-to-Case




**Fig. 7** - Typical Capacitance vs. Collector-to-Emitter Voltage




**Fig. 8** - Typical Gate Charge vs. Gate-to-Emitter Voltage




**Fig. 9** - Typical Switching Losses vs. Gate Resistance




**Fig. 10** - Typical Switching Losses vs. Junction Temperature





**Fig. 11** - Typical Switching Losses vs. Collector-to-Emitter Current




**Fig. 12** - Turn-Off SOA





**Fig. 13b - Pulsed Collector Current Test Circuit**




\* Driver same type  
as D.U.T., VC = 480V



## D<sup>2</sup>Pak Package Outline



### MINIMUM RECOMMENDED FOOTPRINT



### NOTES:

- 1 DIMENSIONS AFTER SOLDER DIP.
- 2 DIMENSIONING & TOLERANCING PER ANSI Y14.5M, 1982.
- 3 CONTROLLING DIMENSION : INCH.
- 4 HEATSINK & LEAD DIMENSIONS DO NOT INCLUDE BURRS.

### LEAD ASSIGNMENTS

- 1 - GATE
- 2 - DRAIN
- 3 - SOURCE

Note: For the most current drawings please refer to the IR website at:  
<http://www.irf.com/package/>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[International Rectifier:](#)

[IRG4BC30U-SPBF](#) [IRG4BC30U-STRRP](#)