








PANEL THICKNESS	X
0.75–1.25 [0.30–0.49]	19.2 [.756]
1.25–2.0 [.049–.079]	19.4 [.764]
2.0–3.0 [.079–.118]	19.8 [.780]



SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
DN	OFF	DN
1a-1	OPEN	1-1b




CIRCUIT: SPDT



- NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X \pm 0.4$
 $X.XX \pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY.
4. RATING: 15A @ 125VAC OR 6A @ 250VAC
5. MECHANICAL LIFE: 15,000 cycles
6. ELECTRICAL LIFE: 10,000 cycles
7. INSULATION RESISTANCE: >1000 Mega Ω
8. CONTACT RESISTANCE: <20 Mega Ω
9. DIELECTRIC STRENGTH: >1500 V 1 minute
>3000 V between poles
10. HOUSING/ACTUATOR COLOR: BLACK



					TITLE
					R1966D BLK BLK CF
A	11662	RELEASED	12/10/02	CJB	
REV.	ECN No.	DESCRIPTION	DATE	CHKD	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					
SCALE		DATE	DR	DWG	REV
1.5:1		-- --	-- --	M309300	A