


High Frequency (Up to 40 GHz) Resistor, Thin Film Surface Mount Chip



LINKS TO ADDITIONAL RESOURCES



FC series chip resistors are designed with low internal reactance. They function as almost pure resistors on a very high range of frequencies. The specialized laser edge trimming allows for precision tolerances to 0.1 %.

FEATURES

- Small standard size 0402 case size
- Edge trimmed block resistors
- High purity alumina substrate
- Ohmic range (10 Ω to 1000 Ω)
- Small internal reactance (< 10 m Ω)
- Low TCR (down to ± 25 ppm/ $^{\circ}$ C)
- Epoxy bondable termination available
- Material categorization: for definitions of compliance please see www.vishay.com/doc299912


RoHS*
Available

HALOGEN
FREE
Available

GREEN
(5-2008)
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

APPLICATIONS

- Low noise amplifiers
- Attenuation
- Line termination

STANDARD ELECTRICAL SPECIFICATIONS

TEST	SPECIFICATIONS	CONDITIONS
Material	Passivated nichrome	-
Resistance Range	10 Ω to 1000 Ω	Case size dependent
TCR: Absolute	± 25 ppm/ $^{\circ}$ C to ± 100 ppm/ $^{\circ}$ C	-55 $^{\circ}$ C to +125 $^{\circ}$ C
Tolerance: Absolute	± 0.1 % to ± 5.0 %	+25 $^{\circ}$ C
Stability: Absolute	$\Delta R \pm 0.02$ %	2000 h at 70 $^{\circ}$ C
Stability: Ratio	-	-
Voltage Coefficient	0.1 ppm/V	-
Working Voltage	30 V to 75 V	-
Operating Temperature Range	-55 $^{\circ}$ C to +155 $^{\circ}$ C	-
Storage Temperature Range	-55 $^{\circ}$ C to +155 $^{\circ}$ C	-
Noise	< -35 dB	-
Shelf Life Stability: Absolute	$\Delta R \pm 0.01$ %	1 year at +25 $^{\circ}$ C

COMPONENT RATINGS

CASE SIZE	POWER RATING (mW)	WORKING VOLTAGE (V)	RESISTANCE RANGE (Ω)
0402	50	30	10 to 1000
0505	125	37	20 to 1000
0603	125	50	10 to 1000
0805	200	50	10 to 1000
1005	250	75	10 to 1000
1206	330	75	10 to 1000

**DIMENSIONS** in inches (millimeters)

	CASE SIZE	LENGTH	WIDTH W (± 0.005)	THICKNESS T (± 0.0015)	TOP PAD D (± 0.005)	BOTTOM PAD E (± 0.005)
	0402	0.042 $\pm$ 0.008 (1.067 $\pm$ 0.203)	0.022 (0.559)	0.015 (0.381)	0.010 (0.254)	0.010 (0.254)
	0505	0.055 $\pm$ 0.006 (1.397 $\pm$ 0.152)	0.050 (1.270)	0.015 (0.381)	0.010 (0.254)	0.015 (0.381)
	0603	0.064 $\pm$ 0.006 (1.626 $\pm$ 0.152)	0.032 (0.813)	0.015 (0.381)	0.012 (0.305)	0.015 (0.381)
	0805	0.080 $\pm$ 0.006 (2.032 $\pm$ 0.152)	0.050 (1.270)	0.015 (0.381)	0.016 $\pm$ 0.008 (0.406 $\pm$ 0.203)	0.015 (0.381)
	1005	0.105 $\pm$ 0.008 (2.667 $\pm$ 0.203)	0.050 (1.270)	0.015 (0.381)	0.015 (0.381)	0.015 (0.381)
	1206	0.126 $\pm$ 0.008 (3.200 $\pm$ 0.203)	0.063 (1.600)	0.015 (0.381)	0.020 $\pm$ 0.005/- 0.010 (0.508 $\pm$ 0.127/- 0.254)	

MECHANICAL SPECIFICATIONS

Resistive Element	Passivated nichrome
Substrate Material	Alumina
Terminations	Pre-soldered or gold
Lead (Pb)-free Option	96.5 % Sn, 3.0 % Ag, 0.5 % Cu
Tin/Lead Option	Sn63
Lead (Pb)-free Finish and Tin / Lead	Hot solder dip

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: FC1206E1001BBTS

F	C	1	2	0	6	E	1	0	0	1	B		B		T	S
F	C	1	2	0	6	K	1	0	0	0	B	T	B	S	T	S
GLOBAL MODEL	CASE SIZE	TCR CHARACTERISTIC		RESISTANCE		TOLERANCE		TERMINATION (1, 2 or 3 digits)					PACKAGING			
FC	0402 0505 0603 0805 1005 1206	E = 25 ppm/°C H = 50 ppm/°C K = 100 ppm/°C		The first 3 digits are significant figures and the last digit specifies the number of zeros to follow. "R" designates the decimal point. Example: 10R0 = 10 Ω 1000 = 100 Ω 1001 = 1 kΩ		B = 0.1 % D = 0.5 % F = 1 % G = 2 % J = 5 %		T = top sided Au (gold) term Au over Ni epoxy bondable RoHS-compliant - e4 B = wraparound Sn/Pb solder 63 % Sn/37 % Pb with nickel barrier G = wraparound Au over Ni (gold) termination epoxy bondable RoHS-compliant - e4 TB = top sided Sn/Pb solder 63 % Sn/37 % Pb with nickel barrier TBS = top sided lead (Pb)-free solder with nickel barrier RoHS-compliant - e1 S = wraparound lead (Pb)-free solder 96.5 % Sn/3.0 % Ag/0.5 %Cu RoHS-compliant - e1					BS = BULK 100 min., 1 mult. WS = WAFFLE 100 min., 1 mult. TAPE AND REEL T0 = 100 min., 100 mult. T1 = 1000 min., 1000 mult. ⁽¹⁾ T3 = 300 min., 300 mult. T5 = 500 min., 500 mult. TF = full reel TS = 100 min., 1 mult.			


Historical Part Number Example: FC1206E1001BBT (for reference purposes only)

FC	1206	E	1001	B	B	T
SERIES	CASE SIZE	TCR CHARACTERISTIC	RESISTANCE	TOLERANCE	TERMINATION	PACKAGING

Note

(1) Preferred packaging code


TYPICAL HIGH FREQUENCY PERFORMANCE ELECTRICAL MODEL AND TESTING




The lumped circuit above was used to model the data at the bonding pad-resistor reference plane. High frequency testing was performed by Modelithics, Inc. on parts mounted to quartz test boards. Quartz test boards were chosen to minimize the contribution of the board effects at high frequencies.

INTERNAL IMPEDANCE


0402 Flip chip






0603 Flip chip



0402 Wraparound



DERATING CURVE

VSWR FC Series 0402 size 50 Ω

VSWR FC Series 0402 size 100 Ω




Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.