

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

AD00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	AL2	REVISED PER ECO-11-004820	11MAR11	RK	HMR

DATE CODE

AMP XXXX
3-435802-8
OFF

PIN 1 IDENT DOT

.38±.02

.022±.002 TYP

.100 TYP

A±.02

DATE CODE

AMP XXXX
435802-1
OFF

PIN 1 IDENT DOT

.38±.02

.022±.002 TYP

.100 TYP

A±.02

CLOSE
←
OPEN
→

.14±.02 TYP

.012 TYP

.19±.01

.315±.010

.02^{+.01}_{-.00}
STANDOFF, 4 PLC

.29±.02 TYP

MOUNTING SURFACE

FIG 1

CLOSE
←
OPEN
→

.14±.02 TYP

.012 TYP

.19±.01

.315±.010

.02^{+.01}_{-.00}
STANDOFF, 4 PLC

.29±.02 TYP

MOUNTING SURFACE

FIG 2

CONTACT ARRANGEMENT

NO POSITION MARKING.

NO PART NO. MARKING.

STRIPPABLE TAPE SEAL, SEE FIGURE 8.

OBSOLETE PARTS: OBSOLETE CIS
STREAMLINING PER D.RENAUD/D.SINISI

1

2

3

4

5

6

FOR ADDITIONAL SPECIFICATIONS SEE AMP PRODUCT SPEC 108-7519.

SWITCH SHOWN IN OPEN POSITION.

ALL CHARACTERS AND ROCKERS ARE WHITE, HOUSING IS BLACK.

STAMPING WILL VARY ON 2 AND 3 POSITION TOPS DUE TO SPACE RESTRICTIONS.

STRIPPABLE TRANSPARENT SEAL, SEE FIG 6.

.315 DIMENSION APPLIES AT TERMINAL TIPS. TERMINALS ARE .300^{+.010}_{-.000} AT MOUNTING SURFACE.

FIG 2	FIG 3A& 7	—	1.08	10	6-435802-3
FIG 1	FIG 3B	9	.88	8	3-435802-8
FIG 2	7 8	5	.58	5	3-435802-1
FIG 2	7 8	5	.88	8	3-435802-0
FIG 2	7 8	5	.48	4	2-435802-9
FIG 1	7	—	.28	2	2-435802-8
OBSOLETE	7	5	.28	2	2-435802-7
OBSOLETE	7	5	1.08	10	2-435802-6
OBSOLETE	FIG 4	—	.88	8	2-435802-5
OBSOLETE	7	5	.88	8	2-435802-4
OBSOLETE	FIG 2	FIG 3A& 5	.48	4	2-435802-3
FIG 2			1.28	12	2-435802-2
FIG 2			1.18	11	2-435802-1
FIG 2			1.08	10	2-435802-0
FIG 2	FIG 3A	5	.98	9	1-435802-9
FIG 2			.78	7	1-435802-8
FIG 2			.68	6	1-435802-7
FIG 2			.58	5	1-435802-6
FIG 2			.48	4	1-435802-5
FIG 2			.38	3	1-435802-4
FIG 2	FIG 3B	5	.28	2	1-435802-3
FIG 2			1.28	12	1-435802-2
FIG 1	FIG 3B	5	.28	2	1-435802-0
FIG 2			.88	8	435802-9
FIG 2			1.08	10	435802-8
FIG 2	FIG 3A		.98	9	435802-7
FIG 2			.78	7	435802-6
FIG 2			.68	6	435802-5
FIG 2			.58	5	435802-4
FIG 2			.48	4	435802-3
FIG 2	FIG 3A		.38	3	435802-2
FIG 2	FIG 3A		.88	8	435802-1
HOUSING	MARKING	PROTECTIVE SEAL	A	NO OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R. TALLEY 9-19-89

CHK R. MILLER 9-19-89

APVD H. LEITER 9-19-89

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS: INCHES

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

FINISH CONTACTS: PLATED .000030 MIN GOLD IN CONTACT AREA OVER .000050 MIN NICKEL

TE Connectivity

SWITCH ASSY, DIP, TYPE C, 7000 SERIES, SPST, SIDE ACTUATED

SIZE A2

CAGE CODE 00779

DRAWING NO C=435802

RESTRICTED TO

SCALE 4:1

SHEET 1 of 2

REV AL2




FIG 3A




FIG 3B




FIG 4





FIG 5



PROTECTIVE SEAL

FIG 6






FIG 7



PROTECTIVE SEAL

FIG 8

 $.010 \pm .010$ $.005^{+.010}_{-.005}$
TYP

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. TALLEY 9-19-89	 TE Connectivity				
		CHK R. MILLER 9-19-89					
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD H. LEITER 9-19-89	NAME SWITCH ASSY, DIP, TYPE C, 7000 SERIES, SPST, SIDE ACTUATED				
	0 PLC ± -	PRODUCT SPEC —					
	1 PLC ± -	APPLICATION SPEC —					
	2 PLC ± -	—					
	3 PLC ± .005	—					
4 PLC ± -	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-435802	RESTRICTED TO —		
MATERIAL SEE SHEET 1	FINISH SEE SHEET 1	CUSTOMER DRAWING			SCALE 4:1	SHEET 2 of 2	REV AL2