

1

2

3

4

5

6

7

8

REFERENCE SPECIFICATIONS

-NFC 93425 (in compliance with HE 507)

PHYSICAL CHARACTERISTICS

-INSULATOR MATERIAL: THERMOPLASTIC UL94V0

-CONTACT MATERIAL: PHOSPHOR BRONZE(SIGNAL CONTACT)

BRASS (POWERS CONTACT)

-ACCESSORIES: BRASS

-SHELLS: STEEL

ELECTRICAL CHARACTERISTICS

-NOMINAL CURRENT: 7.5A (SIGNAL CONTACT)

30A or 40A (POWER CONTACT)

-CONTACT RESISTANCE: <=7.3 m Ohms(SIGNAL and POWER)

-CONTACT/CONTACT : >=1000 V

-CONTACT/GROUND : >=1200 V

-INSULATION RESISTANCE: >=5000 MOhms

ENVIRONMENTAL CHARACTERISTICS

- CLIMATIC CATEGORY: 55/125/21

TEMPERATURE RANGE -55°C TO +125°C

DAMP HEAT STEADY STATE 21 DAYS

SALT SPRAY 48 HOURS

MECHANICAL CHARACTERISTICS

- RETENTION AGAINST TORQUE: - Threaded insert: 0.7 N.m minimum

- Female screw : 0.5 N.m minimum

NOTE RoHS INFORMATION

- The "LF" products meet european union Directives and other country regulations as described in GS-22-008.

- The housing will withstand exposure to 260°C peak temperature for 3.5 seconds in a wave solder application with a 1.6mm minimum thick circuit board. See application notes/procedures if they are available.

- Termination plating spec:

- Signal contacts: Ni + Gold

- Power contacts: Ni 1.27µm+Sn 2.5 to 7.5µ,pure bright

- Active area plating spec:

- Signal and power contacts: Ni + Gold

- Shell plating :2 to 4µm Cu + nickel + 3 to 10µmm Sn,pure bright

- Accessories: Sn pure bright + nickel

- Packaging spec: See GS-14-920

Series

Shell size: E A B C D (see sheet 3)

Front accessory definition (see sheet 2)

blank:without accessory

L :threaded insert M3

O :threaded insert UNC 4-40

V :female screw UNC 4-40

Layout of contacts (see sheet 3)

Contacts

S :Socket

Termination type

5 Right angle/Europe standard

Plating

00 200 matings/unmatings

43 500 matings/unmatings

PCB accessories definition(see sheet 2)

A :without accessory

H :Metal brackets+harpoons for PCB 2.40mm

G :Metal brackets+harpoons for PCB 1.60mm

M :Metal brackets

Power contacts

00 :Not fitted with power contact (signal contacts always fitted)

30 :Fitted with power contacts 30 Amp.

40 :Fitted with power contacts 40 Amp.

DBL13W3S500G30LF

See note RoHS

TABLE 1:PCB HOLE DIAMETERS

POWER CONTACTS			ACCESSORIES	SIGNAL CONTACT
30 A	2.00	Ø2.40	Ø3.10	Ø0.9 min
40 A	2.80	Ø3.10		
Max current power	ØA ^{+0.1} ₀	PCB HOLE ±0.1	PCB HOLE ±0.1	PCB HOLE

Dr M PESSON 2005-10-11

Eng P LEGARE 2005-10-11

Chr

Appr

rev	ecn no	dr	date
A	LS05-0101	MPE	2005-10-11
B	LS06-0208	LGO	2006-12-12
C	LS07-0273	MPE	2007/10/31
D	F09-0092	LSA	2009/09/16
E	F10-0060	LSA	2010/06/01
-	-	-	-
-	-	-	-

www.fciconnect.com

surface ISO 1302

tolerance std ISO 406 ISO 1101

projection

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED

ANGULAR

LINEAR

0° ±2°

0.X ±0.3

0.XX ±0.1

0.XXX ±0.05

size A2

Scale 2:1

Product family

ECN F10-0060

Spec ref

FCI

title SUB FEMALE DMW EUROPE

mixed power right angled solder

dwg no C01-8639-2300

Rev. E

catalog no

CUSTOMER


sheet 1 of 7

13W3 FOR EXAMPLE

Ø A

Copyright FCI.

PDM: Rev:E STATUSReleased Printed: Oct 01, 2010



FRONT ACCESSORY	Blank Without	L insert M3 O insert UNC 4.40	V insert UNC 4.40	Blank Without	L insert M3 O insert UNC 4.40	V insert UNC 4.40
PCB ACCESSORIES	A Without	A Without	A Without	M Metal brackets	M Metal brackets	M Metal bracket

FRONT ACCESSORY	Blank Without	L insert M3 O insert UNC 4.40	V insert UNC 4.40	Blank Without	L insert M3 O insert UNC 4.40	V insert UNC 4.40
PCB ACCESSORIES	G Metal brackets + harpoons for PCB 1.60mm	G Metal brackets + harpoons for PCB 1.60mm	G Metal brackets + harpoons for PCB 1.60mm	H Metal brackets + harpoons for PCB 2.40mm	H Metal brackets + harpoons for PCB 2.40mm	H Metal brackets + harpoons for PCB 2.40mm

www.fciconnect.com			surface - ✓ ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	M PESSON	2005-10-11	ANGULAR	LINEAR	0.X ±0.3		size A2	Scale			
Eng	P LEGARE	2005-10-11			0.XX ±0.1			2:1			
Chr					0.XXX ±0.05			ECN F10-0060			
Appr			Product family					- Spec ref			
			SUB FEMALE DMW EUROPE			dwg no			C01-8639-2300		
			mixed power right angled solder						Rev. E		
			catalog no			-			CUSTOMER		
									sheet 2 of 7		

FCI
Copyright FCI.

REV E - 2006-03-28

SCALE: 4

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.

FCI

Copyright FCI.





FCI

Copyright FCI.

FCI





Copyright FCI.

5W1





LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I

Floating signal contacts


11W1

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I


7W2

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet ISIDE VIEW FOR ALL LAYOUTS
(except size D)

VIEW WITHOUT POWERS CONTACTS



VIEW WITH POWERS CONTACTS




Copyright FCI.

REV E - 2006-03-28

www.fciconnect.com			surface	✓	tolerance std	projection	mm
			ISO 1302		ISO 406 ISO 1101		
			TOLERANCES UNLESS OTHERWISE SPECIFIED				
Dr	M PESSON	2005-10-11	ANGULAR	LINEAR	0.X	±0.3	size
Eng	P LEGARE	2005-10-11			0.XX	±0.1	A2
Chr					0.XXX	±0.05	ECN
Appr			0° ±2°				F10-0060
			Product family		Spec ref		
FCI			SUB FEMALE DMW EUROPE			dwg no	
			mixed power right angled solder			C01-8639-2300	
			catalog no			CUSTOMER	
						sheet 4 of 7	
						Rev.	E


13W3

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I













9W4

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



17W2

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



Floating signal contacts

www.fciconnect.com			surface ISO 1302		- ✓ tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M PESSON	2005-10-11	ANGULAR LINEAR		0.X	±0.3	size A2	Scale 2:1		
Eng	P LEGARE	2005-10-11			0.XX	±0.1				
Chr			0° ±2°		0.XXX	±0.05	ECN		F10-0060	
Appr			Product family				-	Spec ref		
			title SUB FEMALE DMW EUROPE mixed power right angled solder			dwg no C01-8639-2300		Rev. E		
catalog no										
			-			CUSTOMER		sheet 5 of 7		



Copyright FCI.

REV E - 2006-03-28

1

2

3

4

5

6


7

8

21W1

LAYOUT AND CONNECTOR DIMENSIONS


For PCB hole diameters see table I sheet I



27W2

LAYOUT AND CONNECTOR DIMENSIONS

For PCB hole diameters see table I sheet I



Copyright FCI.

REV E - 2006-03-28

2

3

4

5

6


8

www.fciconnect.com			surface	-	tolerance std	projection	mm	
			ISO 1302	✓	ISO 406	ISO 1101		
			TOLERANCES UNLESS OTHERWISE SPECIFIED					
Dr	M PESSON	2005-10-11	ANGULAR		0.X	±0.3	size	Scale
Eng	P LEGARE	2005-10-11		LINEAR	0.XX	±0.1	A2	2:1
Chr			0°	±2°	0.XXX	±0.05	ECN	F10-0060
Appr			Product family			-	Spec ref	
FCI			SUB FEMALE DMW EUROPE			dwg no		Rev.
			mixed power right angled solder			C01-8639-2300		E
			catalog no			CUSTOMER		sheet 6 of 7

21W A4

LAYOUT AND CONNECTOR DIMENSIONS


For PCB hole diameters see table 1 sheet 1



25W 3

LAYOUT AND CONNECTOR DIMENSIONS


For PCB hole diameters see table 1 sheet 1



24W 7

LAYOUT AND CONNECTOR DIMENSIONS

For PCB hole diameters see table 1 sheet 1



www.fciconnect.com			Surface ISO 1302		- ✓ tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M PESSON	2005-10-11	ANGULAR	LINEAR	0.X	±0.3	size	A2	Scale	2:1
Eng	P LEGARE	2005-10-11			0.XX	±0.1				
Chr					0° ±2°	0.XXX	±0.05	ECN	F10-0060	
Appr			Product family				-	Spec ref		
		title	SUB FEMALE DMW EUROPE mixed power right angled solder				dwg no	C01-8639-2300		Rev. E
			catalog no	-	CUSTOMER		sheet 7 of 7			