



LED driver is built in the lamp head

Low voltage power AC24V or DC24V is available. Also, special voltage can be specified.





777-7962 NO PLUG 777-77971 NO PLUG 777-7974 NO PLUG

LED driver is built in the base

Equipped with a LED driver for directly connecting to voltage of AC power. (100V~260V) (50Hz/60Hz) with plug. (For high voltage)



777-7978 EU PLUG 777-7987 EU PLUG 777-8016 UK PLUG
777-8025 UK PLUG 777-8028 UK PLUG



Feature

- Various lighting angles to select 25°, 60° and 80°. Standard lighting angle is 60°.
- Power of each LED bulb is 1W x 6pcs.
- 2W bulb is available upon request.
- LED driver can be externally mounted for increasing LED bulbs.
- Reinforced lens for high crack-resistance.
- Reinforced lens provides clear (transparent) or sand blasted (foggy) surface to choose from.
- Well prevention for explosion, dust, coolant and lubricant.
- Furnished with 1.8 meters of cord without plug. (For low voltage)
- Long service life up to 40,000 lighting hours.
- Applicable for semiconductor manufacturing equipment and clean room.
- Suitable for temperature range -30° ~ +60°.
- Free of infrared ray and ultraviolet ray radiation.