

BAT54- Series




200mW SMD Schottky Barrier Diode

Small Signal Diode



Features :

- Fast switching speed.
- Surface device type mounting.
- Moisture sensitivity level 1.
- Matte Tin (Sn) lead finish with Nickel (Ni) underplate.



SOT-23

Mechanical Data



Case


Terminal

High temperature soldering guaranteed
Marking Code


: SOT-23 small outline plastic package.
: Matte tin plated, lead free., solderable per MIL-STD-202, Method 208 guaranteed.
: 260°C/10s.
: KL1, KL2, KL3, KL4.

Dimensions	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	2.8	3	0.11	0.118
B	1.2	1.4	0.047	0.055
C	0.3	0.5	0.012	0.02
D	1.8	2	0.071	0.079
E	2.25	2.55	0.089	0.1
F	0.9	1.2	0.035	0.043
G	0.55 REF.		0.022 REF.	


Pin Configuration




BAT54



BAT54A



BAT54C



BAT54S



BAT54- Series



200mW SMD Schottky Barrier Diode

Marking Information

Package	Part Number	Packing	Marking
SOT-23	BAT54	3K / 7 Inches Reel	KL1
	BAT54A		KL2
	BAT54C		KL3
	BAT54S		KL4


Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Maximum Ratings

Type Number	Symbol	Value	Units
Peak Repetitive Peak reverse Voltage Working Peak Reverse Voltage DC Reverse Voltage	V_{RRM} V_{RWM} V_R	30	V
Forward Continuous Current	I_F	200	mA
Repetitive Peak Forward Current	I_{FRM}	200	
Forward Surge Current at $t < 1.0s$	I_{FSM}	600	
Power Dissipation	P_d	200	mW
Thermal Resistance, Junction to Ambient air	$R_{\theta JA}$	500	°C/W
Operating and Storage Temperature	T_j, T_{STG}	-55 to 150	°C

Suggested PAD Layout



Dimensions : Millimetres

Electrical Characteristics


Type Number	Symbol	Min.	Max.	Units
Reverse Breakdown Voltage $I_R = 100\mu A$	$V_{(BR)}$	30	-	V
Forward Voltage $I_F = 0.1mA$ $I_F = 1mA$ $I_F = 10mA$ $I_F = 30mA$ $I_F = 100mA$	V_F	-	0.24	
		-	0.32	
		-	0.4	
		-	0.5	
		-	1	
Reverse Current $V_R = 25V$	I_R	-	2	μA
Total Capacitance $V_R = 1V, f = 1 MHz$	C_T	-	10	pF
Reverse Recovery Time $I_F = I_R = 10mA, R_L = 100\Omega, I_{RR} = 1mA$	t_{rr}	-	5	nS

BAT54- Series


200mW SMD Schottky Barrier Diode



Tape and Reel specification




Item	Symbol	Dimension (mm)
Carrier width	A	3.15 ±0.1
Carrier length	B	2.77 ±0.1
Carrier depth	C	1.22 ±0.1
Sprocket hole	d	1.50 ±0.1
Reel outside diameter	D	178 ±1
Reel inner diameter	D1	55 Min.
Feed hole width	D2	13.0 ±0.2
Sprocket hole position	E	1.75 ±0.1
Punch hole position	F	3.50 ±0.05
Sprocket hole pitch	P0	4.00 ±0.1
Embossment centre	P1	2.00 ±0.05
Overall tape thickness	T	0.229 ±0.013
Tape width	W	8.10 ±0.2
Reel width	W1	12.30 ±0.2




Rating and Characteristic Curves

Typical Forward Characteristics



Typical Reverse Characteristics





BAT54- Series



200mW SMD Schottky Barrier Diode

Rating and Characteristic Curves



Part Number Table

Description	Part Number
Diode, Schottky, SOT-23	BAT54
	BAT54A
	BAT54C
	BAT54S

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.

