




PART NO.

HV Series

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	S. R	8/5/06	K. S	8/5/06	N. K	22/5/06



Lead Wire Dimensions

ϕD	5 - 13	16 - 25
ϕd	0.6	0.8

Dimensions : Millimetres

Dimensions : Millimetres

Features:

- Low Impedance characteristics.
- Case sizes are smaller than conventional general-purpose capacitors, with very high performance.
- Can size larger than 8mm diameter has safety vent on rubber bun.
- General purpose 85°C.
- Axial leaded electrolytic.

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2004.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

S. Ram

DATE:

08/05/06

CHECKED BY:

K. Suresh

DATE:

08/05/06

APPROVED BY:

N. Kiwomya

DATE:

22/05/06

DRAWING TITLE:

HV Series - Axial Electrolytic Capacitors

SIZE
A

DWG NO.

M10000225

ELECTRONIC FILE
208517_1_DWGREV
A

SCALE: NTS

U.O.M.: mm

SHEET: 1 OF 5

	PART NO. HV Series	REVISIONS																						
		ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE														
		-	A	RELEASED	S. R	8/5/06	K. S	8/5/06	N. K	22/5/06														
Characteristics																								
Item	Characteristic																							
Operating temperature range	-25°C to +85°C.																							
Capacitance tolerance	±20% (at 20°C, 120Hz).																							
Leakage current	I = 0.03CV +15µA (CV ≤1000) I = 0.02CV +30µA (C >1000) after 5 minutes applying the rated DC working voltage at 20°C where C = rated capacitance in µF V = rated DC working voltage in V.																							
Dissipation factor (tan δ) (At 20°C, 120Hz)	<table><tr><td>Rated Voltage (V)</td><td>160</td><td>200</td><td>250</td><td>350</td><td>400</td><td>450</td></tr><tr><td>Tan δ</td><td>0.15</td><td>0.15</td><td>0.20</td><td>0.20</td><td>0.24</td><td>0.24</td></tr></table>							Rated Voltage (V)	160	200	250	350	400	450	Tan δ	0.15	0.15	0.20	0.20	0.24	0.24	For capacitors whose capacitance exceeds 1000µF, the specification of tan δ is increased by 0.02 for every addition of 1000µF.		
	Rated Voltage (V)	160	200	250	350	400	450																	
Tan δ	0.15	0.15	0.20	0.20	0.24	0.24																		
Surge voltage	<table><tr><td>Rated Voltage (V)</td><td>160</td><td>200</td><td>250</td><td>350</td><td>400</td><td>450</td></tr><tr><td>Surge Voltage (V)</td><td>200</td><td>250</td><td>300</td><td>400</td><td>450</td><td>500</td></tr></table>							Rated Voltage (V)	160	200	250	350	400	450	Surge Voltage (V)	200	250	300	400	450	500			
Rated Voltage (V)	160	200	250	350	400	450																		
Surge Voltage (V)	200	250	300	400	450	500																		
Low temperature characteristics	1. Impedance ratio at 120Hz.																							
	<table><tr><td>Rated Voltage (V)</td><td>160</td><td>200</td><td>250</td><td>350</td><td>400</td><td>450</td></tr><tr><td>Z (- 25°C)/Z (20°C)</td><td>4</td><td>8</td><td>8</td><td>12</td><td>13</td><td>16</td></tr></table>							Rated Voltage (V)	160	200	250	350	400	450	Z (- 25°C)/Z (20°C)	4	8	8	12	13	16			
Rated Voltage (V)	160	200	250	350	400	450																		
Z (- 25°C)/Z (20°C)	4	8	8	12	13	16																		
Load life (After 1000 hours application of rated voltage at 85°C, capacitors meet the characteristics requirements listed at right)	Leakage Current		Initial specified value or less																					
	Capacitance Change		within ±20% of initial value																					
	Tan δ		200% or less of initial specified value																					
Shelf life	After leaving capacitors under no load at 85°C for 1000 hours and applying voltage they meet the specified value for load life characteristics listed above.																							
Marking	Printed with white colour letter on black sleeve.																							
This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2004.																								
TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.		DRAWN BY:		DATE:		DRAWING TITLE: HV Series - Axial Electrolytic Capacitors																		
		S. Ram		08/05/06																				
		CHECKED BY:		DATE:		SIZE A	DWG NO. M10000225	ELECTRONIC FILE 208517_1_DWG	REV A															
		K. Suresh		08/05/06																				
		APPROVED BY:		DATE:						SCALE: NTS		U.O.M.: mm		SHEET: 2 OF 5										
N. Kiwomya		22/05/06																						

SHEET: 4 OF 4