


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2070	A	Released	JN	09-03-09	JWM	09-03-09	JWM	09-03-09



Specification

1. Rated Voltage: 12VDC
2. Operating Voltage: 3~16VDC
3. Max. Rated Current: 35(20)mA at 12VDC
4. Min. Sound Pressure Level: 100(92)dB at 12VDC/30cm
5. Resonant Frequency: 3.2±0.5KHz
6. Tone Nature: Continuous + Fast Pulse
7. Case Material: ABS/White
8. Operating Temperature: -20~+60°C
9. Store Temperature: -30~+70°C
10. Weight: 21g
 - Black: Ground (-)
 - Red: Continuous (+)
 - Yellow: Fast Pulse (-)

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:	DATE:
Jason Nash	09-03-09
CHECKED BY:	DATE:
Jason Nash	09-03-09
APPROVED BY:	DATE:
Jason Nash	09-03-09

DRAWING TITLE:			
SIZE		DWG. NO.	ELECTRONIC FILE
A		MCKPI-G4514L-4017	25R0706.dwg
SCALE:	NTS	U.O.M.: INCHES [mm]	HEET: 1 OF 1