





REV.	DATE	DESCRIPTION
NC	11/27/02	INITIAL RELEASE



RECOMMENDED CABLE
STRIPPING DIMENSIONS



NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
2. CRIMPED CONTACT PIN
SQ. CRIMP SIZE .043"

			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		APPROVALS		DATE		Amphenol - Connex CONNECTOR CORPORATION MCX CRIMP PLUG (FOR RG-58A/U, 58C/U CABLE)							
8					DRAWN		G.R.S.						11/27/02			
7			CHECKED													
6			ISSUED													
5																
4	FERRULE	COPPER	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .XXX = ± 0.005" .XX = ± 0.010" .X = ± 0.020"		SIZE		FSCM NO.		DWG. NO.		REV.				
3	CONTACT PIN	BRASS	GOLD			A		99001		252180.DWG		NC				
2	INSULATOR	TEFLON	NATURAL													
1	BODY	BER. COPPER	GOLD			SCALE		NA		PART NO.		252180		SHEET 1 OF 1		
DESCRIPTION			MATERIAL	FINISH	DO NOT SCALE DRAWING											