








LED SPECS	UNITS	ULTRA RED
FORWARD CURRENT	mA	20 TYP.
FORWARD VOLTAGE	V	1.95 TYP. - 2.5 MAX.
LUMINOUS INTENSITY	MCD	1800 TYP.



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. RATING: 12VDC @ 50mA
4. CONTACT RESISTANCE: 100m Ω MAX.
5. INSULATION RESISTANCE: 100M Ω MIN., 500VDC
- ▲ 6. OPERATING FORCE: 160 $\pm$ 50gf
7. TRAVEL: 0.2 $\pm$ 0.1mm
8. OPERATING TEMPERATURE: -40°C to 85°C
9. OPERATING LIFE: 500,000 CYCLES
- ▲ 10. LED: ULTRA RED
11. ▲ DENOTES CRITICAL PARAMETERS
12. 2011/65/EU (ROHS) COMPLIANT
13. PACKAGING: 100 PIECES PER TRAY



J	22986	Update LED	8/31/17	MW	TITLE TL1260RQRBLK			
REV	PCR NO	DESCRIPTION	DATE	BY	SCALE	DATE	DR	REV
					4:1	5/11/2007	TN	J
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED							DWG B200002	