





SUGGESTED MATING TAB




- 1
- MATL: #2 HARD BRASS OR NICKEL PLATE STEEL.
- 2
- NO BURRS PERMISSIBLE AT HOLE.
- 3
- TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMPERATURE IS OVER 225°F
- 4
- MUST BE FLAT WITHIN 0.076 [0.003] OVER THIS LENGTH.
- 5
- HOLE MUST BE SYMMETRICAL ABOUT TAB ϕ WITHIN 0.076 [0.003].
- *
- TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.




SECTION A-A



SECTION B-B
ROTATED 90° CW



SECTION D-D



SECTION C-C

This specification lists various figures which indicate the direction a product comes off the top of the reel.




Figure 6

Contact portion

- 1
- CONTINUOUS STRIP ON REELS.
- 2
- ACCEPTS #22-#18 SINGLE WIRE SIZES, WIRE CRIMP IS 2.03 [0.080], F TYPE.
- 3
- FITS INSULATION RANGE 2.29-3.30 [0.090-0.130] DIA, INSULATION CRIMP IS 3.94 [0.155] F TYPE.

OBSOLETE

REELING
107-3 FIG.6

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

MATERIAL
BRASS

SEE TABLE

DWN JR RUTH 6/26/98
CHK MS FEHER 6/26/98
APVD E HOWARD 6/26/98
PRODUCT SPEC
APPLICATION SPEC

WEIGHT 0
CUSTOMER DRAWING

TIN		1217097-2	
-		-1217097-1-	
FINISH		PART NO.	
TE Connectivity			
NAME RECEPTACLE, POSITIVE-LOCK, MARK III, 4.75 [0.187] SERIES -			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	 1217097	-
		SCALE 6:1	SHEET 1 of 1
			REV F1