

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

HC

00

P

LTR

DESCRIPTION

DATE

DWN

APVD


0

RELEASED ON TYCO FORMAT

13MAY03

GV

DC

**MATERIAL:**

CENTER CONDUCTOR— BERYLLIUM COPPER PER ASTM-B-196, ALLOY C17300, COND H.

OUTER CONDUCTOR— STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303


DIELECTRIC— PTFE FLOUROCARBON PER ASTM-D-4894

PLATING:

INNER CONDUCTOR— GOLD PER MIL-G-45204

OUTER CONDUCTOR— PASSIVATED PER QQ-P-35

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHESTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± .010
4 PLC	± -
ANGLES	± 1°

MATERIAL

FINISH

DWN

12MAY03

G. VIERA

CHK

13MAY03

D. CAMELIO

APVD

13MAY03

D. CAMELIO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME

HI-FREQUENCY "N" (18 GHz) JACK
TO "SMA" PLUG ADAPTER
(3682-2241-00)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1058664-1

-

SCALE 5:1

SHEET 1 OF 1

REV 0