

HONEYWELL PART NUMBER
41SM301
PRODUCT CODE TYC7838

REV	DOCUMENT	CHANGED BY	CHECK
2	0038112	KVS 04JUN08	ASD

B


A

A

B


A

A



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREW OF Ø.087 MAX ON .375 ± .002 CENTERS
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F
 - 4 REVERSED TERMINAL DESIGNATION
 - 5 - CAUTION: TERMINAL DESIGNATION ON SWITCH CASE INDICATES CIRCUITRY OF SWITCH IN OPERATED POSITION (PLUNGER DEPRESSED)

RELEASE NO.	200677
REPLACES	X113048 - SM

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 		DRAWN	VK	25 OCT 07						
OPERATING FORCE — — — 3 — 5 OZ		CONTACT ARRANGEMENT S P D T					CHECK	RJ	25 OCT 07						
RELEASE FORCE— — — — — 1 OZ MIN		APPROVALS	KEMA, CE	11A 250V ~ T85 1E4 5A 30 Vdc T85 1E4 		- 0.030 0.015 0.005 - -	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE					
DIFFERENTIAL TRAVEL— — — .004 MAX				UL, CSA	11A 1/4 HP 125 250 VAC 5A 30 VDC  		BRAND L190	INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
OVERTRAVEL — — — — — .005 MIN								RASTER			B	I	41SM301		2
										SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[41SM3-T](#)