





used for: DIN 41617

Art.-Nr. Part-No.	Polzahl No. of pos.	A ± 0.3	B ± 0.1	C ± 0.1
102A10049X	13	45.8	40	12x2.5=30
102A10069X	21	65.8	60	20x2.5=50
102A10089X	31	90.8	85	30x2.5=75



Leiterplattenbohrbild
P.C.B.-HOLE DRILLINGS (b)



Bemerkung:

1. Isolierkörper: PC GF UL 94 V-1, grau (C)
2. Kontakte: Cu-Legierung
Veredelung: Au über Ni
3. Bedruckung: Art.-Nr. CONEC ABC

NOTES:

1. INSULATOR: PC GF UL 94 V-1, GREY (C)
2. CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
3. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GMBH
DO NOT ALTER CAD DRAWING BY HAND

2 x c	Ä 4154	08.11.2011	K.H.	d-old
1 x b	Ä 3723	18.08.2010	K.H.	
a	Original			
rev.	description	date	name	

tolerance		 dim. in mm
2002	date	name
drawn	22.11.	Parei
appd.	22.11.	Kühle
norm	DIN 41617	
d-old		
		

scale:		2:1
material:		SEE NOTES
title:		FEMALE CONNECTOR 13-31pos. with straight solder pins
dwg no:		10K1A002
part no:		SEE TABLE
DIN-A 3 sh: 1/1		