


PLAIN - SEALED IP68								
BOX SIZE (MM)					ORDER CODE			
PCB GUIDE	L	W	H	Size	Plain	Powder Coated	Nylon Coated	
	88.9	34.9	30.5	A	480-0010	481-0010 **	482-0010 **	
	114.3	63.5	30.5	B	480-0020	481-0020 **	482-0020 **	
	114.3	88.9	55.9	C	480-0030	481-0030 **	482-0030 **	
	114.3	64.5	55.9	D	480-0040	481-0040 **	482-0040 **	
	171.5	120.6	55.9	E	480-0050	481-0050 **	482-0050 **	
	171.5	120.6	106.7	F	480-0060	481-0060 **	482-0060 **	
	222.3	146	56	G	480-0070	481-0070 **	482-0070 **	
	222.3	146	106.7	H	480-0080	481-0080 **	482-0080 **	
*	275	175	66	J	480-0090	481-0090 **	482-0090 **	
*	139.7	101.6	77	K	480-0100	481-0100 **	482-0100 **	
*	165	127	77	L	480-0110	481-0110 **	482-0110 **	
*	120	100	36	M	480-0120	481-0120 **	482-0120 **	
*	250	250	100.3	N	480-0130	481-0130 **	482-0130 **	
*	80	55	26	P	480-0140	481-0140 **	482-0140 **	
*	60	55	31	Q	480-0150	481-0150 **	482-0150 **	
* Boxes with PCB guides				** Colour option - Code Suffix: Grey = A Blue = B Black = E				
FLANGED - SEALED IP68								
BOX SIZE (MM)					ORDER CODE			
PCB GUIDE	L	L (exc Flg)	W	H	Size	Plain	Powder Coated	Nylon Coated
*	114.3	89.2	35.15	30.5	A	483-0010	484-0010**	485-0010**
*	139.7	114.1	63.6	30.5	B	483-0020	484-0020**	485-0020**
*	139.7	114.2	63.7	55.9	C	483-0030	484-0030**	485-0030**
*	139.7	114.7	89.15	55.9	D	483-0040	484-0040**	485-0040**
*	202	171.8	120.8	55.9	E	483-0050	484-0050**	485-0050**
*	202	171.8	120.8	106.7	F	483-0060	484-0060**	485-0060**
*	252	222.6	146.4	55.9	G	483-0070	484-0070**	485-0070**
*	170	140	101.6	77	K	483-0100	484-0100**	485-0100**
*	152	120	100.2	36	M	483-0120	484-0120**	485-0120**
* Boxes with PCB guides				** Colour option - Code Suffix: Grey = A Blue = B Black = E				



- A RANGE OF DIE CAST ALUMINUM ENCLOSURE SEALED TO BS EN 60529:1992 IP66, IP67 AND IP68 (5Mtrs for 1 hour)
- HARD NEOPRENE RUBBER SBR133 SEAL WITH SELF ADHESIVE CCS130106 BACKING
- MIN SEAL THICKNESS 3.0MM - MIN SEAL FRAME WIDTH 4.0MM
- MIN ENCLOSURE WALL THICKNESS 1.5MM
- MIN ENCLOSURE LID THICKNESS 1.5MM

INTERPOLATED SIZES ARE PERMITTED PROVIDED THE MINIMUM CENTRES ARE MAINTAINED IN ACCORDANCE WITH THE 455/459 SERIES SPECIFICATION

PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF DEM MANUFACTURING. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF DEM MANUFACTURING IS PROHIBITED. 	Drawn by W.COXON 27/05/09		UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETRES LINEAR TOLERANCES: NO DECIMAL PLACES ±0.5mm 1 DECIMAL PLACE ±0.1mm 2 DECIMAL PLACES ±0.03mm ANGULAR TOLERANCES: ±1° MATERIAL:	A3	TITLE: GENERAL SPECIFICATION FOR IP68 RANGE OF ENCLOSURES
	FINISH: AS ABOVE				
	THIRD ANGLE PROJECTION	DEBUR AND BREAK SHARP EDGES			
	IF IN DOUBT ASK DO NOT SCALE DRAWING				
TEL: +44 1724 273200 F-MAIL: SALES@DEM-UK.COM WEBSITE: WWW.DEM-UK.COM			WEIGHT: 4565864.119	SCALE:1:2	SHEET 1 OF 1
				DWG NO. 48x SPEC IP68 RANGE	01 ISSUE