



Produkt Informationen



WX 2020 Set

Bestellnummer : T0053421699

Power unit with 2 channels

Power unit WX 2, 200 W, 2x soldering iron WXP 120, 120 W, 24 V, with Fast Response Technology, 2x soldering tip XT B and 2x safety rest WDH 10

Technical Data

This station is ESD safe.



Dimensions L x W x H: 170 x 151 x 130 mm (6,69 x 5,94 x 5,12 inch)

Weight: approx. 3,2 kg

Channels: 2

Power supply: 230 V, 50 Hz

Power consumption: 200 W (255 W)

Protection class: I

Temperature range: Adjustable from 50°C - 550°C (150°F - 999°F)
Adjustable temperature range varies among tools

Temperature accuracy: ± 9°C (± 17°F)

Temperature stability: ± 2°C (± 4°F)

Equipotential bonding: Via 3,5 mm pawl socket on back of device

Material touch panel: Made of antistatic coated material

Dimensions touch panel: 74 x 38 mm

Resolution: 255 x 127 (128) dots

Display backlighting: 4 LEDs

Equipotential bonding:

The 3,5 mm switch offers four different options:

- a) Hard grounded without plug (original delivery)
- b) Equipotential bonding: with plug, compensation line on center contact
- c) Potential free: with plug
- d) Soft grounded: with plug and soldered resistor grounded via selected resistor

USB interface:

USB interface in front of firmware updates, parameterization and monitoring
USB interface supports all standard USBflash drive types

Power unit WX 2

- Innovative operation concept
- Robust touch screen with ESD safe glass
- Intuitive use with turn-click-wheel with enter key and finger guide.
- Blue LED backlighting
- Multilingual menu navigation
- High functionality
- No safety rest with Stop & Go function needed thanks to integrated acceleration sensor
- Optimized precision, better stability by sensor in the soldering iron
- Specific parameterization of tool by storage medium in hand piece.
- Visual process control via blue LED ring light
- All WX tools connectable