

Ø 10 mm Film Dielectric Trimmers

TEST VOLTAGE (DC) FOR 1 MINUTE:

300 V

MAXIMUM CONTACT RESISTANCE:

10 mΩ

MINIMUM INSULATION RESISTANCE:

10000 MΩ

CATEGORY TEMPERATURE RANGE:**PP**

- 40 to + 70 °C

PC, PTFE

- 40 to + 85 °C

CLIMATIC CATEGORY (IEC 60068):**PP**

40/070/21

PC, PTFE

40/085/21

MINIMUM STORAGE TEMPERATURE:

- 55 °C

RELATED SPECIFICATION:

IEC 60418-1 and 4

EFFECTIVE ANGLE OF ROTATION:

180°

OPERATING TORQUE:

2 to 25 mNm

MAXIMUM AXIAL THRUST:

2 N

FEATURES

- Housing diameter 10 mm
- For a basic grid of 2.54 mm (0.1") or 2.50 mm
- Top and bottom or top adjustment
- Vertical and horizontal versions
- Round or hexagonal head

**RoHS**
COMPLIANT**APPLICATIONS**

- For consumer and industrial equipment

DESCRIPTION:

The vanes of the trimmer are stacked on a sturdy plastic base. The color of the base indicates the maximum capacitance (see Electrical Data Table). The dielectric is a film of polypropylene (PP), polycarbonate (PC) or polytetrafluorethylene (PTFE), which supports the vanes in such a way that good stability is ensured and no microphony can occur.

Flux absorption between the vanes is prevented.

Cleaning with solvents is not advised.

Versions are available with either a vertical spindle, or a horizontal spindle.

Both versions have top adjustment by means of a screwdriver or trimming key and bottom adjustment by means of a key.

QUALITY LEVEL:

Sampling and data evaluation for quality level in accordance with "MIL-STD-105D" and "IEC 60410":

< 0.15 % major defects

< 0.65 % minor defects


Each capacitor is tested for minimum $C_{\min}$ and is also subjected to the full test voltage.

 $C_{\min}$ / $C_{\max}$:

2.5/15 to 7/105 pF


RATED VOLTAGE (DC):

150 V




Trimmers 2281 808 series, vertical version

Dimensions in millimeters.





The large hole is for bottom adjustment and the diameter is determined by user's requirements.

Hole pattern



R = rotor, S = stator

Hole pattern




R = rotor, S = stator

Hole pattern

ADJUSTMENT

For top adjustment a screwdriver or trimming key can be used; for bottom adjustment a key is required as shown below



Bottom adjustment key

Trimmers 2281 808 series, horizontal version

Dimensions in millimeters

ORDERING INFORMATION

C_{min}/C_{max} (pF)	CATALOG NUMBER 2281 808 OR BFC2 808*						
	HORIZONTAL VERSION		VERTICAL VERSION				
	HOLE PATTERN 5 mm × 10 mm		HOLE PATTERN 5 mm × 10 mm		HOLE PATTERN 7.5 mm × 5 mm		
	ROUND HEAD	HEX. HEAD	ROUND HEAD	HEX. HEAD	ROUND HEAD	HEX. HEAD	ROUND HEAD
	TOP AND BOTTOM ADJUSTMENT		TOP AND BOTTOM ADJUSTMENT				TOP ADJUSTMENT
2.5/15	61159	-	31159	-	32159	-	-
3/22.5	61229	-	31229	-	32229	-	-
5.5/40	61409	-	31409	-	32409	-	-
5.5/50	-	-	01029	-	01006	-	-
5.5/65	61659	64659	31659	34659	32659	-	01001
6/80	61809	64809	31809	34809	32809	35809	-
7/105	61101	64101	31101	-	32101	-	-
6/120	-	-	31121	-	-	-	-

* ordering code for SAP system

**Mounting:**

The trimmer can be mounted on printed-circuit boards with a grid of 2.50 mm or 2.54 mm and a minimum hole diameter of 1.25 mm.

PACKAGING:

Bulk packaged in cardboard boxes lined with expanded plastic. For smallest packaging quantities (SPQ) see Electrical Data Table.

ELECTRICAL DATA

GUARANTEED MAX. C _{min} / MIN. C _{max} AT 200 kHz (pF)	SPINDLE	SHAPE OF HEAD	FIG.	ADJ. MODE	DIEL.	TAN δ AT C _{max} × 10 ⁻⁴		TEMP. COEFF. (10 ⁻⁶ /K)	MIN. f _{res} AT C _{max} (MHz)	COL. OF BASE	SPQ	CATALOG NUMBER 2281 or BFC2*
						1 MHz	100 MHz					
2.5/15	vertical	round	1	top + bottom	PP	≤ 10	≤ 25	- 200 ± 700	420	blue	800	 808 31159
	2		800								 808 32159	
	horizontal		3								700	 808 61159
3/22.5	vertical	round	1	top + bottom	PP	≤ 10	≤ 25	- 200 ± 700	200	green	800	 808 31229
	2		800								 808 32229	
	horizontal		3								700	 808 61229
5.5/40	vertical	round	1	top + bottom	PP	≤ 10	≤ 25	- 200 ± 400	200	grey	800	 808 31409
	2		800								 808 32409	
	horizontal		3								700	 808 61409
5.5/50	vertical	round	1	top + bottom	PTFE	≤ 10	≤ 25	- 200 ± 400	170	yellow	800	 808 01029
			2								800	 808 01006
5.5/65	vertical	round	2	top	PP	≤ 10	≤ 25	- 200 ± 500	170	yellow	800	 808 01001
		round	1	top + bottom							800	 808 31659
		round	2								800	 808 32659
		hexag.	1								700	 808 34659
	horizontal	round	3								700	 808 61659
		hexag.	3								600	 808 64659
		hexag.	3								600	 808 64659
6/80	vertical	round	1	top + bottom	PC	≤ 70	-	- 50 ± 400	170	red	800	 808 31809
		hexag.	1								700	 808 34809
		round	2								800	 808 32809
		hexag.	2								700	 808 35809
	horizontal	round	3								700	 808 61809
		hexag.	3								600	 808 64809
		hexag.	3								600	 808 64809
7/105	vertical	round	1	top + bottom	PC	≤ 70	-	- 50 ± 400	170	violet	800	 808 31101
		round	2								800	 808 32101
	horizontal	round	3								700	 808 61101
		hexag.	3								600	 808 64101
6/120	vertical	round	2	top + bottom	PC	≤ 70	-	- 50 ± 400	170	violet	800	 808 31121

* ordering code for SAP system

TEST PROCEDURES AND REQUIREMENTS

IEC 60418-1 CLAUSE	IEC 60068 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS
4.2		method of mounting	method A	
14		capacitance drift	after TC measurement	$\Delta C/C: \leq 4.5\%$ for $C_{max} < 40$ pF; $\Delta C/C: \leq 2.5\%$ for $C_{max} \geq 40$ pF
19		thrust	axial thrust of 2 N	$\Delta C/C: \leq 0.3\%$
21		robustness of terminations:		
21.1	Ua	tensile	1 N	no damage
21.2	Ub	bending	1 cycle	no damage

IEC 60418-1 CLAUSE	IEC 60068 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS
22	Na	rapid change of temperature	1 cycle; 0.5 hours at lower and 0.5 hours at upper category temperature	$\Delta C/C: \leq 1.5 \%$
23	T Ta Tb	soldering: solderability resistance to heat	solder bath immersion 3 mm; 235 °C; 2 s solder bath: 260 °C; 10 s	good wetting no mechanical damage no mechanical damage
24	Eb	impact bump	4000 ± 10 bumps; 40 g; 6 ms	$\Delta C/C: \leq 0.4 \%$; no mechanical damage
25	Fc	vibration	frequency 10 to 55 Hz; amplitude 0.35 mm; 1.5 hours	$\Delta C/C: \leq 0.8 \%$; no mechanical damage
26	B	climatic sequence:		$\Delta C/C: \leq 3 \%$ for $C_{\max} < 80 \text{ pF}$; $\Delta C/C: \leq 6 \%$ for $C_{\max} \geq 80 \text{ pF}$ $\tan \delta: \leq 15 \times 10^{-4}$ for $C_{\max} < 80 \text{ pF}$; $\tan \delta: \leq 80 \times 10^{-4}$ for $C_{\max} \geq 80 \text{ pF}$ $R_{\text{ins}}: \geq 10000 \text{ M}\Omega$; rotor contact R: $\leq 10 \text{ }\Omega$
26.1		dry heat	16 hours at upper category temperature	
26.2		damp heat accelerated, first cycle	1 cycle; 24 hours; + 40 °C; 95 to 100 % RH	voltage proof: 300 V for 1 minute
26.3		cold	16 hours; - 40 °C	visual examination: no mechanical damage
26.5		damp heat accelerated, remaining cycles	1 cycle; 24 hours; + 40 °C; 95 to 100 % RH	operating torque: 2 to 35 mNm
27	Ca	damp heat steady state	21 days; + 40 °C; 90 to 95 % RH	$\Delta C/C:$ $\leq 3 \%$ for $C_{\max} < 100 \text{ pF}$; $\leq 3 \%$ for $C_{\max} \geq 100 \text{ pF}$ $\tan \delta: \leq 20 \times 10^{-4}$ for $C_{\max} < 80 \text{ pF}$; $\tan \delta: \leq 80 \times 10^{-4}$ for $C_{\max} \geq 80 \text{ pF}$ $R_{\text{ins}}: \geq 10000 \text{ M}\Omega$; rotor contact R: $\leq 10 \text{ m}\Omega$ voltage proof: 300 V for 1 minute visual examination: no mechanical damage operating torque: 2 to 35 mNm
29		mechanical endurance	10 cycles	$\Delta C/C: \leq 1 \%$ $\Delta C/C$ after axial thrust: $\leq 0.4 \%$; rotor contact R: $\leq 10 \text{ m}\Omega$ voltage proof: 300 V for 1 minute visual examination: no mechanical damage operating torque: 1.5 to 37 mNm



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.