


Disc Ceramic Capacitors



General Specifications - Class III Semi Conducting

DIELECTRIC - CLASS III

A thin dielectric layer is grown on a disc of conductive ceramic. Very large capacitances can be obtained due to reduced thickness of this barrier layer and its inherently high dielectric constant. Due to its small dimensions, they are a less expensive replacement of multilayer ceramic or polyester capacitors. An equivalent circuit is shown below:



Meets IEC 324 (1970).

HOW TO ORDER

5Z	H	104	Z	A	C	A	A
Product Code	Voltage	Capacitance	Tolerance	Lead Forming	Capacitor Diameter	Finishing	Packaging

PERFORMANCE CHARACTERISTICS CLASS III


Measured at	1.0 kHz / 0.1 Vrms / 25°C	
Dissipation Factor (%)	$C_R \leq 22 \text{ nF} \rightarrow Y5V, Y5U \leq 7.5\%$ $C_R > 22 \text{ nF} \rightarrow Y5V, Y5P \leq 5.0\%$	
Tolerance	$Y5P \rightarrow \pm 20\% / -20 + 50\%$ $Y5U \rightarrow \pm 20\% / -20 + 50\%$ $Y5V \rightarrow -20\% + 50\% / -20 + 80\%$	
Insulation Resistance (IR)	Y5P	$\geq 12 \text{ M}\Omega$
	Y5U	$4.7 \text{ nF} \dots 100 \text{ nF} \rightarrow \geq 10 \text{ M}\Omega$ $200 \text{ nF} \rightarrow \geq 1 \text{ M}\Omega$
	Y5V	$\geq 100 \text{ M}\Omega$
Dielectric Strength NOTE: Charging current limited to 50 mA	Between leads	$V_t = 1.25 V_R$
	Body insulation	$V_R = 25V \quad V_t = 100V \text{ (DC)}$ $V_R = 50V \quad V_t = 150V \text{ (DC)}$
Operating Temperature Range (°C)	-30... +85°C	
Climate Category	30 / 85 / 21	

Disc Ceramic Capacitors

General Specifications - Class III Semi Conducting



TEMPERATURE COEFFICIENT – TYPICAL CURVES



PHENOLIC COATED – CAPACITANCE VS. DISC DIAMETER

millimeters (inches)

Class III	$\Delta C/C$ (max.) $\pm 12\%$ Range -30... +85°C		$\Delta C/C$ (max.) +30 -65% Range -30... +85°C		$\Delta C/C$ (max.) +30 -65% Range -30... +85°C
Temp. Coefficient	Y5P		Y5U		Y5V
Digits 1,2,3 of P.N.	5WF	5WH	5YF	5YH	5ZH
Rated Voltage (V _R)	25 VDC	50 VDC	25 VDC	50 VDC	50 VDC
C _R (pF)					
4,700	5.0 (0.197)	5.0 (0.197)	5.0 (0.197)	5.0 (0.197)	5.0 (0.197)
10,000	6.0 (0.236)	6.0 (0.236)		6.0 (0.236)	
22,000	7.0 (0.276)	8.0 (0.315)			
33,000	8.0 (0.315)	9.0 (0.354)	6.0 (0.236)	7.0 (0.276)	6.0 (0.236)
47,000	9.0 (0.354)		7.0 (0.276)	8.0 (0.315)	
50,000					
68,000	11.0 (0.433)	11.0 (0.433)	8.0 (0.315)	9.0 (0.354)	6.0 (0.236)
100,000					
200,000					10.0 (0.394)

Note: Damp Heat Steady State: 90... 95% R.H. 40°C / 21 days. No voltage to be applied.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AVX:

[5WH103MDCAE](#) [5WH103MDCAA](#) [5ZH104ZOCJM](#) [5WF103MECAI](#) [5WH103KECAE](#) [5WH103MECAA](#)
[5ZH103MEDAA](#) [5WH473ZOGAM](#) [5ZH104MEDAA](#) [5ZH104ZEDAA](#) [5WF503MXGAA](#) [5YH104MEEAA](#)
[5WF104MEJAA](#) [5WF473MEGAE](#) [5ZH104ZOCAM](#) [5ZH103ZECOA](#) [5WH103MACJI](#) [5WH103ZACJH](#) [5YH103ZAAJA](#)
[5YH103ZAAJI](#) [5YH473ZOEAM](#) [5ZF104ZOCAM](#) [5ZH104MACJI](#) [5ZH104ZACAH](#) [5ZH104ZACJA](#) [5ZH104ZACJI](#)
[5ZH104ZOCJA](#) [5ZH104ZOCJL](#)