

MATERIAL NUMBER	# OF COLUMNS	DIM "A" MAX	DIM "B"
75710-***5	5	25.90	14.80
75710-***6	6	29.60	18.50
75710-***8	8	37.00	25.90
75710-***0	10	44.40	33.30

75710-****

MODULE TYPE -- TAIL PLATING TYPE

GUIDE LEFT -- MATTE TIN (FORMERLY TIN/LEAD)= 2

GUIDE LEFT -- MATTE TIN = 3

POLARIZATION KEY ORIENTATION

0 = NO KEY

1 = A 5 = E

2 = B 6 = F

3 = C 7 = G

4 = D 8 = H

OF COLUMNS/PLATING

05 = 5 COL 30 GOLD

06 = 6 COL 30 GOLD

08 = 8 COL 30 GOLD

10 = 10 COL 30 GOLD

55 = 5 COL W/ESD 30 GOLD

56 = 6 COL W/ESD 30 GOLD

58 = 8 COL W/ESD 30 GOLD

50 = 10 COL W/ESD 30 GOLD

25 = 5 COL 10 GOLD (MAPS)

26 = 6 COL 10 GOLD (MAPS)

28 = 8 COL 10 GOLD (MAPS)


20 = 10 COL 10 GOLD (MAPS)

65 = 5 COL W/ESD 10 GOLD (MAPS)

66 = 6 COL W/ESD 10 GOLD (MAPS)

68 = 8 COL W/ESD 10 GOLD (MAPS)

60 = 10 COL W/ESD 10 GOLD (MAPS)



SEE SHEET 1 EC NO: UCP2013-4121 DRAWN: RHIPPLE 2013/04/01 CHKD: MWOLFE 2013/04/01 APPR: SMILLER 2013/07/15 D	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY JLAURX	DATE 2007/03/06	TITLE I-TRAC DAUGHTERCARD 11 ROW SIGNAL MODULE GUIDE LEFT SALES DWG molex	DOCUMENT NO. SD-75710-002	SHEET NO. 2 OF 2
			4 PLACES	± ---	± ---	CHECKED BY BPISZCZOR	DATE 2007/03/06			
			3 PLACES	± ---	± ---	APPROVED BY CBIXLER	DATE 2007/03/06			
			2 PLACES	± 0.13	± ---	MATERIAL NO. SEE CHART				
			1 PLACE	± 0.25	± ---	ANGULAR ±1/2°				
			0 PLACE	±	±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		