



Series 680 Program Header and Cover

FEATURES

- Complete versatility for programming within the unit itself, thus eliminating the need for DIP switches in many situations.
- Available pre-programmed from Aries, or do-it-yourself using Aries Hand Tool P/N T-680. Consult Data Sheet 22002 for Programming Tool information.
- Available with plain (solid) or "top-slot" press-on covers. Plain covers protect programs while "top-slot" covers allow programming of opposing pins through square openings on top.

GENERAL SPECIFICATIONS

- STANDARD BODY AND COVER: black UL 94V-0 Glass filled 4/6 Nylon
- PINS: Brass 260 3/4-hard, ASTM B-36
- PIN PLATING: "-T" 50-150 μ [1.27 μ] min. matte Sn per ASTM B545-97(2004) e1 over 50 μ [1.27 μ] min. Ni per SAE AMS-QQ-N-290B; "-TL" 50-150 μ [1.27 - 3.81 μ] min. 60/40 Sn/Pb per SAE AMS-P-81728 over 50 μ [1.27 μ] min. Ni per SAE AMS-QQ-N-290B
- CURRENT RATING: 1 amp
- OPERATING TEMPERATURE: 221°F [105°C]

MOUNTING CONSIDERATIONS

- SUGGESTED PCB HOLE SIZE: 0.032 $\pm$ 0.002 [0.81 $\pm$ 0.05] dia.


ALL DIMENSIONS: INCHES [MILLIMETERS]

ALL TOLERANCES: $\pm$ 0.005 [0.13] UNLESS OTHERWISE SPECIFIED

"A" # PINS PER ROW $\times$ 0.100 [2.54] +0.050 [1.27]

"B" (# PINS PER ROW -1) $\times$ 0.100 [2.54]

CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS



CUSTOMIZATION: In addition to the standard products shown on this page, Aries specializes in custom design and production. Special materials, platings, sizes, and configurations can be furnished, depending on the quantity. **NOTE:** Aries reserves the right to change product general specifications without notice.

ORDERING INFORMATION

XX-680-19X XX X

No. of Pins
4 thru 24
Series
Interconnection Styles
see below


Optional Top Slot = "C"
preassembled to header
Style 191 only
Plating
T = Sn
TL = Sn/Pb

COVER ORDERING INFORMATION

XX-68X-10

No. of Pins
4 thru 24
Cover Series
655 = Plain
658 = Top Slot

Cover No.



	STYLE 190 All pins interconnected, both adjacent and opposing
	STYLE 191 Opposing pins interconnected only.



ARIES
ELECTRONICS, INC.

Bristol, PA 19007-6810 USA
TEL (215) 781-9956 • FAX (215) 781-9845
WWW.ARIESELEC.COM • INFO@ARIESELEC.COM



PRINTOUTS OF THIS DOCUMENT MAY BE OUT OF DATE AND SHOULD BE CONSIDERED UNCONTROLLED

16005
Rev. AA