


HW-14-08-G-S-300-100



DW-11-20-T-D-825

(2.54 mm) .100"

DW, EW, ZW, HW-TH SERIES

FLEXIBLE .025" SQ BOARD STACKERS

Mates with:SSW, SSQ, ESW, ESQ,
CES, SLW, BSW, BCS,
SSM, HLE, PHF**Cable Mates:**

IDSS, IDSD, SMSD, SMSS

SPECIFICATIONSFor complete specifications
see www.samtec.com?DW,
www.samtec.com?EW,
www.samtec.com?ZW or
www.samtec.com?HW-TH**Insulator Material:**DW, EW, ZW: Black Glass
Filled Polyester
HW: Natural Liquid
Crystal Polymer**Terminal Material:**

Phosphor Bronze

Plating:

Au or Sn over

50 μ " (1.27 μ m) Ni**Operating Temp Range:**

-55 °C to +125 °C with Gold

-55 °C to +105 °C with Tin

RoHS Compliant:

Yes

Lead-Free Solderable:





DW, EW, ZW:

No, Lead Wave Only




HW: Yes

RECOGNITIONSFor complete scope of
recognitions see
www.samtec.com/quality**ALSO AVAILABLE
(MOQ Required)**

- Other platings
- Contact Samtec.

Notes:For added mechanical stability,
Samtec recommends
mechanical board spacers be
used in applications with gold or
selective gold plated connectors.
Contact ipg@samtec.com for
more information.This Series is non-standard,
non-returnable.**TYPE
STRIP****DW**
= (2.79 mm)
.110" Tail**EW**
= (8.38 mm)
.330" Tail**ZW**
= Custom Tail**HW**
= High Temp
Custom Tail**NO. PINS
PER ROW****LEAD
STYLE****PLATING
OPTION****ROW
OPTION****STACKER
HEIGHT****OTHER
OPTIONS****Specify LEAD STYLE
from chart**

LEAD STYLE	OAL
-07	(10.92) .430
-08	(13.46) .530
-09	(18.54) .730
-10	(21.08) .830
-11	(23.62) .930
-12	(26.16) 1.030
-13	(31.24) 1.230
-14	(36.32) 1.430
-15	(16.00) .630
-16	(11.30) .445
-17	(12.19) .480
-19	(33.78) 1.330
-20	(28.70) 1.130

01 thru 50**-S**
= Single
Row**-D**
= Double
Row**-T**
= Triple
Row**-Q**
= Double
Row .200"
(5.08 mm)
row space**-“XXX”**
= Stacker
Height
(in inches)
(5.08 mm)
.200"
minimum
Example:
-250
= (6.35 mm)
.250"**-“XXX”**
= ZW or HW
Tail Length
(in inches)
(1.40 mm)
.055"
minimum
Example:
-250
= (6.35 mm)
.250"**-F**
= Gold flash on contact,
Matte Tin on tail**-L**
= 10 μ " (0.25 μ m)
Gold on contact area
of longer tail,
Matte Tin on tail**-G**
= 10 μ " (0.25 μ m)
Gold on contact area
of longer tail,
Gold flash on balance**-T**
= Matte Tin**-LL**
= Locking
Lead
(Shortest
dimension
between the
tail and the
post is the
end that will
be crimped.
Available
on tails from
(2.29 mm)
.090" to
(7.87 mm)
.310" only.)
Single row, 01
& 02 positions
& -Q row not
available**-“XXX”**
= Polarized
Specify omitted
pin position

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.