



© COPYRIGHT 2014 BY INDUSTRIAL FIBER OPTICS, INC.
ALL RIGHTS RESERVED.

LIGHT PIPE PREPARATION / INSTALLATION:



NOTES:


1. ROHS COMPLIANT
2. UL 94V-2 FLAMMABILITY RATING
3. -40°C TO 85°C OPERATING TEMPERATURE
4. SUITABLE FOR LIGHT PIPE WITH Ø2.2mm JACKET AND OPTICAL CORE NO GREATER THAN Ø1.5mm
5. DO NOT INSTALL PRIOR TO SOLDERING
6. FOR BEST RESULTS USE ONLY NARROW VIEWING ANGLE NON-DIFFUSED LEDS WITH OUTPUT POWER GREATER THAN 100mcd
7. NOT RECOMMENDED FOR DATA COMMUNICATIONS



METRIC

REVISIONS

REV	DESCRIPTION	ECO	DATE	DWN	APVD
A	Initial release		11/12/2008	BB	RD
B	Revised strip length from 1.0 ± .25	0034	9/17/2009	BB	KS
B1	Redrew, added overall dimensions		7/21/2014	BB	WR



PART IS MADE OF BLACK NYLON

UNLESS OTHERWISE SPECIFIED

DIMENSIONS MILLIMETERS [IN.]

DIMENSIONS ARE FOR
REFERENCE ONLY
NO TOLERANCES MAY BE
IMPLIED FROM THIS DOCUMENT

PRODUCT 51 0410

MATERIAL Nylon 66

FINISH None

DRAWN BY B. Bidwell

DATE 7/22/2014

CHECKED BY W. Rowe

DATE 7/22/2014

Industrial Fiber Optics
TEMPE, AZ 85281

NAME

SMT LED to Light Pipe

SIZE
A

SCALE
2:1

PART NUMBER
51 0310

REV
B1

DO NOT SCALE DRAWING

Sheet 1 of 1