




DUAL-IN-LINE SOCKETS

SERIES 110...001 • STANDARD SOLDER TAIL • OPEN FRAME



- All DIP sockets accept .015" - .025" diameter and standard IC leads
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Series 110 uses MM #1001 pins. See page 165 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION							
	A	B	C									
10	0.5	0.2	0.3	40	110-XX-210-41-001000							
4	0.2	0.3	0.4	102	110-XX-304-41-001000							
6	0.3	0.3	0.4	67	110-XX-306-41-001000							
8	0.4	0.3	0.4	50	110-XX-308-41-001000							
10	0.5	0.3	0.4	40	110-XX-310-41-001000							
14	0.7	0.3	0.4	28	110-XX-314-41-001000							
16	0.8	0.3	0.4	25	110-XX-316-41-001000							
18	0.9	0.3	0.4	22	110-XX-318-41-001000							
20	1.0	0.3	0.4	20	110-XX-320-41-001000							
22	1.1	0.3	0.4	18	110-XX-322-41-001000							
24	1.2	0.3	0.4	16	110-XX-324-41-001000							
28	1.4	0.3	0.4	14	110-XX-328-41-001000							
20	1.0	0.4	0.5	20	110-XX-420-41-001000							
22	1.1	0.4	0.5	18	110-XX-422-41-001000							
24	1.2	0.4	0.5	16	110-XX-424-41-001000							
28	1.4	0.4	0.5	14	110-XX-428-41-001000							
32	1.6	0.4	0.5	12	110-XX-432-41-001000							
24	1.2	0.6	0.7	16	110-XX-624-41-001000							
28	1.4	0.6	0.7	14	110-XX-628-41-001000							
32	1.6	0.6	0.7	12	110-XX-632-41-001000							
36	1.8	0.6	0.7	11	110-XX-636-41-001000							
40	2.0	0.6	0.7	10	110-XX-640-41-001000							
42	2.1	0.6	0.7	9	110-XX-642-41-001000							
48	2.4	0.6	0.7	8	110-XX-648-41-001000							
50	2.5	0.6	0.7	8	110-XX-650-41-001000							
52	2.6	0.6	0.7	7	110-XX-652-41-001000							
50	2.5	0.9	1.0	8	XX=Plating Code See Below	110-XX-950-41-001000			RoHS-2 2011/65/EU			
52	2.6	0.9	1.0	7		110-XX-952-41-001000						
64	3.2	0.9	1.0	6		110-XX-964-41-001000						
SPECIFY PLATING CODE XX =					11	13	91	93	99	41	43	44
Sleeve (Pin) 					10 μ" Au	10 μ" Au	200 μ" Sn/Pb	200 μ" Sn/Pb	200 μ" Sn/Pb	200 μ" Sn	200 μ" Sn	200 μ" Sn
Contact (Clip) 					10 μ" Au	30 μ" Au	10 μ" Au	30 μ" Au	100 μ" Sn/Pb	10 μ" Au	30 μ" Au	100 μ" Sn

XX=Plating Code
See Below

RoHS-2
2011/65/EU

