

SPECIFICATION CONTROL DRAWING

55PC1214

TITLE

ONE CONDUCTOR CABLE, SHIELDED, JACKETED, 600 VOLT

Date

3-1-94


Revision

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.

COMPONENT WIRE - 55PC0214

SHIELD - TIN-COATED COPPER

JACKET - RADIATION-CROSSLINKED,
MODIFIED ETFE



CONSTRUCTION DETAILS

PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
			LOWER SPEC LIMIT	TARGET WALL	LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC1214-26.*	26	38	.0050	.0060	.060	.064	.068	4.40	4.68
55PC1214-24.*	24	38	.0050	.0060	.065	.069	.073	5.28	5.57
55PC1214-22.*	22	38	.0050	.0060	.071	.075	.079	6.59	6.89
55PC1214-20.*	20	38	.0050	.0060	.080	.083	.087	8.62	8.96
55PC1214-18.*	18	38	.0050	.0060	.089	.093	.097	11.43	11.84
55PC1214-16.*	16	38	.0050	.0060	.097	.100	.104	13.68	14.11

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

CROSSLINKING PROOF TEST: 300 ± 3°C for 1 hour

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms), 60 Hz, 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100 % test

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL):

1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "*" in the part numbers above shall be replaced by a color code designator with a dash separating the component wire color from the jacket color.

Example: AWG 22, white component wire;
white jacket: 55PC1214-22-9-9

COLOR AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

Raychem

Raychem Corporation
300 Constitution Drive, Menlo Park, Calif. 94025
1-800-2 RAYCHEM FAX: 1-415-361-6100