Advantages of a Full Featured 700 Series Relay

Since the launch of the 700 series relays in 2000, this product line has continuously evolved both functionally and visually. The 700 series product line has the perfect mix of historical Magnecraft relay quality combined with a dynamic arsenal of options. When mated with the Magnecraft sockets and accessories, these RoHs compliant relays provide a complete modular system that will meet all your plug-in relay requirements in a package that is both visually appealing and functionally outstanding.

Removable Lock-Down Door
When Activated, Locks Push Button and Contacts in the Powered Position.

Color-Coded Push Button
Allows Manual Operation of Relay.
AC Coils Red or DC Coils Blue.

Finger Grip Cover
Easy Removal of Relay from Socket.

Gold Flashed Contacts
Prevents Premature Oxidation and Increases Shelf-life.

- **Offers a "one stop solution" for your power management system.**
- **Several Contact configurations and materials to meet your individual needs.**
- **Plug-In switching capabilities from 10 mA to 20 Amps.**
- **Several Feature Code and Operation combinations available for all budgets.**
- **Ejector clips, ribbed relay housings and space-saving sockets allow for easy removal from crowded DIN rails.**
- **Color and appearance designed for high visibility in all environments.**
- **Wiring diagrams include NEMA and IEC standards.**
- **Engineering availability allows for customized relay solutions.**

Contact Viewing Window
Shows Position of Contacts.

Isolated Input and Output Terminals
Separates Control Circuits from Load Circuits.

Slim Design
Minimizes Space on DIN Rail.

Module Compatible
Allows for Optional Protection or LED Modules to be Used With Sockets.

2-Way Side or DIN Rail Mounting System
Retrofits Existing Panel Mounting and 35mm DIN Rail.

Magnecraft
Your Contact for Industrial Relays

The Complete System Solution!

Flag Indicator
Shows Relay Status in Manual or Powered Condition.

Bi-Polar LED Status Lamp
Shows Coil "ON" or "OFF" Status.



I.D. Tag/Write-On Plastic Label
Used for Identification of Relays in Multi-Relay Circuits.

Mating Hold-Down Clip Available
Safely Secures Relay to Socket.



Finger-Safe
Protects Operators from Live Circuits.

I.D. Tag/Write-On Plastic Label
Used to Match Wire Identification Tags with Socket Connections.

Internal Coil Bus Jumper System
Allows Connection to Adjacent Sockets Without Additional Wiring.

Advantages of a Plain Cover 700 Series Relay

The Plain Cover Super Series relays support budget minded applications with premium performance. Maintaining the same ratings and internal components as the Full Feature Series; the Plain Cover Series perform as well as premium relays while maintaining low costs by offering several option configurations.

Finger Grip Cover
Easy Removal of Relay from Socket.

Contact Viewing Window
Shows Position of Contacts.

Gold Flashed Contacts
Prevents Premature Oxidation and Increases Shelf-life.

- **Offers a "one stop solution" for your power management system.**
- **Several Contact configurations and materials to meet your individual needs.**
- **Plug-In switching capabilities from 10 mA to 20 Amps.**
- **Several Feature Code and Operation combinations available for all budgets.**
- **Ejector clips, ribbed relay housings and space-saving sockets allow for easy removal from crowded DIN rails.**
- **Color and appearance designed for high visibility in all environments.**
- **Wiring diagrams include NEMA and IEC standards.**
- **Engineering availability allows for customized relay solutions.**

Isolated Input and Output Terminals
Separates Control Circuits from Load Circuits.

Slim Design
Minimizes Space on DIN Rail.

Module Compatible
Allows for Optional Protection or LED Modules to be Used With Sockets.

2-Way Side or DIN Rail Mounting System
Retrofits Existing Panel Mounting and 35mm DIN Rail.

Magnecraft
Your Contact for Industrial Relays

The Complete System Solution!

Flag Indicator
Shows Relay Status in Manual or Powered Condition.

Optional Bi-Polar LED Status Lamp
Shows Coil "ON" or "OFF" Status.



I.D. Tag/Write-On Plastic Label
Used for Identification of Relays in Multi-Relay Circuits.



Mating Hold-Down Clip Available
Safely Secures Relay to Socket.

Finger-Safe
Protects Operators from Live Circuits.

783 Ice Cube Relays/3PDT, 15 Amp Rating (DC & AC)

UL Listed When Used With Magnecraft Sockets.

UL Recognized File No. E43641



General Specifications (UL 508)

Contact Characteristics			Units	783XCX
Number and type of Contacts				3PDT
Contact materials				Silver Alloy
Thermal (Carrying) Current			A	15
Maximum Switching Voltage			V	300
Switching Current @ Voltage		~	Resistive	15A @ 120V 50/60Hz
		~	Resistive	12A @ 277V 50/60Hz
		⎓	Resistive	12A @ 28V
			HP	1/2 @ 120VAC
			HP	3/4 @ 250 VAC
			Pilot Duty	B300
Minimum Switching Requirement			mA	100 @ 5VDC (.5W)
Coil Characteristics				
Voltage Range		~	V	6....240
		⎓	V	6....125
Operating Range	% of Nominal	~		85% to 110%
		⎓		80% to 110%
Average consumption		~	VA	1.5
		⎓	W	1.4
Drop-out voltage threshold		~		15%
		⎓		10%
Performance Characteristics				
Electrical Life (UL508)	Operations @ Rated Current		(Resistive)	200,000
Mechanical Life	Unpowered			10,000,000
Operating time (response time)			ms	20
Dielectric strength	Between coil and contact	~	V(rms)	2500
	Between poles	~	V(rms)	2500
	Between contacts	~	V(rms)	1500
Environment				
Product certifications	Standard version			UL, CSA, CE
Ambient air temperature	Storage		°C	-40...+85
around the device	Operation		°C	-40...+55
Vibration resistance	Operational		g-n	3, 10 - 55 Hz
Shock resistance			g-n	10
Degree of protection				IP 40
Weight			grams	60

783XCX



NEMA
IEC

Wiring Diagram
Bottom View

Full Featured Dimensions



Plain Cover Dimensions



Full Featured

Plain Cover

Standard Part Numbers

BOLD-FACED PART NUMBERS ARE NORMALLY STOCKED

Nominal Voltage	Coil Resistance	3PDT Part Number (Full Feature) 15 Amp	3PDT Part Number (Plain Cover) 15 Amp
AC Operated			
6 VAC 50/60 Hz	6 Ohms	783XCXM4L-6A	783XCXC-6A
12 VAC 50/60 Hz	25.3 Ohms	783XCXM4L-12A	**783XCXC-12A**
24 VAC 50/60 Hz	103 Ohms	783XCXM4L-24A	**783XCXC-24A**
120 VAC 50/60 Hz	2770 Ohms	**783XCXM4L-120A**	**783XCXC-120A**
220-230 VAC 50/60 Hz	10800 Ohms	**783XCXM4L-220/230A**	**783XCXC-220/230A**
240 VAC 50/60 Hz	12100 Ohms	**783XCXM4L-240A**	**783XCXC-240A**
DC Operated			
6 VDC	25 Ohms	783XCXM4L-6D	**783XCXC-6D**
12 VDC	100 Ohms	**783XCXM4L-12D**	**783XCXC-12D**
24 VDC	400 Ohms	**783XCXM4L-24D**	**783XCXC-24D**
48 VDC	1600 Ohms	783XCXM4L-48D	**783XCXC-48D**
110-125 VDC	8600 Ohms	783XCXM4L-110/125D	**783XCXC-110/125D**

Custom Relay Part Number Builder

783	XCX		T	M4L-	240A
Series	**Contact Configuration**	**Cover Options**	**Terminal Style**	**Feature Options**	**Coil Voltage**
783	XCX = 3PDT	Full Feature = No Code	Plug In = No Code	Side Push Button = M	VAC = 6 - 240A
		Plain Cover = C	PC terminal = T	Locking Push Button = M4	VDC = 6 - 125D
				Bi-Polar LED = L	

Relay Adapters

16-783C1
Section 3, p.14-16

16-783C
Section 3, p.14-16

70-783D11-1 SOCKET

16-783SC *(Coming Soon)*
Metal Hold-Down Clip
Section 3, p.8-11