



## ■ Features :

- Universal AC input / Full range
- Built-in active PFC function
- High efficiency up to 84%
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Forced air cooling by built-in DC fan
- 1U low profile 36mm
- Conformal coated
- Built-in cooling fan ON-OFF control
- ZVS technology to reduce power dissipation
- LED indicator for power on
- 3 years warranty




## SPECIFICATION


MODEL	HDP-240	
OUTPUT	OUTPUT NUMBER	V1 V2
	DC VOLTAGE	+3.8V +2.8V
	RATED CURRENT	41.5A 25A
	CURRENT RANGE (max.)	0 ~ 50A 0 ~ 27.5A
	RATED POWER	227.7W (typ.) 241W (max.)
	OUTPUT POWER (max.)	241W continue. V1 total power output shall not exceed 200W (max. 50A) ; V2 total power output shall not exceed 82.5W (max. 27.5A) (The V1 & V2 combine total power output shall not exceed 241W)
	RIPLPE & NOISE (max.) Note.2	100mVp-p 100mVp-p
	VOLTAGE ADJ. RANGE Note.6	3.6 ~ 4V 2.5 ~ 3V
	VOLTAGE TOLERANCE Note.3	±2.0% ±2.0%
	LINE REGULATION	±0.5% ±0.5%
INPUT	LOAD REGULATION	±2.0% ±2.0%
	SETUP, RISE TIME	1000ms, 50ms/230VAC 2500ms, 50ms/115VAC at full load
	HOLD UP TIME (Typ.)	16ms/230VAC 16ms/115VAC at full load
	VOLTAGE RANGE Note.5	90 ~ 264VAC 127 ~ 370VDC
	FREQUENCY RANGE	47 ~ 63Hz
	POWER FACTOR (Typ.)	PF≥0.94/230VAC PF≥0.98/115VAC at full load
PROTECTION	EFFICIENCY (Typ.)	84%
	AC CURRENT (Typ.)	3.3A/115VAC 1.3A/230VAC
	INRUSH CURRENT (Typ.)	30A/115VAC 45A/230VAC
	LEAKAGE CURRENT	<0.7mA / 240VAC
	OVERLOAD	V1+V2: 105 ~ 150% max. output power ; or V2: 125 ~ 170% rated current Protection type: Hiccup mode, recovers automatically after fault condition is removed
	OVER VOLTAGE	V1: 4.37 ~ 5.13V V2: 3.22 ~ 3.78V Protection type : Shut down o/p voltage, re-power on to recover
FUNCTION	OVER TEMPERATURE	Shut down o/p voltage, re-power on to recovery
	FAN CONTROL (Typ.)	RTH4≥50°C Fan on ; RTH4≤45°C Fan off
	WORKING TEMP.	-30 ~ +70°C (Refer to "Derating Curve")
	WORKING HUMIDITY	20 ~ 90% RH non-condensing
	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH
	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)
ENVIRONMENT	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes
	SAFETY STANDARDS	UL60950-1, TUV EN60950-1, CCC GB4943.1 approved
	WITHSTAND VOLTAGE	I/P-O/P:3KVAC I/P-FG:2KVAC O/P-FG:0.5KVAC
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C/ 70% RH
	EMC EMISSION	Compliance to EN55032 (CISPR32), GB9254, class B, EN61000-3-2,-3, GB17625.1
SAFETY & EMC (Note 4)	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024, EN61000-6-2, heavy industry level, criteria A
	MTBF	111.3K hrs min. MIL-HDBK-217F (25°C)
	DIMENSION	215*115*36mm (L*W*H)
	PACKING	1Kg; 15pcs/16Kg/0.7CUFT
NOTE	1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. 3. Tolerance : includes set up tolerance, line regulation and load regulation. 4. The power supply is considered a component which will be installed into a final equipment. All the EMC tests are been executed by mounting the unit on a 360mm*360mm metal plate with 1mm of thickness. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on <a href="http://www.meanwell.com">http://www.meanwell.com</a> ) 5. Derating may be needed under low input voltages. Please check the derating curve for more details. 6. Output voltage between V1 and V2 should be higher than 1.0V(V1-V2≥1.0V).	

## ■ Mechanical Specification


Case No.206A Unit:mm



## ■ Block Diagram



## ■ Derating Curve



## ■ Output Derating VS Input Voltage

