

7938A Multi-Conductor - Category 5e DataTuff® 10 Million Flex Twisted Pair Cable



For more Information
please call

1-800-Belden1



General Description:

24 AWG stranded (7x32) bare copper alloy conductors, bonded pairs, polyolefin insulation, polyester separator, TPE inner jacket, Beldfoil® shield (100% coverage), 85% TC Braid, industrial grade sunlight-, oil and Weld splatter-resistant TPE jacket. Ripcord.

Usage (Overall)

Suitable Applications:

Industrial Ethernet, Harsh Environments, Robotic Applications, Flexible Applications, 100MHz Category 5e, Industrial Patch Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Outdoor, RJ-45 Compatible*

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	7x32	CA - Copper Alloy

Total Number of Conductors:

8

Insulation

Insulation Material:

Insulation Material
PO - Polyolefin

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Wall (in.)	Nom. Dia. (in.)
TPE	0.020	0.254

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)	Dia. (in.)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100.000	
	Braid	TC - Tinned Copper	85.000	0.282

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
Industrial Grade TPE - Theroplastic Elastomer	0.030

Outer Jacket Diameter:

Nom. Dia. (in.)
0.342

Outer Jacket Ripcord:

Yes

Overall Cable

Overall Cabling Separator Material:

Polyester

Overall Nominal Diameter:

0.342 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe and Blue
2	White/Orange Stripe and Orange
3	White/Green Stripe and Green
4	White/Brown Stripe and Brown

Mechanical Characteristics (Overall)

Storage Temperature Range:

-40°C To +80°C

Installation Temperature Range:

-25°C To +75°C

Operating Temperature Range:

-40°C To +80°C

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

7938A Multi-Conductor - Category 5e DataTuff® 10 Million Flex Twisted Pair Cable

Bulk Cable Weight:	60 lbs/1000 ft.
Max. Recommended Pulling Tension:	40 lbs.
Min. Bend Radius/Minor Axis:	3.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/17/2008
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	NEMA WC-63.1 Category 5e Patch, ICEA 661 Category 5 Patch,

Flame Test

UL Flame Test:	UL1581 Vertical Tray (VW-1)
C(UL) Flame Test:	FT1

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes
Oil Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)
15.000

Maximum Capacitance Unbalance:

Capacitance (pF/ft)
330.000

Nominal Velocity of Propagation:

VP (%)
69.000

Maximum Delay:

Delay (ns/100 m)
510.000

Typical Delay Skew:

Delay Skew (ns/ft)
12.000

Max. Delay Skew:

Delay Skew (ns/100 m)
45.000

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
11.000

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
3.000

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

7938A Multi-Conductor - Category 5e DataTuff® 10 Million Flex Twisted Pair Cable

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min. RL (dB)	Min. SRL (dB)
1	2.500	65.3	62.3	62.8	59.8	20.000	23.0
4	4.900	56.3	53.3	51.4	48.4	23.000	23.0
8	6.900	51.8	48.8	44.9	41.9	24.500	24.5
10	7.800	50.3	47.3	42.5	39.5	25.000	25.0
16	9.900	47.3	44.3	37.4	34.4	25.000	25.0
20	11.100	45.8	42.8	34.7	31.7	25.000	25.0
25	12.500	44.3	41.3	21.8	28.8	24.300	24.3
31.25	14.100	42.9	39.9	28.8	25.8	23.600	23.6
62.5	20.400	38.4	35.4	18.0	15.0	21.500	21.5
100	26.400	35.3	32.3	8.9	5.9	20.100	20.1

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	100 ± 15	63.8	60.8
4	100 ± 15	100 ± 15	51.7	48.7
8	100 ± 15	100 ± 15	45.7	42.7
10	100 ± 15	100 ± 15	43.8	40.8
16	100 ± 15	100 ± 15	39.7	36.7
20	100 ± 15	100 ± 15	37.7	34.7
25	100 ± 15	100 ± 15	35.8	32.8
31.25	100 ± 15	100 ± 15	33.9	30.9
62.5	100 ± 15	100 ± 15	27.8	24.8
100	100 ± 15	100 ± 15	23.8	20.8

Notes (Overall)

Notes: Operating temperatures are subject to length de-rating. Cable passes -40C Cold Bend per UL 1581. *Special RJ45 plugs required. See WWW. BELDEN.COM - Tools - Connector Cross Reference.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7938A B591000	1,000 FT	69.000 LB	BLACK, MATTE	C	4 PR #24 PP TPE SH TPE
7938A B59500	500 FT	35.000 LB	BLACK, MATTE	C	4 PR #24 PP TPE SH TPE

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 06-26-2014

© 2014 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.