





DESCRIPTION: ABOVE PCB, DECK AND PUSH ROD LOCATION ARE AS VIEWED BY USER.

PRODUCT NO. 71240-XXXXX	PUSH-ROD LOCATION		STAND-OFF HEIGHT	(A) CLOSEST TO PCB EJ HDR. ASSY 71299-XXXXX	(B) FARTEST FROM PCB EJ HDR. ASSY 71299-XXXXX	MATING RECEPTACLE (C)	MOUNTING STYLE TO PCB AND PUSH-ROD SIDE
	DECK CLOSEST TO PCB	DECK FARTHEST FROM PCB					
000CA	LEFT	RIGHT	0.0	100CA	005CA	100 POSITION (2X50) 0.8mm RECEPTACLES PART NO. 73277-101000	
020CA	LEFT	RIGHT	2.2	120CA	025CA		
040CA	LEFT	RIGHT	4.3	140CA	045CA		
050CA	LEFT	RIGHT	5.0	150CA	055CA		
100CA	RIGHT	LEFT	0.0	000CA	105CA		
120CA	RIGHT	LEFT	2.2	020CA	125CA		
140CA	RIGHT	LEFT	4.3	040CA	145CA		
150CA	RIGHT	LEFT	5.0	050CA	155CA		
200CA	RIGHT	RIGHT	0.0	000CA	005CA		
220CA	RIGHT	RIGHT	2.2	020CA	025CA		
240CA	RIGHT	RIGHT	4.3	040CA	045CA		
250CA	RIGHT	RIGHT	5.0	050CA	055CA		
300CA	LEFT	LEFT	0.0	100CA	105CA		
320CA	LEFT	LEFT	2.2	120CA	125CA		
340CA	LEFT	LEFT	4.3	140CA	145CA		
350CA	LEFT	LEFT	5.0	150CA	155CA		

NOTE:

1. SEE 71299 FOR SINGLE DECK APPLICATIONS.






ORDERING INFORMATION

ORDER:

- 1 (A) DECK CLOSEST TO PCB
- 2 (B) DECK FARTEST FROM PCB
- 3 (C) 2 EACH MATING RECEPTACLES

mat'l. code		surface		tolerance		projection		product family	
ISO 1302		ISO 406		ISO 1181		ISO 1181		ISO 1181	
l	tr	ec	n	dr	date	tolerances unless otherwise specified		title	
H	N08-0060	M	Z	04/09/08	angles	.X±.3	MM	CARDBUS EJECT ASS'Y SMT TYPE 123	
J	ELX-N-011400	ZK	04/14/12	linear	.XX±.13	.XXX±.051	scale 3/4		
		dr		D.SHEAFFER		8/7/95		dwg no	
		E		V80376		RHG		sheet 1 of 12	
		F		V02257		TFG		size	
		G		N05-0111		W B		A4	
				04/20/05		appd		type	
						D.BRANN		CUSTOMER	
						8/7/95		Drawing	
sheet	revision	J	J	J	J	J	J	J	J
index	sheet	1	2	3	4	5	6	7	8

DESCRIPTION: ABOVE PCB, DECK AND PUSH ROD LOCATION ARE AS VIEWED BY USER.

PRODUCT NO. 71240-XXXXX	PUSH-ROD LOCATION		STAND-OFF HEIGHT	(A) CLOSEST TO PCB	(B) FARTEST FROM PCB	MATING RECEPTACLE (C)	MOUNTING STYLE TO PCB AND PUSH-ROD SIDE
	DECK CLOSEST TO PCB	DECK FARTHEST FROM PCB		EJ HDR. ASSY 71299-XXXXX	EJ HDR. ASSY 71299-XXXXX		
000CALF	LEFT	RIGHT	0.0	100CALF	005CALF	100 POSITION (2X50) 0.8mm RECEPTACLES PART NO. 73277-101402LF	
020CALF	LEFT	RIGHT	2.2	120CALF	025CALF		
040CALF	LEFT	RIGHT	4.3	140CALF	045CALF		
050CALF	LEFT	RIGHT	5.0	150CALF	055CALF		
100CALF	RIGHT	LEFT	0.0	000CALF	105CALF		
120CALF	RIGHT	LEFT	2.2	020CALF	125CALF		
140CALF	RIGHT	LEFT	4.3	040CALF	145CALF		
150CALF	RIGHT	LEFT	5.0	050CALF	155CALF		
200CALF	RIGHT	RIGHT	0.0	000CALF	005CALF		
220CALF	RIGHT	RIGHT	2.2	020CALF	025CALF		
240CALF	RIGHT	RIGHT	4.3	040CALF	045CALF		
250CALF	RIGHT	RIGHT	5.0	050CALF	055CALF		
300CALF	LEFT	LEFT	0.0	100CALF	105CALF		
320CALF	LEFT	LEFT	2.2	120CALF	125CALF		
340CALF	LEFT	LEFT	4.3	140CALF	145CALF		
350CALF	LEFT	LEFT	5.0	150CALF	155CALF		
351CALF	LEFT	LEFT	5.0	151CALF	156CALF		

NOTE:

1. SEE 71299 FOR SINGLE DECK APPLICATIONS.





ORDERING INFORMATION

ORDER:

- (A) DECK CLOSEST TO PCB
- (B) DECK FARTEST FROM PCB
- (C) 2 EACH MATING RECEPTACLES

mat'l. code		surface ISO 1302		tolerance ISO 406 ISO 1181		projection ISO 1181		product family CARDBUS	
ltr ecn no dr date		tolerances unless otherwise specified		linear .XX±.13		angular ±2°		title CARDBUS EJECT ASS'Y SMT TYPE 123	
J		linear .XXX±.051		scale 3/4		MM		dwg no 71240	
dr D.SHEAFFER		8/7/95		enr D.BRANN		8/7/95		sheet 2 of 2	
chr D.BRANN		8/7/95		app D.BRANN		8/7/95		size A4	
type CUSTOMER		Drawing							
sheet index		revision sheet							

DESCRIPTION: BELOW PCB, DECK AND PUSH ROD LOCATION ARE AS VIEWED BY USER

PRODUCT NO. 71240-XXXXX	PUSH-ROD LOCATION		STAND-OFF HEIGHT	Ⓐ CLOSEST TO PCB	Ⓑ FARTEST FROM PCB	MATING RECEPTACLE Ⓒ	MOUNTING STYLE TO PCB AND PUSH-ROD SIDE
	DECK CLOSEST TO PCB	DECK FARTHEST FROM PCB		EJ HDR. ASSY 71299-XXXXX	EJ HDR. ASSY 71299-XXXXX		
520CA	RIGHT	LEFT	2.2	520CA	625CA	100 POSITION (2X50) 0.8mm RECEPTACLES PART NO. 73277-101000	
540CA	RIGHT	LEFT	4.3	540CA	645CA		
550CA	RIGHT	LEFT	5.0	550CA	655CA		
620CA	LEFT	RIGHT	2.2	620CA	525CA		
640CA	LEFT	RIGHT	4.3	640CA	545CA		
650CA	LEFT	RIGHT	5.0	650CA	555CA		
720CA	RIGHT	RIGHT	2.2	520CA	525CA		
740CA	RIGHT	RIGHT	4.3	540CA	545CA		
750CA	RIGHT	RIGHT	5.0	550CA	555CA		
820CA	LEFT	LEFT	2.2	620CA	625CA		
840CA	LEFT	LEFT	4.3	640CA	645CA		
850CA	LEFT	LEFT	5.0	650CA	655CA		

NOTE:

- SEE 71299 FOR SINGLE DECK APPLICATIONS.
- BELOW P.C.B., 0.0mm STAND-OFF IS NOT AVAILABLE.

ORDERING INFORMATION

ORDER:

- (A) DECK CLOSEST TO PCB
- (B) DECK FARTEST FROM PCB
- (C) 2 EACH MATING RECEPTACLES

mat'l. code		surface ISO 1302		tolerance ISO 406 ISO 1181		projection ISO 1181		product family CARDBUS	
ltr ecn no dr date		tolerances unless otherwise specified		title		CARD BUS EJECT ASS'Y SMT TYPE 123			
J		angles	linear	.X±.3	MM				
		±2°		.XX±.13					
				.XXX±.051	scale 3/4				
		dr	D.SHEAFFER	8/7/95					
		engr	D.BRANN	8/7/95		dwg no		sheet 3 of 2	
		chr	D.BRANN	8/7/95		71240		A4	
		appd	D.BRANN	8/7/95		type CUSTOMER		Drawing	
sheet index	revision sheet								

DESCRIPTION: BELOW PCB, DECK AND PUSH ROD LOCATION ARE AS VIEWED BY USER

PRODUCT NO. 71240-XXXXX	PUSH-ROD LOCATION		STAND-OFF HEIGHT	Ⓐ CLOSEST TO PCB	Ⓑ FARTEST FROM PCB	MATING RECEPTACLE Ⓒ	MOUNTING STYLE TO PCB AND PUSH-ROD SIDE
	DECK CLOSEST TO PCB	DECK FARTEST FROM PCB		EJ HDR. ASSY 71299-XXXXX	EJ HDR. ASSY 71299-XXXXX		
520CALF	RIGHT	LEFT	2.2	520CALF	625CALF	100 POSITION (2X50) 0.8mm RECEPTACLES PART NO. 73277-101402LF	
540CALF	RIGHT	LEFT	4.3	540CALF	645CALF		
550CALF	RIGHT	LEFT	5.0	550CALF	655CALF		
620CALF	LEFT	RIGHT	2.2	620CALF	525CALF		
640CALF	LEFT	RIGHT	4.3	640CALF	545CALF		
650CALF	LEFT	RIGHT	5.0	650CALF	555CALF		
720CALF	RIGHT	RIGHT	2.2	520CALF	525CALF		
740CALF	RIGHT	RIGHT	4.3	540CALF	545CALF		
750CALF	RIGHT	RIGHT	5.0	550CALF	555CALF		
820CALF	LEFT	LEFT	2.2	620CALF	625CALF		
840CALF	LEFT	LEFT	4.3	640CALF	645CALF		
850CALF	LEFT	LEFT	5.0	650CALF	655CALF		

NOTE:

- SEE 71299 FOR SINGLE DECK APPLICATIONS.
- BELOW P.C.B., 0.0mm STAND-OFF IS NOT AVAILABLE.

ORDERING INFORMATION

ORDER:

- Ⓐ DECK CLOSEST TO PCB
- Ⓑ DECK FARTEST FROM PCB
- Ⓒ 2 EACH MATING RECEPTACLES


mat'l. code		surface	tolerance	projection	product family
ISO 1302		ISO 406	ISO 1101	0.8	CARDBUS
ltr	ecn	no	dr	date	tolerances unless otherwise specified
J					angles
					linear
					±.3
					±.13
					±.051
					scale 3/4
		dr	D.SHEAFFER	8/7/95	
		engr	D.BRANN	8/7/95	
		chr	D.BRANN	8/7/95	
		appd	D.BRANN	8/7/95	
sheet	revision				dwg no
index	sheet				71240
					type CUSTOMER
					Drawing

FCI CONFIDENTIAL







This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of this information shown on this document may be used in any way or disclosed to others without the written consent of FCI.
Copyright FCI.

PRODUCT NUMBER
71240-****
71240-****LF



MATING RECEPTACLE
SHOWN FOR APPLICATION
CLARITY ONLY
MUST BE PURCHASED
SEPARATELY



mat'l. code	surface	tolerance	projection	product family
	ISO 1302	ISO 406 ISO 1101		CARDBUS
ltr ecn no dr date	tolerances unless otherwise specified			
J	angles	.X±.3	MM	CARDBUS EJECT ASS'Y SMT TYPE 123
	linear	.XX±.13	scale 3/4	
		.XXX±.051		
dr	D.SHEAFFER	8/7/95	FCI	dwg no
enr	D.BRANN	8/7/95		71240
chr	D.BRANN	8/7/95		sheet 5 of 2
app	D.BRANN	8/7/95		size A4
type	CUSTOMER	Drawing		
sheet index	revision sheet			






FCI CONFIDENTIAL



FCIconnect.com

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of this information shown on this document may be used in any way or disclosed to others without the written consent of FCI.
Copyright FCI.

PRODUCT NUMBER
71240-****
71240-****LF








mat'l. code		surface	tolerance	projection	product family
ISO 1302		ISO 406	ISO 1101	ISO 1101	CARDBUS
ltr ecn no dr date		tolerances unless otherwise specified			title
J		angles	.X±.3	MM	CARDBUS EJECT ASS'Y
		linea	.XX±.13		SMT TYPE 123
		±2°	.XXX±.051	scale 3/4	
dr	D.SHEAFFER	8/7/95	FCI		
enr	D.BRANN	8/7/95			
chr	D.BRANN	8/7/95			
appd	D.BRANN	8/7/95			
sheet index	revision sheet				dwg no 71240 sheet 6 of 2 size A4
					type CUSTOMER Drawing

FCI CONFIDENTIAL

FCI

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of this information shown on this document may be used in any way or disclosed to others without the written consent of FCI.
Copyright FCI.







PRODUCT NUMBER
71240-****
71240-****LF



mat'l. code		surface	tolerance	projection	product family
ISO 1302		ISO 406	ISO 1181	ISO 1181	CARDBUS
ltr ecn no dr date		tolerances unless otherwise specified			title
J		angles	.X±.3	MM	CARDBUS EJECT ASS'Y
		linear	.XX±.13		SMT TYPE 123
		±2°	.XXX±.051	scale 3/4	
dr	D.SHEAFFER	8/7/95			dwg no
enr	D.BRANN	8/7/95			71240
chr	D.BRANN	8/7/95			sheet 7 of 2
app	D.BRANN	8/7/95			size A4
sheet index		revision			type CUSTOMER Drawing
	sheet				




PRODUCT NUMBER
71240-*****
71240-*****LF


MATING RECEPTACLE
SHOWN FOR APPLICATION
CLARITY ONLY
MUST BE PURCHASED
SEPARATELY




mat'l. code	surface	tolerance	projection	product family
	ISO 1302	ISO 406 ISO 1181		CARDBUS
ltr ecn no dr date	tolerances unless otherwise specified	title		
J	angles	.X±.3	MM	CARDBUS EJECT ASS'Y
	linea	.XX±.13		SMT TYPE 123
	±2'	.XXX±.051	scale 3/4	
	dr	D.SHEAFFER 8/7/95		dwg no
	enr	D.BRANN 8/7/95		71240
	chr	D.BRANN 8/7/95		sheet 8 of 2
	app	D.BRANN 8/7/95		A4
sheet index	revision sheet			type CUSTOMER Drawing

P.C.B. LAYOUT FOR 2.2mm STANDOFF




mat'l. code				surface		tolerance		projection		product family	
				ISO 1302		ISO 406 ISO 1181				CARDBUS	
ltr	ecn	no	dr	date	tolerances unless otherwise specified						
J					angles		.X±.3				
					linear		r.XX±.13				
					±2°		.XXX±.051		scale 3/4		
			dr		D.SHEAFFER	8/7/95				dwg no	
			engr		D.BRANN	8/7/95				sheet 9 of 2	
			chr		D.BRANN	8/7/95				size	
			appd		D.BRANN	8/7/95				A4	
sheet index		revision sheet							type CUSTOMER Drawing		

P.C.B. LAYOUT FOR 4.3 AND 5.0mm STANDOFFS



SCALE 2:1



P.C.B.
LAYOUT 3
ABOVE PCB
AS ASSEMBLED


P.C.B.
LAYOUT 4
BELOW PCB
AS ASSEMBLED

mat'l. code		surface	tolerance	projection	product family
ISO 1302		ISO 406	ISO 1181	ISO 1181	CARDBUS
ltr	ecn	no	dr	date	tolerances unless otherwise specified
J					angles
					linear
					±2"
					dr D.SHEAFFER 8/7/95
					enr D.BRANN 8/7/95
					chr D.BRANN 8/7/95
					app D.BRANN 8/7/95
sheet	revision				
index	sheet				

CARDBUS EJECT ASS'Y
SMT TYPE 123

dwg no 71240 sheet 10 of 2 size A4

type CUSTOMER Drawing

mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1181		projection 		product family CARDBUS			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
J				angles linear		.X±.3				CARDBUS EJECT ASS'Y SMT TYPE 123			
				±2'		.XXX±.051		scale 3/4					
				dr	D.SHEAFFER	8/7/95				dwg no		sheet #1 of 2	size
				engr	D.BRANN	8/7/95				71240		A4	
				chr	D.BRANN	8/7/95							
				appa	D.BRANN	8/7/95							
sheet index		revision sheet								type CUSTOMER		Drawing	

1			2			3			4			5			6		
HEADER PINOUT	TYPE	BTB 100 POS RECEPTACLE	HEADER PINOUT	TYPE	BTB 100 POS RECEPTACLE	SHIELD PINOUT	TYPE	BTB 100 POS RECEPTACLE	SHIELD PINOUT	TYPE	BTB 100 POS RECEPTACLE	SHIELD PINOUT	TYPE	BTB 100 POS RECEPTACLE	SHIELD PINOUT	TYPE	BTB 100 POS RECEPTACLE
1	GND	1	35	GND	51	1	GND	4 & 54	1	GND	4 & 54	1	GND	4 & 54	1	GND	4 & 54
2	SIG	2	36	DET	52	2	GND	7 & 57	2	GND	7 & 57	2	GND	7 & 57	2	GND	7 & 57
3	SIG	3	37	SIG	53	3	GND	10 & 60	3	GND	10 & 60	3	GND	10 & 60	3	GND	10 & 60
4	SIG	5	38	SIG	55	4	GND	13 & 63	4	GND	13 & 63	4	GND	13 & 63	4	GND	13 & 63
5	SIG	6	39	SIG	56	5	GND	16 & 66	5	GND	16 & 66	5	GND	16 & 66	5	GND	16 & 66
6	SIG	8	40	SIG	58	6	GND	19 & 69	6	GND	19 & 69	6	GND	19 & 69	6	GND	19 & 69
7	SIG	9	41	SIG	59	7	GND	22 & 72	7	GND	22 & 72	7	GND	22 & 72	7	GND	22 & 72
8	SIG	11	42	SIG	61	8	GND	25 & 75	8	GND	25 & 75	8	GND	25 & 75	8	GND	25 & 75
9	SIG	12	43	SIG	62	9	GND	26 & 76	9	GND	26 & 76	9	GND	26 & 76	9	GND	26 & 76
10	SIG	14	44	SIG	64	10	GND	29 & 79	10	GND	29 & 79	10	GND	29 & 79	10	GND	29 & 79
11	SIG	15	45	SIG	65	11	GND	32 & 82	11	GND	32 & 82	11	GND	32 & 82	11	GND	32 & 82
12	SIG	17	46	SIG	67	12	GND	35 & 85	12	GND	35 & 85	12	GND	35 & 85	12	GND	35 & 85
13	SIG	18	47	SIG	68	13	GND	38 & 88	13	GND	38 & 88	13	GND	38 & 88	13	GND	38 & 88
14	SIG	20	48	SIG	70	14	GND	41 & 91	14	GND	41 & 91	14	GND	41 & 91	14	GND	41 & 91
15	SIG	21	49	SIG	71	15	GND	44 & 94	15	GND	44 & 94	15	GND	44 & 94	15	GND	44 & 94
16	SIG	23	50	SIG	73	16	GND	47 & 97	16	GND	47 & 97	16	GND	47 & 97	16	GND	47 & 97
17	PWR	24	51	PWR	74												
18	SIG	27	52	SIG	77												
19	SIG	28	53	SIG	78												
20	SIG	30	54	SIG	80												
21	SIG	31	55	SIG	81												
22	SIG	33	56	SIG	83												
23	SIG	34	57	SIG	84												
24	SIG	36	58	SIG	86												
25	SIG	37	59	SIG	87												
26	SIG	39	60	SIG	89												
27	SIG	40	61	SIG	90												
28	SIG	42	62	SIG	92												
29	SIG	43	63	SIG	93												
30	SIG	45	64	SIG	95												
31	SIG	46	65	SIG	96												
32	SIG	48	66	SIG	98												
33	SIG	49	67	DET	99												
34	GND	50	68	GND	100												

NOTES:

- 8mm MIN CARD EJECT.
- EJECT TRAVEL: 9.5mm
- MATERIAL:
 - HEADER ASSY:
PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK - ABOVE PCB
HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK - BELOW PCB
PIN: PHOSPHOR BRONZE
PCB: FR4
 - EJECT MECHANISM ASSY:
PLASTIC GUIDE: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
PLASTIC PUSH-ROD BUTTON: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
COVER PLATE, EJECT PLATE, LINK ARM,
PUSH ROD: STAINLESS STEEL
EMI CONTACT: PHOSPHOR BRONZE
 - .8 BTB RECEPTACLE: (73277-101000 FOR TIN LEAD)
.8 BTB RECEPTACLE: (73277-101402LF FOR LEAD FREE)
PLASTIC: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
CONTACT: BeCu
- FINISH (PIN)
UNDER PLATING: 0.5um Ni
CONTACT AREA: 0.076 μ m MIN. GOLD

SOLDER TAIL: TIN LEAD OPTION: 2.5um Sn-Pb
LEAD FREE OPTION: 2.5um PURE TIN

DIM "X"	4.25 $\pm$ 0.1	3.5 $\pm$ 0.1	5.0 $\pm$ 0.1
	OTHERS	36,67	1,17,34,35,51,68

- RECOMMENDED SCREW TORQUE: 1.0 TO 1.5 MAX in-lbs. (1.2-1.7 cm-kgs).
RECOMMENDED HOLD-DOWN: 2mm SCREWS AND HEX NUTS.
SEE DRAWINGS 95121 AND 92869 FOR CHARTED INFORMATION.
- ORDER MATING RECEPTACLES SEPARATELY.
- IF LEAD FREE P.N.THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- IF LEAD FREE P/N.THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCIBLED IN GS-22-008
- LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION
- PRODUCT SPEC:110-263

mat'l. code		surface ISO 1302		tolerance ISO 406 ISO 1101		projection ISO 1101		product family CARDBUS		
ltr ecn ncdr date		tolerances unless otherwise specified		title		dwg no		sheet2 of 2 size		
J		angles	linear	.X $\pm$.3 .XX $\pm$.13 .XXX $\pm$.051	MM	CARDBUS EJECT ASS'Y SMT TYPE 123		A4		
		dr	D.SHEAFFER	8/7/95	FCI		71240		A4	
		engr	D.BRANN	8/7/95			type CUSTOMER		Drawing	
		chr	D.BRANN	8/7/95						
		appd	D.BRANN	8/7/95						
sheet index	revision sheet									