


# SMD/BLOCK Type EMI Suppression Filters

# EMIFIL<sup>®</sup>



*Innovator  
in Electronics*

**Murata  
Manufacturing Co., Ltd.**















⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

C31E.pdf  
Aug.1,2013

## Introduction

Murata Manufacturing Co., Ltd. has been developing the EMI suppression device market since the invention of 3 terminal capacitor DS310 series in 1979. Also, we have been striving to develop and popularize new noise countermeasure technologies as well as new products in the concept of "Develop unique products," to become our customer's best solution partner. We hope you can find the key solution to your noise problem.

### Explanation of symbols in this catalog

	Features of each series	Features of each item
All Products	 <b>Flow</b> Flow soldering available	 <b>New</b> New product
	 <b>Reflow</b> Reflow soldering available	 <b>Kit</b> Exist in design kit
	 <b>Hi Power</b> Meets large current lines	 <b>≥1A</b> Rated current 1A or more
Chip Ferrite Bead		 <b>≥3A</b> Rated current 3A or more
		 <b>≥10A</b> Rated current 10A or more
	 <b>GHz</b> Meets high frequency noise up to 1-2GHz	
LC Combined Type Filter	 <b>Hi-GHz</b> Meets ultra high frequency noise up to 10GHz	
		 <b>DTV</b> Low cut-off frequency type for UHF band noise, which affects digital TV tuner
		 <b>HD</b> For high speed differential signal lines (USB2.0/LVDS/IEEE1394 etc.)
Chip Common Mode Choke Coil		 <b>UD</b> For ultra high speed differential signal lines (HDMI/DVI/Display Port/USB3.0 etc.)
		 <b>Imp Match</b> Line impedance has been matched to transmission lines

### EU RoHS Compliant

- All the products in this catalog comply with EU RoHS.
- EU RoHS is "the European Directive 2011/65/EU on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment."
- For more details, please refer to our website 'Murata's Approach for EU RoHS' (<http://www.murata.com/info/rohs.html>).

# CONTENTS

Selection Guide for Noise Suppression Filters .....	2
EMI Filter Selection by Application .....	4
•Digital Still Camera .....	4
•Blu-ray/DVD .....	6
•Smartphone .....	5
•LCD-TV .....	7
EMI Filter Selection by Circuits and Noise Frequency...	8
Product Guide .....	10



## BL Chip Ferrite Bead

Series Introduction .....	14
Part Numbering .....	16
Series Lineup .....	17
Product Detail .....	23
⚠Caution/Notice .....	96
Soldering and Mounting .....	97
Packaging .....	101
Design Kits .....	102

Chip Ferrite Bead



## NF Chip EMIFIL®

Series Introduction .....	108
Part Numbering .....	110
Series Line Up .....	113
Product Detail .....	116
⚠Caution/Notice .....	146
Soldering and Mounting .....	147
Packaging .....	153
Design Kits .....	155

Chip EMIFIL®



## DL/PL Chip Common Mode Choke Coil

Series Introduction .....	160
Part Numbering .....	162
Series Line Up .....	164
Product Detail .....	167
⚠Caution/Notice .....	192
Soldering and Mounting .....	194
Packaging .....	200
Design Kits .....	202

Chip Common Mode Choke Coil



## BNX Block Type EMIFIL®

Series Line Up .....	206
Function Example .....	206
Product Detail .....	209
⚠Caution/Notice .....	213
Soldering and Mounting .....	215
Packaging .....	219
Design Kits .....	220

Block Type EMIFIL®



## EA Microwave Absorber

Part Numbering .....	222
Product Detail .....	223
Notice .....	226




Product Guide by Size .....	227
Part Number Quick Reference .....	228
Alphabetic Product Name Index .....	228
Introduction of Related Catalogs .....	229
Introduction of EMI/MLCC/Inductor special web site "EMICON-FUN!" .....	230

Microwave Absorber


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Selection Guide for Noise Suppression Filters

### ●Features & Suitable Circuits

Type	Features	Suitable Circuits
<b>Ferrite Bead</b> <b>BLM/BLA Series</b> 	<ul style="list-style-type: none"> <li>• Miniaturized</li> <li>• GND connection unnecessary</li> <li>• Effective at low impedance line</li> </ul>	<ul style="list-style-type: none"> <li>• Application set with less noise radiation</li> <li>• Low impedance line</li> </ul>
<b>Capacitor Type</b> <b>NFM/NFA/NFE/NFR/NFL/NFW Series</b> 	<ul style="list-style-type: none"> <li>• Great noise suppression effect</li> <li>• With effect as By-Pass capacitor (Lineup for Power)</li> <li>• Good noise separation from signal (LC filter for Signal)</li> <li>• Effective at high impedance line</li> </ul>	<ul style="list-style-type: none"> <li>• Application set with higher noise radiation</li> <li>• High impedance line</li> <li>• Circuit with By-Pass capacitor</li> <li>• Circuit driven by high frequency</li> </ul>
<b>Common Mode Choke Coil</b> 	<ul style="list-style-type: none"> <li>• Possible to suppress noise with less affect of ultra high speed signal</li> <li>• Great effect for common mode noise</li> <li>• Less magnetic saturation by current</li> </ul>	<ul style="list-style-type: none"> <li>• High speed differential signal line</li> <li>• I/F cable driver</li> <li>• Power line</li> </ul>

### ●Example



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




## ● Advantages to Using Common Mode Choke Coils




### 1. Great Effect for Common Mode Noise

Differential mode inductors work as a half impedance for common mode noise. Common Mode Choke Coils are effective for common mode noise.



### 2. Possible to Suppress Noise with Less Affect of Ultra High Speed Signal

Common Mode Choke Coils can suppress Noise with less affect of Signal, even if the frequency range of Signal and Noise are the same, because they separate each conductive mode of current.





### 3. Less Magnetic Saturation by Current

Common Mode Choke Coils are effective for noise suppression of DC power lines, due to their less magnetic saturation at high power current, that comes from their construction of cancelling magnetic flux of differential mode current at each coil.

## Digital Still Camera


Application Sample



**Note** • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# Smartphone


Application Sample



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Blu-ray/DVD


Application Sample



△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# LCD-TV

Application Sample



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# EMI Filter Selection by Circuits and Noise Frequency

## ●Chip Ferrite Bead / Chip EMIFIL®


Circuit Type?		Noise Frequency?	
Noise Frequency: Under 1GHz	Power Line	General Signal Line Under 10MHz	High Speed Signal Line Over 10MHz
	<b>Inductor Type</b> (Suppression Effect: Normal) <ul style="list-style-type: none"> <li><b>BLM02AX</b> 01005/Imp.10-120Ω p23</li> <li><b>BLM03AX</b> 0201/0.2-1A/Imp.10-1000Ω p28</li> <li><b>BLM03PG</b> 0201/0.75-0.9A/Imp.22-33Ω p25</li> <li><b>Low DC Resistance / High Current Type</b></li> <li><b>BLM03PX</b> 0201/1-1.8A/Imp.22-80Ω p26</li> <li><b>BLM15AX</b> 0402/0.35-1.74A/Imp.10-1000Ω p38</li> <li><b>BLM15PX</b> 0402/0.9-3A/Imp.33-600Ω p34</li> <li><b>BLM15PG/PD</b> 0402/1-2.2A/Imp.10-120Ω p36</li> <li><b>BLM18P</b> 0603/0.5-3A/Imp.30-470Ω p48</li> <li><b>BLM21P</b> 0805/1.5-6A/Imp.22-330Ω p64</li> <li><b>BLM31P</b> 1206/1.5-6A/Imp.33-600Ω p73</li> <li><b>BLM41P</b> 1806/1.5-6A/Imp.60-1000Ω p75</li> <li><b>Low DC Resistance Type</b></li> <li><b>BLM18K</b> 0603/1.3-6A/Imp.26-600Ω p50</li> <li><b>BLM18S</b> 0603/1.5-6A/Imp.26-330Ω p52</li> </ul>	<ul style="list-style-type: none"> <li><b>BLM03A</b> 0201/Imp.10-1000Ω p30</li> <li><b>BLM15A</b> 0402/Imp.10-1000Ω p40</li> <li><b>BLM18A</b> 0603/Imp.120-1000Ω p54</li> <li><b>BLM18T</b> 0603/Imp.120-1000Ω p60</li> <li><b>BLM18R</b> 0603/Imp.120-1000Ω p61</li> <li><b>BLM21A</b> 0805/Imp.120-1000Ω p66</li> <li><b>BLM21R</b> 0805/Imp.120-1000Ω p71</li> <li><b>Array Type</b></li> <li><b>BLA2AA</b> 0804/Imp.120-1000Ω p77</li> <li><b>BLA31A</b> 1206/Imp.30-1000Ω p80</li> </ul>	<ul style="list-style-type: none"> <li><b>BLM03B</b> 0201/Imp.10-600Ω p32</li> <li><b>BLM15BX</b> 0402/0.25-0.6A/Imp.75-1800Ω p42</li> <li><b>BLM15B</b> 0402/Imp.5-1800Ω p44</li> <li><b>BLM18B</b> 0603/Imp.5-2500Ω p56</li> <li><b>BLM21B</b> 0805/Imp.5-2700Ω p68</li> <li><b>Array Type</b></li> <li><b>BLA2AB</b> 0804/Imp.10-1000Ω p77</li> <li><b>BLA31B</b> 1206/Imp.120-1000Ω p80</li> </ul>
	<b>Capacitor Type</b> (Suppression Effect: High) <ul style="list-style-type: none"> <li><b>NFM18PC</b> 0603/2-4A/Cap.0.1-2.2μF p119</li> <li><b>NFM21PC</b> 0805/2-6A/Cap.0.1-4.7μF p122</li> <li><b>NFM3DP</b> 1205/2A/Cap.0.022μF p123</li> <li><b>NFM31P</b> 1206/6A/Cap.27μF p124</li> <li><b>NFM31K</b> 1206/6-10A/Cap.0.01-0.1μF p125</li> <li><b>NFM41P</b> 1806/2-6A/Cap.0.2-1.5μF p126</li> <li><b>T Circuit Filter Feed Through Type</b></li> <li><b>NFE31P</b> 1206/6A/Cap.22-2200pF p116</li> <li><b>NFE61P</b> 2706/2A/Cap.33-4700pF p117</li> <li><b>Block Type</b></li> <li><b>BNX022/023</b> 10-15A/Range1MHz-2GHz p209</li> </ul>	<ul style="list-style-type: none"> <li><b>NFM18C</b> 0603/Cap.22-22000pF p127</li> <li><b>NFM21C</b> 0805/Cap.22-22000pF p128</li> <li><b>NFM3DC</b> 1205/Cap.22-22000pF p129</li> <li><b>NFM41C</b> 1806/Cap.22-22000pF p130</li> <li><b>Array Type</b></li> <li><b>NFA31C</b> 1206/Cap.22-22000pF p131</li> <li><b>T Circuit Filter Feed Through Type</b></li> <li><b>NFE31P</b> 1206/Cap.22-2200pF p116</li> <li><b>NFE61P</b> 2706/Cap.33-4700pF p117</li> </ul>	<b>LC Combined</b> <ul style="list-style-type: none"> <li><b>NFL15ST</b> 0402/Cut off 150-500MHz p132</li> <li><b>NFL18ST</b> 0603/Cut off 50-500MHz p133</li> <li><b>NFL18SP</b> 0603/Cut off 150-500MHz p135</li> <li><b>NFL21S</b> 0805/Cut off 10-500MHz p136</li> <li><b>NFW31S</b> 1206/Cut off 10-500MHz p142</li> </ul> <b>RC Combined</b> <ul style="list-style-type: none"> <li><b>NFR21G</b> 0805/22-100Ω/Cap.10-100pF p144</li> </ul> <b>Array Type (RC/LC Combined)</b> <ul style="list-style-type: none"> <li><b>NFA31G</b> 1206/6.8-100Ω/Cap.10-100pF p145</li> <li><b>NFA18S</b> 0603/Cut off 50-480MHz p137</li> <li><b>NFA21S</b> 0805/Cut off 50-330MHz p140</li> </ul>
	<b>Inductor Type</b> (Suppression Effect: Normal) <ul style="list-style-type: none"> <li><b>BLM18HE</b> 0603/0.5-0.8A/Imp.600-1500Ω p89</li> <li><b>BLM03EB</b> 0201/0.4-0.6A/Imp.25-50Ω p84</li> <li><b>BLM15EG</b> 0402/0.7-1.5A/Imp.120-220Ω p87</li> <li><b>BLM18EG</b> 0603/0.5-2A/Imp.100-600Ω p93</li> </ul>	<ul style="list-style-type: none"> <li><b>BLM03HG</b> 0201/Imp.600-1000Ω p82</li> <li><b>BLM15HG</b> 0402/Imp.600-1000Ω p85</li> <li><b>BLM18HG</b> 0603/Imp.470-1000Ω p89</li> <li><b>BLM18HK</b> 0603/Imp.330-1000Ω p89</li> </ul>	<ul style="list-style-type: none"> <li><b>BLM03HD</b> 0201/Imp.330-1000Ω p82</li> <li><b>BLM03HB</b> 0201/Imp.190Ω p82</li> <li><b>BLM15HD</b> 0402/Imp.600-1800Ω p85</li> <li><b>BLM15HB</b> 0402/Imp.120-220Ω p85</li> <li><b>BLM18HD</b> 0603/Imp.470-1000Ω p89</li> <li><b>BLM18HE</b> 0603/Imp.600-1500Ω p89</li> <li><b>BLM18HB</b> 0603/Imp.120-330Ω p89</li> </ul>
	<b>Capacitor Type</b> (Suppression Effect: High) <ul style="list-style-type: none"> <li><b>NFM18PS</b> 0603/2A/Cap.0.47-1.0μF p118</li> <li><b>NFM21PS</b> 0805/4A/Cap.10μF p121</li> </ul>		<b>LC Combined</b> <ul style="list-style-type: none"> <li><b>NFL18ST</b> 0603/Cut off 50-500MHz p133</li> </ul> <b>Array Type (LC Combined)</b> <ul style="list-style-type: none"> <li><b>NFA18S</b> 0603/Cut off 50-480MHz p137</li> <li><b>NFA21S</b> 0805/Cut off 50-330MHz p140</li> </ul>
Noise Frequency: GHz Band (800MHz to 2.5GHz)		<b>Inductor Type</b> <ul style="list-style-type: none"> <li><b>BLM15GG</b> 0402/Imp.220-470Ω p88</li> <li><b>BLM18GG</b> 0603/Imp.470Ω p95</li> </ul>	<ul style="list-style-type: none"> <li><b>BLM15GA</b> 0402/Imp.75Ω p88</li> </ul>
Noise Frequency: High-GHz Band (1GHz to 10GHz)			

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



## ●Chip Common Mode Choke Coil

## Circuit Type?



## Guide of Digits in this Chart:

## ●for BLM03P

0201/0.75-0.9A/Imp.22-33Ω

Size (inch) Rated Current Impedance

## ●for BNX022/023

10-15A/Range1MHz-2GHz

Rated Current Effective Frequency Range

## ●for NFR21G

0805/22-100Ω/Cap.10-100pF

Size (inch) Resistance Capacitance

## ●for NFA18S

0603/Cut off 50-480MHz

Size (inch) Cut-off Frequency

## ●for DLW5BS

2020/0.5-5A/Imp.190-3000Ω

Size (inch) Rated Current Impedance



## Inductor Type

		Series	Size Code Inch (mm)	Impedance (Ω) at 100MHz			Effective Frequency Range (Applicable Frequency Ranges are only for reference.)						
				10	100	1000	10kHz	100kHz	1MHz	10MHz	100MHz	1GHz	10GHz
For General Band Noise	Universal Type [ Power Lines / Signal Lines ]	BLM02AX <sup>p23</sup>	01005 (0402)	10	70	120							
		BLM03AX <sup>p28</sup>	0201 (0603)	10	80	120 240 600 1000							
		BLM15AX <sup>p38</sup>	0402 (1005)	10	30	70 120 220 600 1000							
	Signal Lines Type	For General Signal Lines	BLM03AG <sup>p30</sup>	0201 (0603)	10	80 70 120 240 600 1000							
			BLM15AG <sup>p40</sup>	0402 (1005)	10	70 120 220 600 1000							
			BLM18A <sup>p54</sup>	0603 (1608)		220 120 150 330 470 600 1000							
			BLM21A <sup>p66</sup>	0805 (2012)		220 120 150 330 470 600 1000							
			BLM18T <sup>p60</sup>	0603 (1608)		120 220 600 1000							
			BLA2AA <sup>p77</sup> (4 circuits array)	0804 (2010)		120 220 600 1000							
			BLA31A <sup>p80</sup> (4 circuits array)	1206 (3216)		30 60 120 220 600 1000							
		For High Speed Signal Lines	BLM03B <sup>p32</sup>	0201 (0603)	10 22	33 56 80 47 75 120 240 470 600							
			BLM15B <sup>p42</sup>	0402 (1005)	5 10 22 33	47 75 120 220 470 600 1800							
			BLM18B <sup>p56</sup>	0603 (1608)	5 10 22	47 60 75 140 220 120 150 330 470 600 1500 2200							
			BLM21B <sup>p68</sup>	0805 (2012)	5	75 200 330 470 750 1500 2200 2700 60 120 150 220 420 600 1000 1800 2250							
			BLA2AB <sup>p77</sup> (4 circuits array)	0804 (2010)	10 22	47 75 120 220 470 600 1000							
			BLA31B <sup>p80</sup> (4 circuits array)	1206 (3216)		120 220 600 470 1000							
			BLM18R <sup>p61</sup>	0603 (1608)		120 220 600 470 1000							
			BLM21R <sup>p71</sup>	0805 (2012)		120 220 600 470 1000							
	Power Lines Type	BLM03PX* <sup>p26</sup>	0201 (0603)		33 (1.5A) 22 (1.8A)	80 (1A)							
		BLM03PG <sup>p25</sup>	0201 (0603)		33 (0.75A) 22 (0.9A)								
		BLM15P* <sup>p34</sup>	0402 (1005)		33 (3A) 80 (1.5A/2.3A) 180 (1.5A) 220 (1.4A) 470 (1A) 10 (1A) 30 (2.2A) 60 (1.7A/2.5A) 120 (1.3A/2A) 330 (1.2A) 600 (0.9A)								
		BLM18P* <sup>p48</sup>	0603 (1608)		33 (3A) 120 (2A) 220 (1.4A) 470 (1A) 30 (1A) 60 (0.5A) 180 (1.5A) 330 (1.2A)								
		BLM21P* <sup>p64</sup>	0805 (2012)		30 (4A) 220 (2A) 22 (6A) 60 (3.5A) 120 (3A) 330 (1.5A)								
		BLM31P* <sup>p73</sup>	1206 (3216)		50 (3.5A) 390 (2A) 33 (6A) 120 (3.5A) 600 (1.5A)								
		BLM41P* <sup>p75</sup>	1806 (4516)		75 (3.5A) 470 (2A) 60 (6A) 180 (3.5A) 1000 (1.5A)								
		BLM18K* <sup>p50</sup> (Low DC Resistance Type)	0603 (1608)		30 (5A) 70 (3.5A) 220 (2.2A) 470 (1.5A) 26 (6A) 100 (3A) 120 (3A) 330 (1.7A) 600 (1.3A)								
		BLM18S* <sup>p52</sup> (Low DC Resistance Type)	0603 (1608)		70 (4A) 220 (2.5A) 26 (6A) 120 (3A) 330 (1.5A)								
	Signal Lines Type	Universal Type [ Power Lines / Signal Lines ]	BLM03EB* <sup>p84</sup>	0201 (0603)		25 (0.6A) 50 (0.4A)							
			BLM15EG* <sup>p87</sup>	0402 (1005)		220 (0.7A) 120 (1.5A)							
			BLM18EG* <sup>p93</sup>	0603 (1608)		120 (2A) 330 (0.5A) 470 (0.5A) 100 (2A) 220 (2A/1A) 390 (0.5A) 600 (0.5A)							
			BLM18HE* <sup>p89</sup>	0603 (1608)		1000 (0.6A) 600 (0.8A) 1500 (0.5A)							
		Signal Lines Type	BLM03HG <sup>p82</sup>	0201 (0603)		600 1000							
			BLM03HD <sup>p82</sup>	0201 (0603)		600 330 470 1000							
			BLM03HB <sup>p82</sup>	0201 (0603)		190							
			BLM15HG <sup>p85</sup>	0402 (1005)		600 1000							
			BLM15HD <sup>p85</sup>	0402 (1005)		600 1000 1800							
			BLM15HB <sup>p85</sup>	0402 (1005)		120 220							
			BLM18HG <sup>p89</sup>	0603 (1608)		600 470 1000							
			BLM18HD <sup>p89</sup>	0603 (1608)		600 470 1000							
			BLM18HB <sup>p89</sup>	0603 (1608)		120 220 330							
			BLM18HK <sup>p89</sup>	0603 (1608)		600 330 470 1000							
For High-GHz Band Noise	Signal Lines Type	BLM15GG <sup>p88</sup>	0402 (1005)		220 470								
		BLM15GA <sup>p88</sup>	0402 (1005)		75								
		BLM18GG <sup>p95</sup>	0603 (1608)		470								

\* The derating of rated current is required for some items according to the operating temperature on each product page.

⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

NF□

Capacitor Type	Series	Size Code Inch (mm)	Capacitance (F)							Effective Frequency Range (Applicable Frequency Ranges are only for reference.)						
			10p	100p	1000p	10000p	0.1μ	1μ	10μ	10kHz	100kHz	1MHz	10MHz	100MHz	1GHz	10GHz
Signal Lines Type	NFM18C <sup>p127</sup>	0603 (1608)		22 47 100 220	470 2200	1000	22000									
	NFM21C <sup>p128</sup>	0805 (2012)		22 47 100 220	470 2200	1000	22000									
	NFM3DC <sup>p129</sup>	1205 (3212)		22 47 100 220	470 2200	1000	22000									
	NFM41C <sup>p130</sup>	1806 (4516)		22 47 100 220	470 2200	1000	22000									
	NFA31C (4 circuits array) <sup>p131</sup>	1206 (3216)		22 47 100 220	470 2200	1000	22000									
Power Lines Type	NFM18P <sup>p118</sup>	0603 (1608)					0.22 1.0 0.1 0.47 2.2									
	NFM21P <sup>p121</sup>	0805 (2012)					0.22 1.0 4.7 0.1 0.47 2.2 10									
	NFM3DP* <sup>p123</sup>	1205 (3212)				22000										
	NFM31P <sup>p124</sup>	1206 (3216)						27								
	NFM31K* <sup>p125</sup>	1206 (3216)				10000 22000 15000	0.1									
	NFM41P <sup>p126</sup>	1806 (4516)					0.2 1.5									
Universal Type [ Power Lines / Signal Lines ]	NFE31P <sup>p116</sup>	1206 (3216)		22 47 100 220	470 2200 1500											
	NFE61P <sup>p117</sup>	2706 (6816)		33 68 180	100 360 1000 680 4700											

NF□

LC(RC) Combined Type	Series	Size Code Inch (mm)	Cut-off Frequency (MHz)							Effective Frequency Range (Applicable Frequency Ranges are only for reference.)						
			10	100	500					10kHz	100kHz	1MHz	10MHz	100MHz	1GHz	10GHz
Signal Lines Type	NFL15ST <sup>p132</sup>	0402 (1005)			150 200 300 500											
	NFL18ST <sup>p133</sup>	0603 (1608)		50 70 100	200 300 500											
	NFL18SP <sup>p135</sup>	0603 (1608)			150 200 300 500											
	NFL21S <sup>p136</sup>	0805 (2012)	10	20	50 70 100 150 200 300 400	500										
	NFA18S (4 circuits array) <sup>p137</sup>	0603 (1608)			50 130 180 220 300 350 480											
	NFA21S (4 circuits array) <sup>p140</sup>	0805 (2012)			50 80 200 300 330	280 310										
	NFW31S <sup>p142</sup>	1206 (3216)	10	20	50 100 150 200 300 500	400										
	NFR21G <sup>p144</sup>	0805 (2012)														
	NFA31G (4 circuits array) <sup>p145</sup>	1206 (3216)														

\* The derating of rated current is required for some items according to the operating temperature on each product page.

## DL

### Common Mode Choke Coils

Signal Lines Type	Series	Size Code Inch (mm)	Common Mode Impedance (Ω) at 100MHz			Effective Frequency Range (Applicable Frequency Ranges are only for reference.)				
			100	500	1000	1MHz	10MHz	100MHz	1GHz	10GHz
For Audio Lines	<b>DLM11G</b> <sup>p174</sup>	0504 (1210)		600						
	<b>DLM11S</b> <sup>p175</sup>	0504 (1210)	45 90							
	<b>DLP0QSN</b> <sup>p176</sup>	025020 (0605)	60							
	<b>DLP0QSA</b> <sup>p176</sup>	025020 (0605)	15 7 35							
	<b>DLP0NSC</b> <sup>p177</sup>	03025 (0806)	28							
	<b>DLP0NSN</b> <sup>p177</sup>	03025 (0806)	35 90 67 120							
	<b>DLP0NSA</b> <sup>p177</sup>	03025 (0806)	15 7							
	<b>DLP11SN</b> <sup>p179</sup>	0504 (1210)	67 90 120 160 200 280 330	240						
	<b>DLP11SA</b> <sup>p179</sup>	0504 (1210)	35 90 67							
	<b>DLP11RN</b> <sup>p180</sup>	0504 (1210)	45							
	<b>DLP11RB</b> <sup>p180</sup>	0504 (1210)	15 40							
	<b>DLP11TB</b> <sup>p181</sup>	0504 (1210)	80							
	<b>DLP31S</b> <sup>p182</sup>	1206 (3216)	120 220 550							
	<b>DLP1NDN</b> (2 circuits array) <sup>p183</sup>	05025 (1506)	35 90 67							
	<b>DLP2ADA</b> (2 circuits array) <sup>p184</sup>	0804 (2010)	35 90 67							
	<b>DLP2ADN</b> (2 circuits array) <sup>p184</sup>	0804 (2010)	90 120 160 200 280	240						
	<b>DLP31DN</b> (2 circuits array) <sup>p186</sup>	1206 (3216)	90 130 200 320 440							
	<b>DLW21S</b> <sup>p187</sup>	0805 (2012)	67 90 120 180 260 370 500							
	<b>DLW21H</b> <sup>p189</sup>	0805 (2012)	67 90 120 180							
	<b>DLW31SN</b> <sup>p190</sup>	1206 (3216)	90 160 260 600 1000 2200							
Universal Type [ Power Lines / Signal Lines ]	<b>DLW5AH/ DLW5BS*</b> <sup>p167</sup>	2014 / 2020 (5036) / (5050)	190 350 1000 1500 4000 3000							
	<b>DLW5AT*/DLW5BT*</b> <sup>p169</sup>	2014 / 2020 (5036) / (5050)	50 110 230 330 500 1000 1400 850 1100 2700							

## PL

### Large Current Common Mode Choke Coil for Automotive Available

Large Current Type for Automotive Available	Series	Size Code Inch (mm)	Common Mode Impedance (Ω) at 100MHz			Effective Frequency Range (Applicable Frequency Ranges are only for reference.)				
			100	500	1000	100kHz	1MHz	10MHz	100MHz	1GHz
	<b>PLT10HH*</b> <sup>p191</sup>	—	45 100	400 500	900 1000 (at 10MHz)					

## BNX

### Block EMIFIL®

Power Lines Type	Series	Height (mm)	Rated Voltage (Vdc)	Rated Current (A)	Effective Frequency Range (Applicable Frequency Ranges are only for reference.)				
					10kHz	100kHz	1MHz	10MHz	100MHz
SMD Type	<b>BNX022*</b> <sup>p209</sup>	3.1	50	10					
	<b>BNX023*</b> <sup>p209</sup>	3.1	100	15					
	<b>BNX024*</b> <sup>p209</sup>	3.5	50	15					
	<b>BNX025*</b> <sup>p209</sup>	3.5	25	15					
	<b>BNX002</b> <sup>p211</sup>	13 max.	50	10					
	<b>BNX003</b> <sup>p211</sup>	13 max.	150	10					
	<b>BNX005</b> <sup>p211</sup>	13.5 max.	50	15					
	<b>BNX012*</b> <sup>p212</sup>	8.0 max.	50	15					
	<b>BNX016*</b> <sup>p212</sup>	8.0 max.	25	15					

\* The derating of rated current is required for some items according to the operating temperature on each product page.

⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



## Chip Ferrite Bead

Series Introduction .....	14
Part Numbering .....	16
Series Line Up .....	17
Product Detail .....	23
⚠Caution/Notice .....	96
Soldering and Mounting .....	97
Packaging .....	101
Design Kits .....	102

Chip Ferrite Bead

Chip EMIFIL®



Chip Common Mode Choke Coil

Block Type EMIFIL®


Microwave Absorber

# BL Series Introduction


## ●Example of Chip Ferrite Bead BLM Series Structure



Cross Section



## ●Line Up Classification of Chip Ferrite Bead



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




## ●Difference between BLM A type and B type (HG type vs HD/HB/HE type)


A type: Impedance curve rises from low frequency range. Suppresses noise in a wide frequency range.

B type: Impedance curve rises sharply. Less damage to signal waveforms.


### ■Comparison of Impedance Curve



### ■Comparison of Resistance Element




### ■Comparison of Test Effect (25MHz)




BLM\_B Series has less damage to high speed signal waveform.

Waveform

No filter






BLM18AG601SN1



BLM18BD601SN1



Spectrum



Spectrum has been reduced from low frequency range.

Noise frequency has been reduced without reducing signals of low frequency.

# BL Chip Ferrite Bead Part Numbering

(Part Number)

<b>BL</b>	<b>M</b>	<b>18</b>	<b>AG</b>	<b>102</b>	<b>S</b>	<b>N</b>	<b>1</b>	<b>D</b>
①	②	③	④	⑤	⑥	⑦	⑧	⑨

## ① Product ID

Product ID	
<b>BL</b>	Chip Ferrite Beads

## ② Type

Code	Type
<b>A</b>	Array Type
<b>M</b>	Ferrite Bead Single Type

## ③ Dimensions (L×W)

Code	Dimensions (L×W)	EIA
<b>02</b>	0.4×0.2mm	01005
<b>03</b>	0.6×0.3mm	0201
<b>15</b>	1.0×0.5mm	0402
<b>18</b>	1.6×0.8mm	0603
<b>2A</b>	2.0×1.0mm	0804
<b>21</b>	2.0×1.25mm	0805
<b>31</b>	3.2×1.6mm	1206
<b>41</b>	4.5×1.6mm	1806

## ④ Characteristics/Applications

Code <sup>*1</sup>	Characteristics/Applications	Series
<b>AG</b>	For General Use	<b>BLM03/15/18/21, BLA2A/31</b>
<b>AX</b>		<b>BLM02/03/15</b>
<b>TG</b>		<b>BLM18</b>
<b>BA</b>	For High-speed Signal Lines	<b>BLM15/18</b>
<b>BB</b>		<b>BLM03/15/18/21, BLA2A</b>
<b>BC</b>		<b>BLM03/15</b>
<b>BD</b>		<b>BLM03/15/18/21, BLA2A/31</b>
<b>BX</b>		<b>BLM15</b>
<b>PD</b>		<b>BLM15</b>
<b>PG</b>	For Power Lines	<b>BLM03/15/18/21/31/41</b>
<b>PX</b>		<b>BLM03/15</b>
<b>KG</b>	For Power Lines (Low DC Resistance Type)	<b>BLM18</b>
<b>SG</b>		
<b>RK</b>	For Digital Interface	<b>BLM18/21</b>
<b>HG</b>	For GHz Band General Use	<b>BLM03/15/18</b>
<b>EB</b>	For GHz Band High-speed Signal Lines (Low Direct Current Type)	<b>BLM03</b>
<b>EG</b>	For GHz Band General Use (Low DC Resistance Type)	<b>BLM15/18</b>
<b>HB</b>	For GHz Band High-speed Signal Lines	<b>BLM03/15/18</b>
<b>HD</b>		<b>BLM03/15/18</b>
<b>HE</b>		<b>BLM18</b>
<b>HK</b>	For GHz Band Digital Interface	<b>BLM18</b>
<b>GA</b>	For High-GHz Band High-speed Signal Lines	<b>BLM15</b>
<b>GG</b>	For High-GHz Band General Use	<b>BLM15/18</b>

<sup>\*1</sup> Frequency characteristics vary with each code.

## ⑨ Packaging

Code	Packaging	Series
<b>K</b>	Embossed Taping (ø330mm Reel)	<b>BLM21 <sup>*1</sup>/31/41</b>
<b>L</b>	Embossed Taping (ø180mm Reel)	
<b>B</b>	Bulk	All Series
<b>J</b>	Paper Taping (ø330mm Reel)	<b>BLM03/15/18 <sup>*3</sup>/21 <sup>*2</sup>, BLA2A/31</b>
<b>D</b>	Paper Taping (ø180mm Reel)	<b>BLM02/03/15/18/21 <sup>*2</sup>, BLA2A/31</b>

<sup>\*1</sup> BLM21BD222SN1/BLM21BD272SN1 only. <sup>\*2</sup> Except for BLM21BD222SN1/BLM21BD272SN1 <sup>\*3</sup> Except for BLM18T

## ⑤ Impedance

Expressed by three figures. The unit is in ohm (Ω) at 100MHz. The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures.

## ⑥ Electrode

Expressed by a letter.

Ex.)	Code	Electrode
	<b>S/T</b>	Sn Plating
	<b>A</b>	Au Plating

## ⑦ Category

Code	Category
<b>N</b>	Standard Type

## ⑧ Number of Circuits

Code	Number of Circuits
<b>1</b>	1 Circuit
<b>4</b>	4 Circuits

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

C31E.pdf  
Aug.1,2013

Size Code (Inch)	Thickness (mm)	Type	Part Number	Impedance		Rated Current	New Kit $\geq 1A$ GHz Flow $R_{eff}$					
				at 100MHz/20°C	at 1GHz/20°C		$\geq 3A$	Hi-GHz				
01005	0.2	Universal Type [Power lines/Signal lines]	BLM02AX100SN1	10ohm $\pm$ 5ohm	-	750mA						$R_{eff}$
	0.2		BLM02AX700SN1	70ohm $\pm$ 25%	-	300mA						$R_{eff}$
	0.2		BLM02AX121SN1	120ohm $\pm$ 25%	-	250mA						$R_{eff}$
0201	0.3	For General Signal Lines	BLM03AG100SN1	10ohm(Typ.)	-	500mA	Kit					$R_{eff}$
	0.3		BLM03AG700SN1	70ohm(Typ.)	-	200mA	Kit					$R_{eff}$
	0.3		BLM03AG800SN1	80ohm $\pm$ 25%	-	200mA	Kit					$R_{eff}$
	0.3		BLM03AG121SN1	120ohm $\pm$ 25%	-	200mA	Kit					$R_{eff}$
	0.3		BLM03AG241SN1	240ohm $\pm$ 25%	-	200mA	Kit					$R_{eff}$
	0.3		BLM03AG601SN1	600ohm $\pm$ 25%	-	100mA	Kit					$R_{eff}$
	0.3		BLM03AG102SN1	1000ohm $\pm$ 25%	-	100mA	Kit					$R_{eff}$
	0.3		BLM03AX100SN1	10ohm(Typ.)	-	1000mA	Kit	$\geq 1A$				$R_{eff}$
	0.3	Universal Type [Power lines/Signal lines]	BLM03AX800SN1	80ohm $\pm$ 25%	-	500mA	Kit					$R_{eff}$
	0.3		BLM03AX121SN1	120ohm $\pm$ 25%	-	450mA	Kit					$R_{eff}$
	0.3		BLM03AX241SN1	240ohm $\pm$ 25%	-	350mA	Kit					$R_{eff}$
	0.3		BLM03AX601SN1	600ohm $\pm$ 25%	-	250mA	Kit					$R_{eff}$
	0.3		BLM03AX102SN1	1000ohm $\pm$ 25%	-	200mA	Kit					$R_{eff}$
	0.3		BLM03BD750SN1	75ohm $\pm$ 25%	-	300mA	Kit					$R_{eff}$
	0.3	For High Speed Signal Lines (Sharp Impedance Curve)	BLM03BD121SN1	120ohm $\pm$ 25%	-	250mA	Kit					$R_{eff}$
	0.3		BLM03BD241SN1	240ohm $\pm$ 25%	-	200mA	Kit					$R_{eff}$
	0.3		BLM03BD471SN1	470ohm $\pm$ 25%	-	215mA	Kit					$R_{eff}$
	0.3		BLM03BD601SN1	600ohm $\pm$ 25%	-	200mA	Kit					$R_{eff}$
	0.3		BLM03BB100SN1	10ohm $\pm$ 25%	-	300mA	Kit					$R_{eff}$
	0.3		BLM03BB220SN1	22ohm $\pm$ 25%	-	200mA	Kit					$R_{eff}$
	0.3		BLM03BB470SN1	47ohm $\pm$ 25%	-	200mA	Kit					$R_{eff}$
	0.3		BLM03BB750SN1	75ohm $\pm$ 25%	-	200mA	Kit					$R_{eff}$
	0.3		BLM03BB121SN1	120ohm $\pm$ 25%	-	100mA	Kit					$R_{eff}$
	0.3		BLM03BC330SN1	33ohm $\pm$ 25%	-	150mA	Kit					$R_{eff}$
	0.3		BLM03BC560SN1	56ohm $\pm$ 25%	-	100mA	Kit					$R_{eff}$
	0.3		BLM03BC800SN1	80ohm $\pm$ 25%	-	100mA	Kit					$R_{eff}$
	0.3	For Power Lines	BLM03PG220SN1	22ohm $\pm$ 25%	-	900mA	Kit					$R_{eff}$
	0.3		BLM03PG330SN1	33ohm $\pm$ 25%	-	750mA	Kit					$R_{eff}$
	0.3		BLM03PX220SN1	22ohm $\pm$ 25%	-	1800mA	Kit	$\geq 1A$				$R_{eff}$
	0.3		BLM03PX330SN1	33ohm $\pm$ 25%	-	1500mA	Kit	$\geq 1A$				$R_{eff}$
	0.3		BLM03PX800SN1	80ohm $\pm$ 25%	-	1000mA	Kit	$\geq 1A$				$R_{eff}$
	0.3	For GHz Band Noise	BLM03HG601SN1	600ohm $\pm$ 25%	1000ohm $\pm$ 40%	150mA	Kit		GHz			$R_{eff}$
	0.3		BLM03HG102SN1	1000ohm $\pm$ 25%	1800ohm $\pm$ 40%	125mA	Kit		GHz			$R_{eff}$
	0.3		BLM03EB250SN1	25ohm $\pm$ 25%	105ohm $\pm$ 40%	600mA	New Kit		GHz			$R_{eff}$
	0.3		BLM03EB500SN1	50ohm $\pm$ 25%	255ohm $\pm$ 40%	400mA	New Kit		GHz			$R_{eff}$
	0.3		BLM03HD331SN1	330ohm $\pm$ 25%	-	200mA	Kit		GHz			$R_{eff}$
	0.3		BLM03HD471SN1	470ohm $\pm$ 25%	-	175mA	Kit		GHz			$R_{eff}$
	0.3		BLM03HD601SN1	600ohm $\pm$ 25%	-	150mA	Kit		GHz			$R_{eff}$
	0.3		BLM03HD102SN1	1000ohm $\pm$ 25%	-	120mA	Kit		GHz			$R_{eff}$
	0.3		BLM03HB191SN1	190ohm $\pm$ 25%	1150ohm $\pm$ 40%	150mA	New Kit		GHz			$R_{eff}$
	0.3											
0402	0.5	For General Signal Lines	BLM15AG100SN1	10ohm(Typ.)	-	1000mA	Kit	$\geq 1A$				$R_{eff}$
	0.5		BLM15AG700SN1	70ohm(Typ.)	-	600mA	Kit					$R_{eff}$
	0.5		BLM15AG121SN1	120ohm $\pm$ 25%	-	550mA	Kit					$R_{eff}$
	0.5		BLM15AG221SN1	220ohm $\pm$ 25%	-	450mA	Kit					$R_{eff}$
	0.5		BLM15AG601SN1	600ohm $\pm$ 25%	-	300mA	Kit					$R_{eff}$
	0.5		BLM15AG102SN1	1000ohm $\pm$ 25%	-	300mA	Kit					$R_{eff}$
	0.5	Universal Type [Power lines/Signal lines]	BLM15AX100SN1	10ohm(Typ.)	-	1740mA	Kit	$\geq 1A$				$R_{eff}$
	0.5		BLM15AX300SN1	30ohm $\pm$ 25%	-	1100mA	Kit	$\geq 1A$				$R_{eff}$
	0.5		BLM15AX700SN1	70ohm $\pm$ 25%	-	780mA	Kit					$R_{eff}$
	0.5		BLM15AX121SN1	120ohm $\pm$ 25%	-	700mA	Kit					$R_{eff}$
	0.5		BLM15AX221SN1	220ohm $\pm$ 25%	-	600mA	Kit					$R_{eff}$
	0.5		BLM15AX601SN1	600ohm $\pm$ 25%	-	500mA	Kit					$R_{eff}$
	0.5		BLM15AX102SN1	1000ohm $\pm$ 25%	-	350mA	Kit					$R_{eff}$

Continued on the following page.

Size Code (Inch)	Thickness (mm)	Type	Part Number	Impedance		Rated Current	New	Kit	$\geq 1A$	GHz	Flow	R <sub>eff</sub>	
				at 100MHz/20°C	at 1GHz/20°C				$\geq 3A$	Hi <sub>GHz</sub>			
0402	0.5	For High Speed Signal Lines (Sharp Impedance Curve)	p42 BLM15BX750SN1	75ohm±25%	-	600mA	New	Kit				R <sub>eff</sub>	
	0.5		BLM15BX121SN1	120ohm±25%	-	600mA	New	Kit				R <sub>eff</sub>	
	0.5		BLM15BX221SN1	220ohm±25%	-	450mA	New	Kit				R <sub>eff</sub>	
	0.5		BLM15BX471SN1	470ohm±25%	-	350mA	New	Kit				R <sub>eff</sub>	
	0.5		BLM15BX601SN1	600ohm±25%	-	350mA	New	Kit				R <sub>eff</sub>	
	0.5		BLM15BX102SN1	1000ohm±25%	-	300mA	New	Kit				R <sub>eff</sub>	
	0.5		BLM15BX182SN1	1800ohm±25%	-	250mA	New	Kit				R <sub>eff</sub>	
	0.5		p44 BLM15BD750SN1	75ohm±25%	-	300mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BD121SN1	120ohm±25%	-	300mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BD221SN1	220ohm±25%	-	300mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BD471SN1	470ohm±25%	-	200mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BD601SN1	600ohm±25%	-	200mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BD102SN1	1000ohm±25%	-	200mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BD182SN1	1800ohm±25%	-	100mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BB050SN1	5ohm±25%	-	500mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BB100SN1	10ohm±25%	-	300mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BB220SN1	22ohm±25%	-	300mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BB470SN1	47ohm±25%	-	300mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BB750SN1	75ohm±25%	-	300mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BB121SN1	120ohm±25%	-	300mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BB221SN1	220ohm±25%	-	200mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BC121SN1	120ohm±25%	-	350mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BC241SN1	240ohm±25%	-	250mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BA050SN1	5ohm±25%	-	300mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BA100SN1	10ohm±25%	-	300mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BA220SN1	22ohm±25%	-	300mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BA330SN1	33ohm±25%	-	300mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BA470SN1	47ohm±25%	-	200mA		Kit				R <sub>eff</sub>	
	0.5		BLM15BA750SN1	75ohm±25%	-	200mA		Kit				R <sub>eff</sub>	
	0.5		p34 BLM15PX330SN1	For Power Lines	33ohm±25%	-	3000mA	New	Kit	$\geq 3A$			R <sub>eff</sub>
	0.5		BLM15PX600SN1		60ohm±25%	-	2500mA	New	Kit	$\geq 1A$			R <sub>eff</sub>
	0.5		BLM15PX800SN1		80ohm±25%	-	2300mA	New	Kit	$\geq 1A$			R <sub>eff</sub>
	0.5		BLM15PX121SN1		120ohm±25%	-	2000mA	New	Kit	$\geq 1A$			R <sub>eff</sub>
	0.5		BLM15PX181SN1		180ohm±25%	-	1500mA	New	Kit	$\geq 1A$			R <sub>eff</sub>
	0.5	BLM15PX221SN1	220ohm±25%		-	1400mA	New	Kit	$\geq 1A$			R <sub>eff</sub>	
	0.5	BLM15PX331SN1	330ohm±25%		-	1200mA	New	Kit	$\geq 1A$			R <sub>eff</sub>	
	0.5	BLM15PX471SN1	470ohm±25%		-	1000mA	New	Kit	$\geq 1A$			R <sub>eff</sub>	
	0.5	BLM15PX601SN1	600ohm±25%		-	900mA	New	Kit				R <sub>eff</sub>	
	0.5	p36 BLM15PG100SN1	10ohm(Typ.)		-	1000mA		Kit	$\geq 1A$			R <sub>eff</sub>	
	0.5	BLM15PD300SN1	30ohm±25%		-	2200mA		Kit	$\geq 1A$			R <sub>eff</sub>	
	0.5	BLM15PD600SN1	60ohm±25%		-	1700mA		Kit	$\geq 1A$			R <sub>eff</sub>	
	0.5	BLM15PD800SN1	80ohm±25%		-	1500mA		Kit	$\geq 1A$			R <sub>eff</sub>	
	0.5	BLM15PD121SN1	120ohm±25%		-	1300mA		Kit	$\geq 1A$			R <sub>eff</sub>	
0.5	For GHz Band Noise	p85 BLM15HG601SN1	600ohm±25%	1000ohm±40%	300mA		Kit		GHz		R <sub>eff</sub>		
0.5		For General Signal Lines	BLM15HG102SN1	1000ohm±25%	1400ohm±40%	250mA		Kit		GHz		R <sub>eff</sub>	
0.5			p85 BLM15HD601SN1	600ohm±25%	1400ohm±40%	300mA		Kit		GHz		R <sub>eff</sub>	
0.5		For High Speed Signal Lines (Sharp Impedance Curve)	BLM15HD102SN1	1000ohm±25%	2000ohm±40%	250mA		Kit		GHz		R <sub>eff</sub>	
0.5			BLM15HD182SN1	1800ohm±25%	2700ohm±40%	200mA		Kit		GHz		R <sub>eff</sub>	
0.5			BLM15HB121SN1	120ohm±25%	500ohm±40%	300mA		Kit		GHz		R <sub>eff</sub>	
0.5			BLM15HB221SN1	220ohm±25%	900ohm±40%	250mA		Kit		GHz		R <sub>eff</sub>	
0.5		Universal Type [Power Lines/Signal Lines]	p87 BLM15EG121SN1	120ohm±25%	145ohm(Typ.)	1500mA		Kit	$\geq 1A$	GHz		R <sub>eff</sub>	
0.5	BLM15EG221SN1		220ohm±25%	270ohm(Typ.)	700mA		Kit		GHz		R <sub>eff</sub>		
0.5	For High-GHz Band Noise	p88 BLM15GG221SN1	220ohm±25%	600ohm±40%	300mA		Kit		Hi <sub>GHz</sub>		R <sub>eff</sub>		
0.5		For General Signal Lines	BLM15GG471SN1	470ohm±25%	1200ohm±40%	200mA		Kit		Hi <sub>GHz</sub>		R <sub>eff</sub>	
0.5		For High Speed Signal Lines	p88 BLM15GA750SN1	75ohm±25%	1000ohm±40%	200mA		Kit		Hi <sub>GHz</sub>		R <sub>eff</sub>	

Continued on the following page. 



Size Code (Inch)	Thickness (mm)	Type	Part Number	Impedance		Rated Current	New	Kit	$\geq 1A$ $\geq 3A$	$\geq 1GHz$ $\geq 3GHz$	Flow	Reflow
				at 100MHz/20°C	at 1GHz/20°C							
0603	0.8	For General Signal Lines	p54 BLM18AG121SN1	120ohm $\pm$ 25%	-	500mA		Kit			Flow	Reflow
	0.8		BLM18AG151SN1	150ohm $\pm$ 25%	-	500mA		Kit			Flow	Reflow
	0.8		BLM18AG221SN1	220ohm $\pm$ 25%	-	500mA		Kit			Flow	Reflow
	0.8		BLM18AG331SN1	330ohm $\pm$ 25%	-	500mA		Kit			Flow	Reflow
	0.8		BLM18AG471SN1	470ohm $\pm$ 25%	-	500mA		Kit			Flow	Reflow
	0.8		BLM18AG601SN1	600ohm $\pm$ 25%	-	500mA		Kit			Flow	Reflow
	0.8		BLM18AG102SN1	1000ohm $\pm$ 25%	-	400mA		Kit			Flow	Reflow
	0.6		p60 BLM18TG121TN1	120ohm $\pm$ 25%	-	200mA					Flow	Reflow
	0.6		BLM18TG221TN1	220ohm $\pm$ 25%	-	200mA					Flow	Reflow
	0.6		BLM18TG601TN1	600ohm $\pm$ 25%	-	200mA					Flow	Reflow
	0.6		BLM18TG102TN1	1000ohm $\pm$ 25%	-	100mA					Flow	Reflow
	0.8	For High Speed Signal Lines (Sharp Impedance Curve)	p56 BLM18BD470SN1	47ohm $\pm$ 25%	-	500mA		Kit			Flow	Reflow
	0.8		BLM18BD121SN1	120ohm $\pm$ 25%	-	200mA		Kit			Flow	Reflow
	0.8		BLM18BD151SN1	150ohm $\pm$ 25%	-	200mA		Kit			Flow	Reflow
	0.8		BLM18BD221SN1	220ohm $\pm$ 25%	-	200mA		Kit			Flow	Reflow
	0.8		BLM18BD331SN1	330ohm $\pm$ 25%	-	200mA		Kit			Flow	Reflow
	0.8		BLM18BD421SN1	420ohm $\pm$ 25%	-	200mA		Kit			Flow	Reflow
	0.8		BLM18BD471SN1	470ohm $\pm$ 25%	-	200mA		Kit			Flow	Reflow
	0.8		BLM18BD601SN1	600ohm $\pm$ 25%	-	200mA		Kit			Flow	Reflow
	0.8		BLM18BD102SN1	1000ohm $\pm$ 25%	-	100mA		Kit			Flow	Reflow
	0.8		BLM18BD152SN1	1500ohm $\pm$ 25%	-	50mA		Kit			Flow	Reflow
	0.8		BLM18BD182SN1	1800ohm $\pm$ 25%	-	50mA		Kit			Flow	Reflow
	0.8		BLM18BD222SN1	2200ohm $\pm$ 25%	-	50mA		Kit			Flow	Reflow
	0.8		BLM18BD252SN1	2500ohm $\pm$ 25%	-	50mA		Kit			Flow	Reflow
	0.8		BLM18BB050SN1	5ohm $\pm$ 25%	-	700mA		Kit			Flow	Reflow
	0.8		BLM18BB100SN1	10ohm $\pm$ 25%	-	700mA		Kit			Flow	Reflow
	0.8		BLM18BB220SN1	22ohm $\pm$ 25%	-	600mA		Kit			Flow	Reflow
	0.8		BLM18BB470SN1	47ohm $\pm$ 25%	-	550mA		Kit			Flow	Reflow
	0.8		BLM18BB600SN1	60ohm $\pm$ 25%	-	550mA		Kit			Flow	Reflow
	0.8		BLM18BB750SN1	75ohm $\pm$ 25%	-	500mA		Kit			Flow	Reflow
	0.8		BLM18BB121SN1	120ohm $\pm$ 25%	-	500mA		Kit			Flow	Reflow
	0.8		BLM18BB141SN1	140ohm $\pm$ 25%	-	450mA					Flow	Reflow
	0.8		BLM18BB151SN1	150ohm $\pm$ 25%	-	450mA		Kit			Flow	Reflow
	0.8		BLM18BB221SN1	220ohm $\pm$ 25%	-	450mA		Kit			Flow	Reflow
	0.8		BLM18BB331SN1	330ohm $\pm$ 25%	-	400mA		Kit			Flow	Reflow
	0.8		BLM18BB471SN1	470ohm $\pm$ 25%	-	300mA		Kit			Flow	Reflow
	0.8		BLM18BA050SN1	5ohm $\pm$ 25%	-	500mA		Kit			Flow	Reflow
	0.8		BLM18BA100SN1	10ohm $\pm$ 25%	-	500mA		Kit			Flow	Reflow
	0.8		BLM18BA220SN1	22ohm $\pm$ 25%	-	500mA					Flow	Reflow
	0.8		BLM18BA470SN1	47ohm $\pm$ 25%	-	300mA		Kit			Flow	Reflow
	0.8		BLM18BA750SN1	75ohm $\pm$ 25%	-	300mA		Kit			Flow	Reflow
	0.8		BLM18BA121SN1	120ohm $\pm$ 25%	-	200mA		Kit			Flow	Reflow
	0.8	For Digital Interface Lines	p61 BLM18RK121SN1	120ohm $\pm$ 25%	-	200mA		Kit			Flow	Reflow
	0.8		BLM18RK221SN1	220ohm $\pm$ 25%	-	200mA					Flow	Reflow
	0.8		BLM18RK471SN1	470ohm $\pm$ 25%	-	200mA		Kit			Flow	Reflow
	0.8		BLM18RK601SN1	600ohm $\pm$ 25%	-	200mA		Kit			Flow	Reflow
	0.8		BLM18RK102SN1	1000ohm $\pm$ 25%	-	200mA		Kit			Flow	Reflow

Continued on the following page. 

Size Code (Inch)	Thickness (mm)	Type	Part Number	Impedance		Rated Current	New Kit $\geq 1A$ GHz $\geq 3A$ Hi-Ohm F <sub>low</sub> R <sub>eflow</sub>			
				at 100MHz/20°C	at 1GHz/20°C					
0603	0.8	Standard Type	p48 BLM18PG300SN1	30ohm(Typ.)	-	1000mA	K <sub>it</sub>	$\geq 1A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.8		BLM18PG330SN1	33ohm $\pm 25\%$	-	3000mA	K <sub>it</sub>	$\geq 3A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.8		BLM18PG600SN1	60ohm(Typ.)	-	500mA	K <sub>it</sub>		F <sub>low</sub>	R <sub>eflow</sub>
	0.8		BLM18PG121SN1	120ohm $\pm 25\%$	-	2000mA	K <sub>it</sub>	$\geq 1A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.8		BLM18PG181SN1	180ohm $\pm 25\%$	-	1500mA	K <sub>it</sub>	$\geq 1A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.8		BLM18PG221SN1	220ohm $\pm 25\%$	-	1400mA	K <sub>it</sub>	$\geq 1A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.8		BLM18PG331SN1	330ohm $\pm 25\%$	-	1200mA	K <sub>it</sub>	$\geq 1A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.8		BLM18PG471SN1	470ohm $\pm 25\%$	-	1000mA	K <sub>it</sub>	$\geq 1A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.6	For Power Lines	p50 BLM18KG260TN1	26ohm $\pm 25\%$	-	6000mA	K <sub>it</sub>	$\geq 3A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.6		BLM18KG300TN1	30ohm $\pm 25\%$	-	5000mA	K <sub>it</sub>	$\geq 3A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.6		BLM18KG700TN1	70ohm $\pm 25\%$	-	3500mA	K <sub>it</sub>	$\geq 3A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.6		BLM18KG101TN1	100ohm $\pm 25\%$	-	3000mA	K <sub>it</sub>	$\geq 3A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.6		BLM18KG121TN1	120ohm $\pm 25\%$	-	3000mA	K <sub>it</sub>	$\geq 3A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.8		BLM18KG221SN1	220ohm $\pm 25\%$	-	2200mA	K <sub>it</sub>	$\geq 1A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.8		BLM18KG331SN1	330ohm $\pm 25\%$	-	1700mA	K <sub>it</sub>	$\geq 1A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.8		BLM18KG471SN1	470ohm $\pm 25\%$	-	1500mA	K <sub>it</sub>	$\geq 1A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.8	Low DC Resistance Type	BLM18KG601SN1	600ohm $\pm 25\%$	-	1300mA	K <sub>it</sub>	$\geq 1A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.5		p52 BLM18SG260TN1	26ohm $\pm 25\%$	-	6000mA	K <sub>it</sub>	$\geq 3A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.5		BLM18SG700TN1	70ohm $\pm 25\%$	-	4000mA	K <sub>it</sub>	$\geq 3A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.5		BLM18SG121TN1	120ohm $\pm 25\%$	-	3000mA	K <sub>it</sub>	$\geq 3A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.5		BLM18SG221TN1	220ohm $\pm 25\%$	-	2500mA	K <sub>it</sub>	$\geq 1A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.5		BLM18SG331TN1	330ohm $\pm 25\%$	-	1500mA	K <sub>it</sub>	$\geq 1A$	F <sub>low</sub>	R <sub>eflow</sub>
	0.8	For General Signal Lines	p89 BLM18HG471SN1	470ohm $\pm 25\%$	600ohm(Typ.)	200mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18HG601SN1	600ohm $\pm 25\%$	700ohm(Typ.)	200mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18HG102SN1	1000ohm $\pm 25\%$	1000ohm(Typ.)	100mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8	For High Speed Signal Lines (Sharp Impedance Curve)	p89 BLM18HE601SN1	600ohm $\pm 25\%$	600ohm(Typ.)	800mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18HE102SN1	1000ohm $\pm 25\%$	1000ohm(Typ.)	600mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18HE152SN1	1500ohm $\pm 25\%$	1500ohm(Typ.)	500mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18HD471SN1	470ohm $\pm 25\%$	1000ohm(Typ.)	100mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18HD601SN1	600ohm $\pm 25\%$	1200ohm(Typ.)	100mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18HD102SN1	1000ohm $\pm 25\%$	1700ohm(Typ.)	50mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8	For GHz Band Noise	BLM18HB121SN1	120ohm $\pm 25\%$	500ohm $\pm 40\%$	200mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18HB221SN1	220ohm $\pm 25\%$	1100ohm $\pm 40\%$	100mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18HB331SN1	330ohm $\pm 25\%$	1600ohm $\pm 40\%$	50mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8	For Digital Interface Lines	p89 BLM18HK331SN1	330ohm $\pm 25\%$	400ohm $\pm 40\%$	200mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18HK471SN1	470ohm $\pm 25\%$	600ohm $\pm 40\%$	200mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18HK601SN1	600ohm $\pm 25\%$	700ohm $\pm 40\%$	100mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18HK102SN1	1000ohm $\pm 25\%$	1200ohm $\pm 40\%$	50mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.5	Universal Type [Power lines/Signal lines]	p93 BLM18EG101TN1	100ohm $\pm 25\%$	140ohm(Typ.)	2000mA	K <sub>it</sub>	$\geq 1A$	GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18EG121SN1	120ohm $\pm 25\%$	145ohm(Typ.)	2000mA	K <sub>it</sub>	$\geq 1A$	GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18EG221SN1	220ohm $\pm 25\%$	260ohm(Typ.)	2000mA	K <sub>it</sub>	$\geq 1A$	GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.5		BLM18EG221TN1	220ohm $\pm 25\%$	300ohm(Typ.)	1000mA	K <sub>it</sub>	$\geq 1A$	GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.5		BLM18EG331TN1	330ohm $\pm 25\%$	450ohm(Typ.)	500mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18EG391TN1	390ohm $\pm 25\%$	520ohm(Typ.)	500mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18EG471SN1	470ohm $\pm 25\%$	550ohm(Typ.)	500mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
	0.8		BLM18EG601SN1	600ohm $\pm 25\%$	700ohm(Typ.)	500mA	K <sub>it</sub>		GHz	F <sub>low</sub> R <sub>eflow</sub>
0805	0.8	For High-GHz Band Noise	p95 BLM18GG471SN1	470ohm $\pm 25\%$	1800ohm $\pm 30\%$	200mA	K <sub>it</sub>		Hi-Ohm	R <sub>eflow</sub>
	0.85	For General Signal Lines	p66 BLM21AG121SN1	120ohm $\pm 25\%$	-	800mA	K <sub>it</sub>		F <sub>low</sub>	R <sub>eflow</sub>
	0.85		BLM21AG151SN1	150ohm $\pm 25\%$	-	800mA	K <sub>it</sub>		F <sub>low</sub>	R <sub>eflow</sub>
	0.85		BLM21AG221SN1	220ohm $\pm 25\%$	-	800mA	K <sub>it</sub>		F <sub>low</sub>	R <sub>eflow</sub>
	0.85		BLM21AG331SN1	330ohm $\pm 25\%$	-	700mA	K <sub>it</sub>		F <sub>low</sub>	R <sub>eflow</sub>
	0.85		BLM21AG471SN1	470ohm $\pm 25\%$	-	700mA	K <sub>it</sub>		F <sub>low</sub>	R <sub>eflow</sub>
	0.85		BLM21AG601SN1	600ohm $\pm 25\%$	-	600mA	K <sub>it</sub>		F <sub>low</sub>	R <sub>eflow</sub>
	0.85		BLM21AG102SN1	1000ohm $\pm 25\%$	-	500mA	K <sub>it</sub>		F <sub>low</sub>	R <sub>eflow</sub>
	0.85									
	0.85									
	0.85									

Continued on the following page. 



Size Code (Inch)	Thickness (mm)	Type	Part Number	Impedance		Rated Current	New Kit $\geq 1A$ GHz $\geq 3A$ Hi-Off Flow Reflow			
				at 100MHz/20°C	at 1GHz/20°C					
0805	0.85	For High Speed Signal Lines (Sharp Impedance Curve)	<i>p68</i> BLM21BD121SN1	120ohm $\pm$ 25%	-	200mA	Kit		Flow	Reflow
	0.85		BLM21BD151SN1	150ohm $\pm$ 25%	-	200mA			Flow	Reflow
	0.85		BLM21BD221SN1	220ohm $\pm$ 25%	-	200mA	Kit		Flow	Reflow
	0.85		BLM21BD331SN1	330ohm $\pm$ 25%	-	200mA			Flow	Reflow
	0.85		BLM21BD421SN1	420ohm $\pm$ 25%	-	200mA	Kit		Flow	Reflow
	0.85		BLM21BD471SN1	470ohm $\pm$ 25%	-	200mA	Kit		Flow	Reflow
	0.85		BLM21BD601SN1	600ohm $\pm$ 25%	-	200mA	Kit		Flow	Reflow
	0.85		BLM21BD751SN1	750ohm $\pm$ 25%	-	200mA			Flow	Reflow
	0.85		BLM21BD102SN1	1000ohm $\pm$ 25%	-	200mA	Kit		Flow	Reflow
	0.85		BLM21BD152SN1	1500ohm $\pm$ 25%	-	200mA	Kit		Flow	Reflow
	0.85		BLM21BD182SN1	1800ohm $\pm$ 25%	-	200mA	Kit		Flow	Reflow
	0.85		BLM21BD222TN1	2200ohm $\pm$ 25%	-	200mA	Kit		Flow	Reflow
	1.25		BLM21BD222SN1	2250ohm(Typ.)	-	200mA	Kit		Flow	Reflow
	1.25		BLM21BD272SN1	2700ohm $\pm$ 25%	-	200mA	Kit		Flow	Reflow
	0.85		BLM21BB050SN1	5ohm $\pm$ 25%	-	1000mA	Kit		Flow	Reflow
	0.85		BLM21BB600SN1	60ohm $\pm$ 25%	-	800mA	Kit		Flow	Reflow
	0.85		BLM21BB750SN1	75ohm $\pm$ 25%	-	700mA	Kit		Flow	Reflow
	0.85		BLM21BB121SN1	120ohm $\pm$ 25%	-	600mA	Kit		Flow	Reflow
	0.85		BLM21BB151SN1	150ohm $\pm$ 25%	-	600mA			Flow	Reflow
	0.85		BLM21BB201SN1	200ohm $\pm$ 25%	-	500mA			Flow	Reflow
	0.85		BLM21BB221SN1	220ohm $\pm$ 25%	-	500mA	Kit		Flow	Reflow
	0.85		BLM21BB331SN1	330ohm $\pm$ 25%	-	400mA	Kit		Flow	Reflow
	0.85		BLM21BB471SN1	470ohm $\pm$ 25%	-	400mA	Kit		Flow	Reflow
	0.85	For Digital Interface Lines	<i>p71</i> BLM21RK121SN1	120ohm $\pm$ 25%	-	200mA			Flow	Reflow
	0.85		BLM21RK221SN1	220ohm $\pm$ 25%	-	200mA			Flow	Reflow
	0.85		BLM21RK471SN1	470ohm $\pm$ 25%	-	200mA			Flow	Reflow
	0.85		BLM21RK601SN1	600ohm $\pm$ 25%	-	200mA			Flow	Reflow
	0.85		BLM21RK102SN1	1000ohm $\pm$ 25%	-	200mA			Flow	Reflow
	0.85	For Power Lines	<i>p64</i> BLM21PG220SN1	22ohm $\pm$ 25%	-	6000mA	Kit $\geq 3A$		Flow	Reflow
	0.85		BLM21PG300SN1	30ohm(Typ.)	-	4000mA	Kit $\geq 3A$		Flow	Reflow
	0.85		BLM21PG600SN1	60ohm $\pm$ 25%	-	3500mA	Kit $\geq 3A$		Flow	Reflow
	0.85		BLM21PG121SN1	120ohm $\pm$ 25%	-	3000mA	Kit $\geq 3A$		Flow	Reflow
	0.85		BLM21PG221SN1	220ohm $\pm$ 25%	-	2000mA	Kit $\geq 1A$		Flow	Reflow
	0.85		BLM21PG331SN1	330ohm $\pm$ 25%	-	1500mA	Kit $\geq 1A$		Flow	Reflow
	1.1		<i>p73</i> BLM31PG330SN1	33ohm $\pm$ 25%	-	6000mA	Kit $\geq 3A$		Flow	Reflow
1206	1.1	For Power Lines	BLM31PG500SN1	50ohm(Typ.)	-	3500mA	Kit $\geq 3A$		Flow	Reflow
	1.1		BLM31PG121SN1	120ohm $\pm$ 25%	-	3500mA	Kit $\geq 3A$		Flow	Reflow
	1.1		BLM31PG391SN1	390ohm $\pm$ 25%	-	2000mA	Kit $\geq 1A$		Flow	Reflow
	1.1		BLM31PG601SN1	600ohm $\pm$ 25%	-	1500mA	Kit $\geq 1A$		Flow	Reflow
	1.6		<i>p75</i> BLM41PG600SN1	60ohm(Typ.)	-	6000mA	Kit $\geq 3A$		Flow	Reflow
1806	1.6	For Power Lines	BLM41PG750SN1	75ohm(Typ.)	-	3500mA	Kit $\geq 3A$		Flow	Reflow
	1.6		BLM41PG181SN1	180ohm $\pm$ 25%	-	3500mA	Kit $\geq 3A$		Flow	Reflow
	1.6		BLM41PG471SN1	470ohm $\pm$ 25%	-	2000mA	Kit $\geq 1A$		Flow	Reflow
	1.6		BLM41PG102SN1	1000ohm $\pm$ 25%	-	1500mA	Kit $\geq 1A$		Flow	Reflow
	0.5	For General Signal Lines	<i>p77</i> BLA2AAG121SN4	120ohm $\pm$ 25%	-	100mA			Reflow	
0804	0.5		BLA2AAG221SN4	220ohm $\pm$ 25%	-	50mA			Reflow	
	0.5		BLA2AAG601SN4	600ohm $\pm$ 25%	-	50mA			Reflow	
	0.5		BLA2AAG102SN4	1000ohm $\pm$ 25%	-	50mA			Reflow	
	0.5	For High Speed Signal Lines	<i>p77</i> BLA2ABD750SN4	75ohm $\pm$ 25%	-	200mA			Reflow	
	0.5		BLA2ABD121SN4	120ohm $\pm$ 25%	-	200mA			Reflow	
	0.5		BLA2ABD221SN4	220ohm $\pm$ 25%	-	100mA			Reflow	
	0.5		BLA2ABD471SN4	470ohm $\pm$ 25%	-	100mA			Reflow	
	0.5		BLA2ABD601SN4	600ohm $\pm$ 25%	-	100mA			Reflow	
	0.5		BLA2ABD102SN4	1000ohm $\pm$ 25%	-	50mA			Reflow	
	0.5		BLA2ABB100SN4	10ohm $\pm$ 25%	-	200mA			Reflow	
	0.5		BLA2ABB220SN4	22ohm $\pm$ 25%	-	200mA			Reflow	
	0.5		BLA2ABB470SN4	47ohm $\pm$ 25%	-	200mA			Reflow	
	0.5		BLA2ABB121SN4	120ohm $\pm$ 25%	-	50mA			Reflow	
	0.5		BLA2ABB221SN4	220ohm $\pm$ 25%	-	50mA			Reflow	

Continued on the following page. 

Size Code (Inch)	Thickness (mm)	Type	Part Number	Impedance		Rated Current	New	Kit	$\geq 1A$ $\geq 3A$	GHz Hi-GHz	Flow	R <sub>efflow</sub>
				at 100MHz/20°C	at 1GHz/20°C							
1206	0.8	For General Signal Lines	BLA31AG300SN4	30ohm $\pm$ 25%	-	200mA					Flow	R <sub>efflow</sub>
	0.8		BLA31AG600SN4	60ohm $\pm$ 25%	-	200mA					Flow	R <sub>efflow</sub>
	0.8		BLA31AG121SN4	120ohm $\pm$ 25%	-	150mA					Flow	R <sub>efflow</sub>
	0.8		BLA31AG221SN4	220ohm $\pm$ 25%	-	150mA					Flow	R <sub>efflow</sub>
	0.8		BLA31AG601SN4	600ohm $\pm$ 25%	-	100mA					Flow	R <sub>efflow</sub>
	0.8		BLA31AG102SN4	1000ohm $\pm$ 25%	-	50mA					Flow	R <sub>efflow</sub>
	0.8	For High Speed Signal Lines	BLA31BD121SN4	120ohm $\pm$ 25%	-	150mA					Flow	R <sub>efflow</sub>
	0.8		BLA31BD221SN4	220ohm $\pm$ 25%	-	150mA					Flow	R <sub>efflow</sub>
	0.8		BLA31BD471SN4	470ohm $\pm$ 25%	-	100mA					Flow	R <sub>efflow</sub>
	0.8		BLA31BD601SN4	600ohm $\pm$ 25%	-	100mA					Flow	R <sub>efflow</sub>
	0.8		BLA31BD102SN4	1000ohm $\pm$ 25%	-	50mA					Flow	R <sub>efflow</sub>


# BLM02AX Series (01005 Size)




High spec ferrite bead ultra low dc resistance 0402mm size.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	20000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range
BLM02AX100SN1□	10ohm ±5 ohm	750mA	0.07ohm max.	-55°C to +125°C
BLM02AX700SN1□	70ohm ±25%	300mA	0.4ohm max.	-55°C to +125°C
BLM02AX121SN1□	120ohm ±25%	250mA	0.5ohm max.	-55°C to +125°C


Number of Circuits: 1

## Impedance-Frequency Characteristics




## Impedance-Frequency Characteristics


BLM02AX100SN1



BLM02AX700SN1



BLM02AX121SN1



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Excellent for Both Signal and Power Lines. Multi Function Chip Ferrite Bead BLM□□AX Series

### Feature


- 1/2 the DC resistance than conventional type utilizing the latest technology
  - New ferrite material
  - Optimum ferrite firing condition
  - Fine piling technology
  - Advanced coil pattern design technology
- Improved stability of performance at heat shock
- Wide line-up from 10 to 1000ohm(@100MHz) useful for signal line

### Advantage


- High Rated Current
  - Good for miniaturization of high power equipment
- Lower Voltage down at Ferrite bead
  - Good for Battery driven equipment by saving running voltage margin
- Higher Reliability

#### Drastically Reduced DC Resistance

DC Resistance Comparison



#### Test Result - Heat Shock



△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# BLM03PG Series (0201 Size)




## 0201 size for power lines.


\*Please refer to the products designed for both power lines and signal lines.



### Dimensions



### Equivalent Circuit



### Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	15000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

### Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM03PG220SN1□	22ohm ±25%	900mA	0.065ohm max.	-55°C to +125°C	Kit
BLM03PG330SN1□	33ohm ±25%	750mA	0.090ohm max.	-55°C to +125°C	Kit


Number of Circuits: 1

### Impedance-Frequency Characteristics




### Impedance-Frequency Characteristics

BLM03PG220SN1



BLM03PG330SN1



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLM03PX Series (0201 Size)



Improved DC resistance meets larger current.



## Dimensions



## Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	15000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM03PX220SN1□	22ohm ±25%	1800mA	0.040ohm max.	-55°C to +125°C	Kit ≥1A
BLM03PX330SN1□	33ohm ±25%	1500mA	0.055ohm max.	-55°C to +125°C	Kit ≥1A
BLM03PX800SN1□	80ohm ±25%	1000mA	0.130ohm max.	-55°C to +125°C	Kit ≥1A

Number of Circuits: 1

## Impedance-Frequency Characteristics




## Notice (Rating)

In operating temperature exceeding +85°C derating of current is necessary for BLM03PX\_SN1 series.

Please apply the derating curve shown in chart according to the operating temperature.

### Derating of Rated Current




Continued on the following page.




## ■ Impedance-Frequency Characteristics


BLM03PX220SN1



BLM03PX330SN1



BLM03PX800SN1



0201 Size  
Chip Ferrite Bead

Chip EMIFIL®

Chip Common Mode Choke Coil

Block Type EMIFIL®

Microwave Absorber

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLM03AX Series (0201 Size)



High Spec Ferrite Bead Ultra low dc resistance and wide impedance line up. Fit for both power lines and signal lines.



## Dimensions



## Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	15000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## Rated Value (□: packaging code)


Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM03AX100SN1□	10ohm (Typ.)	1000mA	0.05ohm max.	-55°C to +125°C	Kit $\geq 1A$
BLM03AX800SN1□	80ohm $\pm 25\%$	500mA	0.18ohm max.	-55°C to +125°C	Kit
BLM03AX121SN1□	120ohm $\pm 25\%$	450mA	0.23ohm max.	-55°C to +125°C	Kit
BLM03AX241SN1□	240ohm $\pm 25\%$	350mA	0.38ohm max.	-55°C to +125°C	Kit
BLM03AX601SN1□	600ohm $\pm 25\%$	250mA	0.85ohm max.	-55°C to +125°C	Kit
BLM03AX102SN1□	1000ohm $\pm 25\%$	200mA	1.25ohm max.	-55°C to +125°C	Kit

Number of Circuits: 1

## Impedance-Frequency Characteristics



## Impedance-Frequency Characteristics




Continued on the following page.


⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


BLM03AX241SN1



BLM03AX601SN1



BLM03AX102SN1



0201 Size  
Chip Ferrite Bead

Chip EMIFIL®

Chip Common Mode Choke Coil

Block Type EMIFIL®

Microwave Absorber

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLM03AG Series (0201 Size)



0201 size for general signal lines.



## Dimensions



## Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	15000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## Rated Value (□: packaging code)


Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM03AG100SN1□	10ohm (Typ.)	500mA	0.1ohm max.	-55°C to +125°C	Kit
BLM03AG700SN1□	70ohm (Typ.)	200mA	0.4ohm max.	-55°C to +125°C	Kit
BLM03AG800SN1□	80ohm ±25%	200mA	0.4ohm max.	-55°C to +125°C	Kit
BLM03AG121SN1□	120ohm ±25%	200mA	0.5ohm max.	-55°C to +125°C	Kit
BLM03AG241SN1□	240ohm ±25%	200mA	0.8ohm max.	-55°C to +125°C	Kit
BLM03AG601SN1□	600ohm ±25%	100mA	1.5ohm max.	-55°C to +125°C	Kit
BLM03AG102SN1□	1000ohm ±25%	100mA	2.5ohm max.	-55°C to +125°C	Kit

Number of Circuits: 1

## Impedance-Frequency Characteristics



## Impedance-Frequency Characteristics




Continued on the following page.


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


BLM03AG121SN1




BLM03AG241SN1



BLM03AG601SN1



BLM03AG102SN1



0201 Size  
Chip Ferrite Bead

Chip EMIFIL®

Chip Common Mode Choke Coil

Block Type EMIFIL®

Microwave Absorber

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




# BLM03B Series (0201 Size)



0201 size for high speed signal lines.



## ■ Dimensions



## ■ Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	15000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000

Refer to pages from p.97 to p.100 for mounting information.


## ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM03BD750SN1□	75ohm ±25%	300mA	0.4ohm max.	-55°C to +125°C	Kit
BLM03BD121SN1□	120ohm ±25%	250mA	0.5ohm max.	-55°C to +125°C	Kit
BLM03BD241SN1□	240ohm ±25%	200mA	0.8ohm max.	-55°C to +125°C	Kit
BLM03BD471SN1□	470ohm ±25%	215mA	1.5ohm max.	-55°C to +125°C	Kit
BLM03BD601SN1□	600ohm ±25%	200mA	1.7ohm max.	-55°C to +125°C	Kit
BLM03BB100SN1□	10ohm ±25%	300mA	0.4ohm max.	-55°C to +125°C	Kit
BLM03BB220SN1□	22ohm ±25%	200mA	0.5ohm max.	-55°C to +125°C	Kit
BLM03BB470SN1□	47ohm ±25%	200mA	0.7ohm max.	-55°C to +125°C	Kit
BLM03BB750SN1□	75ohm ±25%	200mA	1.0ohm max.	-55°C to +125°C	Kit
BLM03BB121SN1□	120ohm ±25%	100mA	1.5ohm max.	-55°C to +125°C	Kit
BLM03BC330SN1□	33ohm ±25%	150mA	0.85ohm max.	-55°C to +125°C	Kit
BLM03BC560SN1□	56ohm ±25%	100mA	1.05ohm max.	-55°C to +125°C	Kit
BLM03BC800SN1□	80ohm ±25%	100mA	1.40ohm max.	-55°C to +125°C	Kit


Number of Circuits: 1

## ■ Impedance-Frequency Characteristics

### BLM03BD Series




### BLM03BB Series



Continued on the following page. ↗


⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Impedance-Frequency Characteristics  
BLM03BC Series




■ Impedance-Frequency Characteristics


BLM03BD750SN1




BLM03BD121SN1




BLM03BD241SN1




BLM03BD471SN1




BLM03BD601SN1




BLM03BB100SN1




BLM03BB220SN1




BLM03BB470SN1




BLM03BB750SN1




BLM03BB121SN1




BLM03BC330SN1



BLM03BC560SN1



BLM03BC800SN1




# BLM15PX Series (0402 Size)



3A max, high performance type for power lines up to 600ohm.



## Dimensions



## Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM15PX330SN1□	33ohm ±25%	3000mA	0.022ohm max.	-55°C to +125°C	New Kit ≥3A
BLM15PX600SN1□	60ohm ±25%	2500mA	0.032ohm max.	-55°C to +125°C	New Kit ≥1A
BLM15PX800SN1□	80ohm ±25%	2300mA	0.038ohm max.	-55°C to +125°C	New Kit ≥1A
BLM15PX121SN1□	120ohm ±25%	2000mA	0.055ohm max.	-55°C to +125°C	New Kit ≥1A
BLM15PX181SN1□	180ohm ±25%	1500mA	0.090ohm max.	-55°C to +125°C	New Kit ≥1A
BLM15PX221SN1□	220ohm ±25%	1400mA	0.10ohm max.	-55°C to +125°C	New Kit ≥1A
BLM15PX331SN1□	330ohm ±25%	1200mA	0.15ohm max.	-55°C to +125°C	New Kit ≥1A
BLM15PX471SN1□	470ohm ±25%	1000mA	0.20ohm max.	-55°C to +125°C	New Kit ≥1A
BLM15PX601SN1□	600ohm ±25%	900mA	0.23ohm max.	-55°C to +125°C	New Kit

Number of Circuits: 1

## Impedance-Frequency Characteristics




## Notice (Rating)

In operating temperature exceeding +85°C, derating of current is necessary for BLM15PX series.

Please apply the derating curve shown in chart according to the operating temperature.


### Derating of Rated Current




Continued on the following page.

## Impedance-Frequency Characteristics


BLM15PX330SN1




BLM15PX600SN1




BLM15PX800SN1




BLM15PX121SN1




BLM15PX181SN1




BLM15PX221SN1




BLM15PX331SN1



BLM15PX471SN1



BLM15PX601SN1



0402 Size  
Chip Ferrite Bead

Chip EMIFIL®

Chip Common Mode Choke Coil

Block Type EMIFIL®

Microwave Absorber

# BLM15PG/BLM15PD Series (0402 Size)




## 0402 size for power lines.

\*Please refer to the products which are designed for both power lines and signal lines.



### ■ Dimensions



### ■ Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM15PG100SN1□	10ohm (Typ.)	1000mA	0.025ohm max.	-55°C to +125°C	Kit ≥1A
BLM15PD300SN1□	30ohm ±25%	2200mA	0.035ohm max.	-55°C to +125°C	Kit ≥1A
BLM15PD600SN1□	60ohm ±25%	1700mA	0.06ohm max.	-55°C to +125°C	Kit ≥1A
BLM15PD800SN1□	80ohm ±25%	1500mA	0.07ohm max.	-55°C to +125°C	Kit ≥1A
BLM15PD121SN1□	120ohm ±25%	1300mA	0.09ohm max.	-55°C to +125°C	Kit ≥1A

Number of Circuits: 1

### ■ Impedance-Frequency Characteristics




### ■ Notice (Rating)

In operating temperature exceeding +85°C, derating of current is necessary for BLM15PD series.

Please apply the derating curve shown in chart according to the operating temperature.


Derating of Rated Current




Continued on the following page.

## Impedance-Frequency Characteristics


BLM15PG100SN1




BLM15PD300SN1




BLM15PD600SN1



BLM15PD800SN1



BLM15PD121SN1






# BLM15AX Series (0402 Size)



High Spec Ferrite Bead Ultra low dc resistance and wide impedance line up. Fit for both power lines and signal lines.



## ■ Dimensions



## ■ Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM15AX100SN1□	10ohm (Typ.)	1740mA	0.015ohm max.	-55°C to +125°C	Kit $\geq 1A$
BLM15AX300SN1□	30ohm $\pm 25\%$	1100mA	0.06ohm max.	-55°C to +125°C	Kit $\geq 1A$
BLM15AX700SN1□	70ohm $\pm 25\%$	780mA	0.1ohm max.	-55°C to +125°C	Kit
BLM15AX121SN1□	120ohm $\pm 25\%$	700mA	0.13ohm max.	-55°C to +125°C	Kit
BLM15AX221SN1□	220ohm $\pm 25\%$	600mA	0.18ohm max.	-55°C to +125°C	Kit
BLM15AX601SN1□	600ohm $\pm 25\%$	500mA	0.34ohm max.	-55°C to +125°C	Kit
BLM15AX102SN1□	1000ohm $\pm 25\%$	350mA	0.49ohm max.	-55°C to +125°C	Kit

Number of Circuits: 1


## ■ Impedance-Frequency Characteristics




Continued on the following page.

## Impedance-Frequency Characteristics


BLM15AX100SN1




BLM15AX300SN1




BLM15AX700SN1




BLM15AX121SN1




BLM15AX221SN1



BLM15AX601SN1



BLM15AX102SN1




# BLM15AG Series (0402 Size)



0402 size for general signal lines.



## Dimensions



## Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## Rated Value (□: packaging code)


Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM15AG100SN1□	10ohm (Typ.)	1000mA	0.025ohm max.	-55°C to +125°C	Kit ≥1A
BLM15AG700SN1□	70ohm (Typ.)	600mA	0.15ohm max.	-55°C to +125°C	Kit
BLM15AG121SN1□	120ohm ±25%	550mA	0.19ohm max.	-55°C to +125°C	Kit
BLM15AG221SN1□	220ohm ±25%	450mA	0.29ohm max.	-55°C to +125°C	Kit
BLM15AG601SN1□	600ohm ±25%	300mA	0.52ohm max.	-55°C to +125°C	Kit
BLM15AG102SN1□	1000ohm ±25%	300mA	0.65ohm max.	-55°C to +125°C	Kit

Number of Circuits: 1

## Impedance-Frequency Characteristics



## Impedance-Frequency Characteristics




Continued on the following page.


⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## ■ Impedance-Frequency Characteristics


BLM15AG221SN1



BLM15AG601SN1



BLM15AG102SN1



0402 Size  
Chip Ferrite Bead

Chip EMIFIL®

Chip Common Mode Choke Coil

Block Type EMIFIL®

Microwave Absorber

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLM15BX Series (0402 Size)



0402 size for high speed signal lines, low DC resistance.



## Dimensions



## Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM15BX750SN1□	75ohm ±25%	600mA	0.15ohm max.	-55°C to +125°C	New Kit
BLM15BX121SN1□	120ohm ±25%	600mA	0.17ohm max.	-55°C to +125°C	New Kit
BLM15BX221SN1□	220ohm ±25%	450mA	0.27ohm max.	-55°C to +125°C	New Kit
BLM15BX471SN1□	470ohm ±25%	350mA	0.41ohm max.	-55°C to +125°C	New Kit
BLM15BX601SN1□	600ohm ±25%	350mA	0.46ohm max.	-55°C to +125°C	New Kit
BLM15BX102SN1□	1000ohm ±25%	300mA	0.65ohm max.	-55°C to +125°C	New Kit
BLM15BX182SN1□	1800ohm ±25%	250mA	0.90ohm max.	-55°C to +125°C	New Kit

Number of Circuits: 1


## Impedance-Frequency Characteristics




Continued on the following page.

## ■ Impedance-Frequency Characteristics


BLM15BX750SN1




BLM15BX121SN1




BLM15BX221SN1




BLM15BX471SN1




BLM15BX601SN1



BLM15BX102SN1



BLM15BX182SN1






# BLM15B Series (0402 Size)



0402 size for high speed signal lines.



## ■ Dimensions



## ■ Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000

Refer to pages from p.97 to p.100 for mounting information.

## ■ Rated Value (□: packaging code)


Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM15BD750SN1□	75ohm ±25%	300mA	0.20ohm max.	-55°C to +125°C	Kit
BLM15BD121SN1□	120ohm ±25%	300mA	0.30ohm max.	-55°C to +125°C	Kit
BLM15BD221SN1□	220ohm ±25%	300mA	0.40ohm max.	-55°C to +125°C	Kit
BLM15BD471SN1□	470ohm ±25%	200mA	0.60ohm max.	-55°C to +125°C	Kit
BLM15BD601SN1□	600ohm ±25%	200mA	0.65ohm max.	-55°C to +125°C	Kit
BLM15BD102SN1□	1000ohm ±25%	200mA	0.90ohm max.	-55°C to +125°C	Kit
BLM15BD182SN1□	1800ohm ±25%	100mA	1.40ohm max.	-55°C to +125°C	Kit
BLM15BB050SN1□	5ohm ±25%	500mA	0.08ohm max.	-55°C to +125°C	Kit
BLM15BB100SN1□	10ohm ±25%	300mA	0.10ohm max.	-55°C to +125°C	Kit
BLM15BB220SN1□	22ohm ±25%	300mA	0.20ohm max.	-55°C to +125°C	Kit
BLM15BB470SN1□	47ohm ±25%	300mA	0.35ohm max.	-55°C to +125°C	Kit
BLM15BB750SN1□	75ohm ±25%	300mA	0.40ohm max.	-55°C to +125°C	Kit
BLM15BB121SN1□	120ohm ±25%	300mA	0.55ohm max.	-55°C to +125°C	Kit
BLM15BB221SN1□	220ohm ±25%	200mA	0.80ohm max.	-55°C to +125°C	Kit
BLM15BC121SN1□	120ohm ±25%	350mA	0.45ohm max.	-55°C to +125°C	Kit
BLM15BC241SN1□	240ohm ±25%	250mA	0.70ohm max.	-55°C to +125°C	Kit
BLM15BA050SN1□	5ohm ±25%	300mA	0.10ohm max.	-55°C to +125°C	Kit
BLM15BA100SN1□	10ohm ±25%	300mA	0.20ohm max.	-55°C to +125°C	Kit
BLM15BA220SN1□	22ohm ±25%	300mA	0.30ohm max.	-55°C to +125°C	Kit
BLM15BA330SN1□	33ohm ±25%	300mA	0.40ohm max.	-55°C to +125°C	Kit
BLM15BA470SN1□	47ohm ±25%	200mA	0.60ohm max.	-55°C to +125°C	Kit
BLM15BA750SN1□	75ohm ±25%	200mA	0.80ohm max.	-55°C to +125°C	Kit

Number of Circuits: 1


Continued on the following page.

## Impedance-Frequency Characteristics


### BLM15BD Series




### BLM15BB Series



### BLM15BC Series




### BLM15BA Series




## Impedance-Frequency Characteristics


### BLM15BD750SN1




### BLM15BD121SN1




### BLM15BD221SN1




### BLM15BD471SN1



### BLM15BD601SN1



### BLM15BD102SN1




Continued on the following page.


**Note** • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


BLM15BD182SN1




BLM15BB050SN1




BLM15BB100SN1




BLM15BB220SN1




BLM15BB470SN1




BLM15BB750SN1




BLM15BB121SN1




BLM15BB221SN1




BLM15BC121SN1




BLM15BC241SN1




BLM15BA050SN1




BLM15BA100SN1




BLM15BA220SN1



BLM15BA330SN1



BLM15BA470SN1




Continued on the following page.

⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## ■ Impedance-Frequency Characteristics

BLM15BA750SN1



0402 Size  
Chip Ferrite Bead

Chip EMIFIL®

Chip Common Mode Choke Coil

Block Type EMIFIL®

Microwave Absorber

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# BLM18P Series (0603 Size)




## 0603 size for power lines.

\*Please refer to the products designed for both power lines and signal lines.



### ■ Dimensions



### ■ Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM18PG300SN1□	30ohm (Typ.)	1000mA	0.05ohm max.	-55°C to +125°C	Kit $\geq 1A$
BLM18PG330SN1□	33ohm $\pm 25\%$	3000mA	0.025ohm max.	-55°C to +125°C	Kit $\geq 3A$
BLM18PG600SN1□	60ohm (Typ.)	500mA	0.10ohm max.	-55°C to +125°C	Kit
BLM18PG121SN1□	120ohm $\pm 25\%$	2000mA	0.05ohm max.	-55°C to +125°C	Kit $\geq 1A$
BLM18PG181SN1□	180ohm $\pm 25\%$	1500mA	0.09ohm max.	-55°C to +125°C	Kit $\geq 1A$
BLM18PG221SN1□	220ohm $\pm 25\%$	1400mA	0.10ohm max.	-55°C to +125°C	Kit $\geq 1A$
BLM18PG331SN1□	330ohm $\pm 25\%$	1200mA	0.15ohm max.	-55°C to +125°C	Kit $\geq 1A$
BLM18PG471SN1□	470ohm $\pm 25\%$	1000mA	0.20ohm max.	-55°C to +125°C	Kit $\geq 1A$

Number of Circuits: 1

### ■ Impedance-Frequency Characteristics




### ■ Notice (Rating)

In operating temperature exceeding +85°C, derating of current is necessary for BLM18PG series.

Please apply the derating curve shown in chart according to the operating temperature.


Derating of Rated Current




Continued on the following page.

## Impedance-Frequency Characteristics


BLM18PG300SN1




BLM18PG330SN1




BLM18PG600SN1




BLM18PG121SN1




BLM18PG181SN1




BLM18PG221SN1



BLM18PG331SN1



BLM18PG471SN1





# BLM18K Series (0603 Size)




6A max, high performance type for power lines up to 600ohm.


\*Please refer to the products designed for both power lines and signal lines.



## ■ Dimensions



## ■ Equivalent Circuit



## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range		
BLM18KG260TN1□	26ohm ±25%	6000mA	0.007ohm max.	-55°C to +125°C	Kit	≥3A
BLM18KG300TN1□	30ohm ±25%	5000mA	0.010ohm max.	-55°C to +125°C	Kit	≥3A
BLM18KG700TN1□	70ohm ±25%	3500mA	0.022ohm max.	-55°C to +125°C	Kit	≥3A
BLM18KG101TN1□	100ohm ±25%	3000mA	0.030ohm max.	-55°C to +125°C	Kit	≥3A
BLM18KG121TN1□	120ohm ±25%	3000mA	0.030ohm max.	-55°C to +125°C	Kit	≥3A
BLM18KG221SN1□	220ohm ±25%	2200mA	0.050ohm max.	-55°C to +125°C	Kit	≥1A
BLM18KG331SN1□	330ohm ±25%	1700mA	0.080ohm max.	-55°C to +125°C	Kit	≥1A
BLM18KG471SN1□	470ohm ±25%	1500mA	0.130ohm max.	-55°C to +125°C	Kit	≥1A
BLM18KG601SN1□	600ohm ±25%	1300mA	0.150ohm max.	-55°C to +125°C	Kit	≥1A

Number of Circuits: 1

## ■ Impedance-Frequency Characteristics




## ■ Notice (Rating)

In operating temperature exceeding +85°C, derating of current is necessary for BLM18KG series.

Please apply the derating curve shown in chart according to the operating temperature.

### Derating of Rated Current




Continued on the following page.


△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


BLM18KG260TN1




BLM18KG300TN1




BLM18KG700TN1




BLM18KG101TN1




BLM18KG121TN1




BLM18KG221SN1




BLM18KG331SN1



BLM18KG471SN1



BLM18KG601SN1



# BLM18S Series (0603 Size)




## 6A max, high performance type for power lines.


\*Please refer to the products designed for both power lines and signal lines.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
J	330mm Reel Paper Tape	30000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range		
BLM18SG260TN1□	26ohm ±25%	6000mA	0.007ohm max.	-55°C to +125°C	Kit	≥3A
BLM18SG700TN1□	70ohm ±25%	4000mA	0.020ohm max.	-55°C to +125°C	Kit	≥3A
BLM18SG121TN1□	120ohm ±25%	3000mA	0.025ohm max.	-55°C to +125°C	Kit	≥3A
BLM18SG221TN1□	220ohm ±25%	2500mA	0.040ohm max.	-55°C to +125°C	Kit	≥1A
BLM18SG331TN1□	330ohm ±25%	1500mA	0.070ohm max.	-55°C to +125°C	Kit	≥1A

Number of Circuits: 1

### ■ Impedance-Frequency Characteristics




### ■ Notice (Rating)

In operating temperature exceeding +85°C, derating of current is necessary for BLM18SG series.

Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current




Continued on the following page.


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## ■ Impedance-Frequency Characteristics


BLM18SG260TN1




BLM18SG700TN1




BLM18SG121TN1



BLM18SG221TN1



BLM18SG331TN1



# BLM18A Series (0603 Size)




## 0603 size for general signal lines.

\*Please refer to BLM15A for downsizing.



### ■ Dimensions



### ■ Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM18AG121SN1□	120ohm $\pm 25\%$	500mA	0.18ohm max.	-55°C to +125°C	Kit
BLM18AG151SN1□	150ohm $\pm 25\%$	500mA	0.25ohm max.	-55°C to +125°C	Kit
BLM18AG221SN1□	220ohm $\pm 25\%$	500mA	0.25ohm max.	-55°C to +125°C	Kit
BLM18AG331SN1□	330ohm $\pm 25\%$	500mA	0.30ohm max.	-55°C to +125°C	Kit
BLM18AG471SN1□	470ohm $\pm 25\%$	500mA	0.35ohm max.	-55°C to +125°C	Kit
BLM18AG601SN1□	600ohm $\pm 25\%$	500mA	0.38ohm max.	-55°C to +125°C	Kit
BLM18AG102SN1□	1000ohm $\pm 25\%$	400mA	0.50ohm max.	-55°C to +125°C	Kit


Number of Circuits: 1

### ■ Impedance-Frequency Characteristics




### ■ Impedance-Frequency Characteristics


BLM18AG121SN1



BLM18AG151SN1



BLM18AG221SN1




Continued on the following page.


⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## ■ Impedance-Frequency Characteristics


BLM18AG331SN1




BLM18AG471SN1



BLM18AG601SN1



BLM18AG102SN1





# BLM18B Series (0603 Size)




## 0603 size for high speed signal lines.

\*Please refer to BLM15B for downsizing.



### ■ Dimensions



### ■ Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000

Refer to pages from p.97 to p.100 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM18BD470SN1□	47ohm $\pm 25\%$	500mA	0.30ohm max.	-55°C to +125°C	Kit
BLM18BD121SN1□	120ohm $\pm 25\%$	200mA	0.40ohm max.	-55°C to +125°C	Kit
BLM18BD151SN1□	150ohm $\pm 25\%$	200mA	0.40ohm max.	-55°C to +125°C	Kit
BLM18BD221SN1□	220ohm $\pm 25\%$	200mA	0.45ohm max.	-55°C to +125°C	Kit
BLM18BD331SN1□	330ohm $\pm 25\%$	200mA	0.50ohm max.	-55°C to +125°C	Kit
BLM18BD421SN1□	420ohm $\pm 25\%$	200mA	0.55ohm max.	-55°C to +125°C	Kit
BLM18BD471SN1□	470ohm $\pm 25\%$	200mA	0.55ohm max.	-55°C to +125°C	Kit
BLM18BD601SN1□	600ohm $\pm 25\%$	200mA	0.65ohm max.	-55°C to +125°C	Kit
BLM18BD102SN1□	1000ohm $\pm 25\%$	100mA	0.85ohm max.	-55°C to +125°C	Kit
BLM18BD152SN1□	1500ohm $\pm 25\%$	50mA	1.20ohm max.	-55°C to +125°C	Kit
BLM18BD182SN1□	1800ohm $\pm 25\%$	50mA	1.50ohm max.	-55°C to +125°C	Kit
BLM18BD222SN1□	2200ohm $\pm 25\%$	50mA	1.50ohm max.	-55°C to +125°C	Kit
BLM18BD252SN1□	2500ohm $\pm 25\%$	50mA	1.50ohm max.	-55°C to +125°C	Kit
BLM18BB050SN1□	5ohm $\pm 25\%$	700mA	0.05ohm max.	-55°C to +125°C	Kit
BLM18BB100SN1□	10ohm $\pm 25\%$	700mA	0.10ohm max.	-55°C to +125°C	Kit
BLM18BB220SN1□	22ohm $\pm 25\%$	600mA	0.20ohm max.	-55°C to +125°C	Kit
BLM18BB470SN1□	47ohm $\pm 25\%$	550mA	0.25ohm max.	-55°C to +125°C	Kit
BLM18BB600SN1□	60ohm $\pm 25\%$	550mA	0.25ohm max.	-55°C to +125°C	Kit
BLM18BB750SN1□	75ohm $\pm 25\%$	500mA	0.30ohm max.	-55°C to +125°C	Kit
BLM18BB121SN1□	120ohm $\pm 25\%$	500mA	0.30ohm max.	-55°C to +125°C	Kit
BLM18BB141SN1□	140ohm $\pm 25\%$	450mA	0.35ohm max.	-55°C to +125°C	
BLM18BB151SN1□	150ohm $\pm 25\%$	450mA	0.37ohm max.	-55°C to +125°C	Kit
BLM18BB221SN1□	220ohm $\pm 25\%$	450mA	0.45ohm max.	-55°C to +125°C	Kit
BLM18BB331SN1□	330ohm $\pm 25\%$	400mA	0.58ohm max.	-55°C to +125°C	Kit
BLM18BB471SN1□	470ohm $\pm 25\%$	300mA	0.85ohm max.	-55°C to +125°C	Kit
BLM18BA050SN1□	5ohm $\pm 25\%$	500mA	0.20ohm max.	-55°C to +125°C	Kit
BLM18BA100SN1□	10ohm $\pm 25\%$	500mA	0.25ohm max.	-55°C to +125°C	Kit
BLM18BA220SN1□	22ohm $\pm 25\%$	500mA	0.35ohm max.	-55°C to +125°C	
BLM18BA470SN1□	47ohm $\pm 25\%$	300mA	0.55ohm max.	-55°C to +125°C	Kit
BLM18BA750SN1□	75ohm $\pm 25\%$	300mA	0.70ohm max.	-55°C to +125°C	Kit
BLM18BA121SN1□	120ohm $\pm 25\%$	200mA	0.90ohm max.	-55°C to +125°C	Kit


Number of Circuits: 1

Continued on the following page.


△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


### BLM18BD Series (47ohm to 420ohm)




### BLM18BD Series (470ohm to 2500ohm)




### BLM18BB Series (5ohm to 75ohm)




### BLM18BB Series (120ohm to 470ohm)



### BLM18BA Series (5ohm to 220ohm)




### BLM18BA Series (47ohm to 120ohm)




## Impedance-Frequency Characteristics


### BLM18BD470SN1



### BLM18BD121SN1



### BLM18BD151SN1




Continued on the following page.


**Note** • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


BLM18BD221SN1




BLM18BD331SN1




BLM18BD421SN1




BLM18BD471SN1




BLM18BD601SN1




BLM18BD102SN1




BLM18BD152SN1




BLM18BD182SN1




BLM18BD222SN1




BLM18BD252SN1




BLM18BB050SN1




BLM18BB100SN1




BLM18BB220SN1



BLM18BB470SN1



BLM18BB600SN1



Continued on the following page.

⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Chip Ferrite Bead  
0603 Size

Chip EMIFIL®


Chip Common Mode Choke Coil

Block Type EMIFIL®


Microwave Absorber

## Impedance-Frequency Characteristics


BLM18BB750SN1




BLM18BB121SN1




BLM18BB141SN1




BLM18BB151SN1




BLM18BB221SN1




BLM18BB331SN1




BLM18BB471SN1




BLM18BA050SN1




BLM18BA100SN1




BLM18BA220SN1




BLM18BA470SN1



BLM18BA750SN1



BLM18BA121SN1




# BLM18T Series (0603 Size)



Thin 0603 size for general signal lines.



## ■ Dimensions



## ■ Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range
BLM18TG121TN1□	120ohm ±25%	200mA	0.25ohm max.	-55°C to +125°C
BLM18TG221TN1□	220ohm ±25%	200mA	0.30ohm max.	-55°C to +125°C
BLM18TG601TN1□	600ohm ±25%	200mA	0.45ohm max.	-55°C to +125°C
BLM18TG102TN1□	1000ohm ±25%	100mA	0.60ohm max.	-55°C to +125°C


Number of Circuits: 1

## ■ Impedance-Frequency Characteristics




## ■ Impedance-Frequency Characteristics


### BLM18TG121TN1




### BLM18TG221TN1



### BLM18TG601TN1



### BLM18TG102TN1



⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLM18R Series (0603 Size)




For digital I/F. Reduces the distortion of waveform created by resonance.



## ■ Dimensions



## ■ Equivalent Circuit



## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## ■ Rated Value (□: packaging code)


Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM18RK121SN1□	120ohm $\pm 25\%$	200mA	0.25ohm max.	-55°C to +125°C	Kit
BLM18RK221SN1□	220ohm $\pm 25\%$	200mA	0.30ohm max.	-55°C to +125°C	
BLM18RK471SN1□	470ohm $\pm 25\%$	200mA	0.50ohm max.	-55°C to +125°C	Kit
BLM18RK601SN1□	600ohm $\pm 25\%$	200mA	0.60ohm max.	-55°C to +125°C	Kit
BLM18RK102SN1□	1000ohm $\pm 25\%$	200mA	0.80ohm max.	-55°C to +125°C	Kit

Number of Circuits: 1

## ■ Impedance-Frequency Characteristics



## ■ Impedance-Frequency Characteristics




Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




## ■ Impedance-Frequency Characteristics

BLM18RK601SN1




BLM18RK102SN1



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Waveform Distortion Suppressing Performance of BLM□□R Series

### Measuring Circuits




#### Type of Filter


#### EMI Suppression Effect / Description

##### Initial (No filter)


##### Signal waveform (100nsec/div, 2V/div)



##### Expand (10nsec/div, 2V/div)



##### Spectrum




Ringing is caused on the signal waveform.


Such ringing contains several hundred MHz harmonic components and generates noise.

##### Resistor (47Ω) is used


##### Signal waveform (100nsec/div, 2V/div)



##### Expand (10nsec/div, 2V/div)



##### Spectrum




Comparing initial waveform, ringing is suppressed a little.


However, high level waveform distortion still remains.

##### BLM18RK221SN1 (220Ω at 100MHz) is used


##### Signal waveform (100nsec/div, 2V/div)



##### Expand (10nsec/div, 2V/div)



##### Spectrum



BLM18R has excellent performance for noise suppression and waveform distortion suppression.

BLM18R suppresses drastically not only the spectrum level in more than 100MHz range but waveform distortion.

# BLM21P Series (0805 Size)




## 0805 size for power lines.

\*Please refer to the products designed for both power lines and signal lines. \*Please refer to BLM18K for downsizing.



### Dimensions



### Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

### Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

### Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range		
BLM21PG220SN1□	22ohm ±25%	6000mA	0.009ohm max.	-55°C to +125°C	Kit	≥3A
BLM21PG300SN1□	30ohm (Typ.)	4000mA	0.014ohm max.	-55°C to +125°C	Kit	≥3A
BLM21PG600SN1□	60ohm ±25%	3500mA	0.02ohm max.	-55°C to +125°C	Kit	≥3A
BLM21PG121SN1□	120ohm ±25%	3000mA	0.03ohm max.	-55°C to +125°C	Kit	≥3A
BLM21PG221SN1□	220ohm ±25%	2000mA	0.045ohm max.	-55°C to +125°C	Kit	≥1A
BLM21PG331SN1□	330ohm ±25%	1500mA	0.07ohm max.	-55°C to +125°C	Kit	≥1A

Number of Circuits: 1

### Impedance-Frequency Characteristics




### Notice (Rating)

In operating temperature exceeding +85°C, derating of current is necessary for BLM21PG series.

Please apply the derating curve shown in chart according to the operating temperature.

#### Derating of Rated Current




Continued on the following page.


△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## ■ Impedance-Frequency Characteristics


BLM21PG220SN1




BLM21PG300SN1




BLM21PG600SN1




BLM21PG121SN1



BLM21PG221SN1



BLM21PG331SN1



0805 Size  
Chip Ferrite Bead

Chip EMIFIL®

Chip Common Mode Choke Coil

Block Type EMIFIL®

Microwave Absorber

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLM21A Series (0805 Size)



0805 size for general signal lines.



## Dimensions



## Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM21AG121SN1□	120ohm ±25%	800mA	0.10ohm max.	-55°C to +125°C	Kit
BLM21AG151SN1□	150ohm ±25%	800mA	0.10ohm max.	-55°C to +125°C	Kit
BLM21AG221SN1□	220ohm ±25%	800mA	0.13ohm max.	-55°C to +125°C	Kit
BLM21AG331SN1□	330ohm ±25%	700mA	0.16ohm max.	-55°C to +125°C	Kit
BLM21AG471SN1□	470ohm ±25%	700mA	0.19ohm max.	-55°C to +125°C	Kit
BLM21AG601SN1□	600ohm ±25%	600mA	0.21ohm max.	-55°C to +125°C	Kit
BLM21AG102SN1□	1000ohm ±25%	500mA	0.28ohm max.	-55°C to +125°C	Kit


Number of Circuits: 1

## Impedance-Frequency Characteristics




## Impedance-Frequency Characteristics


BLM21AG121SN1



BLM21AG151SN1



BLM21AG221SN1




Continued on the following page.


⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


BLM21AG331SN1




BLM21AG471SN1



BLM21AG601SN1



BLM21AG102SN1




# BLM21B Series (0805 Size)



0805 size for high speed signal lines.



## ■ Dimensions



## ■ Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## ■ Packaging

• All except for BLM21BD222SN1/21BD272SN1

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000

• BLM21BD222SN1/21BD272SN1 only

Code	Packaging	Minimum Quantity
L	180mm Reel Plastic Tape	3000
K	330mm Reel Plastic Tape	10000
B	Bulk(Bag)	1000

Refer to pages from p.97 to p.100 for mounting information.

## ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM21BD121SN1□	120ohm ±25%	200mA	0.25ohm max.	-55°C to +125°C	Kit
BLM21BD151SN1□	150ohm ±25%	200mA	0.25ohm max.	-55°C to +125°C	
BLM21BD221SN1□	220ohm ±25%	200mA	0.25ohm max.	-55°C to +125°C	Kit
BLM21BD331SN1□	330ohm ±25%	200mA	0.30ohm max.	-55°C to +125°C	
BLM21BD421SN1□	420ohm ±25%	200mA	0.30ohm max.	-55°C to +125°C	Kit
BLM21BD471SN1□	470ohm ±25%	200mA	0.35ohm max.	-55°C to +125°C	Kit
BLM21BD601SN1□	600ohm ±25%	200mA	0.35ohm max.	-55°C to +125°C	Kit
BLM21BD751SN1□	750ohm ±25%	200mA	0.40ohm max.	-55°C to +125°C	
BLM21BD102SN1□	1000ohm ±25%	200mA	0.40ohm max.	-55°C to +125°C	Kit
BLM21BD152SN1□	1500ohm ±25%	200mA	0.45ohm max.	-55°C to +125°C	Kit
BLM21BD182SN1□	1800ohm ±25%	200mA	0.50ohm max.	-55°C to +125°C	Kit
BLM21BD222TN1□	2200ohm ±25%	200mA	0.60ohm max.	-55°C to +125°C	Kit
BLM21BD222SN1□	2250ohm (Typ.)	200mA	0.60ohm max.	-55°C to +125°C	Kit
BLM21BD272SN1□	2700ohm ±25%	200mA	0.80ohm max.	-55°C to +125°C	Kit
BLM21BB050SN1□	5ohm ±25%	1000mA	0.02ohm max.	-55°C to +125°C	Kit
BLM21BB600SN1□	60ohm ±25%	800mA	0.13ohm max.	-55°C to +125°C	Kit
BLM21BB750SN1□	75ohm ±25%	700mA	0.16ohm max.	-55°C to +125°C	Kit
BLM21BB121SN1□	120ohm ±25%	600mA	0.19ohm max.	-55°C to +125°C	Kit
BLM21BB151SN1□	150ohm ±25%	600mA	0.21ohm max.	-55°C to +125°C	
BLM21BB201SN1□	200ohm ±25%	500mA	0.26ohm max.	-55°C to +125°C	
BLM21BB221SN1□	220ohm ±25%	500mA	0.26ohm max.	-55°C to +125°C	Kit
BLM21BB331SN1□	330ohm ±25%	400mA	0.33ohm max.	-55°C to +125°C	Kit
BLM21BB471SN1□	470ohm ±25%	400mA	0.40ohm max.	-55°C to +125°C	Kit


Number of Circuits: 1

Continued on the following page.




## Impedance-Frequency Characteristics

### BLM21BD Series




### BLM21BB Series




## Impedance-Frequency Characteristics


### BLM21BD121SN1




### BLM21BD151SN1




### BLM21BD221SN1




### BLM21BD331SN1




### BLM21BD421SN1




### BLM21BD471SN1




### BLM21BD601SN1



### BLM21BD751SN1



### BLM21BD102SN1




Continued on the following page.


**Note** • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


BLM21BD152SN1




BLM21BD182SN1




BLM21BD222TN1




BLM21BD222SN1




BLM21BD272SN1




BLM21BB050SN1




BLM21BB600SN1




BLM21BB750SN1




BLM21BB121SN1




BLM21BB151SN1




BLM21BB201SN1




BLM21BB221SN1



BLM21BB331SN1



BLM21BB471SN1



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLM21R Series (0805 Size)




For digital I/F. Reduces the distortion of waveform created by resonance.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## Rated Value (□: packaging code)


Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range
BLM21RK121SN1□	120ohm ±25%	200mA	0.15ohm max.	-55°C to +125°C
BLM21RK221SN1□	220ohm ±25%	200mA	0.20ohm max.	-55°C to +125°C
BLM21RK471SN1□	470ohm ±25%	200mA	0.25ohm max.	-55°C to +125°C
BLM21RK601SN1□	600ohm ±25%	200mA	0.30ohm max.	-55°C to +125°C
BLM21RK102SN1□	1000ohm ±25%	200mA	0.50ohm max.	-55°C to +125°C

Number of Circuits: 1

## Impedance-Frequency Characteristics



## Impedance-Frequency Characteristics




Continued on the following page.


**Note** • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics

BLM21RK601SN1



BLM21RK102SN1



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# BLM31P Series (1206 Size)




## 1206 size for power lines.


\*Please refer to the products designed for both power lines and signal lines.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	3000
K	330mm Reel Embossed Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range		
BLM31PG330SN1□	33ohm $\pm 25\%$	6000mA	0.009ohm max.	-55°C to +125°C	Kit	$\geq 3A$
BLM31PG500SN1□	50ohm (Typ.)	3500mA	0.015ohm max.	-55°C to +125°C	Kit	$\geq 3A$
BLM31PG121SN1□	120ohm $\pm 25\%$	3500mA	0.02ohm max.	-55°C to +125°C	Kit	$\geq 3A$
BLM31PG391SN1□	390ohm $\pm 25\%$	2000mA	0.05ohm max.	-55°C to +125°C	Kit	$\geq 1A$
BLM31PG601SN1□	600ohm $\pm 25\%$	1500mA	0.08ohm max.	-55°C to +125°C	Kit	$\geq 1A$

Number of Circuits: 1

### ■ Impedance-Frequency Characteristics




### ■ Notice (Rating)

In operating temperature exceeding +85°C, derating of current is necessary for BLM31PG series.

Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current




Continued on the following page.


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


BLM31PG330SN1




BLM31PG500SN1




BLM31PG121SN1



BLM31PG391SN1



BLM31PG601SN1



# BLM41P Series (1806 Size)




## 1806 size for power lines.


\*Please refer to the products designed for both power lines and signal lines.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	2500
K	330mm Reel Embossed Tape	8000
B	Bulk(Bag)	1000

Refer to pages from p.97 to p.100 for mounting information.


### ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range		
BLM41PG600SN1□	60ohm (Typ.)	6000mA	0.009ohm max.	-55°C to +125°C	Kit	≥3A
BLM41PG750SN1□	75ohm (Typ.)	3500mA	0.015ohm max.	-55°C to +125°C	Kit	≥3A
BLM41PG181SN1□	180ohm ±25%	3500mA	0.02ohm max.	-55°C to +125°C	Kit	≥3A
BLM41PG471SN1□	470ohm ±25%	2000mA	0.05ohm max.	-55°C to +125°C	Kit	≥1A
BLM41PG102SN1□	1000ohm ±25%	1500mA	0.09ohm max.	-55°C to +125°C	Kit	≥1A


Number of Circuits: 1

### ■ Impedance-Frequency Characteristics

#### BLM41PG Series (60ohm to 75ohm)



#### BLM41PG Series (180ohm to 1000ohm)




### ■ Notice (Rating)

In operating temperature exceeding +85°C, derating of current is necessary for BLM41PG series.

Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current




Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




## Impedance-Frequency Characteristics


BLM41PG600SN1




BLM41PG750SN1




BLM41PG181SN1



BLM41PG471SN1



BLM41PG102SN1



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLA2AA/BLA2AB Series (0804 Size)




4-line array, 0804 size.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000

Refer to pages from p.97 to p.100 for mounting information.


## Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range
BLA2AAG121SN4□	120ohm ±25%	100mA	0.50ohm max.	-55°C to +125°C
BLA2AAG221SN4□	220ohm ±25%	50mA	0.70ohm max.	-55°C to +125°C
BLA2AAG601SN4□	600ohm ±25%	50mA	1.10ohm max.	-55°C to +125°C
BLA2AAG102SN4□	1000ohm ±25%	50mA	1.30ohm max.	-55°C to +125°C
BLA2ABD750SN4□	75ohm ±25%	200mA	0.20ohm max.	-55°C to +125°C
BLA2ABD121SN4□	120ohm ±25%	200mA	0.35ohm max.	-55°C to +125°C
BLA2ABD221SN4□	220ohm ±25%	100mA	0.40ohm max.	-55°C to +125°C
BLA2ABD471SN4□	470ohm ±25%	100mA	0.65ohm max.	-55°C to +125°C
BLA2ABD601SN4□	600ohm ±25%	100mA	0.80ohm max.	-55°C to +125°C
BLA2ABD102SN4□	1000ohm ±25%	50mA	1.00ohm max.	-55°C to +125°C
BLA2ABB100SN4□	10ohm ±25%	200mA	0.1ohm max.	-55°C to +125°C
BLA2ABB220SN4□	22ohm ±25%	200mA	0.2ohm max.	-55°C to +125°C
BLA2ABB470SN4□	47ohm ±25%	200mA	0.35ohm max.	-55°C to +125°C
BLA2ABB121SN4□	120ohm ±25%	50mA	0.60ohm max.	-55°C to +125°C
BLA2ABB221SN4□	220ohm ±25%	50mA	0.90ohm max.	-55°C to +125°C


Number of Circuits: 4

## Impedance-Frequency Characteristics

### BLA2AAG Series




### BLA2ABD Series



Continued on the following page.


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics BLA2ABB Series




## Impedance-Frequency Characteristics


BLA2AAG121SN4




BLA2AAG221SN4




BLA2AAG601SN4




BLA2AAG102SN4




BLA2ABD750SN4




BLA2ABD121SN4




BLA2ABD221SN4



BLA2ABD471SN4



BLA2ABD601SN4




Continued on the following page.


⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


BLA2ABD102SN4




BLA2ABB100SN4




BLA2ABB220SN4




BLA2ABB470SN4



BLA2ABB121SN4



BLA2ABB221SN4



0804 Size  
Chip Ferrite Bead

Chip EMIFIL®

Chip Common Mode Choke Coil

Block Type EMIFIL®

Microwave Absorber

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLA31A/BLA31B Series (1206 Size)




## 4-line array, 1206 size.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

### ■ Rated Value (□: packaging code)


Part Number	Impedance (at 100MHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range
BLA31AG300SN4□	30ohm ±25%	200mA	0.10ohm max.	-55°C to +125°C
BLA31AG600SN4□	60ohm ±25%	200mA	0.15ohm max.	-55°C to +125°C
BLA31AG121SN4□	120ohm ±25%	150mA	0.20ohm max.	-55°C to +125°C
BLA31AG221SN4□	220ohm ±25%	150mA	0.25ohm max.	-55°C to +125°C
BLA31AG601SN4□	600ohm ±25%	100mA	0.35ohm max.	-55°C to +125°C
BLA31AG102SN4□	1000ohm ±25%	50mA	0.45ohm max.	-55°C to +125°C
BLA31BD121SN4□	120ohm ±25%	150mA	0.30ohm max.	-55°C to +125°C
BLA31BD221SN4□	220ohm ±25%	150mA	0.35ohm max.	-55°C to +125°C
BLA31BD471SN4□	470ohm ±25%	100mA	0.40ohm max.	-55°C to +125°C
BLA31BD601SN4□	600ohm ±25%	100mA	0.45ohm max.	-55°C to +125°C
BLA31BD102SN4□	1000ohm ±25%	50mA	0.55ohm max.	-55°C to +125°C

Number of Circuits: 4

### ■ Impedance-Frequency Characteristics BLA31AG Series




### BLA31BD Series




Continued on the following page.

## Impedance-Frequency Characteristics


BLA31AG300SN4




BLA31AG600SN4




BLA31AG121SN4




BLA31AG221SN4




BLA31AG601SN4




BLA31AG102SN4




BLA31BD121SN4




BLA31BD221SN4




BLA31BD471SN4



BLA31BD601SN4



BLA31BD102SN4



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLM03H Series (0201 Size)



0201 size for GHz band noise.



## ■ Dimensions



## ■ Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	15000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000

Refer to pages from p.97 to p.100 for mounting information.


## ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Impedance (at 1GHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM03HG601SN1□	600ohm ±25%	1000ohm ±40%	150mA	1.6ohm max.	-55°C to +125°C	Kit
BLM03HG102SN1□	1000ohm ±25%	1800ohm ±40%	125mA	2.6ohm max.	-55°C to +125°C	Kit
BLM03HD331SN1□	330ohm ±25%	750ohm ±40%	200mA	1.0ohm max.	-55°C to +125°C	Kit
BLM03HD471SN1□	470ohm ±25%	1000ohm ±40%	175mA	1.3ohm max.	-55°C to +125°C	Kit
BLM03HD601SN1□	600ohm ±25%	1500ohm ±40%	150mA	1.7ohm max.	-55°C to +125°C	Kit
BLM03HD102SN1□	1000ohm ±25%	2300ohm ±40%	120mA	2.9ohm max.	-55°C to +125°C	Kit
BLM03HB191SN1□	190ohm ±25%	1150ohm ±40%	150mA	2.0ohm max.	-55°C to +125°C	New Kit


Number of Circuits: 1

## ■ Impedance-Frequency Characteristics


### BLM03HG Series



### BLM03HD Series



### BLM03HB Series




Continued on the following page.

▲Note • Please read rating and ▲CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




## Impedance-Frequency Characteristics


BLM03HG601SN1




BLM03HG102SN1




BLM03HD331SN1




BLM03HD471SN1




BLM03HD601SN1



BLM03HD102SN1



BLM03HB191SN1




# BLM03E Series (0201 Size)




For GHz band noise and capable of large current.



## ■ Dimensions



## ■ Equivalent Circuit



## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	15000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Impedance (at 1GHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM03EB250SN1□	25ohm ±25%	105ohm ±40%	600mA	0.26ohm max.	-55°C to +125°C	New Kit
BLM03EB500SN1□	50ohm ±25%	255ohm ±40%	400mA	0.58ohm max.	-55°C to +125°C	New Kit

Number of Circuits: 1


## ■ Impedance-Frequency Characteristics



## ■ Notice (Rating)


In operating temperature exceeding +85°C, derating of current is necessary for BLM03E series.  
Please apply the derating curve shown in chart according to the operating temperature.

### Derating of Rated Current




## ■ Impedance-Frequency Characteristics

### BLM03EB250SN1



### BLM03EB500SN1



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLM15H Series (0402 Size)



0402 size for GHz band noise.



## Dimensions



## Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000

Refer to pages from p.97 to p.100 for mounting information.


## Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Impedance (at 1GHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM15HG601SN1□	600ohm ±25%	1000ohm ±40%	300mA	0.7ohm max.	-55°C to +125°C	Kit
BLM15HG102SN1□	1000ohm ±25%	1400ohm ±40%	250mA	1.1ohm max.	-55°C to +125°C	Kit
BLM15HD601SN1□	600ohm ±25%	1400ohm ±40%	300mA	0.85ohm max.	-55°C to +125°C	Kit
BLM15HD102SN1□	1000ohm ±25%	2000ohm ±40%	250mA	1.25ohm max.	-55°C to +125°C	Kit
BLM15HD182SN1□	1800ohm ±25%	2700ohm ±40%	200mA	2.2ohm max.	-55°C to +125°C	Kit
BLM15HB121SN1□	120ohm ±25%	500ohm ±40%	300mA	0.7ohm max.	-55°C to +125°C	Kit
BLM15HB221SN1□	220ohm ±25%	900ohm ±40%	250mA	1.0ohm max.	-55°C to +125°C	Kit


Number of Circuits: 1

## Impedance-Frequency Characteristics


### BLM15HG Series (For General Signal Lines)



### BLM15HD Series (For High Speed Signal Lines)



### BLM15HB Series (For High Speed Signal Lines)




Continued on the following page.


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


BLM15HG601SN1




BLM15HG102SN1




BLM15HD601SN1




BLM15HD102SN1




BLM15HD182SN1



BLM15HB121SN1



BLM15HB221SN1



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLM15E Series (0402 Size)




For GHz band noise, also capable to large current.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Impedance (at 1GHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM15EG121SN1□	120ohm ±25%	145ohm (Typ.)	1500mA	0.095ohm max.	-55°C to +125°C	Kit ≥1A
BLM15EG221SN1□	220ohm ±25%	270ohm (Typ.)	700mA	0.28ohm max.	-55°C to +125°C	Kit

Number of Circuits: 1


## Impedance-Frequency Characteristics



## Notice (Rating)


In operating temperature exceeding +85°C, derating of current is necessary for BLM15E series.  
Please apply the derating curve shown in chart according to the operating temperature.

### Derating of Rated Current




## Impedance-Frequency Characteristics

### BLM15EG121SN1



### BLM15EG221SN1




# BLM15G Series (0402 Size)



Available up to high-GHz band noise.



## ■ Dimensions



## ■ Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
J	330mm Reel Paper Tape	50000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## ■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Impedance (at 1GHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM15GG221SN1□	220ohm ±25%	600ohm ±40%	300mA	0.7ohm max.	-55°C to +125°C	Kit
BLM15GG471SN1□	470ohm ±25%	1200ohm ±40%	200mA	1.3ohm max.	-55°C to +125°C	Kit
BLM15GA750SN1□	75ohm ±25%	1000ohm ±40%	200mA	1.3ohm max.	-55°C to +125°C	Kit


Number of Circuits: 1

## ■ Impedance-Frequency Characteristics




## ■ Impedance-Frequency Characteristics


BLM15GG221SN1



BLM15GG471SN1



BLM15GA750SN1



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# BLM18H Series (0603 Size)




0603 size for GHz band noise. BLM18HE also supports power lines.

\*Please refer to BLM15H for downsizing.



## Dimensions



## Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000

Refer to pages from p.97 to p.100 for mounting information.


## Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Impedance (at 1GHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM18HG471SN1□	470ohm ±25%	600ohm (Typ.)	200mA	0.85ohm max.	-55°C to +125°C	Kit
BLM18HG601SN1□	600ohm ±25%	700ohm (Typ.)	200mA	1.00ohm max.	-55°C to +125°C	Kit
BLM18HG102SN1□	1000ohm ±25%	1000ohm (Typ.)	100mA	1.60ohm max.	-55°C to +125°C	Kit
BLM18HE601SN1□	600ohm ±25%	600ohm (Typ.)	800mA	0.25ohm max.	-55°C to +125°C	Kit
BLM18HE102SN1□	1000ohm ±25%	1000ohm (Typ.)	600mA	0.35ohm max.	-55°C to +125°C	Kit
BLM18HE152SN1□	1500ohm ±25%	1500ohm (Typ.)	500mA	0.50ohm max.	-55°C to +125°C	Kit
BLM18HD471SN1□	470ohm ±25%	1000ohm (Typ.)	100mA	1.20ohm max.	-55°C to +125°C	Kit
BLM18HD601SN1□	600ohm ±25%	1200ohm (Typ.)	100mA	1.50ohm max.	-55°C to +125°C	Kit
BLM18HD102SN1□	1000ohm ±25%	1700ohm (Typ.)	50mA	1.80ohm max.	-55°C to +125°C	Kit
BLM18HB121SN1□	120ohm ±25%	500ohm ±40%	200mA	0.50ohm max.	-55°C to +125°C	Kit
BLM18HB221SN1□	220ohm ±25%	1100ohm ±40%	100mA	0.80ohm max.	-55°C to +125°C	Kit
BLM18HB331SN1□	330ohm ±25%	1600ohm ±40%	50mA	1.20ohm max.	-55°C to +125°C	Kit
BLM18HK331SN1□	330ohm ±25%	400ohm ±40%	200mA	0.50ohm max.	-55°C to +125°C	Kit
BLM18HK471SN1□	470ohm ±25%	600ohm ±40%	200mA	0.70ohm max.	-55°C to +125°C	Kit
BLM18HK601SN1□	600ohm ±25%	700ohm ±40%	100mA	0.90ohm max.	-55°C to +125°C	Kit
BLM18HK102SN1□	1000ohm ±25%	1200ohm ±40%	50mA	1.50ohm max.	-55°C to +125°C	Kit


Number of Circuits: 1

## Impedance-Frequency Characteristics

### BLM18HG Series (For General Signal Lines)



### BLM18HE Series (For High Speed Signal Lines)




Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




## Impedance-Frequency Characteristics


### BLM18HD Series (For High Speed Signal Lines)



### BLM18HB Series (For High Speed Signal Lines)



### BLM18HK Series (For Digital Interface Lines)




## Notice (Rating)

In operating temperature exceeding +85°C, derating of current is necessary for BLM18HE series.


Please apply the derating curve shown in chart according to the operating temperature.

### Derating of Rated Current




## Impedance-Frequency Characteristics


### BLM18HG471SN1




### BLM18HG601SN1




### BLM18HG102SN1




### BLM18HE601SN1



### BLM18HE102SN1



### BLM18HE152SN1




Continued on the following page.


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


BLM18HD471SN1




BLM18HD601SN1




BLM18HD102SN1




BLM18HB121SN1




BLM18HB221SN1




BLM18HB331SN1




BLM18HK331SN1




BLM18HK471SN1



BLM18HK601SN1



BLM18HK102SN1



0603 Size  
Chip Ferrite Bead

Chip EMIFIL®


Chip Common Mode Choke Coil

Block Type EMIFIL®

Microwave Absorber




Noise Suppression of BLM18H  
in UHF Range

Testing Circuit




Type of Filter

EMI Suppression Effect / Description

Initial  
(No filter)Conventional Type  
BLM18AG102SN1  
(1000Ω at 100MHz)Current BLM18AG are effective in  
suppressing noise in the range between  
300MHz and 700MHz.for GHz Noise Suppression  
BLM18HG102SN1  
(1000Ω at 100MHz)In addition to the effectiveness of  
current BLM, BLM18HG suppresses  
noise in the range beyond 700MHz.

Comparison between BLM18HG102SN1 and BLM18AG102SN1 (Current Item)



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BLM18E Series (0603 Size)



For GHz band noise, also capable to large current.



## Dimensions



□ : Electrode  
(in mm)

## Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## Rated Value (□: packaging code)


Part Number	Impedance (at 100MHz/20°C)	Impedance (at 1GHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM18EG101TN1□	100ohm ±25%	140ohm (Typ.)	2000mA	0.045ohm max.	-55°C to +125°C	Kit ≥1A
BLM18EG121SN1□	120ohm ±25%	145ohm (Typ.)	2000mA	0.04ohm max.	-55°C to +125°C	Kit ≥1A
BLM18EG221SN1□	220ohm ±25%	260ohm (Typ.)	2000mA	0.05ohm max.	-55°C to +125°C	Kit ≥1A
BLM18EG221TN1□	220ohm ±25%	300ohm (Typ.)	1000mA	0.15ohm max.	-55°C to +125°C	Kit ≥1A
BLM18EG331TN1□	330ohm ±25%	450ohm (Typ.)	500mA	0.21ohm max.	-55°C to +125°C	Kit
BLM18EG391TN1□	390ohm ±25%	520ohm (Typ.)	500mA	0.3ohm max.	-55°C to +125°C	Kit
BLM18EG471SN1□	470ohm ±25%	550ohm (Typ.)	500mA	0.21ohm max.	-55°C to +125°C	Kit
BLM18EG601SN1□	600ohm ±25%	700ohm (Typ.)	500mA	0.35ohm max.	-55°C to +125°C	Kit

Number of Circuits: 1

## Impedance-Frequency Characteristics BLM18EG\_TN1 Series



## BLM18EG\_SN1 Series




## Notice (Rating)

In operating temperature exceeding +85°C, derating of current is necessary for BLM18EG series.

Please apply the derating curve shown in chart according to the operating temperature.

### Derating of Rated Current




Continued on the following page.


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Impedance-Frequency Characteristics


BLM18EG101TN1




BLM18EG121SN1




BLM18EG221SN1




BLM18EG221TN1




BLM18EG331TN1




BLM18EG391TN1



BLM18EG471SN1



BLM18EG601SN1




# BLM18G Series (0603 Size)



Available up to high-GHz band noise.



## Dimensions



## Equivalent Circuit



(Resistance element becomes dominant at high frequencies.)

## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
J	330mm Reel Paper Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.97 to p.100 for mounting information.

## Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Impedance (at 1GHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range	
BLM18GG471SN1□	470ohm $\pm 25\%$	1800ohm $\pm 30\%$	200mA	1.0ohm $\pm 0.3$ ohm	-55°C to +125°C	Kit


Number of Circuits: 1

## Impedance-Frequency Characteristics



## Impedance-Frequency Characteristics

### BLM18GG471SN1



## ⚠ Caution

## ● Rating

1. About the Rated Current  
Do not use products beyond the rated current as this may create excessive heat and deteriorate the insulation resistance.
2. About the Excessive Surge Current  
Excessive surge current ( pulse current or rush current) than specified rated current applied to the product may cause a critical failure, such as an open circuit, burnout caused by excessive temperature rise. Please contact us in advance in case of applying the surge current.

## ● Soldering and Mounting

- Self-heating  
Please provide special attention when mounting chip ferrite beads BLM\_AX/P/K/S series in close proximity to other products that radiate heat.  
The heat generated by other products may deteriorate the insulation resistance and cause excessive heat in this component.

## Notice

## ● Storage and Operating Conditions

## &lt;Operating Environment&gt;

Do not use products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.

Do not use products in the environment close to the organic solvent.


## &lt;Storage and Handling Requirements&gt;

1. Storage Period  
BLM15E/15H/15G series should be used within 12 months, the other series should be used within 6 months.  
Solderability should be checked if this period is exceeded.
2. Storage Conditions
  - (1) Storage temperature: -10 to +40°C  
Relative humidity: 15 to 85%  
Avoid sudden changes in temperature and humidity.
  - (2) Do not store products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.


## ● Handling

1. Resin Coating  
Using resin for coating/molding products may affect the products performance.  
So please pay careful attention in selecting resin.  
Prior to use, please make the reliability evaluation with the product mounted in your application set.
2. Handling of a Substrate  
After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate.  
Excessive mechanical stress may cause cracking in the Product.

Bending



Twisting



## ● Notice (Soldering and Mounting)

1. Cleaning  
Failure and degradation of a product are caused by the cleaning method. When you clean in conditions that are not in mounting information, please contact Murata engineering.
2. Soldering  
Reliability decreases with improper soldering methods.  
Please solder by the standard soldering conditions shown in mounting information.
3. Other  
Noise suppression levels resulting from Murata's EMI suppression filters EMIFIL® may vary, depending on the circuits and ICs used, type of noise, mounting pattern, mounting location, and other operating conditions. Be sure to check and confirm in advance the noise suppression effect of each filter, in actual circuits, etc. before applying the filter in a commercial-purpose equipment design.

⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



## 1. Standard Land Pattern Dimensions


Land Pattern  
+ Solder Resist

Land Pattern  
Solder Resist

(in mm)

BLM02  
BLM03  
BLM15  
BLM18  
BLM21  
BLM31  
BLM41


●Reflow and Flow  
BLM Series



Type	Soldering	a	b	c
BLM02	Reflow	0.16-0.2	0.4-0.56	0.2-0.23
BLM03	Reflow	0.2-0.3	0.6-0.9	0.3
BLM15	Reflow	0.4	1.2-1.4	0.5
BLM18	Flow (except 18G)	0.7	2.2-2.6	0.7
	Reflow		1.8-2.0	
BLM21	Flow/ Reflow	1.2	3.0-4.0	1.0

• Except for BLM03PG·PX·EB/15AX·PD·PG·PX/  
18PG·KG·SG/21PG. And BLM02/03/15/18G  
is specially adapted for reflow soldering.

## BLM□□AX/P/K/S/E




Type	Rated Current (A)	Soldering	a	b	c	Land Pad Thickness and Dimension d		
						18μm	35μm	70μm
BLM03AX	0.9max.	Reflow	0.2-0.3	0.6-0.9	0.3	0.3	0.3	0.3
BLM03P□ BLM03EB	1.8max.					1.2	0.7	0.3
BLM15AX	1.5max.	Reflow	0.4	1.2-1.4	0.5	0.5	0.5	0.5
BLM15PD	2.2max.					1.2	0.7	0.5
BLM15PG BLM15PX	3.0max.					2.4	1.2	0.5
BLM18PG	0.5-1.5	Flow/ Reflow	0.7	Flow 2.2-2.6 Reflow 1.8-2.0	0.7	0.7	0.7	0.7
BLM18KG	1.7-2.5					1.2	0.7	0.7
BLM18SG	3-4					2.4	1.2	0.7
	5-6					6.4	3.3	1.65
BLM21PG	1.5		1.2	3.0-4.0	1.0	1.0	1.0	1.0
	2					1.2	1.0	1.0
	3-4					2.4	1.2	1.0
	6					6.4	3.3	1.65
BLM31PG	1.5-2	Flow/ Reflow	2.0	4.2-5.2	1.2	1.2	1.2	1.2
	3.5					2.4	1.2	1.2
	6					6.4	3.3	1.65
BLM41PG	1.5-2		3.0	5.5-6.5	1.2	1.2	1.2	1.2
	3.5					2.4	1.2	1.2
	6					6.4	3.3	1.65


• Do not apply narrower pattern than listed above to  
BLM□□AX/P/K/S.  
Narrow pattern can cause excessive heat or open circuit.

BLA2A  
BLA31

## ●Reflow Soldering



## ●Reflow and Flow




• If there are high amounts of self-heating on pattern, the  
contact points of PCB and part may become damaged.

### ● PCB Warping

PCB should be designed so that products are not subjected to the mechanical stress caused by warping the board.

Products should be located in the sideways direction (Length:  $a < b$ ) to the mechanical stress.



## 2. Solder Paste Printing and Adhesive Application

When reflow soldering the chip ferrite beads, the printing must be conducted in accordance with the following cream solder printing conditions.

If too much solder is applied, the chip will be prone to damage by mechanical and thermal stress from the PCB and may crack.

Standard land dimensions should be used for resist and copper foil patterns.

When flow soldering the chip ferrite beads, apply the adhesive in accordance with the following conditions. If too much adhesive is applied, then it may overflow into the land or termination areas and yield poor solderability. In contrast, if insufficient adhesive is applied, or if the adhesive is not sufficiently hardened, then the chip may become detached during flow soldering process.

(in mm)

Series	Solder Paste Printing	Adhesive Application
<b>BLM</b>	<ul style="list-style-type: none"> <li>● Ensure that solder is applied smoothly to a minimum height of 0.2mm to 0.3mm at the end surface of the part.</li> <li>● Guideline of solder paste thickness: 50-80<math>\mu</math>m: BLM02 100-150<math>\mu</math>m: BLM03 100-200<math>\mu</math>m: BLM15/18/21/31/41</li> </ul>	<p>■ <b>BLM18/21/31/41 Series</b> (Except for BLM18G Series) Coating amount is illustrated in the following diagram.</p> <p>a: 20-70<math>\mu</math>m b: 30-35<math>\mu</math>m c: 50-105<math>\mu</math>m</p>
<b>BLA</b>	<ul style="list-style-type: none"> <li>● Guideline of solder paste thickness: 100-150<math>\mu</math>m: BLA2A 150-200<math>\mu</math>m: BLA31</li> </ul> <p>BLA31: 0.4, 0.7, 0.8, 0.7, 0.8</p> <p>BLA2A: 1.75, 0.5, 0.5, 1.5, 0.25, 0.25</p>	<p>■ <b>BLA31 Series</b> Coating amount is illustrated in the following diagram.</p> <p>a: 20-70<math>\mu</math>m b: 30-35<math>\mu</math>m c: 50-105<math>\mu</math>m</p>

### 3. Standard Soldering Conditions

#### (1) Soldering Methods

Use flow and reflow soldering methods only.

Use standard soldering conditions when soldering chip ferrite beads.

In cases where several different parts are soldered, each having different soldering conditions, use those conditions requiring the least heat and minimum time.

Solder: Use Sn-3.0Ag-0.5Cu solder. Use of Sn-Zn based solder will deteriorate performance of products.

If using BLA series with Sn-Zn based solder, please contact Murata in advance.


Flux:

- Use Rosin-based flux.  
In case of using RA type solder, products should be cleaned completely with no residual flux.
- Do not use strong acidic flux (with chlorine content exceeding 0.20wt%)
- Do not use water-soluble flux.

For additional mounting methods, please contact Murata.


#### (2) Soldering Profile

##### ● Flow Soldering Profile (Sn-3.0Ag-0.5Cu Solder)



Series	Pre-heating		Standard Profile			Limit Profile		
	Temp. (T1)	Time. (t1)	Temp. (T2)	Time. (t2)	Cycle of Flow	Temp. (T3)	Time. (t2)	Cycle of Flow
<b>BLM</b> (Except for <b>BLM02/03/15/18G</b> ) <b>BLA31</b>	150°C	60s min.	250°C	4 to 6s	2 times max.	265±3°C	5s max.	2 times max.

##### ● Reflow Soldering Profile (Sn-3.0Ag-0.5Cu Solder)



Series	Standard Profile				Limit Profile			
	Heating		Peak Temperature (T2)	Cycle of Reflow	Heating		Peak Temperature (T4)	Cycle of Reflow
	Temp. (T1)	Time. (t1)			Temp. (T3)	Time. (t2)		
<b>BLM</b> <b>BLA</b>	220°C min.	30 to 60s	245±3°C	2 times max.	230°C min.	60s max.	260°C/10s	2 times max.

## (3) Reworking with Solder Iron

The following conditions must be strictly followed when using a soldering iron. (Except for BLM02 Series)

Pre-heating: 150°C 60s min.

Soldering iron power output / Tip diameter:

80W max. / ø3mm max.

Temperature of soldering iron tip / Soldering time / Times:  
350°C max. / 3-4s / 2 times

Do not allow the tip of the soldering iron to directly contact the chip.

For additional methods of reworking with a soldering iron, please contact Murata engineering.

**4. Cleaning**

Following conditions should be observed when cleaning chip ferrite beads.

(1) Cleaning Temperature: 60°C max. (40°C max. for alcohol type cleaner)

(2) Ultrasonic

Output: 20W/liter max.

Duration: 5 minutes max.

Frequency: 28 to 40kHz

(3) Cleaning Agent

The following list of cleaning agents have been tested on the individual components. Evaluation of final assembly should be completed prior to production.

(a) Alcohol cleaning agent

Isopropyl alcohol (IPA)

(b) Aqueous cleaning agent


Pine Alpha ST-100S

(4) Ensure that flux residue is completely removed.

Component should be thoroughly dried after aqueous agent has been removed with deionized water.

(5) BLM\_G type is processed with resin. On rinsing the product, using water for ultrasonic cleaning may affect the resin quality used for the product by water element. In case of set cleaning conditions, please make sure the reliability according to the cleaning conditions.


### ■ Minimum Quantity and Dimensions of 8mm Width Paper / Embossed Tape



(There are holes in the cavities of the BLM21BD222SN1/  
BD272SN1 and BLM31 only.  $\phi 1.0^{+0.3}_{-0}$ )


- \*1 BLM02/03/15:  $2.0 \pm 0.05$   
BLM18S/18T/BLA2A:  $2.0 \pm 0.1$
- \*2 BLA2A/31:  $2.0 \pm 0.1$
- \*3 BLA2A/31:  $3.5 \pm 0.1$

<Embossed>



c: Depth of Cavity  
(Embossed Tape)

<Paper>



BLM02/03


c: Total Thickness of Tape  
(Paper Tape)

Dimension of the cavity of embossed tape is measured at the bottom side.

Part Number	Dimensions				Minimum Qty. (pcs.)				
					ø180mm Reel		ø330mm Reel		Bulk
	a	b	c	d	Paper Tape	Embossed Tape	Paper Tape	Embossed Tape	
BLM02	0.45	0.25	0.40 max.	-	20000	-	-	-	1000
BLM03	0.70	0.40	0.55 max.	-	15000	-	50000	-	1000
BLM15	1.15	0.65	0.8 max.	-	10000	-	50000	-	1000
BLM18A/B/P/R/H/G	1.85	1.05	1.1 max.	-	4000	-	10000	-	1000
BLM18EG/KG_TN	1.85	1.05	0.85 max.	-	4000	-	10000	-	1000
BLM18EG/KG_SN			1.1 max.						
BLM18S	1.85	1.05	0.90 max.	-	10000	-	30000	-	1000
BLM18T	1.85	1.05	0.90 max.	-	10000	-	-	-	1000
BLM21	2.25	1.45	1.1 max.	-	4000	-	10000	-	1000
BLM31	3.5	1.9	1.3	0.2	-	3000	-	10000	1000
BLM21BD222SN1/272SN1	2.25	1.45	1.3	0.2	-	3000	-	10000	1000
BLA2A	2.2	1.2	0.8 max.	-	10000	-	50000	-	1000
BLA31	3.4	1.8	1.1 max.	-	4000	-	10000	-	1000

(in mm)

### ■ Minimum Quantity and Dimensions of 12mm Width Embossed Tape




Dimension of the cavity is measured at the bottom side.

Part Number	Dimensions			Minimum Qty. (pcs.)		
	a	b	c	ø180mm Reel	ø330mm Reel	Bulk
BLM41	4.8	1.9	1.75	2500	8000	1000

(in mm)

"Minimum Quantity" means the number of units of each delivery or order. The quantity should be an integral multiple of the "Minimum Quantity."

**Note** • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



●EKEMBL03L (Chip Ferrite Beads 01005 Size / 0201 Size)

No.	Part Number	Quantity (pcs.)	Impedance typ. (at 100MHz, 20 degrees C)	Rated Current (mA)	DC Resistance (Ω) max.
1	BLM02AX100SN1	20	10Ω±5Ω	750	0.07
2	BLM02AX700SN1	20	70Ω±25%	300	0.4
3	BLM02AX121SN1	20	120Ω±25%	250	0.5
4	BLM03AG100SN1	20	10Ω (Typ.)	500	0.1
5	BLM03AG700SN1	20	70Ω (Typ.)	200	0.4
6	BLM03AG800SN1	20	80Ω±25%	200	0.4
7	BLM03AG121SN1	20	120Ω±25%	200	0.5
8	BLM03AG241SN1	20	240Ω±25%	200	0.8
9	BLM03AG601SN1	20	600Ω±25%	100	1.5
10	BLM03AG102SN1	20	1000Ω±25%	100	2.5
11	BLM03AX100SN1	20	10Ω (Typ.)	1000	0.05
12	BLM03AX800SN1	20	80Ω±25%	500	0.18
13	BLM03AX121SN1	20	120Ω±25%	450	0.23
14	BLM03AX241SN1	20	240Ω±25%	350	0.38
15	BLM03AX601SN1	20	600Ω±25%	250	0.85
16	BLM03AX102SN1	20	1000Ω±25%	200	1.25
17	BLM03BB100SN1	20	10Ω±25%	300	0.4
18	BLM03BB220SN1	20	22Ω±25%	200	0.5
19	BLM03BB470SN1	20	47Ω±25%	200	0.7
20	BLM03BB750SN1	20	75Ω±25%	200	1.0
21	BLM03BB121SN1	20	120Ω±25%	100	1.5
22	BLM03BD750SN1	20	75Ω±25%	300	0.4
23	BLM03BD121SN1	20	120Ω±25%	250	0.5
24	BLM03BD241SN1	20	240Ω±25%	200	0.8
25	BLM03BD471SN1	20	470Ω±25%	215	1.5
26	BLM03BD601SN1	20	600Ω±25%	200	1.7
27	BLM03BC330SN1	20	33Ω±25%	150	0.85
28	BLM03BC560SN1	20	56Ω±25%	100	1.05
29	BLM03BC800SN1	20	80Ω±25%	100	1.40
30	BLM03EB250SN1	20	25Ω±25%	600	0.26
31	BLM03EB500SN1	20	50Ω±25%	400	0.58
32	BLM03HG601SN1	20	600Ω±25%	150	1.6
33	BLM03HG102SN1	20	1000Ω±25%	125	2.6
34	BLM03HB191SN1	20	190Ω±25%	150	2.0
35	BLM03HD331SN1	20	330Ω±25%	200	1.0
36	BLM03HD471SN1	20	470Ω±25%	175	1.3
37	BLM03HD601SN1	20	600Ω±25%	150	1.7
38	BLM03HD102SN1	20	1000Ω±25%	120	2.9
39	BLM03PG220SN1	20	22Ω±25%	900	0.065
40	BLM03PG330SN1	20	33Ω±25%	750	0.090
41	BLM03PX220SN1	20	22Ω±25%	1800	0.040
42	BLM03PX330SN1	20	33Ω±25%	1500	0.055
43	BLM03PX800SN1	20	80Ω±25%	1000	0.130


●EKEMBL15Q (Chip Ferrite Beads 0402 Size)

No.	Part Number	Quantity (pcs.)	Impedance typ. (at 100MHz, 20 degrees C)	Rated Current (mA)	DC Resistance (Ω) max.
1	BLM15AG100SN1	20	10Ω (Typ.)	1000	0.025
2	BLM15AG700SN1	20	70Ω (Typ.)	600	0.15
3	BLM15AG121SN1	20	120Ω±25%	550	0.19
4	BLM15AG221SN1	20	220Ω±25%	450	0.29
5	BLM15AG601SN1	20	600Ω±25%	300	0.52
6	BLM15AG102SN1	20	1000Ω±25%	300	0.65
7	BLM15AX100SN1	20	10Ω (Typ.)	1740	0.015
8	BLM15AX300SN1	20	30Ω±25%	1100	0.06

Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



 Continued from the preceding page.

No.	Part Number	Quantity (pcs.)	Impedance typ. (at 100MHz, 20 degrees C)	Rated Current (mA)	DC Resistance (Ω) max.
9	BLM15AX700SN1	20	70Ω±25%	780	0.10
10	BLM15AX121SN1	20	120Ω±25%	700	0.13
11	BLM15AX221SN1	20	220Ω±25%	600	0.18
12	BLM15AX601SN1	20	600Ω±25%	500	0.34
13	BLM15AX102SN1	20	1000Ω±25%	350	0.49
14	BLM15BA050SN1	20	5Ω±25%	300	0.10
15	BLM15BA100SN1	20	10Ω±25%	300	0.20
16	BLM15BA220SN1	20	22Ω±25%	300	0.30
17	BLM15BA330SN1	20	33Ω±25%	300	0.40
18	BLM15BA470SN1	20	47Ω±25%	200	0.60
19	BLM15BA750SN1	20	75Ω±25%	200	0.80
20	BLM15BB050SN1	20	5Ω±25%	500	0.08
21	BLM15BB100SN1	20	10Ω±25%	300	0.10
22	BLM15BB220SN1	20	22Ω±25%	300	0.20
23	BLM15BB470SN1	20	47Ω±25%	300	0.35
24	BLM15BB750SN1	20	75Ω±25%	300	0.40
25	BLM15BB121SN1	20	120Ω±25%	300	0.55
26	BLM15BB221SN1	20	220Ω±25%	200	0.80
27	BLM15BC121SN1	20	120Ω±25%	350	0.45
28	BLM15BC241SN1	20	240Ω±25%	250	0.70
29	BLM15BD750SN1	20	75Ω±25%	300	0.20
30	BLM15BD121SN1	20	120Ω±25%	300	0.30
31	BLM15BD221SN1	20	220Ω±25%	300	0.40
32	BLM15BD471SN1	20	470Ω±25%	200	0.60
33	BLM15BD601SN1	20	600Ω±25%	200	0.65
34	BLM15BD102SN1	20	1000Ω±25%	200	0.90
35	BLM15BD182SN1	20	1800Ω±25%	100	1.40
36	BLM15BX750SN1	20	75Ω±25%	600	0.15
37	BLM15BX121SN1	20	120Ω±25%	600	0.17
38	BLM15BX221SN1	20	220Ω±25%	450	0.27
39	BLM15BX471SN1	20	470Ω±25%	350	0.41
40	BLM15BX601SN1	20	600Ω±25%	350	0.46
41	BLM15BX102SN1	20	1000Ω±25%	300	0.65
42	BLM15BX182SN1	20	1800Ω±25%	250	0.90
43	BLM15HD601SN1	20	600Ω±25%	300	0.85
44	BLM15HD102SN1	20	1000Ω±25%	250	1.25
45	BLM15HD182SN1	20	1800Ω±25%	200	2.20
46	BLM15HG601SN1	20	600Ω±25%	300	0.70
47	BLM15HG102SN1	20	1000Ω±25%	250	1.10
48	BLM15HB121SN1	20	120Ω±25%	300	0.70
49	BLM15HB221SN1	20	220Ω±25%	250	1.00
50	BLM15EG121SN1	20	120Ω±25%	1500	0.095
51	BLM15EG221SN1	20	220Ω±25%	700	0.28
52	BLM15GG221SN1	20	220Ω±25%	300	0.70
53	BLM15GG471SN1	20	470Ω±25%	200	1.30
54	BLM15GA750SN1	20	75Ω±25%	200	1.30
55	BLM15PG100SN1	20	10Ω (Typ.)	1000	0.025
56	BLM15PD300SN1	20	30Ω±25%	2200	0.035
57	BLM15PD600SN1	20	60Ω±25%	1700	0.06
58	BLM15PD800SN1	20	80Ω±25%	1500	0.07
59	BLM15PD121SN1	20	120Ω±25%	1300	0.09
60	BLM15PX330SN1	20	33Ω±25%	3000	0.022
61	BLM15PX600SN1	20	60Ω±25%	2500	0.032
62	BLM15PX800SN1	20	80Ω±25%	2300	0.038
63	BLM15PX121SN1	20	120Ω±25%	2000	0.055
64	BLM15PX181SN1	20	180Ω±25%	1500	0.090
65	BLM15PX221SN1	20	220Ω±25%	1400	0.10
66	BLM15PX331SN1	20	330Ω±25%	1200	0.15
67	BLM15PX471SN1	20	470Ω±25%	1000	0.20
68	BLM15PX601SN1	20	600Ω±25%	900	0.23

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




## ●EKEMBL18J (Chip Ferrite Beads 0603 Size)

No.	Part Number	Quantity (pcs.)	Impedance typ. (at 100MHz, 20 degrees C)	Rated Current (mA)	DC Resistance (Ω) max.
1	BLM18AG121SN1	20	120Ω±25%	500	0.18
2	BLM18AG151SN1	20	150Ω±25%	500	0.25
3	BLM18AG221SN1	20	220Ω±25%	500	0.25
4	BLM18AG331SN1	20	330Ω±25%	500	0.30
5	BLM18AG471SN1	20	470Ω±25%	500	0.35
6	BLM18AG601SN1	20	600Ω±25%	500	0.38
7	BLM18AG102SN1	20	1000Ω±25%	400	0.50
8	BLM18BA050SN1	20	5Ω±25%	500	0.20
9	BLM18BA100SN1	20	10Ω±25%	500	0.25
10	BLM18BA470SN1	20	47Ω±25%	300	0.55
11	BLM18BA750SN1	20	75Ω±25%	300	0.70
12	BLM18BA121SN1	20	120Ω±25%	200	0.90
13	BLM18BB050SN1	20	5Ω±25%	700	0.05
14	BLM18BB100SN1	20	10Ω±25%	700	0.10
15	BLM18BB220SN1	20	22Ω±25%	600	0.20
16	BLM18BB470SN1	20	47Ω±25%	550	0.25
17	BLM18BB600SN1	20	60Ω±25%	550	0.25
18	BLM18BB750SN1	20	75Ω±25%	500	0.30
19	BLM18BB121SN1	20	120Ω±25%	500	0.30
20	BLM18BB151SN1	20	150Ω±25%	450	0.37
21	BLM18BB221SN1	20	220Ω±25%	450	0.45
22	BLM18BB331SN1	20	330Ω±25%	400	0.58
23	BLM18BB471SN1	20	470Ω±25%	300	0.85
24	BLM18BD470SN1	20	47Ω±25%	500	0.30
25	BLM18BD121SN1	20	120Ω±25%	200	0.40
26	BLM18BD151SN1	20	150Ω±25%	200	0.40
27	BLM18BD221SN1	20	220Ω±25%	200	0.45
28	BLM18BD331SN1	20	330Ω±25%	200	0.50
29	BLM18BD421SN1	20	420Ω±25%	200	0.55
30	BLM18BD471SN1	20	470Ω±25%	200	0.55
31	BLM18BD601SN1	20	600Ω±25%	200	0.65
32	BLM18BD102SN1	20	1000Ω±25%	100	0.85
33	BLM18BD152SN1	20	1500Ω±25%	50	1.20
34	BLM18BD182SN1	20	1800Ω±25%	50	1.50
35	BLM18BD222SN1	20	2200Ω±25%	50	1.50
36	BLM18BD252SN1	20	2500Ω±25%	50	1.50
37	BLM18PG300SN1	20	30Ω (Typ.)	1000	0.05
38	BLM18PG330SN1	20	33Ω±25%	3000	0.025
39	BLM18PG600SN1	20	60Ω (Typ.)	500	0.10
40	BLM18PG121SN1	20	120Ω±25%	2000	0.05
41	BLM18PG181SN1	20	180Ω±25%	1500	0.09
42	BLM18PG221SN1	20	220Ω±25%	1400	0.10
43	BLM18PG331SN1	20	330Ω±25%	1200	0.15
44	BLM18PG471SN1	20	470Ω±25%	1000	0.20
45	BLM18KG260TN1	20	26Ω±25%	6000	0.007
46	BLM18KG300TN1	20	30Ω±25%	5000	0.010
47	BLM18KG700TN1	20	70Ω±25%	3500	0.022
48	BLM18KG101TN1	20	100Ω±25%	3000	0.030
49	BLM18KG121TN1	20	120Ω±25%	3000	0.030
50	BLM18KG221SN1	20	220Ω±25%	2200	0.050
51	BLM18KG331SN1	20	330Ω±25%	1700	0.080
52	BLM18KG471SN1	20	470Ω±25%	1500	0.130
53	BLM18KG601SN1	20	600Ω±25%	1300	0.150
54	BLM18SG260TN1	20	26Ω±25%	6000	0.007
55	BLM18SG700TN1	20	70Ω±25%	4000	0.020
56	BLM18SG121TN1	20	120Ω±25%	3000	0.025
57	BLM18SG221TN1	20	220Ω±25%	2500	0.040
58	BLM18SG331TN1	20	330Ω±25%	1500	0.070

## ●EKEMBL8GB (Chip Ferrite Beads 0603 Size / for High Frequency Type)

No.	Part Number	Quantity (pcs.)	Impedance (at 100MHz, 20 degrees C)	Impedance (at 1GHz, 20 degrees C)	Rated Current (mA)	DC Resistance (Ω) max.
1	BLM18HG471SN1	20	470Ω±25%	600Ω (Typ.)	200	0.85
2	BLM18HG601SN1	20	600Ω±25%	700Ω (Typ.)	200	1.00
3	BLM18HG102SN1	20	1000Ω±25%	1000Ω (Typ.)	100	1.60

Continued on the following page. 

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.


No.	Part Number	Quantity (pcs.)	Impedance (at 100MHz, 20 degrees C)	Impedance (at 1GHz, 20 degrees C)	Rated Current (mA)	DC Resistance (Ω) max.
4	BLM18HB121SN1	20	120Ω±25%	500Ω±40%	200	0.50
5	BLM18HB221SN1	20	220Ω±25%	1100Ω±40%	100	0.80
6	BLM18HB331SN1	20	330Ω±25%	1600Ω±40%	50	1.20
7	BLM18HD471SN1	20	470Ω±25%	1000Ω (Typ.)	100	1.20
8	BLM18HD601SN1	20	600Ω±25%	1200Ω (Typ.)	100	1.50
9	BLM18HD102SN1	20	1000Ω±25%	1700Ω (Typ.)	50	1.80
10	BLM18HE601SN1	20	600Ω±25%	600Ω (Typ.)	800	0.25
11	BLM18HE102SN1	20	1000Ω±25%	1000Ω (Typ.)	600	0.35
12	BLM18HE152SN1	20	1500Ω±25%	1500Ω (Typ.)	500	0.50
13	BLM18HK331SN1	20	330Ω±25%	400Ω (Typ.)	200	0.50
14	BLM18HK471SN1	20	470Ω±25%	600Ω (Typ.)	200	0.70
15	BLM18HK601SN1	20	600Ω±25%	700Ω (Typ.)	100	0.90
16	BLM18HK102SN1	20	1000Ω±25%	1200Ω (Typ.)	50	1.50
17	BLM18EG101TN1	20	100Ω±25%	140Ω (Typ.)	2000	0.045
18	BLM18EG121SN1	20	120Ω±25%	145Ω (Typ.)	2000	0.04
19	BLM18EG221TN1	20	220Ω±25%	300Ω (Typ.)	1000	0.15
20	BLM18EG221SN1	20	220Ω±25%	260Ω (Typ.)	2000	0.05
21	BLM18EG331TN1	20	330Ω±25%	450Ω (Typ.)	500	0.21
22	BLM18EG391TN1	20	390Ω±25%	520Ω (Typ.)	500	0.30
23	BLM18EG471SN1	20	470Ω±25%	550Ω (Typ.)	500	0.21
24	BLM18EG601SN1	20	600Ω±25%	700Ω (Typ.)	500	0.35
25	BLM18GG471SN1	20	470Ω±25%	1800Ω±30%	200	1.30

## ●EKEMBL21F (Chip Ferrite Beads 0805 Size / for Large-current P Type)

No.	Part Number	Quantity (pcs.)	Impedance typ. (at 100MHz, 20 degrees C)	Rated Current (mA)	DC Resistance (Ω) max.
1	BLM21AG121SN1	20	120Ω±25%	800	0.10
2	BLM21AG151SN1	20	150Ω±25%	800	0.10
3	BLM21AG221SN1	20	220Ω±25%	800	0.13
4	BLM21AG331SN1	20	330Ω±25%	700	0.16
5	BLM21AG471SN1	20	470Ω±25%	700	0.19
6	BLM21AG601SN1	20	600Ω±25%	600	0.21
7	BLM21AG102SN1	20	1000Ω±25%	500	0.28
8	BLM21BB050SN1	20	5Ω±25%	1000	0.02
9	BLM21BB600SN1	20	60Ω±25%	800	0.13
10	BLM21BB750SN1	20	75Ω±25%	700	0.16
11	BLM21BB121SN1	20	120Ω±25%	600	0.19
12	BLM21BB221SN1	20	220Ω±25%	500	0.26
13	BLM21BB331SN1	20	330Ω±25%	400	0.33
14	BLM21BB471SN1	20	470Ω±25%	400	0.40
15	BLM21BD121SN1	20	120Ω±25%	200	0.25
16	BLM21BD221SN1	20	220Ω±25%	200	0.25
17	BLM21BD421SN1	20	420Ω±25%	200	0.30
18	BLM21BD471SN1	20	470Ω±25%	200	0.35
19	BLM21BD601SN1	20	600Ω±25%	200	0.35
20	BLM21BD102SN1	20	1000Ω±25%	200	0.40
21	BLM21BD152SN1	20	1500Ω±25%	200	0.45
22	BLM21BD182SN1	20	1800Ω±25%	200	0.50
23	BLM21BD222SN1	20	2250Ω (Typ.)	200	0.60
24	BLM21BD222TN1	20	2200Ω±25%	200	0.60
25	BLM21BD272SN1	20	2700Ω±25%	200	0.80
26	BLM21PG220SN1	20	22Ω±25%	6000	0.009
27	BLM21PG300SN1	20	30Ω (Typ.)	4000	0.014
28	BLM21PG600SN1	20	60Ω±25%	3500	0.02
29	BLM21PG121SN1	20	120Ω±25%	3000	0.03
30	BLM21PG221SN1	20	220Ω±25%	2000	0.045
31	BLM21PG331SN1	20	330Ω±25%	1500	0.07
32	BLM31PG330SN1	20	33Ω±25%	6000	0.009
33	BLM31PG500SN1	20	50Ω (Typ.)	3500	0.015
34	BLM31PG121SN1	20	120Ω±25%	3500	0.02
35	BLM31PG391SN1	20	390Ω (Typ.)	2000	0.05
36	BLM31PG601SN1	20	600Ω (Typ.)	1500	0.08
37	BLM41PG600SN1	20	60Ω (Typ.)	6000	0.009
38	BLM41PG750SN1	20	75Ω (Typ.)	3500	0.015
39	BLM41PG181SN1	20	180Ω (Typ.)	3500	0.02

Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

 Continued from the preceding page.

No.	Part Number	Quantity (pcs.)	Impedance typ. (at 100MHz, 20 degrees C)	Rated Current (mA)	DC Resistance (Ω) max.
40	<b>BLM41PG471SN1</b>	20	470Ω (Typ.)	2000	0.05
41	<b>BLM41PG102SN1</b>	20	1000Ω (Typ.)	1500	0.09



## Chip EMIFIL®

Series Introduction .....	108
Part Numbering .....	110
Series Line Up .....	113
Product Detail .....	116
⚠Caution/Notice .....	146
Soldering and Mounting .....	147
Packaging .....	153
Design Kits .....	155

Chip Ferrite Bead


Chip EMIFIL®

Chip Common Mode Choke Coil

Block Type EMIFIL®


Microwave Absorber






















# NF Series Introduction




## Example of 3-Terminal Capacitor Structure

Chip 3-terminal capacitor is a chip-shaped 3-terminal capacitor designed for noise suppression. Its inner structure, like a feed-through capacitor, makes its ground impedance quite low. Owing to this structure, the 3-terminal capacitor has a good noise suppression effect at a high frequency range up to several hundred MHz.



Series	Equivalent Circuit	Part Number	
<b>NFM Series</b> (3-terminal capacitor)		 <b>NFM18CC</b>	
		 <b>NFM21CC</b>	
		 <b>NFM18PC</b>	
		 <b>NFM18PS</b>	
		 <b>NFM21PC</b>	
<b>NFL / NFW Series</b> (LC filter)		 <b>NFL15ST</b>	
		 <b>NFL18ST</b>	
		 <b>NFL18SP</b>	
		 <b>NFL21SP</b>	
		 <b>NFA21S</b>	
		 <b>NFA18S</b>	
<b>NFR Series</b> (RC filter)		 <b>NFR21GD</b>  <b>NFA31GD</b>	
<b>NFE Series</b> (Feed through capacitor with ferrite cores)		 <b>NFE31PT</b>  <b>NFE61PT</b>	

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



Insertion Loss Sample	Features	Classification		Applications	Example
	Standard of 3-terminal capacitor	<b>NFM_CC</b>	Standard type with varied capacitance	Noise suppression in low speed signal lines	<ul style="list-style-type: none"> <li>Low speed interface lines</li> <li>Sensor</li> </ul>
		<b>NFM_PC</b>	Meet large current, high capacitance available, for power lines	Noise suppression in power lines	<ul style="list-style-type: none"> <li>Individual IC power lines</li> </ul>
	Sharp insertion loss curve enables low damage to signal waveform	<b>NFL_ST</b>	T-type filter, effective in low impedance circuits	Noise suppression in high speed signal lines	<ul style="list-style-type: none"> <li>High speed interface lines</li> <li>Bus lines</li> <li>LCD lines</li> <li>Camera I/Fs</li> <li>High speed analog lines</li> <li>RGB / D terminal</li> </ul>
		<b>NFL_SP</b>	π-type filter, effective in high impedance circuits		
		<b>NFW_SP</b>	π-type filter, designed for low impedance circuits		
		<b>NFA_SL</b>	4-line array, suitable for bus lines or flat cables		
	Limit noise using resistor, also loop back to ground			Noise suppression in signal line with unstable ground	<ul style="list-style-type: none"> <li>Interface lines</li> <li>Clock lines</li> </ul>
	Meets large current, good high frequency performance because of its feed through structure			Noise suppression in power lines / low impedance lines	<ul style="list-style-type: none"> <li>Various power lines</li> <li>Sensor</li> </ul>



# NF Chip EMIFIL® Part Numbering

## Capacitor

(Part Number)

NF	M	3D	CC	102	R	1H	3	L
①	②	③	④	⑤	⑥	⑦	⑧	⑨

\*NFA□□SL/SD Series, please refer to p.112 (LC Combined (2)).

\*NFA□□GD Series, please refer to p.112 (RC Combined).

### ① Product ID

Product ID	
NF	Chip EMIFIL®

### ② Structure

Code	Structure
M	Capacitor Type
A	Capacitor Array Type

### ③ Dimensions (L×W)

Code	Dimensions (L×W)	EIA
18	1.6×0.8mm	0603
21	2.0×1.25mm	0805
3D	3.2×1.25mm	1205
31	3.2×1.6mm	1206
41	4.5×1.6mm	1806

### ④ Features

Code	Features
CC	Capacitor Type for Signal Lines
PC	Capacitor Type for Large Current
PS	High Insertion Loss Type for Large Current
KC	Capacitor Type for Very Large Current

### ⑤ Capacitance

Expressed by three figures. The unit is in pico-farad (pF). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures.

### ⑥ Characteristics

Code	Capacitance Change (Temperature Characteristics)
B	±10%, ±12.5%, +10/-13%
F	+30/-80%, +30/-84%
R	±15%, +15/-18%
U	-750 ±120ppm/°C
S	+350 to -1000ppm/°C

### ⑦ Rated Voltage

Code	Rated Voltage
0J	6.3V
1A	10V
1C	16V
1E	25V
1H	50V
2A	100V

### ⑧ Electrode/Others (NFM Series)

Code	Electrode	Series
3	Sn Plating	NFM

### ⑨ Number of Circuits (NFA□□CC Series)

Code	Number of Circuits
4	4 Circuits

### ⑨ Packaging

Code	Packaging	Series
L	Embossed Taping (ø180mm Reel)	NFM3D/NFM31/NFM41
B	Bulk	All series
D	Paper Taping (ø180mm Reel)	NFM18/NFM21/NFA□□CC

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



## LC Combined (1)

(Part Number)

NF	L	18	ST	107	X	1C	3	L
①	②	③	④	⑤	⑥	⑦	⑧	⑨

### ① Product ID

Product ID	
NF	Chip EMIFIL®

### ② Structure

Code	Structure
L	Multilayer, LC Combined Type
W	Wire Wound, LC Combined Type
E	Block, LC Combined Type

### ③ Dimensions (L×W)

Code	Dimensions (L×W)	EIA
15	1.0×0.5mm	0402
18	1.6×0.8mm	0603
21	2.0×1.25mm	0805
31	3.2×1.6mm	1206
61	6.8×1.6mm	2706

### ④ Features

Code	Features
SP	π Circuit for Signal Lines
ST	T Circuit for Signal Lines
PT	T Circuit for Large Current

### ⑤ Cut-off Frequency (NFL/NFW Series)

Expressed by three figures. The unit is in hertz (Hz). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures.

### ⑤ Capacitance (NFE Series)

Expressed by three figures. The unit is in pico-farad (pF). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures.

### ⑨ Packaging

Code	Packaging	Series
K	Embossed Taping (ø330mm Reel)	NFW31/NFE
L	Embossed Taping (ø180mm Reel)	NFW31/NFE
B	Bulk	NFL18/NFL21/NFE
D	Paper Taping (ø180mm Reel)	NFL15/NFL18/NFL21

### ⑥ Characteristics (NFL/NFW Series)

Code	Characteristics
H/X	Cut-off Frequency

### ⑥ Characteristics (NFE Series)

Code	Capacitance Change (Temperature Characteristics)
B	±10%
C	±20%, ±22%
D	+20/-30%, +22/-33%
E	+20/-55%, +22/-56%
F	+30/-80%, +22/-82%
R	±15%
U	-750 ±120ppm/ °C
Z	Other

### ⑦ Rated Voltage

Code	Rated Voltage
1A	10V
1C	16V
1E	25V
1H	50V
2A	100V

### ⑧ Electrode

Code	Electrode	Series
3/7	Sn Plating	NFL
4	Lead Free Solder Coating	NFW
9	Others	NFE

## LC Combined (2)

(Part Number)

NF	A	21	SL	207	X	1A	4	5	L
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩

\*NFA□□CC Series, please refer to p.110.

\*NFA□□GD Series, please refer to p.112 (RC Combined).

## ① Product ID

Product ID	
NF	Chip EMIFIL®

## ② Structure

Code	Structure
A	Array Type

## ③ Dimensions (L×W)

Code	Dimensions (L×W)	EIA
18	1.6×0.8mm	0603
21	2.0×1.25mm	0805

## ④ Features (1)

Code	Features
SL	L Circuit for Signal Lines
SD	L Circuit for Differential Signal

## ⑤ Cut-off Frequency

Expressed by three figures. The unit is in hertz (Hz). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures.

## ⑥ Features (2)

Code	Features
X	Expressed by a letter
V	

## ⑦ Rated Voltage

Code	Rated Voltage
1A	10V

## ⑧ Number of Circuits

Code	Number of Circuits
4	4 Circuits

## ⑨ Dimensions (T)

Code	Dimensions (T)
5	Low Profile
8	Standard

## ⑩ Packaging

Code	Packaging
B	Bulk
L	Embossed Taping (ø180mm Reel)

## RC Combined

(Part Number)

NF	R	21	GD	470	470	2	L
①	②	③	④	⑤	⑥	⑦	⑧

\*NFA□□CC Series, please refer to p.110.

\*NFA□□SL/SD Series, please refer to p.112 (LC Combined (2)).

## ① Product ID

Product ID	
NF	Chip EMIFIL®

## ② Structure

Code	Structure
R	RC Combined Type
A	RC Combined Array Type

## ③ Dimensions (L×W)

Code	Dimensions (L×W)	EIA
21	2.0×1.25mm	0805
31	3.2×1.6mm	1206

## ④ Features

Code	Features
GD	RC Combined Type for Signal Lines

## ⑧ Packaging

Code	Packaging	Series
L	Embossed Taping (ø180mm Reel)	NFR
B	Bulk	All Series
D	Paper Taping (ø180mm Reel)	NFA□□GD

## ⑤ Capacitance

Expressed by three figures. The unit is in pico-farad (pF). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures.

## ⑥ Resistance

Expressed by three-digit alphanumerics. The unit is in ohm (Ω). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures. If there is a decimal point, it is expressed by the capital letter "R." In this case, all figures are significant digits.

## ⑦ Electrode/Others (NFR Series)


Code	Electrode
2	Sn Plating

## ⑦ Number of Circuits (NFA□□GD Series)

Code	Number of Circuits
4	4 Circuits

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Type	Size Code (Inch)	Thickness (mm)	Part Number	Rated Voltage	Capacitance	Nominal Cut-off Frequency	Rated Current	New	Kit	$\geq 1A$	$\geq 3A$	$\geq 10A$	DTV	Flow	Reflow
Capacitor Type for Signal Lines	p127	0.6	NFM18CC220U1C3	16Vdc	22pF+20%-20%	-	400mA		Kit						Reflow
		0.6	NFM18CC470U1C3	16Vdc	47pF+20%-20%	-	400mA		Kit						Reflow
		0.6	NFM18CC101R1C3	16Vdc	100pF+20%-20%	-	500mA		Kit						Reflow
		0.6	NFM18CC221R1C3	16Vdc	220pF+20%-20%	-	500mA		Kit						Reflow
		0.6	NFM18CC471R1C3	16Vdc	470pF+20%-20%	-	500mA		Kit						Reflow
		0.6	NFM18CC102R1C3	16Vdc	1000pF+20%-20%	-	600mA		Kit						Reflow
		0.6	NFM18CC222R1C3	16Vdc	2200pF+20%-20%	-	700mA		Kit						Reflow
		0.6	NFM18CC223R1C3	16Vdc	22000pF+20%-20%	-	1000mA		Kit	$\geq 1A$					Reflow
	p128	0.85	NFM21CC220U1H3	50Vdc	22pF+20%-20%	-	700mA		Kit						Reflow
		0.85	NFM21CC470U1H3	50Vdc	47pF+20%-20%	-	700mA		Kit						Reflow
		0.85	NFM21CC101U1H3	50Vdc	100pF+20%-20%	-	700mA		Kit						Reflow
		0.85	NFM21CC221R1H3	50Vdc	220pF+20%-20%	-	700mA		Kit						Reflow
		0.85	NFM21CC471R1H3	50Vdc	470pF+20%-20%	-	1000mA		Kit	$\geq 1A$					Reflow
		0.85	NFM21CC102R1H3	50Vdc	1000pF+20%-20%	-	1000mA		Kit	$\geq 1A$					Reflow
		0.85	NFM21CC222R1H3	50Vdc	2200pF+20%-20%	-	1000mA		Kit	$\geq 1A$					Reflow
		0.85	NFM21CC223R1H3	50Vdc	22000pF+20%-20%	-	2000mA		Kit	$\geq 1A$					Reflow
	p129	0.7	NFM3DCC220U1H3	50Vdc	22pF+50%-20%	-	300mA							Flow	Reflow
		0.7	NFM3DCC470U1H3	50Vdc	47pF+50%-20%	-	300mA							Flow	Reflow
		0.7	NFM3DCC101U1H3	50Vdc	100pF+50%-20%	-	300mA							Flow	Reflow
		0.7	NFM3DCC221R1H3	50Vdc	220pF+50%-20%	-	300mA							Flow	Reflow
		0.7	NFM3DCC471R1H3	50Vdc	470pF+50%-20%	-	300mA							Flow	Reflow
		0.7	NFM3DCC102R1H3	50Vdc	1000pF+50%-20%	-	300mA							Flow	Reflow
		0.7	NFM3DCC222R1H3	50Vdc	2200pF+50%-20%	-	300mA							Flow	Reflow
		0.7	NFM3DCC223R1H3	50Vdc	22000pF+50%-20%	-	300mA							Flow	Reflow
	p130	1.0	NFM41CC220U2A3	100Vdc	22pF+50%-20%	-	300mA							Flow	Reflow
		1.0	NFM41CC470U2A3	100Vdc	47pF+50%-20%	-	300mA							Flow	Reflow
		1.0	NFM41CC101U2A3	100Vdc	100pF+50%-20%	-	300mA							Flow	Reflow
		1.0	NFM41CC221U2A3	100Vdc	220pF+50%-20%	-	300mA							Flow	Reflow
		1.0	NFM41CC471R2A3	100Vdc	470pF+50%-20%	-	300mA							Flow	Reflow
		1.0	NFM41CC102R2A3	100Vdc	1000pF+50%-20%	-	300mA							Flow	Reflow
		1.0	NFM41CC222R2A3	100Vdc	2200pF+50%-20%	-	300mA							Flow	Reflow
		1.0	NFM41CC223R2A3	100Vdc	22000pF+50%-20%	-	300mA							Flow	Reflow
Capacitor Array Type for Signal Lines	p131	0.8	NFA31CC220S1E4	25Vdc	22pF+20%-20%	-	200mA		Kit						Reflow
		0.8	NFA31CC470S1E4	25Vdc	47pF+20%-20%	-	200mA		Kit						Reflow
		0.8	NFA31CC101S1E4	25Vdc	100pF+20%-20%	-	200mA		Kit						Reflow
		0.8	NFA31CC221S1E4	25Vdc	220pF+20%-20%	-	200mA		Kit						Reflow
		0.8	NFA31CC471R1E4	25Vdc	470pF+20%-20%	-	200mA		Kit						Reflow
		0.8	NFA31CC102R1E4	25Vdc	1000pF+20%-20%	-	200mA		Kit						Reflow
		0.8	NFA31CC222R1E4	25Vdc	2200pF+20%-20%	-	200mA		Kit						Reflow
		0.8	NFA31CC223R1C4	16Vdc	22000pF+20%-20%	-	200mA		Kit						Reflow

Continued on the following page. 

Type	Size Code (Inch)	Thickness (mm)	Part Number	Rated Voltage	Capacitance	Nominal Cut-off Frequency	Rated Current	New	Kit	$\geq 1A$ $\geq 3A$ $\geq 10A$	DTV	Flow	ReFlow	
Capacitor Type for Power Lines	0603	p118	0.6	NFM18PS474R0J3	6.3Vdc	0.47μF+20%-20%	-	2A		Kit	$\geq 1A$		ReFlow	
			0.6	NFM18PS105R0J3	6.3Vdc	1.0μF+20%-20%	-	2A		Kit	$\geq 1A$		ReFlow	
		p119	0.6	NFM18PC104R1C3	16Vdc	0.1μF+20%-20%	-	2A		Kit	$\geq 1A$		ReFlow	
			0.6	NFM18PC224R0J3	6.3Vdc	0.22μF+20%-20%	-	2A		Kit	$\geq 1A$		ReFlow	
			0.6	NFM18PC474R0J3	6.3Vdc	0.47μF+20%-20%	-	2A		Kit	$\geq 1A$		ReFlow	
			0.6	NFM18PC105R0J3	6.3Vdc	1.0μF+20%-20%	-	4A		Kit	$\geq 1A$		ReFlow	
			0.6	NFM18PC225B0J3	6.3Vdc	2.2μF+20%-20%	-	2A		Kit	$\geq 1A$		ReFlow	
			0.8	NFM18PC225B1A3	10Vdc	2.2μF+20%-20%	-	4A		Kit	$\geq 3A$		ReFlow	
	0805	p121	0.85	NFM21PS106B0J3	6.3Vdc	10μF+20%-20%	-	4A		Kit	$\geq 3A$		ReFlow	
			p122	0.85	NFM21PC104R1E3	25Vdc	0.1μF+20%-20%	-	2A		Kit	$\geq 1A$		ReFlow
		0.85		NFM21PC224R1C3	16Vdc	0.22μF+20%-20%	-	2A		Kit	$\geq 1A$		ReFlow	
		0.85		NFM21PC474R1C3	16Vdc	0.47μF+20%-20%	-	2A		Kit	$\geq 1A$		ReFlow	
		0.85		NFM21PC105B1A3	10Vdc	1.0μF+20%-20%	-	4A		Kit	$\geq 3A$		ReFlow	
		0.85		NFM21PC105B1C3	16Vdc	1.0μF+20%-20%	-	4A		Kit	$\geq 3A$		ReFlow	
		0.85		NFM21PC225B0J3	6.3Vdc	2.2μF+20%-20%	-	4A		Kit	$\geq 3A$		ReFlow	
		0.85	NFM21PC475B1A3	10Vdc	4.7μF+20%-20%	-	6A		Kit	$\geq 3A$		ReFlow		
	1205	p123	0.7	NFM3DPC223R1H3	50Vdc	0.022μF+20%-20%	-	2A			$\geq 1A$		Flow	ReFlow
	1206	p124	1.3	NFM31PC276B0J3	6.3Vdc	27μF+20%-20%	-	6A		Kit	$\geq 3A$		Flow	ReFlow
			p125	1.3	NFM31KC103R1H3	50Vdc	10000pF+20%-20%	-	10A		Kit	$\geq 10A$		Flow
		1.3		NFM31KC103R2A3	100Vdc	10000pF+20%-20%	-	10A		Kit	$\geq 10A$		Flow	ReFlow
		1.3		NFM31KC153R1H3	50Vdc	15000pF+20%-20%	-	10A		Kit	$\geq 10A$		Flow	ReFlow
		1.3		NFM31KC153R2A3	100Vdc	15000pF+20%-20%	-	10A	New	Kit	$\geq 10A$		Flow	ReFlow
		1.3		NFM31KC223R1H3	50Vdc	22000pF+20%-20%	-	10A		Kit	$\geq 10A$		Flow	ReFlow
		1.3		NFM31KC223R2A3	100Vdc	22000pF+20%-20%	-	10A	New	Kit	$\geq 10A$		Flow	ReFlow
		1.3	NFM31KC104R1H3	50Vdc	100000pF+20%-20%	-	6A			$\geq 3A$		Flow	ReFlow	
	1.3	NFM31KC104R2A3	100Vdc	100000pF+20%-20%	-	6A	New	Kit	$\geq 3A$		Flow	ReFlow		
	1806	p126	1.0	NFM41PC204F1H3	50Vdc	0.2μF+80%-20%	-	2A		Kit	$\geq 1A$		Flow	ReFlow
			1.0	NFM41PC155B1E3	25Vdc	1.5μF+20%-20%	-	6A		Kit	$\geq 3A$		Flow	ReFlow
LC Combined Type for Power Lines and Signal Lines	1206	p116	1.6	NFE31PT220R1E9	25Vdc	22pF+30%-30%	-	6A			$\geq 3A$		ReFlow	
			1.6	NFE31PT470C1E9	25Vdc	47pF+50%-20%	-	6A			$\geq 3A$		ReFlow	
			1.6	NFE31PT101C1E9	25Vdc	100pF+80%-20%	-	6A			$\geq 3A$		ReFlow	
			1.6	NFE31PT221D1E9	25Vdc	220pF+50%-20%	-	6A			$\geq 3A$		ReFlow	
			1.6	NFE31PT471F1E9	25Vdc	470pF+50%-20%	-	6A			$\geq 3A$		ReFlow	
			1.6	NFE31PT152Z1E9	25Vdc	1500pF+50%-20%	-	6A		Kit	$\geq 3A$		ReFlow	
			1.6	NFE31PT222Z1E9	25Vdc	2200pF+50%-50%	-	6A			$\geq 3A$		ReFlow	
	2706	p117	1.6	NFE61PT330B1H9	50Vdc	33pF+30%-30%	-	2A			$\geq 1A$		Flow	ReFlow
			1.6	NFE61PT680B1H9	50Vdc	68pF+30%-30%	-	2A			$\geq 1A$		Flow	ReFlow
			1.6	NFE61PT101Z1H9	50Vdc	100pF+30%-30%	-	2A			$\geq 1A$		Flow	ReFlow
			1.6	NFE61PT181B1H9	50Vdc	180pF+30%-30%	-	2A			$\geq 1A$		Flow	ReFlow
			1.6	NFE61PT361B1H9	50Vdc	360pF+20%-20%	-	2A			$\geq 1A$		Flow	ReFlow
			1.6	NFE61PT681B1H9	50Vdc	680pF+30%-30%	-	2A			$\geq 1A$		Flow	ReFlow
			1.6	NFE61PT102E1H9	50Vdc	1000pF+80%-20%	-	2A		Kit	$\geq 1A$		Flow	ReFlow
			1.6	NFE61PT472C1H9	50Vdc	4700pF+80%-20%	-	2A			$\geq 1A$		Flow	ReFlow
LC Combined Multilayer Type for Signal Lines	0402	p132	0.3	NFL15ST157X0J3	6.3Vdc	22pF (Typ.)	150MHz	50mA		Kit		DTV	ReFlow	
			0.3	NFL15ST207X0J3	6.3Vdc	17pF (Typ.)	200MHz	50mA		Kit		DTV	ReFlow	
			0.3	NFL15ST307X0J3	6.3Vdc	12pF (Typ.)	300MHz	50mA		Kit			ReFlow	
			0.3	NFL15ST507X0J3	6.3Vdc	7pF (Typ.)	500MHz	50mA		Kit			ReFlow	
	0603	p133	0.6	NFL18ST506H1A3	10Vdc	110pF (Typ.)	50MHz	75mA		Kit		DTV	ReFlow	
			0.6	NFL18ST706H1A3	10Vdc	70pF (Typ.)	70MHz	75mA		Kit		DTV	ReFlow	
			0.6	NFL18ST107H1A3	10Vdc	50pF (Typ.)	100MHz	75mA		Kit		DTV	ReFlow	
			0.6	NFL18ST207H1A3	10Vdc	22pF (Typ.)	200MHz	100mA		Kit		DTV	ReFlow	
		p134	0.6	NFL18ST307H1A3	10Vdc	16pF (Typ.)	300MHz	100mA		Kit			ReFlow	
			0.6	NFL18ST507H1A3	10Vdc	10pF (Typ.)	500MHz	100mA		Kit			ReFlow	
			0.8	NFL18ST207X1C3	16Vdc	25pF+20%-20%	200MHz	150mA		Kit			ReFlow	
			0.8	NFL18ST307X1C3	16Vdc	18pF+20%-20%	300MHz	200mA		Kit			ReFlow	
			0.8	NFL18ST507X1C3	16Vdc	10pF+20%-20%	500MHz	200mA		Kit			ReFlow	
			p135	0.6	NFL18SP157X1A3	10Vdc	34pF+20%-20%	150MHz	100mA		Kit			ReFlow
				0.6	NFL18SP207X1A3	10Vdc	24pF+20%-20%	200MHz	100mA		Kit			ReFlow
0.6	NFL18SP307X1A3	10Vdc		19pF+20%-20%	300MHz	100mA		Kit			ReFlow			
0.6	NFL18SP507X1A3	10Vdc		11pF+20%-20%	500MHz	100mA		Kit			ReFlow			

Continued on the following page. 



Type	Size Code (Inch)	Thickness (mm)	Part Number	Rated Voltage	Capacitance	Nominal Cut-off Frequency	Rated Current	New	Kit	$\geq 1A$ $\geq 3A$ $\geq 10A$	DTV	Flow	Reflow
LC Combined Multilayer Type for Signal Lines	p136	0.85	NFL21SP106X1C3	16Vdc	670pF+20%-20%	10MHz	100mA		Kit				Reflow
		0.85	NFL21SP206X1C7	16Vdc	240pF+20%-20%	20MHz	100mA		Kit				Reflow
		0.85	NFL21SP506X1C3	16Vdc	84pF+20%-20%	50MHz	150mA		Kit				Reflow
		0.85	NFL21SP706X1C3	16Vdc	76pF+20%-20%	70MHz	150mA		Kit				Reflow
		0.85	NFL21SP107X1C3	16Vdc	44pF+20%-20%	100MHz	200mA		Kit				Reflow
		0.85	NFL21SP157X1C3	16Vdc	28pF+20%-20%	150MHz	200mA		Kit				Reflow
		0.85	NFL21SP207X1C3	16Vdc	22pF+20%-20%	200MHz	250mA		Kit				Reflow
		0.85	NFL21SP307X1C3	16Vdc	19pF+10%-10%	300MHz	300mA		Kit				Reflow
		0.85	NFL21SP407X1C3	16Vdc	16pF+10%-10%	400MHz	300mA		Kit				Reflow
		0.85	NFL21SP507X1C3	16Vdc	12pF+10%-10%	500MHz	300mA		Kit				Reflow
LC Combined Array Type for Signal Lines	p137	0.6	NFA18SL137V1A45	10Vdc	-	130MHz	50mA		Kit		DTV		Reflow
		0.6	NFA18SL187V1A45	10Vdc	-	180MHz	50mA		Kit		DTV		Reflow
		0.6	NFA18SL207V1A45	10Vdc	-	200MHz	50mA		Kit		DTV		Reflow
		0.6	NFA18SL227V1A45	10Vdc	-	220MHz	25mA		Kit		DTV		Reflow
		0.5	NFA18SL307V1A45	10Vdc	-	300MHz	100mA		Kit				Reflow
		0.5	NFA18SL357V1A45	10Vdc	-	350MHz	35mA		Kit				Reflow
		0.5	NFA18SL407V1A45	10Vdc	-	400MHz	100mA		Kit				Reflow
		0.5	NFA18SL487V1A45	10Vdc	-	480MHz	100mA		Kit				Reflow
		0.5	NFA18SL506X1A45	10Vdc	-	50MHz	25mA		Kit				Reflow
	p138	0.6	NFA18SD187X1A45	10Vdc	-	180MHz	25mA		Kit		DTV		Reflow
		0.6	NFA18SD207X1A45	10Vdc	-	200MHz	25mA		Kit		DTV		Reflow
	p139	0.6	NFA18SD207X1A45	10Vdc	-	200MHz	25mA		Kit		DTV		Reflow
		0.6	NFA18SD207X1A45	10Vdc	-	200MHz	25mA		Kit		DTV		Reflow
	p140	0.5	NFA21SL287V1A45	10Vdc	-	280MHz	100mA		Kit				Reflow
		0.5	NFA21SL317V1A45	10Vdc	-	310MHz	100mA		Kit				Reflow
		0.5	NFA21SL337V1A45	10Vdc	-	330MHz	100mA		Kit				Reflow
		0.85	NFA21SL287V1A48	10Vdc	-	280MHz	100mA		Kit				Reflow
		0.85	NFA21SL317V1A48	10Vdc	-	310MHz	100mA		Kit				Reflow
		0.85	NFA21SL337V1A48	10Vdc	-	330MHz	100mA		Kit				Reflow
		0.85	NFA21SL207X1A45	10Vdc	-	200MHz	100mA		Kit				Reflow
		0.5	NFA21SL307X1A45	10Vdc	-	300MHz	100mA		Kit				Reflow
		0.85	NFA21SL506X1A48	10Vdc	-	50MHz	20mA		Kit				Reflow
	p141	0.85	NFA21SL806X1A48	10Vdc	-	80MHz	20mA		Kit				Reflow
		0.85	NFA21SL207X1A48	10Vdc	-	200MHz	100mA		Kit				Reflow
		0.85	NFA21SL307X1A48	10Vdc	-	300MHz	100mA		Kit				Reflow
		0.85	NFA21SL307X1A48	10Vdc	-	300MHz	100mA		Kit				Reflow
		0.85	NFA21SL307X1A48	10Vdc	-	300MHz	100mA		Kit				Reflow
LC Combined Wire Wound Type for Signal Lines	p142	1.8	NFW31SP106X1E4	-	-	10MHz	-		Kit			Flow	Reflow
		1.8	NFW31SP206X1E4	-	-	20MHz	-		Kit			Flow	Reflow
		1.8	NFW31SP506X1E4	-	-	50MHz	-		Kit			Flow	Reflow
		1.8	NFW31SP107X1E4	-	-	100MHz	-		Kit			Flow	Reflow
		1.8	NFW31SP157X1E4	-	-	150MHz	-		Kit			Flow	Reflow
		1.8	NFW31SP207X1E4	-	-	200MHz	-		Kit			Flow	Reflow
		1.8	NFW31SP307X1E4	-	-	300MHz	-		Kit			Flow	Reflow
		1.8	NFW31SP407X1E4	-	-	400MHz	-		Kit			Flow	Reflow
RC Combined Type for Signal Lines	p144	0.5	NFR21GD1002202	50Vdc	10pF+20%-20%	-	50mA						Reflow
		0.5	NFR21GD1004702	50Vdc	10pF+20%-20%	-	35mA						Reflow
		0.5	NFR21GD4702202	50Vdc	47pF+20%-20%	-	50mA						Reflow
		0.5	NFR21GD4704702	50Vdc	47pF+20%-20%	-	35mA						Reflow
		0.5	NFR21GD4706802	50Vdc	47pF+20%-20%	-	30mA						Reflow
		0.5	NFR21GD4701012	50Vdc	47pF+20%-20%	-	25mA						Reflow
		0.5	NFR21GD1012202	50Vdc	100pF+20%-20%	-	50mA						Reflow
		0.5	NFR21GD1014702	50Vdc	100pF+20%-20%	-	35mA						Reflow
		0.5	NFR21GD1016802	50Vdc	100pF+20%-20%	-	30mA						Reflow
RC Combined Array Type for Signal Lines	p145	0.8	NFA31GD1006R84	6Vdc	10pF+20%-20%	-	50mA						Reflow
		0.8	NFA31GD1004704	6Vdc	10pF+20%-20%	-	20mA						Reflow
		0.8	NFA31GD1001014	6Vdc	10pF+20%-20%	-	15mA						Reflow
		0.8	NFA31GD4706R84	6Vdc	47pF+20%-20%	-	50mA						Reflow
		0.8	NFA31GD4703304	6Vdc	47pF+20%-20%	-	20mA						Reflow
		0.8	NFA31GD4704704	6Vdc	47pF+20%-20%	-	20mA						Reflow
		0.8	NFA31GD4701014	6Vdc	47pF+20%-20%	-	15mA						Reflow
		0.8	NFA31GD1016R84	6Vdc	100pF+20%-20%	-	50mA						Reflow
		0.8	NFA31GD1014704	6Vdc	100pF+20%-20%	-	20mA						Reflow
RC Combined Array Type for Signal Lines	p145	0.8	NFA31GD1011014	6Vdc	100pF+20%-20%	-	15mA						Reflow
		0.8	NFA31GD1011014	6Vdc	100pF+20%-20%	-	15mA						Reflow

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# NFE31P Series (1206 Size)




Meets 6A, T-type filter with built-in ferrite bead.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	2000
K	330mm Reel Embossed Tape	8000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

## Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
NFE31PT220R1E9□	22pF ±30%	6A	25Vdc	1000M ohm	-40°C to +85°C	≥3A
NFE31PT470C1E9□	47pF 50/-20%	6A	25Vdc	1000M ohm	-40°C to +85°C	≥3A
NFE31PT101C1E9□	100pF 80/-20%	6A	25Vdc	1000M ohm	-40°C to +85°C	≥3A
NFE31PT221D1E9□	220pF 50/-20%	6A	25Vdc	1000M ohm	-40°C to +85°C	≥3A
NFE31PT471F1E9□	470pF 50/-20%	6A	25Vdc	1000M ohm	-40°C to +85°C	≥3A
NFE31PT152Z1E9□	1500pF 50/-20%	6A	25Vdc	1000M ohm	-40°C to +85°C	Kit ≥3A
NFE31PT222Z1E9□	2200pF ±50%	6A	25Vdc	1000M ohm	-40°C to +85°C	≥3A

Number of Circuit: 1

## Insertion Loss Characteristics



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# NFE61P Series (2706 Size)




## T-type filter with built-in ferrite bead.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	2500
K	330mm Reel Embossed Tape	8000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
NFE61PT330B1H9□	33pF ±30%	2A	50Vdc	1000M ohm	-40°C to +85°C	≥1A
NFE61PT680B1H9□	68pF ±30%	2A	50Vdc	1000M ohm	-40°C to +85°C	≥1A
NFE61PT101Z1H9□	100pF ±30%	2A	50Vdc	1000M ohm	-40°C to +85°C	≥1A
NFE61PT181B1H9□	180pF ±30%	2A	50Vdc	1000M ohm	-40°C to +85°C	≥1A
NFE61PT361B1H9□	360pF ±20%	2A	50Vdc	1000M ohm	-40°C to +85°C	≥1A
NFE61PT681B1H9□	680pF ±30%	2A	50Vdc	1000M ohm	-40°C to +85°C	≥1A
NFE61PT102E1H9□	1000pF 80/-20%	2A	50Vdc	1000M ohm	-40°C to +85°C	Kit ≥1A
NFE61PT472C1H9□	4700pF 80/-20%	2A	50Vdc	1000M ohm	-40°C to +85°C	≥1A

Number of Circuit: 1

### ■ Insertion Loss Characteristics



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



# NFM18PS Series (0603 Size)




## 3-terminal capacitor for power lines whose ground impedance has reduced.


\*Please refer to the products designed for both power lines and signal lines.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
NFM18PS474R0J3□	0.47μF ±20%	2A	6.3Vdc	1000M ohm	-55°C to +125°C	Kit ≥1A
NFM18PS105R0J3□	1.0μF ±20%	2A	6.3Vdc	500M ohm	-55°C to +105°C	Kit ≥1A

Number of Circuit: 1

### ■ Insertion Loss Characteristics



# NFM18PC Series (0603 Size)




## 4A max, 0603 size chip 3-terminal capacitor for power lines.

\*Please refer to the products designed for both power lines and signal lines.


### NFM18PC (0.1 to 0.47μF, 2.2μF - 6.3V)



#### ■ Dimensions



#### ■ Equivalent Circuit




#### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	500


### NFM18PC (1μF, 2.2μF - 10V)



#### ■ Dimensions



#### ■ Equivalent Circuit



#### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

#### ■ Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
NFM18PC104R1C3□	0.1μF ±20%	2A	16Vdc	1000M ohm	-55°C to +125°C	Kit ≥1A
NFM18PC224R0J3□	0.22μF ±20%	2A	6.3Vdc	1000M ohm	-55°C to +125°C	Kit ≥1A
NFM18PC474R0J3□	0.47μF ±20%	2A	6.3Vdc	1000M ohm	-55°C to +125°C	Kit ≥1A
NFM18PC105R0J3□	1.0μF ±20%	4A	6.3Vdc	500M ohm	-55°C to +105°C	Kit ≥1A
NFM18PC225B0J3□	2.2μF ±20%	2A	6.3Vdc	200M ohm	-40°C to +85°C	Kit ≥1A
NFM18PC225B1A3□	2.2μF ±20%	4A	10Vdc	200M ohm	-40°C to +85°C	Kit ≥3A


Number of Circuit: 1

#### ■ Insertion Loss Characteristics



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## • High frequency performance of NFM18PS series



### Chip 3-terminal capacitor

2 terminal MLCC: 2012mm size  
(0.1 $\mu$ Fx10pcs parallel)


NFM18PC105R0J3 1pc  
: 1608mm size (1.0 $\mu$ Fx1)

NFM18PS105R0J3 1pc  
: 1608mm size (1.0 $\mu$ Fx1)

NFM18PS series has better high-frequency performance compared to normal chip 3 terminal capacitors.




## • Optimize of bypass capacitors using chip 3-terminal capacitor

Number of parts can be reduced.  
⇒ • Reduce PCB space  
• Reduce mount cost






## Comparison of performance as a bypass capacitor




### Without capacitor



### With MLCC 0.22 $\mu$ Fx4



### With chip 3-terminal capacitor (NFM) 1 $\mu$ Fx1



Noise suppression effect of NFM series is better than MLCCs (1 NFM is better than 4 MLCCs).


# NFM21PS Series (0805 Size)




2012mm size 3-terminal capacitor with very low ground impedance.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

## Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
NFM21PS106B0J3□	10μF ±20%	4A	6.3Vdc	50M ohm	-40°C to +85°C	Kit ≥3A

Number of Circuit: 1

## Insertion Loss Characteristics



# NFM21PC Series (0805 Size)




**6A max, 0805 size chip 3-terminal capacitor for power lines.**


\*Please refer to the products designed for both power lines and signal lines.



## ■ Dimensions



## ■ Equivalent Circuit



## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

## ■ Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
NFM21PC104R1E3□	0.1μF ±20%	2A	25Vdc	1000M ohm	-55°C to +125°C	Kit ≥1A
NFM21PC224R1C3□	0.22μF ±20%	2A	16Vdc	1000M ohm	-55°C to +125°C	Kit ≥1A
NFM21PC474R1C3□	0.47μF ±20%	2A	16Vdc	1000M ohm	-55°C to +125°C	Kit ≥1A
NFM21PC105B1A3□	1.0μF ±20%	4A	10Vdc	500M ohm	-40°C to +85°C	Kit ≥3A
NFM21PC105B1C3□	1.0μF ±20%	4A	16Vdc	500M ohm	-40°C to +85°C	Kit ≥3A
NFM21PC225B0J3□	2.2μF ±20%	4A	6.3Vdc	200M ohm	-40°C to +85°C	Kit ≥3A
NFM21PC475B1A3□	4.7μF ±20%	6A	10Vdc	100M ohm	-40°C to +85°C	Kit ≥3A

Number of Circuit: 1

## ■ Insertion Loss Characteristics



# NFM3DP Series (1205 Size)




## 1205 size 3-terminal capacitor for power lines.


\*Please refer to the products designed for both power lines and signal lines.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	4000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
NFM3DPC223R1H3□	$0.022\mu\text{F} \pm 20\%$	2A	50Vdc	1000M ohm	$-55^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	$\geq 1\text{A}$

Number of Circuit: 1

### ■ Insertion Loss Characteristics




### ■ Notice (Rating)

When NFM3DP series is used in operating temperature exceeding  $+85^{\circ}\text{C}$ , derating of current is necessary.

Please apply the derating curve shown in chart according to the operating temperature.

#### Derating of Rated Current



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# NFM31P Series (1206 Size)




## 6A/27microF, 1206 size chip 3-terminal capacitor for power lines.


\*Please refer to the products designed for both power lines and signal lines.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	3000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
NFM31PC276B0J3□	27μF ±20%	6A	6.3Vdc	20M ohm	-40°C to +85°C	Kit ≥3A

Number of Circuit: 1

### ■ Insertion Loss Characteristics






# NFM31K Series (1206 Size)




Capable for 10A max. Large current 3-terminal capacitor.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	3000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

## Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range		
NFM31KC103R1H3□	10000pF ±20%	10A	50Vdc	1000M ohm	-55°C to +125°C	Kit	≥10A
NFM31KC103R2A3□	10000pF ±20%	10A	100Vdc	1000M ohm	-55°C to +125°C	Kit	≥10A
NFM31KC153R1H3□	15000pF ±20%	10A	50Vdc	1000M ohm	-55°C to +125°C	Kit	≥10A
NFM31KC153R2A3□	15000pF ±20%	10A	100Vdc	1000M ohm	-55°C to +105°C	New Kit	≥10A
NFM31KC223R1H3□	22000pF ±20%	10A	50Vdc	1000M ohm	-55°C to +125°C	Kit	≥10A
NFM31KC223R2A3□	22000pF ±20%	10A	100Vdc	1000M ohm	-55°C to +105°C	New Kit	≥10A
NFM31KC104R1H3□	100000pF ±20%	6A	50Vdc	1000M ohm	-55°C to +125°C		≥3A
NFM31KC104R2A3□	100000pF ±20%	6A	100Vdc	1000M ohm	-55°C to +105°C	New Kit	≥3A

Number of Circuit: 1

## Insertion Loss Characteristics




## Notice (Rating)

When NFM31K series is used in operating temperatures exceeding +105°C, derating of current is necessary.

Please apply the derating curve shown in chart according to the operating temperature.

### Derating of Rated Current



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# NFM41P Series (1806 Size)




## 6A max, 1806 size chip 3-terminal capacitor for power lines.


\*Please refer to the products designed for both power lines and signal lines.



### Dimensions



### Equivalent Circuit



### Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	4000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

### Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
NFM41PC204F1H3□	$0.2\mu\text{F} +80/-20\%$	2A	50Vdc	1000M ohm	-55°C to +85°C	Kit $\geq 1\text{A}$
NFM41PC155B1E3□	$1.5\mu\text{F} \pm 20\%$	6A	25Vdc	300M ohm	-55°C to +85°C	Kit $\geq 3\text{A}$

Number of Circuit: 1

### Insertion Loss Characteristics




# NFM18C Series (0603 Size)




## 0603 size general 3-terminal capacitor.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
NFM18CC220U1C3□	22pF ±20%	400mA	16Vdc	1000M ohm	-55°C to +125°C	Kit
NFM18CC470U1C3□	47pF ±20%	400mA	16Vdc	1000M ohm	-55°C to +125°C	Kit
NFM18CC101R1C3□	100pF ±20%	500mA	16Vdc	1000M ohm	-55°C to +125°C	Kit
NFM18CC221R1C3□	220pF ±20%	500mA	16Vdc	1000M ohm	-55°C to +125°C	Kit
NFM18CC471R1C3□	470pF ±20%	500mA	16Vdc	1000M ohm	-55°C to +125°C	Kit
NFM18CC102R1C3□	1000pF ±20%	600mA	16Vdc	1000M ohm	-55°C to +125°C	Kit
NFM18CC222R1C3□	2200pF ±20%	700mA	16Vdc	1000M ohm	-55°C to +125°C	Kit
NFM18CC223R1C3□	22000pF ±20%	1000mA	16Vdc	1000M ohm	-55°C to +125°C	Kit ≥1A

Number of Circuit: 1

### ■ Insertion Loss Characteristics



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# NFM21C Series (0805 Size)




## 0805 size general 3-terminal capacitor.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
NFM21CC220U1H3□	22pF ±20%	700mA	50Vdc	1000M ohm	-55°C to +125°C	Kit
NFM21CC470U1H3□	47pF ±20%	700mA	50Vdc	1000M ohm	-55°C to +125°C	Kit
NFM21CC101U1H3□	100pF ±20%	700mA	50Vdc	1000M ohm	-55°C to +125°C	Kit
NFM21CC221R1H3□	220pF ±20%	700mA	50Vdc	1000M ohm	-55°C to +125°C	Kit
NFM21CC471R1H3□	470pF ±20%	1000mA	50Vdc	1000M ohm	-55°C to +125°C	Kit ≥1A
NFM21CC102R1H3□	1000pF ±20%	1000mA	50Vdc	1000M ohm	-55°C to +125°C	Kit ≥1A
NFM21CC222R1H3□	2200pF ±20%	1000mA	50Vdc	1000M ohm	-55°C to +125°C	Kit ≥1A
NFM21CC223R1H3□	22000pF ±20%	2000mA	50Vdc	1000M ohm	-55°C to +125°C	Kit ≥1A

Number of Circuit: 1

### ■ Insertion Loss Characteristics



△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# NFM3DC Series (1205 Size)




## 1205 size general 3-terminal capacitor.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	4000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range
NFM3DCC220U1H3□	22pF +50/-20%	300mA	50Vdc	1000M ohm	-55°C to +125°C
NFM3DCC470U1H3□	47pF +50/-20%	300mA	50Vdc	1000M ohm	-55°C to +125°C
NFM3DCC101U1H3□	100pF +50/-20%	300mA	50Vdc	1000M ohm	-55°C to +125°C
NFM3DCC221R1H3□	220pF +50/-20%	300mA	50Vdc	1000M ohm	-55°C to +125°C
NFM3DCC471R1H3□	470pF +50/-20%	300mA	50Vdc	1000M ohm	-55°C to +125°C
NFM3DCC102R1H3□	1000pF +50/-20%	300mA	50Vdc	1000M ohm	-55°C to +125°C
NFM3DCC222R1H3□	2200pF +50/-20%	300mA	50Vdc	1000M ohm	-55°C to +125°C
NFM3DCC223R1H3□	22000pF +50/-20%	300mA	50Vdc	1000M ohm	-55°C to +125°C

Number of Circuit: 1

### ■ Insertion Loss Characteristics




# NFM41C Series (1806 Size)




## 1806 size general 3-terminal capacitor.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	4000
B	Bulk(Bag)	500


Refer to pages from p.147 to p.152 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range
NFM41CC220U2A3□	22pF +50/-20%	300mA	100Vdc	10000M ohm	-55°C to +125°C
NFM41CC470U2A3□	47pF +50/-20%	300mA	100Vdc	10000M ohm	-55°C to +125°C
NFM41CC101U2A3□	100pF +50/-20%	300mA	100Vdc	10000M ohm	-55°C to +125°C
NFM41CC221U2A3□	220pF +50/-20%	300mA	100Vdc	10000M ohm	-55°C to +125°C
NFM41CC471R2A3□	470pF +50/-20%	300mA	100Vdc	10000M ohm	-55°C to +125°C
NFM41CC102R2A3□	1000pF +50/-20%	300mA	100Vdc	10000M ohm	-55°C to +125°C
NFM41CC222R2A3□	2200pF +50/-20%	300mA	100Vdc	10000M ohm	-55°C to +125°C
NFM41CC223R2A3□	22000pF +50/-20%	300mA	100Vdc	10000M ohm	-55°C to +125°C

Number of Circuit: 1

### ■ Insertion Loss Characteristics



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# NFA31C Series (1206 Size)




4-line chip 3-terminal capacitor array, 1206 size.



## ■ Dimensions



## ■ Equivalent Circuit



## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	100


Refer to pages from p.147 to p.152 for mounting information.

## ■ Rated Value (□: packaging code)

Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
NFA31CC220S1E4□	22pF ±20%	200mA	25Vdc	1000M ohm	-40°C to +85°C	Kit
NFA31CC470S1E4□	47pF ±20%	200mA	25Vdc	1000M ohm	-40°C to +85°C	Kit
NFA31CC101S1E4□	100pF ±20%	200mA	25Vdc	1000M ohm	-40°C to +85°C	Kit
NFA31CC221S1E4□	220pF ±20%	200mA	25Vdc	1000M ohm	-40°C to +85°C	Kit
NFA31CC471R1E4□	470pF ±20%	200mA	25Vdc	1000M ohm	-40°C to +85°C	Kit
NFA31CC102R1E4□	1000pF ±20%	200mA	25Vdc	1000M ohm	-40°C to +85°C	Kit
NFA31CC222R1E4□	2200pF ±20%	200mA	25Vdc	1000M ohm	-40°C to +85°C	Kit
NFA31CC223R1C4□	22000pF ±20%	200mA	16Vdc	1000M ohm	-40°C to +85°C	Kit

Number of Circuit: 4

## ■ Insertion Loss Characteristics



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




# NFL15ST Series (0402 Size)




## T-type LC filter, ultra-compact size of 1005mm



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
B	Bulk(Bag)	500

Refer to pages from p.147 to p.152 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Nominal Cut-off Frequency	Capacitance	Inductance	Insertion Loss 1	Insertion Loss 2	Rated Current	Rated Voltage	
NFL15ST157X0J3□	150MHz	22pF (Typ.)	115nH (Typ.)	6dB max.(0 to 150MHz)	25dB min.(200 to 1000MHz)	50mA	6.3Vdc	Kit DTV
NFL15ST207X0J3□	200MHz	17pF (Typ.)	105nH (Typ.)	6dB max.(0 to 200MHz)	25dB min.(400 to 1000MHz)	50mA	6.3Vdc	Kit DTV
NFL15ST307X0J3□	300MHz	12pF (Typ.)	95nH (Typ.)	6dB max.(0 to 300MHz)	25dB min.(600 to 1000MHz)	50mA	6.3Vdc	Kit
NFL15ST507X0J3□	500MHz	7pF (Typ.)	60nH (Typ.)	6dB max.(0 to 500MHz)	25dB min.(600 to 1000MHz)	50mA	6.3Vdc	Kit


Insulation Resistance (min.): 1000M ohm

Withstand Voltage: 18.9Vdc

Operating Temperature Range: -40°C to +85°C

Number of Circuits: 1

### ■ Insertion Loss Characteristics



# NFL18ST Series (0603 Size)




T-type LC filter. Reduces waveform distortion of high speed signal.

NFL18ST\_H




## Dimensions



\*1 There are no electrical polarity. But there is a directional marking on the top of product to identify inner physical direction.

## Equivalent Circuit




## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	1000


NFL18ST\_X



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	1000

Refer to pages from p.147 to p.152 for mounting information.


## Rated Value (□: packaging code)

Part Number	Nominal Cut-off Frequency	Capacitance	Inductance	Insertion Loss 1	Insertion Loss 2	Rated Current	Rated Voltage	
NFL18ST506H1A3□	50MHz	110pF (Typ.)	350nH (Typ.)	6dB max.(0 to 50MHz)	30dB min.(200 to 1000MHz)	75mA	10Vdc	Kit DTV
NFL18ST706H1A3□	70MHz	70pF (Typ.)	230nH (Typ.)	6dB max.(0 to 70MHz)	30dB min.(300 to 1000MHz)	75mA	10Vdc	Kit DTV
NFL18ST107H1A3□	100MHz	50pF (Typ.)	150nH (Typ.)	6dB max.(0 to 100MHz)	30dB min.(400 to 1000MHz)	75mA	10Vdc	Kit DTV
NFL18ST207H1A3□	200MHz	22pF (Typ.)	110nH (Typ.)	6dB max.(0 to 200MHz)	30dB min.(800 to 2000MHz)	100mA	10Vdc	Kit DTV
NFL18ST307H1A3□	300MHz	16pF (Typ.)	74nH (Typ.)	6dB max.(0 to 300MHz)	30dB min.(1200 to 2000MHz)	100mA	10Vdc	Kit
NFL18ST507H1A3□	500MHz	10pF (Typ.)	42nH (Typ.)	6dB max.(0 to 500MHz)	30dB min.(1700 to 2000MHz)	100mA	10Vdc	Kit

Insulation Resistance (min.): 1000M ohm Withstand Voltage: 30Vdc Operating Temperature Range: -55°C to +125°C Number of Circuits: 1

## Insertion Loss Characteristics

### NFL18ST\_H Series



Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

C31E.pdf  
Aug.1,2013


## ■ Rated Value (□: packaging code)

Part Number	Nominal Cut-off Frequency	Capacitance	Inductance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	Operating Temperature Range	
NFL18ST207X1C3□	200MHz	25pF±20%	110nH±20%	150mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit
NFL18ST307X1C3□	300MHz	18pF±20%	62nH±20%	200mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit
NFL18ST507X1C3□	500MHz	10pF±20%	43nH±20%	200mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit

Number of Circuits: 1

## ■ Insertion Loss Characteristics

## NFL18ST\_X Series




# NFL18SP Series (0603 Size)




PI-type LC filter. Reduces waveform distortion of high speed signal.



## ■ Dimensions



## ■ Equivalent Circuit



## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	1000


Refer to pages from p.147 to p.152 for mounting information.

## ■ Rated Value (□: packaging code)

Part Number	Nominal Cut-off Frequency	Capacitance	Inductance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	Operating Temperature Range	
NFL18SP157X1A3□	150MHz	34pF±20%	100nH±20%	100mA	10Vdc	1000M ohm	30Vdc	-55°C to +125°C	Kit
NFL18SP207X1A3□	200MHz	24pF±20%	80nH±20%	100mA	10Vdc	1000M ohm	30Vdc	-55°C to +125°C	Kit
NFL18SP307X1A3□	300MHz	19pF±20%	60nH±20%	100mA	10Vdc	1000M ohm	30Vdc	-55°C to +125°C	Kit
NFL18SP507X1A3□	500MHz	11pF±20%	38nH±20%	100mA	10Vdc	1000M ohm	30Vdc	-55°C to +125°C	Kit

Number of Circuits: 1

## ■ Insertion Loss Characteristics




# NFL21SP Series (0805 Size)




PI-type LC filter. Reduces waveform distortion of high speed signal.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	1000


Refer to pages from p.147 to p.152 for mounting information.

## Rated Value (□: packaging code)

Part Number	Nominal Cut-off Frequency	Capacitance	Inductance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	Operating Temperature Range	
NFL21SP106X1C3□	10MHz	670pF±20%	680nH±20%	100mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit
NFL21SP206X1C7□	20MHz	240pF±20%	700nH±20%	100mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit
NFL21SP506X1C3□	50MHz	84pF±20%	305nH±20%	150mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit
NFL21SP706X1C3□	70MHz	76pF±20%	185nH±20%	150mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit
NFL21SP107X1C3□	100MHz	44pF±20%	135nH±20%	200mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit
NFL21SP157X1C3□	150MHz	28pF±20%	128nH±20%	200mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit
NFL21SP207X1C3□	200MHz	22pF±20%	72nH±20%	250mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit
NFL21SP307X1C3□	300MHz	19pF±10%	45nH±10%	300mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit
NFL21SP407X1C3□	400MHz	16pF±10%	34nH±10%	300mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit
NFL21SP507X1C3□	500MHz	12pF±10%	31nH±10%	300mA	16Vdc	1000M ohm	50Vdc	-55°C to +125°C	Kit

Number of Circuits: 1

## Insertion Loss Characteristics



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# NFA18SL Series (0603 Size)




## LC filter 4-line array for mobile phones.


NFA18SL 137/187/207/357 V1A45  
NFA18SL506X1A45



### ■ Dimensions



### ■ Equivalent Circuit




### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	4000
B	Bulk(Bag)	1000


NFA18SL227V1A45



### ■ Dimensions



### ■ Equivalent Circuit




### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	4000
B	Bulk(Bag)	1000


NFA18SL 307/407/487 V1A45



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	4000
B	Bulk(Bag)	1000

Refer to pages from p.147 to p.152 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Nominal Cut-off Frequency	Insertion Loss (Cut-off Frequency)	Insertion Loss (470MHz) (min.)	Insertion Loss (800MHz) (min.)	Insertion Loss (900MHz) (min.)	Insertion Loss (2000MHz) (min.)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	Kit
NFA18SL137V1A45□	130MHz	6dB max.	25dB	-	25dB	-	50mA	10Vdc	1000M ohm	30Vdc	Kit
NFA18SL187V1A45□	180MHz	6dB max.	20dB	-	20dB	-	50mA	10Vdc	1000M ohm	30Vdc	Kit
NFA18SL207V1A45□	200MHz	6dB max.	15dB	-	15dB	-	50mA	10Vdc	1000M ohm	30Vdc	Kit
NFA18SL227V1A45□	220MHz	6dB max.	-	-	30dB	30dB	25mA	10Vdc	1000M ohm	30Vdc	Kit
NFA18SL307V1A45□	300MHz	6dB max.	-	20dB	20dB	-	100mA	10Vdc	1000M ohm	30Vdc	Kit
NFA18SL357V1A45□	350MHz	6dB max.	-	-	15dB	13dB	35mA	10Vdc	1000M ohm	30Vdc	Kit
NFA18SL407V1A45□	400MHz	6dB max.	-	18dB	18dB	-	100mA	10Vdc	1000M ohm	30Vdc	Kit
NFA18SL487V1A45□	480MHz	6dB max.	-	15dB	15dB	-	100mA	10Vdc	1000M ohm	30Vdc	Kit

Operating Temperature Range: -40°C to +85°C (NFA18SL 137/187/207/227/357 V1A45), -55°C to +125°C (NFA18SL 307/407/487 V1A45)


Number of Circuits: 4

Continued on the following page.


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## ■ Insertion Loss Characteristics


### NFA18SL 137/187/207 V1A45




### NFA18SL227V1A45



### NFA18SL 307/407/487 V1A45



### NFA18SL357V1A45




## ■ Rated Value (□: packaging code)

Part Number	Nominal Cut-off Frequency	Insertion Loss (Cut-off Frequency)	Insertion Loss (500MHz) (min.)	Insertion Loss (1000MHz) (min.)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	
NFA18SL506X1A45□	50MHz	6dB max.	30dB	25dB	25mA	10Vdc	1000M ohm	30Vdc	Kit

Operating Temperature Range: -40°C to +85°C Number of Circuits: 4

## ■ Insertion Loss Characteristics

### NFA18SL\_X






# NFA18SD Series (0603 Size)




**For differential signal I/F of LCD or camera in mobile phones.**

## ■ Dimensions



## ■ Equivalent Circuit





## ■ Packaging

Code	Packaging	Minimum Quantity
<b>L</b>	180mm Reel Embossed Tape	4000
<b>B</b>	Bulk(Bag)	1000


Refer to pages from p.147 to p.152 for mounting information.

■ Rated Value (□: packaging code)

Part Number	Nominal Cut-off Frequency	Insertion Loss (Cut-off Frequency)	Insertion Loss (500MHz) (min.)	Insertion Loss (900MHz) (min.)	Insertion Loss (1500MHz) (min.)	Insertion Loss (2000MHz) (min.)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	
<b>NFA18SD187X1A45</b>	180MHz	6dB max.	15dB	20dB	20dB	20dB	25mA	10Vdc	1000M ohm	30Vdc	<b>Kit</b> 
<b>NFA18SD207X1A45</b>	200MHz	6dB max.	13dB	20dB	20dB	20dB	25mA	10Vdc	1000M ohm	30Vdc	<b>Kit</b> 

Operating Temperature Range: -40°C to +85°C	Number of Circuits: 4
---	-----------------------

### ■ Insertion Loss Characteristics




# NFA21SL Series (0805 Size)




## L-type LC filter 4-line array for mobile phones.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	4000
B	Bulk(Bag)	1000

Refer to pages from p.147 to p.152 for mounting information.


### ■ Rated Value (□: packaging code)

Part Number	Nominal Cut-off Frequency	Insertion Loss (Cut-off Frequency)	Insertion Loss (800MHz) (min.)	Insertion Loss (900MHz) (min.)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	
NFA21SL287V1A45□	280MHz	6dB max.	25dB	25dB	100mA	10Vdc	1000M ohm	30Vdc	Kit
NFA21SL317V1A45□	310MHz	6dB max.	20dB	20dB	100mA	10Vdc	1000M ohm	30Vdc	Kit
NFA21SL337V1A45□	330MHz	6dB max.	15dB	15dB	100mA	10Vdc	1000M ohm	30Vdc	Kit
NFA21SL287V1A48□	280MHz	6dB max.	25dB	25dB	100mA	10Vdc	1000M ohm	30Vdc	Kit
NFA21SL317V1A48□	310MHz	6dB max.	20dB	20dB	100mA	10Vdc	1000M ohm	30Vdc	Kit
NFA21SL337V1A48□	330MHz	6dB max.	20dB	20dB	100mA	10Vdc	1000M ohm	30Vdc	Kit


Operating Temperature Range: -55°C to +125°C Number of Circuits: 4

### ■ Insertion Loss Characteristics

NFA21SL\_V1A45



NFA21SL\_V1A48



Continued on the following page.


■ Rated Value (□: packaging code)

Part Number	Nominal Cut-off Frequency	Insertion Loss (Cut-off Frequency)	Insertion Loss (500MHz) (min.)	Insertion Loss (800MHz) (min.)	Insertion Loss (1000MHz) (min.)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	
NFA21SL207X1A45□	200MHz	2dB to 7dB	13dB	25dB	25dB	100mA	10Vdc	1000M ohm	30Vdc	Kit
NFA21SL307X1A45□	300MHz	2dB to 7dB	7dB	20dB	25dB	100mA	10Vdc	1000M ohm	30Vdc	Kit
NFA21SL506X1A48□	50MHz	0dB to 6dB	30dB	-	20dB	20mA	10Vdc	1000M ohm	30Vdc	Kit
NFA21SL806X1A48□	80MHz	2dB to 7dB	25dB	-	25dB	20mA	10Vdc	1000M ohm	30Vdc	Kit
NFA21SL207X1A48□	200MHz	2dB to 7dB	13dB	25dB	25dB	100mA	10Vdc	1000M ohm	30Vdc	Kit
NFA21SL307X1A48□	300MHz	2dB to 7dB	7dB	20dB	25dB	100mA	10Vdc	1000M ohm	30Vdc	Kit

Operating Temperature Range: -55°C to +125°C Number of Circuits: 4

■ Insertion Loss Characteristics

NFA21SL\_X




# NFW31S Series (1206 Size)




## Wire-wound PI-type LC filter.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	2000
K	330mm Reel Embossed Tape	7500


Refer to pages from p.147 to p.152 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Nominal Cut-off Frequency	Insertion Loss at 10MHz	Insertion Loss at 20MHz	Insertion Loss at 50MHz	Insertion Loss at 100MHz	Insertion Loss at 150MHz	Insertion Loss at 200MHz	Insertion Loss at 300MHz	Insertion Loss at 400MHz	Insertion Loss at 500MHz	Insertion Loss at 1000MHz	
NFW31SP106X1E4□	10MHz	6dB max.	5dB min.	25dB min.	25dB min.	-	25dB min.	-	-	30dB min.	30dB min.	Kit
NFW31SP206X1E4□	20MHz	-	6dB max.	5dB min.	25dB min.	-	25dB min.	-	-	30dB min.	30dB min.	Kit
NFW31SP506X1E4□	50MHz	-	-	6dB max.	10dB min.	-	30dB min.	-	-	30dB min.	30dB min.	Kit
NFW31SP107X1E4□	100MHz	-	-	-	6dB max.	-	5dB min.	-	-	20dB min.	30dB min.	Kit
NFW31SP157X1E4□	150MHz	-	-	-	-	6dB max.	-	10dB min.	20dB min.	30dB min.	30dB min.	Kit
NFW31SP207X1E4□	200MHz	-	-	-	-	-	6dB max.	-	-	10dB min.	30dB min.	Kit
NFW31SP307X1E4□	300MHz	-	-	-	-	-	-	6dB max.	-	5dB min.	15dB min.	Kit
NFW31SP407X1E4□	400MHz	-	-	-	-	-	-	-	6dB max.	-	10dB min.	Kit
NFW31SP507X1E4□	500MHz	-	-	-	-	-	-	-	-	6dB max.	10dB min.	Kit

Rated Current: 200mA Rated Voltage: 25Vdc Operating Temperature Range: -40°C to +85°C Number of Circuit: 1


### ■ Insertion Loss Characteristics



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Example of EMI Suppression in an Actual Circuit

Measuring Circuit




Type of Filter	Signal Wave Form (20ns/div) 1V/div	EMI Suppression Effect / Description
Signal Waveform and Noise Spectrum before Filter Mounting		
NFW31S Series (Cut-off frequency 50MHz)		<p>NFW31S's steep attenuation characteristic means excellent EMI suppression without waveform cornering.</p>
Conventional Chip Solid Type EMI Filter (NFM41CC 470pF)		<p>3-terminal capacitors suppress signal frequencies as EMI frequencies so the signal waveform is distorted.</p>
Filter Combined with Conventional LCs L: Chip Inductor C: Chip Capacitor (270pF)		<p>Combinations of inductors and capacitors can yield a steep attenuation characteristic, but they require a great deal more mounting space. Moreover, at high frequencies the EMI suppression is less than that obtained by NFW31S.</p>

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# NFR21G Series (0805 Size)




3-terminal RC filter, dampens the noise current and returns back to ground.



## ■ Dimensions



## ■ Equivalent Circuit



## ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	4000
B	Bulk(Bag)	500



Refer to pages from p.147 to p.152 for mounting information.

## ■ Rated Value (□: packaging code)

Part Number	Capacitance	Resistance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range
NFR21GD1002202□	10pF ±20%	22ohm ±30%	50mA	50Vdc	1000M ohm	-40°C to +85°C
NFR21GD1004702□	10pF ±20%	47ohm ±30%	35mA	50Vdc	1000M ohm	-40°C to +85°C
NFR21GD4702202□	47pF ±20%	22ohm ±30%	50mA	50Vdc	1000M ohm	-40°C to +85°C
NFR21GD4704702□	47pF ±20%	47ohm ±30%	35mA	50Vdc	1000M ohm	-40°C to +85°C
NFR21GD4706802□	47pF ±20%	68ohm ±30%	30mA	50Vdc	1000M ohm	-40°C to +85°C
NFR21GD4701012□	47pF ±20%	100ohm ±30%	25mA	50Vdc	1000M ohm	-40°C to +85°C
NFR21GD1012202□	100pF ±20%	22ohm ±30%	50mA	50Vdc	1000M ohm	-40°C to +85°C
NFR21GD1014702□	100pF ±20%	47ohm ±30%	35mA	50Vdc	1000M ohm	-40°C to +85°C
NFR21GD1016802□	100pF ±20%	68ohm ±30%	30mA	50Vdc	1000M ohm	-40°C to +85°C
NFR21GD1011012□	100pF ±20%	100ohm ±30%	25mA	50Vdc	1000M ohm	-40°C to +85°C

Number of Circuit: 1

## ■ Insertion Loss Characteristics



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




# NFA31G Series (1206 Size)




## 3-terminal RC filter array.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	4000
B	Bulk(Bag)	100





Refer to pages from p.147 to p.152 for mounting information.

### ■ Rated Value (□: packaging code)

Part Number	Capacitance	Resistance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range
NFA31GD1006R84□	10pF ±20%	6.8ohm ±40%	50mA	6Vdc	1000M ohm	-40°C to +85°C
NFA31GD1004704□	10pF ±20%	47ohm ±30%	20mA	6Vdc	1000M ohm	-40°C to +85°C
NFA31GD1001014□	10pF ±20%	100ohm ±30%	15mA	6Vdc	1000M ohm	-40°C to +85°C
NFA31GD4706R84□	47pF ±20%	6.8ohm ±40%	50mA	6Vdc	1000M ohm	-40°C to +85°C
NFA31GD4703304□	47pF ±20%	33ohm ±30%	20mA	6Vdc	1000M ohm	-40°C to +85°C
NFA31GD4704704□	47pF ±20%	47ohm ±30%	20mA	6Vdc	1000M ohm	-40°C to +85°C
NFA31GD4701014□	47pF ±20%	100ohm ±30%	15mA	6Vdc	1000M ohm	-40°C to +85°C
NFA31GD1016R84□	100pF ±20%	6.8ohm ±40%	50mA	6Vdc	1000M ohm	-40°C to +85°C
NFA31GD1014704□	100pF ±20%	47ohm ±30%	20mA	6Vdc	1000M ohm	-40°C to +85°C
NFA31GD1011014□	100pF ±20%	100ohm ±30%	15mA	6Vdc	1000M ohm	-40°C to +85°C

Number of Circuit: 4

### ■ Insertion Loss Characteristics



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



## ⚠ Caution

## ● Rating

Do not use products beyond the rated current and rated voltage as this may create excessive heat and deteriorate the insulation resistance.


## ● Soldering and Mounting

## 1. Self-heating

Please provide special attention when mounting chip EMIFIL® NFM□□P/K series in close proximity to other products that radiate heat. The heat generated by other products may deteriorate the insulation resistance and cause excessive heat in this component.

## 2. NFL15ST\_X Series Mounting Direction

Mount products in right direction, because products have a direction. Wrong direction which is 180° rotated from right direction cause fuming or partial dispersion, because input or output signal terminals short-circuit to ground.



## Notice

## ● Storage and Operating Conditions

## &lt;Operating Environment&gt;

Do not use products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.

Do not use products in the environment close to the organic solvent.

## &lt;Storage and Handling Requirements&gt;

## 1. Storage Period

The other series should be used within 12 months. Solderability should be checked if this period is exceeded.

## 2. Storage Conditions

(1) Storage temperature: -10 to +40°C

Relative humidity: 15 to 85%

Avoid sudden changes in temperature and humidity.

(2) Do not store products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.

## ● Notice (Soldering and Mounting)

## 1. Cleaning

Failure and degradation of a product are caused by the cleaning method. When you clean in conditions that are not in mounting information, please contact Murata engineering.

## 2. Soldering

Reliability decreases with improper soldering methods. Please solder by the standard soldering conditions shown in mounting information.

## 3. Other

Noise suppression levels resulting from Murata's EMI suppression filters EMIFIL® may vary, depending on the circuits and ICs used, type of noise, mounting pattern, mounting location, and other operating conditions. Be sure to check and confirm in advance the noise suppression effect of each filter, in actual circuits, etc. before applying the filter in a commercial-purpose equipment design.

## ● Handling

## 1. Resin Coating

Using resin for coating/molding products may affect the products performance.

So please pay careful attention in selecting resin.

Prior to use, please make the reliability evaluation with the product mounted in your application set.


## 2. Caution for Use (NFW Series)

When you hold products with a tweezer, please hold by the sides. Sharp materials, such as a pair of tweezers or other material such as bristles of cleaning brush, should not touch the winding portion of this product to prevent breaking the wire. Mechanical shock should not be applied to the products mounted on the board to prevent breaking the core.


## 3. Handling of a Substrate

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate. Excessive mechanical stress may cause cracking in the Product.

Bending



Twisting



## 1. Standard Land Pattern Dimensions

NF $\square$  series suppress noise by conducting the high-frequency noise element to ground. Therefore, to obtain maximum performance from these filters, the ground pattern should be made as large as possible during the PCB design stage. As shown below, one side of the PCB is used for chip mounting, and the other is used for grounding.


Small diameter feedthrough holes are then used to connect the grounds on each side of the PCB. This reduces the high-frequency impedance of the grounding and maximizes the filter's performance.




NFM18  
NFL15S  
NFL18  
NFM21C  
NFM21P  
NFR21G  
NFL21S

## Reflow Soldering


### NFL15S




NFM18C/NFM18PC  
NFL18ST




NFM18PS




NFM21PS



NFL18SP



NFM21C/NFR21G  
NFM21PC/NFL21S




Please contact us if using thinner land pad than 18 $\mu$ m.

- NF□18, NF□21 are specially adapted for reflow soldering.

NFM3D  
NFM31P  
NFM31K  
NFM41


- Reflow Soldering      Chip mounting side

NFM3DC/NFM3DP/NFM31P/NFM41C/NFM41P



Part Number	Size (mm)						
	a	b	c	d	e	f	g
<b>NFM3DC</b> <b>NFM3DP</b>	1.01	1.42	5.4	4.1	0.2	0.2	4
<b>NFM31P</b>	1.01	1.42	5.4	4.1	2.2	6.3	0
<b>NFM41C</b> <b>NFM41P</b>	1.52	0.3	5.6	0.1	2.2	6.3	0


NFM31K\*1



\*1 For large current design, width of signal land pattern should be wider not less than 1mm per 1A (1mm/A). For example, in case of 10A, signal land pattern width should be 10mm or more. (1mm/A\*10A=10mm)


- Flow Soldering      Chip mounting side

Small diameter thru hole ø0.4




Part Number	Size (mm)						
	a	b	c	d	e	f	g
<b>NFM3DC</b> <b>NFM3DP</b>	1.0	1.4	2.5	4.4	1.0	2.0	2.4
<b>NFM31P</b>	1.0	1.4	2.5	4.4	1.2	2.6	3.0
<b>NFM41C</b> <b>NFM41P</b>	1.5	2.0	3.5	6.0	1.2	2.6	3.0

NFM31K\*1









\*1 For large current design, width of signal land pattern should be wider not less than 1mm per 1A (1mm/A). For example, in case of 10A, signal land pattern width should be 10mm or more.  
(1mm/A\*10A=10mm)

Continued on the following page. 

**Note** • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



 Land Pattern + Solder Resist  
 Land Pattern  
 Solder Resist (in mm)

<b>NFA18S</b> <b>NFA21S</b>	<b>Reflow Soldering</b> <b>NFA18S</b> 	<b>NFA21S</b> 
<b>NFA31G</b> <b>NFA31C</b> <b>NFW31S</b> <b>NFE31P</b>	<ul style="list-style-type: none"> <li>● Reflow Soldering NFA31G/31C</li> </ul>  <p>R0.1 to R0.2 is preferred to obtain high voltage withstanding</p>	<ul style="list-style-type: none"> <li>● Reflow and Flow NFW31S</li> <li>● Reflow Soldering NFE31P</li> </ul> 
<b>NFE61P</b>	<ul style="list-style-type: none"> <li>● Reflow Soldering</li> </ul> 	<ul style="list-style-type: none"> <li>● Flow Soldering</li> </ul> 

# ● PCB Warping

PCB should be designed so that products are not subjected to the mechanical stress caused by warping the board.

Products should be located in the sideways direction (Length:  $a < b$ ) to the mechanical stress.



## 2. Solder Paste Printing and Adhesive Application

When reflow soldering the chip EMI suppression filter, the printing must be conducted in accordance with the following cream solder printing conditions.











If too much solder is applied, the chip will be prone to damage by mechanical and thermal stress from the PCB and may crack.

Standard land dimensions should be used for resist and copper foil patterns.

When flow soldering the EMI suppression filter, apply the adhesive in accordance with the following conditions.

If too much adhesive is applied, then it may overflow into the land or termination areas and yield poor solderability. In contrast, if insufficient adhesive is applied, or if the adhesive is not sufficiently hardened, then the chip may become detached during flow soldering process.










(in mm)

Series	Solder Paste Printing	Adhesive Application
<b>NFM</b> <b>NFR</b> <b>NFL</b>	<p>●Guideline of solder paste thickness:  100-150μm: NFM18/21/3D/31P, NFR, NFL  100-200μm: NFM41</p>	<p>■ <b>NFM3D/31/41 Series</b>  Apply 0.1mg for NFM41C/41 and 0.06mg for NFM3D/NFM31 of bonding agent at each chip. Do not cover electrodes.</p> 
	<p><b>NFL15S</b></p> 	
	<p><b>NFM18C/18PC</b>  <b>NFL18ST</b></p> 	
	<p><b>NFL18SP</b></p> 	
	<p><b>NFM18PS</b></p> 	
	<p><b>NFM21C/21PC</b>  <b>NFR21G/NFL21S</b></p> 	
	<p><b>NFM21PS</b></p> 	
	<p><b>NFM3DC/3DP</b></p> 	
	<p><b>NFM31P/31K</b></p> 	
	<p><b>NFM41C/41P</b></p> 	

Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

(in mm)

Series	Solder Paste Printing	Adhesive Application
NFA	<p>●Guideline of solder paste thickness: 100-200μm: NFA31G/31C 100-150μm: NFA18S/21S</p> <p>NFA31G/31C</p>  <p>NFA21S</p>  <p>NFA18S</p> 	
NFW31S NFE31P	<p>●Guideline of solder paste thickness: 150-200μm</p> 	<p>■ NFW31S Series Apply 0.2mg of bonding agent at each chip.</p>  
NFE61P	<p>●Guideline of solder paste thickness: 150-200μm</p> 	<p>Apply 1.0mg of bonding agent at each chip.</p>  

### 3. Standard Soldering Conditions

#### (1) Soldering Methods

Use flow and reflow soldering methods only.

Use standard soldering conditions when soldering chip EMI suppression filters.

In cases where several different parts are soldered, each having different soldering conditions, use those conditions requiring the least heat and minimum time.

**Solder:** Use Sn-3.0Ag-0.5Cu solder. Use of Sn-Zn based solder will deteriorate performance of products.

If using NFM series with Sn-Zn based solder, please contact Murata in advance.

**Flux:**

- Use Rosin-based flux.


In case of using RA type solder, products should be cleaned completely with no residual flux.

- Do not use strong acidic flux (with chlorine content exceeding 0.20wt%)
- Do not use water-soluble flux.

For additional mounting methods, please contact Murata.


#### (2) Soldering Profile

- Flow Soldering Profile  
(Sn-3.0Ag-0.5Cu Solder)



Series	Pre-heating		Standard Profile			Limit Profile		
			Heating		Cycle of Flow	Heating		Cycle of Flow
	Temp. (T1)	Time. (t1)	Temp. (T2)	Time. (t2)		Temp. (T3)	Time. (t2)	
NFM3D/31/41 NFE61P	150°C	60s min.	250°C	4 to 6s	2 times max.	265±3°C	5s max.	2 times max.
NFW31S	150°C	60s min.	250°C	4 to 6s	2 times max.	265±3°C	5s max.	1 time

- Reflow Soldering Profile  
(Sn-3.0Ag-0.5Cu Solder)



Series	Standard Profile				Limit Profile			
	Heating		Peak Temperature (T2)	Cycle of Reflow	Heating		Peak Temperature (T4)	Cycle of Reflow
	Temp. (T1)	Time. (t1)			Temp. (T3)	Time. (t2)		
NFA, NFE NFL, NFM NFR	220°C min.	30 to 60s	245±3°C	2 times max.	230°C min.	60s max.	260°C/10s	2 times max.
NFW31S	220°C min.	30 to 60s	245±3°C	2 times max.	230°C min.	60s max.	260°C/10s	1 time

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



## (3) Reworking with Solder Iron

The following conditions must be strictly followed when using a soldering iron.

Pre-heating: 150°C 60s min.

Soldering iron power output / Tip diameter:

30W max. / ø3mm max.

Temperature of soldering iron tip / Soldering time / Times:

350°C max. / 3-4s / 2 times\*<sup>1</sup>

\*<sup>1</sup> NFE31PT152Z1E9: 280°C max. / 10s max. / 2 times

Do not allow the tip of the soldering iron to directly contact the chip.

For additional methods of reworking with a soldering iron, please contact Murata engineering.

## 4. Cleaning

Following conditions should be observed when cleaning chip EMI filter.

(1) Cleaning Temperature: 60°C max. (40°C max. for alcohol type cleaner)

(2) Ultrasonic

Output: 20W/liter max.

Duration: 5 minutes max.

Frequency: 28 to 40kHz

(3) Cleaning Agent

The following list of cleaning agents have been tested on the individual components. Evaluation of final assembly should be completed prior to production.

(a) Alcohol cleaning agent

Isopropyl alcohol (IPA)

(b) Aqueous cleaning agent


Pine Alpha ST-100S

(4) Ensure that flux residue is completely removed.

Component should be thoroughly dried after aqueous agent has been removed with deionized water.

## ■ Minimum Quantity and Dimensions of 8mm Width Paper / Embossed Tape

(Paper Tape)




c: Total Thickness of Tape


Part Number	Dimensions				Minimum Qty. (pcs.)				
					ø180mm Reel		ø330mm Reel		Bulk
	a	b	c	d	Paper Tape	Embossed Tape	Paper Tape	Embossed Tape	
NFL15ST	1.12	0.62	0.8 max.	-	10000	-	-	-	500

(in mm)

(Common to Paper Tape / Embossed Tape)



<Embossed>



c: Depth of Cavity  
(Embossed Tape)

<Paper>



c: Total Thickness of Tape  
(Paper Tape)

There are holes in the cavities of the NFM31,  
NFA18S and NFA21S\_48 only.  
NFA18S:  $\phi 0.8 \pm 0.1$ , NFA21S\_48:  $\phi 1.0 \pm 0.2$   
NFM31:  $\phi 1.0 \pm 0.2$


\*1 NFM31:  $3.5 \pm 0.1$

Dimension of the cavity of embossed tape is measured at the bottom side.


Part Number	Dimensions				Minimum Qty. (pcs.)				
					ø180mm Reel		ø330mm Reel		Bulk
	a	b	c	d	Paper Tape	Embossed Tape	Paper Tape	Embossed Tape	
NFM18CC/ NFM18PC (Except for 105R/225B1A) NFM18PS	1.85	1.05	0.9 max.	-	4000	-	-	-	500
NFM18PC105R/225B1A			1.1 max.	-	4000	-	-	-	500
NFL18SP/NFL18ST_H	1.85	1.05	0.9 max.	-	4000	-	-	-	1000
NFL18ST_X			1.1 max.						
NFL21SP	2.3	1.55	1.1 max.	-	4000	-	-	-	500
NFM21	2.3	1.55	1.1 max.	-	4000	-	-	-	500
NFM3D	3.4	1.4	0.85	0.2	-	4000	-	-	500
NFM31	3.5	1.9	1.5	0.25	-	3000	-	-	500
NFA18SL/SD	1.8	1.0	0.7	0.25	-	4000	-	-	1000
NFA21SL_45	2.30	1.55	0.7	0.25	-	4000	-	-	1000
NFA21SL_48	2.25	1.45	1.05	0.25	-	4000	-	-	1000
NFA31GD/31CC	3.5	2.0	1.1 max.	-	4000	-	-	-	100
NFE31PT	3.6	1.8	1.85	0.2	-	2000	-	8000	500
NFR21GD	2.3	1.55	0.7	0.25	-	4000	-	-	500
NFW31SP	3.6	1.9	2.0	0.2	-	2000	-	7500	-

(in mm)

"Minimum Quantity" means the number of units of each delivery or order. The quantity should be an integral multiple of the "Minimum Quantity."

Continued on the following page. 

Minimum Quantity and Dimensions of 12mm Width Embossed Tape




Part Number	Dimensions			Minimum Qty. (pcs.)		
	a	b	c	ø180mm Reel	ø330mm Reel	Bulk
NFM41	4.8	1.8	1.1	4000	-	500
NFE61	7.2	1.9	1.75	2500	8000	500

(in mm)

"Minimum Quantity" means the number of units of each delivery or order. The quantity should be an integral multiple of the "Minimum Quantity."

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



●EKEMNFMCB (Chip EMIFIL® Capacitor Type for Signal Lines)

No.	Part Number	Quantity (pcs.)	Capacitance	Rated Voltage (Vdc)	Rated Current (mA)
1	NFM18CC220U1C3	10	22pF±20%	16	400
2	NFM18CC470U1C3	10	47pF±20%	16	400
3	NFM18CC101R1C3	10	100pF±20%	16	500
4	NFM18CC221R1C3	10	220pF±20%	16	500
5	NFM18CC471R1C3	10	470pF±20%	16	500
6	NFM18CC102R1C3	10	1000pF±20%	16	600
7	NFM18CC222R1C3	10	2200pF±20%	16	700
8	NFM18CC223R1C3	10	22000pF±20%	16	1000
9	NFM21CC220U1H3	10	22pF±20%	50	700
10	NFM21CC470U1H3	10	47pF±20%	50	700
11	NFM21CC101U1H3	10	100pF±20%	50	700
12	NFM21CC221R1H3	10	220pF±20%	50	700
13	NFM21CC471R1H3	10	470pF±20%	50	1000
14	NFM21CC102R1H3	10	1000pF±20%	50	1000
15	NFM21CC222R1H3	10	2200pF±20%	50	1000
16	NFM21CC223R1H3	10	22000pF±20%	50	2000

●EKEMFA31E (Chip EMIFIL® Capacitor Array Type/ RC Combined Array Type)

No.	Part Number	Quantity (pcs.)	Capacitance	Rated Voltage (Vdc)	Rated Current (mA)
1	NFA31CC220S1E4	10	22pF±20%	25	200
2	NFA31CC470S1E4	10	47pF±20%	25	200
3	NFA31CC101S1E4	10	100pF±20%	25	200
4	NFA31CC221S1E4	10	220pF±20%	25	200
5	NFA31CC471R1E4	10	470pF±20%	25	200
6	NFA31CC102R1E4	10	1000pF±20%	25	200
7	NFA31CC222R1E4	10	2200pF±20%	25	200
8	NFA31CC223R1C4	10	22000pF±20%	16	200

●EKEMFL18G (Chip EMIFIL® LC Combined Type)

No.	Part Number	Quantity (pcs.)	Cut-off Frequency	Rated Voltage (Vdc)	Rated Current (mA)
1	NFL15ST157X0J3	10	150MHz	6.3	50
2	NFL15ST207X0J3	10	200MHz	6.3	50
3	NFL15ST307X0J3	10	300MHz	6.3	50
4	NFL15ST507X0J3	10	500MHz	6.3	50
5	NFL18ST506H1A3	10	50MHz	10	75
6	NFL18ST706H1A3	10	70MHz	10	75
7	NFL18ST107H1A3	10	100MHz	10	75
8	NFL18ST207H1A3	10	200MHz	10	100
9	NFL18ST307H1A3	10	300MHz	10	100
10	NFL18ST507H1A3	10	500MHz	10	100
11	NFL18ST207X1C3	10	200MHz	16	150
12	NFL18ST307X1C3	10	300MHz	16	200
13	NFL18ST507X1C3	10	500MHz	16	200
14	NFL18SP157X1A3	10	150MHz	10	100
15	NFL18SP207X1A3	10	200MHz	10	100
16	NFL18SP307X1A3	10	300MHz	10	100
17	NFL18SP507X1A3	10	500MHz	10	100
18	NFL21SP106X1C3	10	10MHz	16	100
19	NFL21SP206X1C7	10	20MHz	16	100
20	NFL21SP506X1C3	10	50MHz	16	150
21	NFL21SP706X1C3	10	70MHz	16	150
22	NFL21SP107X1C3	10	100MHz	16	200
23	NFL21SP157X1C3	10	150MHz	16	200

Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

No.	Part Number	Quantity (pcs.)	Cut-off Frequency	Rated Voltage (Vdc)	Rated Current (mA)
24	NFL21SP207X1C3	10	200MHz	16	250
25	NFL21SP307X1C3	10	300MHz	16	300
26	NFL21SP407X1C3	10	400MHz	16	300
27	NFL21SP507X1C3	10	500MHz	16	300

No.	Part Number	Quantity (pcs.)	Cut-off Frequency	Attenuation (dB min.)										Rated Current	Rated Voltage
				10MHz	20MHz	50MHz	100MHz	150MHz	200MHz	300MHz	400MHz	500MHz	1GHz		
28	NFW31SP106X1E4	10	10MHz	6dB max.	5	25	25	-	25	-	-	30	30	200mA	25V
29	NFW31SP206X1E4	10	20MHz	-	6dB max.	5	25	-	25	-	-	30	30	200mA	25V
30	NFW31SP506X1E4	10	50MHz	-	-	6dB max.	10	-	30	-	-	30	30	200mA	25V
31	NFW31SP107X1E4	10	100MHz	-	-	-	6dB max.	-	5	-	-	20	30	200mA	25V
32	NFW31SP157X1E4	10	150MHz	-	-	-	-	6dB max.	-	10	20	30	30	200mA	25V
33	NFW31SP207X1E4	10	200MHz	-	-	-	-	-	6dB max.	-	-	10	30	200mA	25V
34	NFW31SP307X1E4	10	300MHz	-	-	-	-	-	-	6dB max.	-	5	15	200mA	25V
35	NFW31SP407X1E4	10	400MHz	-	-	-	-	-	-	-	6dB max.	-	10	200mA	25V
36	NFW31SP507X1E4	10	500MHz	-	-	-	-	-	-	-	-	6dB max.	10	200mA	25V

## ●EKEMFA20H (Chip EMIFIL® LC Combined Array Type)

No.	Part Number	Quantity (pcs.)	Cut-off Frequency	Rated Voltage (Vdc)	Rated Current (mA)
1	NFA18SL506X1A45	10	50MHz	10	25
2	NFA18SL137V1A45	10	130MHz	10	50
3	NFA18SL187V1A45	10	180MHz	10	50
4	NFA18SL207V1A45	10	200MHz	10	50
5	NFA18SL227V1A45	10	220MHz	10	25
6	NFA18SL307V1A45	10	300MHz	10	100
7	NFA18SL357V1A45	10	350MHz	10	35
8	NFA18SL407V1A45	10	400MHz	10	100
9	NFA18SL487V1A45	10	480MHz	10	100
10	NFA18SD187X1A45	10	180MHz	10	25
11	NFA18SD207X1A45	10	200MHz	10	25
12	NFA21SL506X1A48	10	50MHz	10	20
13	NFA21SL806X1A48	10	80MHz	10	20
14	NFA21SL207X1A45	10	200MHz	10	100
15	NFA21SL207X1A48	10	200MHz	10	100
16	NFA21SL307X1A45	10	300MHz	10	100
17	NFA21SL307X1A48	10	300MHz	10	100
18	NFA21SL287V1A45	10	280MHz	10	100
19	NFA21SL287V1A48	10	280MHz	10	100
20	NFA21SL317V1A45	10	310MHz	10	100
21	NFA21SL317V1A48	10	310MHz	10	100
22	NFA21SL337V1A45	10	330MHz	10	100
23	NFA21SL337V1A48	10	330MHz	10	100

## ●EKEMNFMPPM (Chip EMIFIL® for Large Current)

No.	Part Number	Quantity (pcs.)	Capacitance	Rated Voltage (Vdc)	Rated Current (A)
1	NFM18PC104R1C3	10	0.1μF±20%	16	2
2	NFM18PC224R0J3	10	0.22μF±20%	6.3	2
3	NFM18PC474R0J3	10	0.47μF±20%	6.3	2
4	NFM18PC105R0J3	10	1μF±20%	6.3	4
5	NFM18PC225B0J3	10	2.2μF±20%	6.3	2
6	NFM18PC225B1A3	10	2.2μF±20%	10	4
7	NFM18PS474R0J3	10	0.47μF±20%	6.3	2
8	NFM18PS105R0J3	10	1μF±20%	6.3	2
9	NFM21PC104R1E3	10	0.1μF±20%	25	2
10	NFM21PC224R1C3	10	0.22μF±20%	16	2
11	NFM21PC474R1C3	10	0.47μF±20%	16	2
12	NFM21PC105B1A3	10	1μF±20%	10	4
13	NFM21PC105B1C3	10	1μF±20%	16	4
14	NFM21PC225B0J3	10	2.2μF±20%	6.3	4
15	NFM21PC475B1A3	10	4.7μF±20%	10	6
16	NFM21PS106B0J3	10	10μF±20%	6.3	4
17	NFM31PC276B0J3	10	27μF±20%	6.3	6
18	NFM41PC204F1H3	10	0.2μF+80/-20%	50	2

Continued on the following page.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

No.	Part Number	Quantity (pcs.)	Capacitance	Rated Voltage (Vdc)	Rated Current (A)
19	NFM41PC155B1E3	10	1.5μF±20%	25	6
20	NFM31KC103R1H3	10	10000pF±20%	50	10
21	NFM31KC103R2A3	10	10000pF±20%	100	10
22	NFM31KC153R1H3	10	15000pF±20%	50	10
23	NFM31KC153R2A3	10	15000pF±20%	100	10
24	NFM31KC223R1H3	10	22000pF±20%	50	10
25	NFM31KC223R2A3	10	22000pF±20%	100	10
26	NFM31KC104R1H3	10	100000pF±20%	50	6
27	NFM31KC104R2A3	10	100000pF±20%	100	6
28	NFE31PT152Z1E9	10	1500pF+50/-20%	25	6
29	NFE31PT222Z1E9	10	2200pF±50%	25	6
30	NFE61PT102E1H9	10	1000pF+80/-20%	50	2
31	NFE61PT472C1H9	10	4700pF+80/-20%	50	2

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



## Memo



**Chip Common Mode Choke Coil**  
Large Current Common Mode Choke Coil for Automotive Available

Series Introduction .....	160
Part Numbering .....	162
Series Line Up .....	164
Product Detail .....	167
⚠Caution/Notice .....	192
Soldering and Mounting .....	194
Packaging .....	200
Design Kits .....	202

Chip Ferrite Bead

Chip EMIFIL®


Chip Common Mode Choke Coil

Block Type EMIFIL®


Microwave Absorber

# DL Series Introduction

Common Mode Current



Differential Mode Current



Magnetic flux caused by common mode current accumulates and works as an inductor.

Magnetic flux caused by differential mode current cancel each other and does not work as an inductor.

Category	Features, Classification	Structure	Part Number	Comments
High cut-off frequency High Coupling (For high speed differential signal lines)	Ultra high cut-off frequency for high speed differential signal lines	Film type	DLP0QSA DLP0NSA DLP11SA DLP11RB DLP11TB DLP2ADA	<ul style="list-style-type: none"> <li>Low profile, small size, suitable for mobile equipment.</li> <li>Tight terminal pitch enables high density layout.</li> <li>Ultra high cut-off frequency and its matching to line impedance enables good transmission of high speed signal.</li> </ul>
		Wound type	DLW21SN_HQ2 DLW21HN_HQ2	<ul style="list-style-type: none"> <li>Ultra high self-resonance frequency enables high cut-off frequency.</li> <li>Its matching to line impedance enables good transmission of high speed signal.</li> </ul>
	High cut-off frequency for high speed differential signal lines	Multilayer type	DLM11SN	Enables noise suppression for differential signal line without distortion in high-speed signal transmission.
		Film type	DLP0QSN DLP0NS DLP11SN DLP11RN DLP2AD	<ul style="list-style-type: none"> <li>Low profile, small size, suitable for mobile equipment.</li> <li>Tight terminal pitch enables high density layout.</li> <li>High cut-off frequency enables good transmission of high speed signal.</li> </ul>
		Wound type	DLW21SN_SQ2 DLW31S DLW21HN_SQ2	<ul style="list-style-type: none"> <li>Ultra high self-resonance frequency enables high cut-off frequency.</li> <li>DLW21H is designed as low profile.</li> </ul>
	For general differential signal lines	Film type	DLP31S DLP31D	<ul style="list-style-type: none"> <li>Low profile, small size, suitable for mobile equipment.</li> <li>Tight terminal pitch enables high density layout.</li> </ul>
Large current High coupling (For power lines)		Wound type	DLW5AH DLW5BS DLW5AT DLW5BT	<ul style="list-style-type: none"> <li>Large current (7A max.), suitable for input connector from an AC adaptor.</li> <li>DLW5AT/DLW5BT is designed as low profile.</li> </ul>
Relative high differential mode impedance Low coupling (For audio lines)		Multilayer type	DLM11G	<ul style="list-style-type: none"> <li>Modified differential mode impedance is higher than other common mode choke coils; this feature makes it possible to suppress both common mode and differential mode noise.</li> <li>Ideal to keep low distortion audio signal.</li> </ul>
Large current Automotive Available (For power lines)	Available up to 18A	Winding type Cased structure	PLT10HH	Large current, high reliability, suitable for motors in automobiles.


△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Skew Improvement Effect of Common Mode Choke Coil


Example of Skew Improvement by Common Mode Choke Coil  
(Tested using pulse generator waveform)

Waveform is equivalent to 1000Mbps signal


Waveform with intentionally made skew (skew: 100ps)



Skew is improved by common mode choke coil



### Mechanism of Skew Improvement





## Noise Suppression of Common Mode Choke Coil in HDMI Line

Device under test / Transmitter : game machine

/ Receiver : projector

/ Cable : HDMI category 2 3m cable

Test resolution / 1080p Deep color 12bit (Data 1.11GHz) DVD play mode




## Test Example of HDMI1.3 Waveform Transmission


~Using ESD protection device

LXES15AAA1-100 (0.05pF)~


Signal frequency : 1.11GHz (Deep color 12bit)



ESD protection device only



Film Type DLP11SN900HL2  
(Cut-off frequency is lowest in the table below)



	Wound Type DLW21SN900HQ2	Film Type DLP11SA900HL2	Film Type Array DLP2ADN900HL4
Cut-off Frequency	Over 10GHz	Around 6GHz	Around 4GHz
Judge	Specification satisfied	Specification satisfied	Specification satisfied
Transition Time	Rise time: 83.4ps Fall time: 77.4ps	Rise time: 90.4ps Fall time: 85.5ps	Rise time: 100ps Fall time: 97.4ps

Each common mode choke coil can keep the waveform and satisfy the specification.

# DL   Chip Common Mode Choke Coil

## Part Numbering

(Part Number)

<b>DL</b>	<b>W</b>	<b>21</b>	<b>S</b>	<b>N</b>	<b>371</b>	<b>S</b>	<b>Q</b>	<b>2</b>	<b>L</b>
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩

### ① Product ID

Product ID	
<b>DL</b>	Chip Common Mode Choke Coils

### ② Structure

Code	Structure
<b>W</b>	Wire Wound Type
<b>M</b>	Multilayer Type
<b>P</b>	Film Type

### ③ Dimensions (L×W)

Code	Dimensions (L×W)	EIA
<b>0Q</b>	0.65×0.5mm	025020
<b>0N</b>	0.85×0.65mm	03025
<b>11</b>	1.25×1.0mm	0504
<b>1N</b>	1.5×0.65mm	05025
<b>21</b>	2.0×1.2mm	0805
<b>2A</b>	2.0×1.0mm	0804
<b>31</b>	3.2×1.6mm	1206
<b>5A</b>	5.0×3.6mm	2014
<b>5B</b>	5.0×5.0mm	2020

### ④ Features (1)

Code	Type
<b>S</b>	Magnetically Shielded One Circuit Type
<b>D</b>	Magnetically Shielded Two Circuit Type
<b>H</b>	Open Magnetic One Circuit Type
<b>G</b>	Magnetically Shielded Audio Type
<b>R/T</b>	One Circuit Low Profile Type

### ⑤ Category

Code	Category
<b>A</b>	Expressed by a letter.
<b>B</b>	
<b>C</b>	
<b>M</b>	
<b>N</b>	
<b>R</b>	

### ⑥ Impedance

Typical impedance at 100MHz is expressed by three figures. The unit is in ohm ( $\Omega$ ). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures.

### ⑦ Circuit

Code	Circuit
<b>S</b>	Expressed by a letter.
<b>M</b>	
<b>H</b>	
<b>U</b>	
<b>T</b>	

### ⑧ Features (2)

Code	Features
<b>D</b>	Expressed by a letter.
<b>K</b>	
<b>L</b>	
<b>Q</b>	
<b>Y</b>	

### ⑨ Number of Signal Lines

Code	Number of Signal Lines
<b>2</b>	Two Lines
<b>4</b>	Four Lines

### ⑩ Packaging

Code	Packaging	Series
<b>K</b>	Embossed Taping ( $\phi$ 330mm Reel)	<b>DLW5AH/DLW5BS/DLW5BT</b>
<b>L</b>	Embossed Taping ( $\phi$ 180mm Reel)	All Series
<b>B</b>	Bulk	All Series
<b>D</b>	Paper Taping ( $\phi$ 180mm Reel)	<b>DLP0QS/DLM11G</b>

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# PL Common Mode Choke Coil Part Numbering

(Part Number) 

PL	T	10H	H	102	6R0	P	N	B
----	---	-----	---	-----	-----	---	---	---

  
1 2 3 4 5 6 7 8 9

## ① Product ID

Product ID	
PL	Common Mode Choke Coils

## ② Type

Code	Type
T	DC Type

## ③ Applications

Code	Applications
10H	for DC Line High-frequency Type

## ④ Features

Code	Features
H	for Automotive

## ⑤ Impedance

Expressed by three figures. The unit is ohm ( $\Omega$ ). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures.

## ⑥ Rated Current

Expressed by three figures. The unit is ampere (A). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures. A decimal point is expressed by the capital letter "R." In this case, all figures are significant digits.

## ⑦ Winding Mode

Code	Winding Mode
P	Aligned Winding Type

## ⑧ Lead Dimensions


Code	Lead Dimensions
N	No Lead Terminal (SMD)

## ⑨ Packaging

Code	Packaging	Series
B	Bulk	PLT10H
L	Embossed Taping ( $\phi 178\text{mm}/\phi 180\text{mm}$ Reel)	PLT10H
K	Embossed Taping ( $\phi 330\text{mm}$ Reel)	PLT10H



Type	Size Code (Inch)	Thickness (mm)	Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	New	Kit	$\geq 1A$	Hd	Zmatch	Flow	RefFlow
Multilayer Type for Audio Lines	0504	p174	0.5	DLM11GN601SD2	600ohm $\pm$ 25%	100mA						RefFlow
Multilayer Type for Differential Signal Lines	0504	p175	0.5	DLM11SN450HY2	45ohm $\pm$ 25%	100mA	New	Kit	Hd	Zmatch		RefFlow
			0.5	DLM11SN900HY2	90ohm $\pm$ 25%	100mA	New	Kit	Hd	Zmatch		RefFlow
Film Type for Differential Signal Lines	025020	p176	0.3	DLP0QSN600HL2	60ohm $\pm$ 25%	50mA		Kit	Hd	Zmatch		RefFlow
			0.3	DLP0QSA070HL2	7ohm $\pm$ 2ohm	100mA	New	Kit	Ud	Zmatch		RefFlow
			0.3	DLP0QSA150HL2	15ohm $\pm$ 5ohm	100mA	New	Kit	Ud	Zmatch		RefFlow
			0.3	DLP0QSA350HL2	35ohm $\pm$ 10ohm	100mA	New	Kit	Ud	Zmatch		RefFlow
			0.45	DLP0NSC280HL2	28ohm $\pm$ 20%	100mA		Kit	Hd	Zmatch		RefFlow
	03025	p177	0.45	DLP0NSN350HL2	35ohm $\pm$ 10ohm	100mA	New	Kit	Hd	Zmatch		RefFlow
			0.45	DLP0NSN670HL2	67ohm $\pm$ 20%	110mA		Kit	Hd	Zmatch		RefFlow
			0.45	DLP0NSN900HL2	90ohm $\pm$ 20%	100mA		Kit	Hd	Zmatch		RefFlow
			0.45	DLP0NSN121HL2	120ohm $\pm$ 20%	90mA		Kit	Hd	Zmatch		RefFlow
			0.45	DLP0NSA070HL2	7ohm $\pm$ 2ohm	100mA	New	Kit	Ud	Zmatch		RefFlow
	0504		0.45	DLP0NSA150HL2	15ohm $\pm$ 5ohm	100mA		Kit	Ud	Zmatch		RefFlow
		p179	0.82	DLP11SN670SL2	67ohm $\pm$ 20%	180mA		Kit	Hd			RefFlow
			0.82	DLP11SN121SL2	120ohm $\pm$ 20%	140mA		Kit	Hd			RefFlow
			0.82	DLP11SN161SL2	160ohm $\pm$ 20%	120mA		Kit	Hd			RefFlow
			0.82	DLP11SN900HL2	90ohm $\pm$ 20%	150mA		Kit	Hd	Zmatch		RefFlow
			0.82	DLP11SN201HL2	200ohm $\pm$ 20%	110mA		Kit	Hd	Zmatch		RefFlow
			0.82	DLP11SN241HL2	240ohm $\pm$ 20%	100mA		Kit	Hd	Zmatch		RefFlow
			0.82	DLP11SN281HL2	280ohm $\pm$ 20%	90mA		Kit	Hd	Zmatch		RefFlow
			0.82	DLP11SN331HL2	330ohm $\pm$ 20%	80mA		Kit	Hd	Zmatch		RefFlow
			0.82	DLP11SA350HL2	35ohm $\pm$ 20%	170mA		Kit	Ud	Zmatch		RefFlow
			0.82	DLP11SA670HL2	67ohm $\pm$ 20%	150mA		Kit	Ud	Zmatch		RefFlow
			0.82	DLP11SA900HL2	90ohm $\pm$ 20%	150mA		Kit	Ud	Zmatch		RefFlow
		p180	0.5	DLP11RN450UL2	45ohm $\pm$ 25%	100mA		Kit	Hd	Zmatch		RefFlow
			0.5	DLP11RB150UL2	15ohm $\pm$ 5ohm	100mA		Kit	Ud	Zmatch		RefFlow
			0.5	DLP11RB400UL2	40ohm $\pm$ 10ohm	100mA		Kit	Ud	Zmatch		RefFlow
		p181	0.3	DLP11TB800UL2	80ohm $\pm$ 25%	100mA		Kit	Ud	Zmatch		RefFlow
	1206	p182	1.15	DLP31SN121ML2	120ohm $\pm$ 20%	100mA			Hd			RefFlow
			1.15	DLP31SN221ML2	220ohm $\pm$ 20%	100mA			Hd			RefFlow
			1.15	DLP31SN551ML2	550ohm $\pm$ 20%	100mA			Hd			RefFlow
Film Array Type for Differential Signal Lines	05025	p183	0.45	DLP1NDN350HL4	35ohm $\pm$ 20%	100mA		Kit	Hd	Zmatch		RefFlow
			0.45	DLP1NDN670HL4	67ohm $\pm$ 20%	80mA		Kit	Hd	Zmatch		RefFlow
			0.45	DLP1NDN900HL4	90ohm $\pm$ 20%	60mA		Kit	Hd	Zmatch		RefFlow
	0804	p184	0.82	DLP2ADA350HL4	35ohm $\pm$ 20%	150mA		Kit	Ud	Zmatch		RefFlow
			0.82	DLP2ADA670HL4	67ohm $\pm$ 20%	130mA		Kit	Ud	Zmatch		RefFlow
			0.82	DLP2ADA900HL4	90ohm $\pm$ 20%	120mA		Kit	Ud	Zmatch		RefFlow
			0.82	DLP2ADN670HL4	67ohm $\pm$ 20%	140mA		Kit	Hd	Zmatch		RefFlow
			0.82	DLP2ADN900HL4	90ohm $\pm$ 20%	130mA		Kit	Hd	Zmatch		RefFlow
			0.82	DLP2ADN121HL4	120ohm $\pm$ 20%	120mA		Kit	Hd	Zmatch		RefFlow
			0.82	DLP2ADN161HL4	160ohm $\pm$ 20%	100mA		Kit	Hd	Zmatch		RefFlow
			0.82	DLP2ADN201HL4	200ohm $\pm$ 20%	90mA		Kit	Hd	Zmatch		RefFlow
			0.82	DLP2ADN241HL4	240ohm $\pm$ 20%	80mA		Kit	Hd	Zmatch		RefFlow
			0.82	DLP2ADN281HL4	280ohm $\pm$ 20%	80mA		Kit	Hd	Zmatch		RefFlow
	1206	p186	1.15	DLP31DN900ML4	90ohm $\pm$ 20%	160mA			Hd			RefFlow
			1.15	DLP31DN131ML4	130ohm $\pm$ 20%	120mA			Hd			RefFlow
			1.15	DLP31DN201ML4	200ohm $\pm$ 20%	100mA			Hd			RefFlow
			1.15	DLP31DN321ML4	320ohm $\pm$ 20%	80mA			Hd			RefFlow
			1.15	DLP31DN441ML4	440ohm $\pm$ 20%	70mA			Hd			RefFlow

Continued on the following page. 



Type	Size Code (Inch)	Thickness (mm)	Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	New	Kit	$\geq 1A$ $\geq 3A$	Hd Ud	Zmatch	Flow	RefFlow
Wire Wound Type for Differential Signal Lines	0805	p187	1.2	DLW21SN670SQ2	67ohm±25%		Kit		Hd			RefFlow
			1.2	DLW21SN900SQ2	90ohm±25%		Kit		Hd			RefFlow
			1.2	DLW21SN121SQ2	120ohm±25%		Kit		Hd			RefFlow
			1.2	DLW21SN181SQ2	180ohm±25%		Kit		Hd			RefFlow
			1.2	DLW21SN261SQ2	260ohm±25%		Kit		Hd			RefFlow
			1.2	DLW21SN371SQ2	370ohm±25%		Kit		Hd			RefFlow
			1.2	DLW21SN501SK2	500ohm±25%		Kit		Hd			RefFlow
			1.2	DLW21SN670HQ2	67ohm±25%		Kit		Ud	Zmatch		RefFlow
			1.2	DLW21SN900HQ2	90ohm±25%		Kit		Ud	Zmatch		RefFlow
			1.2	DLW21SN121HQ2	120ohm±25%		Kit		Ud	Zmatch		RefFlow
			1.2	DLW21SR670HQ2	67ohm±25%		Kit		Ud	Zmatch		RefFlow
		p189	0.9	DLW21HN670SQ2	67ohm±25%		Kit		Hd			RefFlow
			0.9	DLW21HN900SQ2	90ohm±25%		Kit		Hd			RefFlow
			0.9	DLW21HN121SQ2	120ohm±25%		Kit		Hd			RefFlow
			0.9	DLW21HN181SQ2	180ohm±25%		Kit		Hd			RefFlow
			0.9	DLW21HN670HQ2	67ohm±25%	New	Kit		Ud	Zmatch		RefFlow
			0.9	DLW21HN900HQ2	90ohm±25%	New	Kit		Ud	Zmatch		RefFlow
			0.9	DLW21HN121HQ2	120ohm±25%	New	Kit		Ud	Zmatch		RefFlow
	1206	p190	1.9	DLW31SN900SQ2	90ohm±25%				Hd			RefFlow
			1.9	DLW31SN161SQ2	160ohm±25%				Hd			RefFlow
			1.9	DLW31SN261SQ2	260ohm±25%				Hd			RefFlow
			1.9	DLW31SN601SQ2	600ohm±25%				Hd			RefFlow
			1.9	DLW31SN102SQ2	1000ohm±25%				Hd			RefFlow
			1.9	DLW31SN222SQ2	2200ohm±25%				Hd			RefFlow
Wire Wound Type for Power Lines and Signal Lines	2014	p167	4.3	DLW5AHN402SQ2	4000ohm (Typ.)		Kit					RefFlow
		p169	2.2	DLW5ATN111SQ2	110ohm (Typ.)		Kit	$\geq 3A$				RefFlow
			2.2	DLW5ATN401SQ2	400ohm (Typ.)		Kit	$\geq 1A$				RefFlow
			2.2	DLW5ATN501SQ2	500ohm (Typ.)		Kit	$\geq 1A$				RefFlow
			2.2	DLW5ATN851SQ2	850ohm (Typ.)		Kit	$\geq 1A$				RefFlow
			2.2	DLW5ATN272SQ2	2700ohm (Typ.)		Kit	$\geq 1A$				RefFlow
		p172	2.2	DLW5ATN500MQ2	50ohm (Typ.)	New	Kit	$\geq 3A$			Flow	RefFlow
			2.2	DLW5ATN151MQ2	150ohm (Typ.)	New	Kit	$\geq 3A$			Flow	RefFlow
			2.2	DLW5ATN331MQ2	330ohm (Typ.)	New	Kit	$\geq 3A$			Flow	RefFlow
			2.2	DLW5ATN112MQ2	1100ohm (Typ.)	New	Kit	$\geq 1A$			Flow	RefFlow
			2.2	DLW5ATN450TQ2	45ohm (Typ.)	New	Kit	$\geq 3A$				RefFlow
			2.2	DLW5ATN111TQ2	100ohm (Typ.)	New	Kit	$\geq 3A$				RefFlow
			2.2	DLW5ATN231TQ2	230ohm (Typ.)	New	Kit	$\geq 3A$				RefFlow
			2.2	DLW5ATN501TQ2	500ohm (Typ.)	New	Kit	$\geq 1A$				RefFlow
	2020	p167	4.5	DLW5BSM191SQ2	190ohm (Typ.)		Kit	$\geq 3A$				RefFlow
			4.5	DLW5BSM351SQ2	350ohm (Typ.)		Kit	$\geq 1A$				RefFlow
			4.5	DLW5BSM102SQ2	1000ohm (Typ.)		Kit	$\geq 1A$				RefFlow
			4.5	DLW5BSM152SQ2	1500ohm (Typ.)		Kit	$\geq 1A$				RefFlow
			4.5	DLW5BSM302SQ2	3000ohm (Typ.)		Kit					RefFlow
		p169	2.35	DLW5BTM101SQ2	100ohm (Typ.)		Kit	$\geq 3A$				RefFlow
			2.35	DLW5BTM251SQ2	250ohm (Typ.)		Kit	$\geq 3A$				RefFlow
			2.35	DLW5BTM501SQ2	500ohm (Typ.)		Kit	$\geq 3A$				RefFlow
			2.35	DLW5BTM102SQ2	1000ohm (Typ.)		Kit	$\geq 1A$				RefFlow
			2.35	DLW5BTM142SQ2	1400ohm (Typ.)		Kit	$\geq 1A$				RefFlow
		p172	2.35	DLW5BTM101TQ2	100ohm (Typ.)	New	Kit	$\geq 3A$				RefFlow
			2.35	DLW5BTM251TQ2	250ohm (Typ.)	New	Kit	$\geq 3A$				RefFlow
			2.35	DLW5BTM501TQ2	500ohm (Typ.)	New	Kit	$\geq 3A$				RefFlow
			2.35	DLW5BTM142TQ2	1400ohm (Typ.)	New	Kit	$\geq 1A$				RefFlow

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Type	Size	Thickness (mm)	Part Number	Common Mode Impedance (at 10MHz/20°C)	Rated Current	New	Kit	≥3A	Hd	≥10A	Ud	Zmatch	F <sub>low</sub>	R <sub>eflow</sub>
Large Current Common Mode Choke Coil for Automotive Available	12.9x6.6	9.4	PLT10HH450180PN	45ohm (Typ.)	18A	New	Kit	≥10A						R <sub>eflow</sub>
		9.4	PLT10HH101150PN	100ohm (Typ.)	15A	New	Kit	≥10A						R <sub>eflow</sub>
		9.4	PLT10HH401100PN	400ohm (Typ.)	10A		Kit	≥10A						R <sub>eflow</sub>
		9.4	PLT10HH501100PN	500ohm (Typ.)	10A		Kit	≥10A						R <sub>eflow</sub>
		9.4	PLT10HH9016R0PN	900ohm (Typ.)	6A		Kit	≥3A						R <sub>eflow</sub>
	(mm)	9.4	PLT10HH1026R0PN	1000ohm (Typ.)	6A		Kit	≥3A						R <sub>eflow</sub>

# DLW5AH/DLW5BS Series (2014/2020 Size)




5A max, common mode choke coil for power lines.


DLW5AH



## ■ Dimensions



## ■ Equivalent Circuit




## ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	400
K	330mm Reel Embossed Tape	1500
B	Bulk(Bag)	100


DLW5BS



## ■ Dimensions



## ■ Equivalent Circuit



## ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	400
K	330mm Reel Embossed Tape	1500
B	Bulk(Bag)	100


Refer to pages from p.194 to p.197 for mounting information.

## ■ Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLW5AHN402SQ2□	4000ohm (Typ.)	200mA	50Vdc	10M ohm	125Vdc	3.0ohm max.	Kit
DLW5BSM191SQ2□	190ohm (Typ.)	5000mA	50Vdc	10M ohm	125Vdc	0.02ohm max.	Kit $\geq 3A$
DLW5BSM351SQ2□	350ohm (Typ.)	2000mA	50Vdc	10M ohm	125Vdc	0.04ohm max.	Kit $\geq 1A$
DLW5BSM102SQ2□	1000ohm (Typ.)	1500mA	50Vdc	10M ohm	125Vdc	0.06ohm max.	Kit $\geq 1A$
DLW5BSM152SQ2□	1500ohm (Typ.)	1000mA	50Vdc	10M ohm	125Vdc	0.1ohm max.	Kit $\geq 1A$
DLW5BSM302SQ2□	3000ohm (Typ.)	500mA	50Vdc	10M ohm	125Vdc	0.3ohm max.	Kit

Operating Temperature Range: -25°C to +85°C (DLW5AH), -40°C to +85°C (DLW5BS) Number of Circuit: 1

## ■ Impedance-Frequency Characteristics



Continued on the following page.


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

**■ Notice (Rating)**

In operating temperature exceeding +75°C, derating of current is necessary for DLW5BSM191SQ2 series.

Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current






# DLW5AT/DLW5BT Series (2014/2020 Size)


## Low profile wire-wound common choke coil for power lines.



## ■ Dimensions



### ■ Equivalent Circuit




## ■ Packaging


Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	700
K	330mm Reel Embossed Tape	2500
B	Bulk(Bag)	100



## ■ Dimensions



### ■ Equivalent Circuit



## ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	700
K	330mm Reel Embossed Tape	2500
B	Bulk(Bag)	100

Refer to pages from p.194 to p.197 for mounting information.

■ Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance		
DLW5ATN111SQ2□	110ohm (Typ.)	5000mA	50Vdc	10M ohm	125Vdc	0.014ohm±40%	Kit	≥3A
DLW5ATN401SQ2□	400ohm (Typ.)	2000mA	50Vdc	10M ohm	125Vdc	0.024ohm±40%	Kit	≥1A
DLW5ATN501SQ2□	500ohm (Typ.)	1500mA	50Vdc	10M ohm	125Vdc	0.040ohm±40%	Kit	≥1A
DLW5ATN851SQ2□	850ohm (Typ.)	1500mA	50Vdc	10M ohm	125Vdc	0.052ohm±40%	Kit	≥1A
DLW5ATN272SQ2□	2700ohm (Typ.)	1000mA	50Vdc	10M ohm	125Vdc	0.080ohm±40%	Kit	≥1A
DLW5BTM101SQ2□	100ohm (Typ.)	6000mA	50Vdc	10M ohm	125Vdc	0.009ohm±40%	Kit	≥3A
DLW5BTM251SQ2□	250ohm (Typ.)	5000mA	50Vdc	10M ohm	125Vdc	0.014ohm±40%	Kit	≥3A
DLW5BTM501SQ2□	500ohm (Typ.)	4000mA	50Vdc	10M ohm	125Vdc	0.019ohm±40%	Kit	≥3A
DLW5BTM102SQ2□	1000ohm (Typ.)	2000mA	50Vdc	10M ohm	125Vdc	0.024ohm±40%	Kit	≥1A
DLW5BTM142SQ2□	1400ohm (Typ.)	1500mA	50Vdc	10M ohm	125Vdc	0.040ohm±40%	Kit	≥1A


Operating Temperature Range: -40°C to +85°C	Number of Circuit: 1
---	----------------------

Continued on the following page. 


**Note** • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## ■ Impedance-Frequency Characteristics

### DLW5AT Series





### DLW5BT Series



## ■ Notice (Rating)


In operating temperature exceeding +60°C, derating of current is necessary for DLW5AT series. Please apply the derating curve shown in chart according to the operating temperature.

### Derating of Rated Current



In operating temperature exceeding +60°C, derating of current is necessary for the following part name of DLW5BT series. Please apply the derating curve shown in chart according to the operating temperature.

### Derating of Rated Current





# DLW5AT/DLW5BT Series (105degreeC available type)


**Hi**  
Power

Low profile wire-wound common choke coil for power lines. (105degreeC available type)


DLW5AT\_MQ2



## ■ Dimensions



## ■ Equivalent Circuit




## ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	700
K	330mm Reel Embossed Tape	2500
B	Bulk(Bag)	100


DLW5AT\_TQ2



## ■ Dimensions



## ■ Equivalent Circuit




## ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	700
K	330mm Reel Embossed Tape	2500
B	Bulk(Bag)	100


DLW5BT\_TQ2



## ■ Dimensions



## ■ Equivalent Circuit



## ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	700
K	330mm Reel Embossed Tape	2500
B	Bulk(Bag)	100


Refer to pages from p.194 to p.197 for mounting information.

Continued on the following page.


## ■ Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance				
DLW5ATN500MQ2□	50ohm (Typ.)	6000mA	50Vdc	10M ohm	125Vdc	0.009ohm±40%	New	Kit	≥3A	Flow ReFlow
DLW5ATN151MQ2□	150ohm (Typ.)	5000mA	50Vdc	10M ohm	125Vdc	0.014ohm±40%	New	Kit	≥3A	Flow ReFlow
DLW5ATN331MQ2□	330ohm (Typ.)	4000mA	50Vdc	10M ohm	125Vdc	0.019ohm±40%	New	Kit	≥3A	Flow ReFlow
DLW5ATN112MQ2□	1100ohm (Typ.)	2000mA	50Vdc	10M ohm	125Vdc	0.040ohm±40%	New	Kit	≥1A	Flow ReFlow
DLW5ATN450TQ2□	45ohm (Typ.)	7000mA	50Vdc	10M ohm	125Vdc	0.006ohm±40%	New	Kit	≥3A	ReFlow
DLW5ATN111TQ2□	110ohm (Typ.)	5000mA	50Vdc	10M ohm	125Vdc	0.014ohm±40%	New	Kit	≥3A	ReFlow
DLW5ATN231TQ2□	230ohm (Typ.)	4000mA	50Vdc	10M ohm	125Vdc	0.019ohm±40%	New	Kit	≥3A	ReFlow
DLW5ATN501TQ2□	500ohm (Typ.)	2000mA	50Vdc	10M ohm	125Vdc	0.040ohm±40%	New	Kit	≥1A	ReFlow
DLW5BTM101TQ2□	100ohm (Typ.)	6000mA	50Vdc	10M ohm	125Vdc	0.009ohm±40%	New	Kit	≥3A	ReFlow
DLW5BTM251TQ2□	250ohm (Typ.)	5000mA	50Vdc	10M ohm	125Vdc	0.014ohm±40%	New	Kit	≥3A	ReFlow
DLW5BTM501TQ2□	500ohm (Typ.)	4000mA	50Vdc	10M ohm	125Vdc	0.019ohm±40%	New	Kit	≥3A	ReFlow
DLW5BTM142TQ2□	1400ohm (Typ.)	2000mA	50Vdc	10M ohm	125Vdc	0.040ohm±40%	New	Kit	≥1A	ReFlow


Operating Temperature Range: -40°C to +85°C Number of Circuit: 1

■ Impedance-Frequency Characteristics  
DLW5AT\_MQ2 Series

## DLW5AT\_TQ2 Series



## DLW5BT\_TQ2 Series




Continued on the following page.

### ■ Notice (Rating)


In operating temperature exceeding +85°C, derating of current is necessary for DLW5AT series (105 degree C available type). Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current




In operating temperature exceeding +85°C, derating of current is necessary for DLW5BT series (105 degree C available type). Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current



In operating temperature exceeding +85°C, derating of current is necessary for DLW5AT series (105 degree C available type). Please apply the derating curve shown in chart according to the operating temperature.


Derating of Rated Current




# DLM11G Series (0504 Size)




Audio line common choke also effective to differential mode.



## ■ Dimensions



## ■ Equivalent Circuit



## ■ Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	10000
B	Bulk(Bag)	1000


Refer to pages from p.194 to p.197 for mounting information.

## ■ Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	Operating Temperature Range
DLM11GN601SD2□	600ohm ±25%	100mA	5Vdc	100M ohm	25Vdc	0.8ohm max.	-40°C to +85°C

Number of Circuit: 1

## ■ Impedance-Frequency Characteristics




# DLM11S Series (0504 Size)




0504 size multilayer type chip common mode choke coil.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	4000
B	Bulk(Bag)	500


Refer to pages from p.194 to p.197 for mounting information.

## Rated Value (□: packaging code)


Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLM11SN450HY2□	45ohm ±25%	100mA	5Vdc	100M ohm	12.5Vdc	0.7ohm±25%	New Kit HD Amp Match
DLM11SN900HY2□	90ohm ±25%	100mA	5Vdc	100M ohm	12.5Vdc	1.1ohm±25%	New Kit HD Amp Match

Operating Temperature Range: -40°C to +85°C Number of Circuit: 1

## Impedance-Frequency Characteristics



## Differential Mode Transmission Characteristics (Typ.)




# DLPOQS Series (025020 Size)




025020 size, very small chip common mode choke coil, Cut-off frequency 8GHz max. Some of them are ready for DisplayPort or SATA.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
D	180mm Reel Paper Tape	15000
B	Bulk(Bag)	500

Refer to pages from p.194 to p.197 for mounting information.

## Rated Value (□: packaging code)


Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLPOQSN600HL2□	60ohm ±25%	50mA	5Vdc	100M ohm	12.5Vdc	3.8ohm±25%	Kit HD
DLPOQSA070HL2□	7ohm ±2ohm	100mA	5Vdc	100M ohm	12.5Vdc	0.7ohm±25%	New Kit
DLPOQSA150HL2□	15ohm ±5ohm	100mA	5Vdc	100M ohm	12.5Vdc	0.8ohm±25%	New Kit
DLPOQSA350HL2□	35ohm ±10ohm	100mA	5Vdc	100M ohm	12.5Vdc	2.2ohm±25%	New Kit

Operating Temperature Range: -40°C to +85°C Number of Circuit: 1


HD: for high speed differential signal lines UD: for ultra high speed differential signal lines

## Impedance-Frequency Characteristics

### DLPOQSN Series




### DLPOQSA Series




## Differential Mode Transmission Characteristics (Typ.)

### DLPOQSN Series



### DLPOQSA Series




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




# DLP0NS Series (03025 Size)




03025 size, very small chip common mode choke coil, Cut-off frequency 8GHz max. Some of them are ready for mipi, DisplayPort or SATA.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	10000
B	Bulk(Bag)	500

Refer to pages from p.194 to p.197 for mounting information.

## Rated Value (□: packaging code)


Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLP0NSC280HL2□	28ohm ±20%	100mA	5Vdc	100M ohm	12.5Vdc	1.3ohm±25%	Kit HD Imp Match
DLP0NSN350HL2□	35ohm ±10ohm	100mA	5Vdc	100M ohm	12.5Vdc	1.2ohm±25%	New Kit HD Imp Match
DLP0NSN670HL2□	67ohm ±20%	110mA	5Vdc	100M ohm	12.5Vdc	2.4ohm±25%	Kit HD Imp Match
DLP0NSN900HL2□	90ohm ±20%	100mA	5Vdc	100M ohm	12.5Vdc	3.0ohm±25%	Kit HD Imp Match
DLP0NSN121HL2□	120ohm ±20%	90mA	5Vdc	100M ohm	12.5Vdc	3.8ohm±25%	Kit HD Imp Match
DLP0NSA070HL2□	7ohm ±2ohm	100mA	5Vdc	100M ohm	12.5Vdc	0.6ohm±25%	New Kit UD Imp Match
DLP0NSA150HL2□	15ohm ±5ohm	100mA	5Vdc	100M ohm	12.5Vdc	0.95ohm±25%	Kit UD Imp Match

Operating Temperature Range: -40°C to +85°C Number of Circuit: 1


HD: for high speed differential signal lines UD: for ultra high speed differential signal lines

## Impedance-Frequency Characteristics

### DLP0NSC/DLP0NSN Series



### DLP0NSA Series




Continued on the following page.


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## ■ Differential Mode Transmission Characteristics (Typ.)


### DLP0NSC/DLP0NSN Series



### DLP0NSN Series



### DLP0NSA Series




# DLP11S/DLP11R/DLP11T Series (0504 Size)




8GHz cut-off frequency (for HDMI/USB 3.0) is available.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	3000 (DLP11S)
		4000 (DLP11RN/RB)
		5000 (DLP11T)
B	Bulk(Bag)	500

Refer to pages from p.194 to p.197 for mounting information.


## Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLP11SN670SL2□	67ohm ±20%	180mA	5Vdc	100M ohm	12.5Vdc	1.3ohm±25%	Kit HD
DLP11SN121SL2□	120ohm ±20%	140mA	5Vdc	100M ohm	12.5Vdc	2.0ohm±25%	Kit HD
DLP11SN161SL2□	160ohm ±20%	120mA	5Vdc	100M ohm	12.5Vdc	2.7ohm±25%	Kit HD
DLP11SN900HL2□	90ohm ±20%	150mA	5Vdc	100M ohm	12.5Vdc	1.5ohm±25%	Kit HD Imp Match
DLP11SN201HL2□	200ohm ±20%	110mA	5Vdc	100M ohm	12.5Vdc	3.1ohm±25%	Kit HD Imp Match
DLP11SN241HL2□	240ohm ±20%	100mA	5Vdc	100M ohm	12.5Vdc	3.5ohm±25%	Kit HD Imp Match
DLP11SN281HL2□	280ohm ±20%	90mA	5Vdc	100M ohm	12.5Vdc	4.2ohm±25%	Kit HD Imp Match
DLP11SN331HL2□	330ohm ±20%	80mA	5Vdc	100M ohm	12.5Vdc	4.9ohm±25%	Kit HD Imp Match
DLP11SA350HL2□	35ohm ±20%	170mA	5Vdc	100M ohm	12.5Vdc	0.9ohm±25%	Kit UD Imp Match
DLP11SA670HL2□	67ohm ±20%	150mA	5Vdc	100M ohm	12.5Vdc	1.2ohm±25%	Kit UD Imp Match
DLP11SA900HL2□	90ohm ±20%	150mA	5Vdc	100M ohm	12.5Vdc	1.4ohm±25%	Kit UD Imp Match


Operating Temperature Range: -40°C to +85°C Number of Circuit: 1

HD: for high speed differential signal lines UD: for ultra high speed differential signal lines

## Impedance-Frequency Characteristics DLP11SN Series



## DLP11SA Series




Continued on the following page.


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Differential Mode Transmission Characteristics (Typ.)

### DLP11SN Series



### DLP11SA Series



## Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLP11RN450UL2□	45ohm ±25%	100mA	5Vdc	100M ohm	12.5Vdc	0.8ohm±25%	Kit HD
DLP11RB150UL2□	15ohm ±5ohm	100mA	5Vdc	100M ohm	12.5Vdc	0.8ohm±25%	Kit UD
DLP11RB400UL2□	40ohm ±10ohm	100mA	5Vdc	100M ohm	12.5Vdc	1.3ohm±25%	Kit UD

Operating Temperature Range: -40°C to +85°C Number of Circuit: 1

HD: for high speed differential signal lines

UD: for ultra high speed differential signal lines

Differential mode to common mode conversion characteristic (Scd21) at 2.5GHz


DLP11RB: -40dB

Impedance Characteristics between signal lines Z0 (TDR at 50ps)


DLP11RB: 90ohm±15ohm

## Impedance-Frequency Characteristics

### DLP11RN Series




### DLP11RB Series




## Differential Mode Transmission Characteristics (Typ.)

### DLP11RN Series




### DLP11RB Series



Continued on the following page.


⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Rated Value (□: packaging code)


Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLP11TB800UL2□	80ohm ±25%	100mA	5Vdc	100M ohm	12.5Vdc	1.5ohm±25%	Kit UD 

Operating Temperature Range: -40°C to +85°C    Number of Circuit: 1    HD: for high speed differential signal lines    UD: for ultra high speed differential signal lines  
Differential mode to common mode conversion characteristic (Scd21) at 2.5GHz  
DLP11TB: -40dB  
Impedance Characteristics between signal lines Z0 (TDR at 50ps)  
DLP11TB: 90ohm±15ohm

■ Impedance-Frequency Characteristics  
DLP11TB Series



■ Differential Mode Transmission Characteristics (Typ.)  
DLP11TB Series



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# DLP31S Series (1206 Size)




## 1206 size film type chip common mode choke coil.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	3000
B	Bulk(Bag)	500

Refer to pages from p.194 to p.197 for mounting information.


### ■ Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLP31SN121ML2□	120ohm ±20%	100mA	16Vdc	100M ohm	40Vdc	2.0ohm max.	HD
DLP31SN221ML2□	220ohm ±20%	100mA	16Vdc	100M ohm	40Vdc	2.5ohm max.	HD
DLP31SN551ML2□	550ohm ±20%	100mA	16Vdc	100M ohm	40Vdc	3.6ohm max.	HD

Operating Temperature Range: -40°C to +85°C Number of Circuit: 1

HD: for high speed differential signal lines UD: for ultra high speed differential signal lines

### ■ Impedance-Frequency Characteristics



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




# DLP1ND Series (05025 Size)




2 circuits in 05025 size, adapt to HDMI line.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	5000
B	Bulk(Bag)	500

Refer to pages from p.194 to p.197 for mounting information.


## Rated Value ( $\square$ : packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLP1NDN350HL4 $\square$	35ohm $\pm 20\%$	100mA	5Vdc	100M ohm	12.5Vdc	1.8ohm $\pm 25\%$	Kit HD
DLP1NDN670HL4 $\square$	67ohm $\pm 20\%$	80mA	5Vdc	100M ohm	12.5Vdc	2.9ohm $\pm 25\%$	Kit HD
DLP1NDN900HL4 $\square$	90ohm $\pm 20\%$	60mA	5Vdc	100M ohm	12.5Vdc	3.7ohm $\pm 25\%$	Kit HD


Operating Temperature Range: -40°C to +85°C Number of Circuit: 2

HD: for high speed differential signal lines UD: for ultra high speed differential signal lines

## Impedance-Frequency Characteristics



## Differential Mode Transmission Characteristics (Typ.)



**Note** • Please read rating and **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# DLP2AD Series (0804 Size)




2 circuit built-in, 0804 size, HDMI adapted type available, cut-off frequency 6GHz max.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	3000
B	Bulk(Bag)	500

Refer to pages from p.194 to p.197 for mounting information.

## Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLP2ADA350HL4□	35ohm $\pm 20\%$	150mA	5Vdc	100M ohm	12.5Vdc	0.8ohm $\pm 25\%$	Kit UD
DLP2ADA670HL4□	67ohm $\pm 20\%$	130mA	5Vdc	100M ohm	12.5Vdc	1.0ohm $\pm 25\%$	Kit UD
DLP2ADA900HL4□	90ohm $\pm 20\%$	120mA	5Vdc	100M ohm	12.5Vdc	1.4ohm $\pm 25\%$	Kit UD
DLP2ADN670HL4□	67ohm $\pm 20\%$	140mA	5Vdc	100M ohm	12.5Vdc	1.3ohm $\pm 25\%$	Kit HD
DLP2ADN900HL4□	90ohm $\pm 20\%$	130mA	5Vdc	100M ohm	12.5Vdc	1.7ohm $\pm 25\%$	Kit HD
DLP2ADN121HL4□	120ohm $\pm 20\%$	120mA	5Vdc	100M ohm	12.5Vdc	2.0ohm $\pm 25\%$	Kit HD
DLP2ADN161HL4□	160ohm $\pm 20\%$	100mA	5Vdc	100M ohm	12.5Vdc	2.5ohm $\pm 25\%$	Kit HD
DLP2ADN201HL4□	200ohm $\pm 20\%$	90mA	5Vdc	100M ohm	12.5Vdc	3.2ohm $\pm 25\%$	Kit HD
DLP2ADN241HL4□	240ohm $\pm 20\%$	80mA	5Vdc	100M ohm	12.5Vdc	3.8ohm $\pm 25\%$	Kit HD
DLP2ADN281HL4□	280ohm $\pm 20\%$	80mA	5Vdc	100M ohm	12.5Vdc	4.6ohm $\pm 25\%$	Kit HD


Operating Temperature Range: -40°C to +85°C Number of Circuit: 2

HD: for high speed differential signal lines


UD: for ultra high speed differential signal lines

## Impedance-Frequency Characteristics

### DLP2ADA Series



### DLP2ADN Series




Continued on the following page.


⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

■ Differential Mode Transmission Characteristics (Typ.)

DLP2ADA Series



DLP2ADN Series



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# DLP31D Series (1206 Size)




2 circuit built-in, 1206 size, meet IEEE1394,USB,LVDS.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	3000
B	Bulk(Bag)	500

Refer to pages from p.194 to p.197 for mounting information.


## Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLP31DN900ML4□	90ohm ±20%	160mA	10Vdc	100M ohm	25Vdc	1.1ohm max.	HD
DLP31DN131ML4□	130ohm ±20%	120mA	10Vdc	100M ohm	25Vdc	1.1ohm max.	HD
DLP31DN201ML4□	200ohm ±20%	100mA	10Vdc	100M ohm	25Vdc	2.2ohm max.	HD
DLP31DN321ML4□	320ohm ±20%	80mA	10Vdc	100M ohm	25Vdc	3.5ohm max.	HD
DLP31DN441ML4□	440ohm ±20%	70mA	10Vdc	100M ohm	25Vdc	4.3ohm max.	HD

Operating Temperature Range: -40°C to +85°C Number of Circuit: 2

HD: for high speed differential signal lines UD: for ultra high speed differential signal lines

## Impedance-Frequency Characteristics




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# DLW21S Series (0805 Size)



Wire-wound common choke, HDMI available type prepared.



Refer to pages from p.194 to p.197 for mounting information.


## ■ Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLW21SN670SQ2□	67ohm ±25%	400mA	50Vdc	10M ohm	125Vdc	0.25ohm max.	Kit HD
DLW21SN900SQ2□	90ohm ±25%	330mA	50Vdc	10M ohm	125Vdc	0.35ohm max.	Kit HD
DLW21SN121SQ2□	120ohm ±25%	370mA	50Vdc	10M ohm	125Vdc	0.30ohm max.	Kit HD
DLW21SN181SQ2□	180ohm ±25%	330mA	50Vdc	10M ohm	125Vdc	0.35ohm max.	Kit HD
DLW21SN261SQ2□	260ohm ±25%	300mA	50Vdc	10M ohm	125Vdc	0.40ohm max.	Kit HD
DLW21SN371SQ2□	370ohm ±25%	280mA	50Vdc	10M ohm	125Vdc	0.45ohm max.	Kit HD
DLW21SN501SK2□	500ohm ±25%	250mA	50Vdc	10M ohm	125Vdc	0.5ohm max.	Kit HD

Operating Temperature Range: -40°C to +85°C Number of Circuit: 1

HD: for high speed differential signal lines UD: for ultra high speed differential signal lines

## ■ Impedance-Frequency Characteristics



## ■ Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLW21SN670HQ2□	67ohm ±25%	320mA	20Vdc	10M ohm	50Vdc	0.31ohm max.	Kit UD Lmp
DLW21SN900HQ2□	90ohm ±25%	280mA	20Vdc	10M ohm	50Vdc	0.41ohm max.	Kit UD Lmp
DLW21SN121HQ2□	120ohm ±25%	280mA	20Vdc	10M ohm	50Vdc	0.41ohm max.	Kit UD Lmp
DLW21SR670HQ2□	67ohm ±25%	400mA	20Vdc	10M ohm	50Vdc	0.25ohm max.	Kit UD Lmp

Operating Temperature Range: -40°C to +85°C Number of Circuit: 1


HD: for high speed differential signal lines UD: for ultra high speed differential signal lines

DLW21SR670HQ2 is designed to correct line impedance when ESD protection device is also used.


Continued on the following page. ↗

## ■ Impedance-Frequency Characteristics

### DLW21SN\_HQ2 Series




### DLW21SR\_HQ2 Series



## ■ Differential Mode Transmission Characteristics (Typ.)

### DLW21SN\_HQ2 Series



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




# DLW21H Series (0805 Size)




Low profile wire-wound common choke coil, HDMI available type prepared.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	3000
B	Bulk(Bag)	500

Refer to pages from p.194 to p.197 for mounting information.



## Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLW21HN670SQ2□	67ohm ±25%	330mA	50Vdc	10M ohm	125Vdc	0.35ohm max.	Kit HD
DLW21HN900SQ2□	90ohm ±25%	330mA	50Vdc	10M ohm	125Vdc	0.35ohm max.	Kit HD
DLW21HN121SQ2□	120ohm ±25%	280mA	50Vdc	10M ohm	125Vdc	0.45ohm max.	Kit HD
DLW21HN181SQ2□	180ohm ±25%	250mA	50Vdc	10M ohm	125Vdc	0.50ohm max.	Kit HD
DLW21HN670HQ2□	67ohm ±25%	240mA	20Vdc	10M ohm	50Vdc	0.49ohm max.	New Kit UD Imp Match
DLW21HN900HQ2□	90ohm ±25%	220mA	20Vdc	10M ohm	50Vdc	0.59ohm max.	New Kit UD Imp Match
DLW21HN121HQ2□	120ohm ±25%	200mA	20Vdc	10M ohm	50Vdc	0.68ohm max.	New Kit UD Imp Match


Operating Temperature Range: -40°C to +85°C Number of Circuit: 1

HD: for high speed differential signal lines UD: for ultra high speed differential signal lines

## Impedance-Frequency Characteristics



## Differential Mode Transmission Characteristics (Typ.)



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# DLW31S Series (1206 Size)




## 1206 size wire-wound common mode choke coil.



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	2000
B	Bulk(Bag)	500

Refer to pages from p.194 to p.197 for mounting information.


### ■ Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	
DLW31SN900SQ2□	90ohm ±25%	370mA	50Vdc	10M ohm	125Vdc	0.3ohm max.	HD
DLW31SN161SQ2□	160ohm ±25%	340mA	50Vdc	10M ohm	125Vdc	0.4ohm max.	HD
DLW31SN261SQ2□	260ohm ±25%	310mA	50Vdc	10M ohm	125Vdc	0.5ohm max.	HD
DLW31SN601SQ2□	600ohm ±25%	260mA	50Vdc	10M ohm	125Vdc	0.8ohm max.	HD
DLW31SN102SQ2□	1000ohm ±25%	230mA	50Vdc	10M ohm	125Vdc	1.0ohm max.	HD
DLW31SN222SQ2□	2200ohm ±25%	200mA	50Vdc	10M ohm	125Vdc	1.2ohm max.	HD

Operating Temperature Range: -40°C to +85°C Number of Circuit: 1

HD: for high speed differential signal lines UD: for ultra high speed differential signal lines

### ■ Impedance-Frequency Characteristics




△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# PLT10H Series (12.9x6.6mm)




Automotive application available, up to 18A.



## Dimensions



## Equivalent Circuit



## Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	125
K	330mm Reel Embossed Tape	500
B	Bulk(Bag)	50


Refer to pages from p.198 to p.199 for mounting information.

## Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 10MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	Inductance	
PLT10HH450180PN□	45ohm (Typ.)	18A	300Vdc	10M ohm	750Vdc	1.3m ohm±0.5m ohm	0.8μH min.	New Kit ≥10A
PLT10HH101150PN□	100ohm (Typ.)	15A	300Vdc	10M ohm	750Vdc	1.8m ohm±0.5m ohm	2.0μH min.	New Kit ≥10A
PLT10HH401100PN□	400ohm (Typ.)	10A	100Vdc	10M ohm	250Vdc	3.6m ohm±0.5m ohm	6μH min.	Kit ≥10A
PLT10HH501100PN□	500ohm (Typ.)	10A	100Vdc	10M ohm	250Vdc	3.6m ohm±0.5m ohm	9μH min.	Kit ≥10A
PLT10HH9016R0PN□	900ohm (Typ.)	6A	100Vdc	10M ohm	250Vdc	8.0m ohm±0.5m ohm	14μH min.	Kit ≥3A
PLT10HH1026R0PN□	1000ohm (Typ.)	6A	100Vdc	10M ohm	250Vdc	8.0m ohm±0.5m ohm	20μH min.	Kit ≥3A

Operating Temperature Range (Self-temperature rise is included): -55°C to +105°C (PLT10HH 501100/1026R0 PN), -55°C to +125°C (PLT10HH 450180/101150/401100/9016R0 PN) Number of Circuit: 1

## Impedance-Frequency Characteristics




## Notice (Rating)

In operating temperature exceeding +65°C, derating of current is necessary for PLT10H series.

Please apply the derating curve shown in chart according to the operating temperature.

### Derating of Rated Current



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## ⚠ Caution

## ● Rating

Do not use products beyond the rated current and rated voltage as this may create excessive heat and deteriorate the insulation resistance.


## ● Soldering and Mounting

## 1. Self-heating

Please provide special attention when mounting chip common mode choke coils DLW5 series in close proximity to other products that radiate heat. The heat generated by other products may deteriorate the insulation resistance and cause excessive heat in this component.

## 2. Mounting Direction

Mount Chip Common Mode Choke Coils in right direction. Wrong direction, which is 90 degrees rotated from right direction, causes not only open or short circuit but also flames or other serious trouble.



## Notice

## ● Storage and Operating Conditions

## &lt;Operating Environment&gt;

Do not use products in a chemical atmosphere such as chlorine gas, acid or sulfide gas. Do not use products in the environment close to the organic solvent.

## &lt;Storage and Handling Requirements&gt;

## 1. Storage Period

DLM11G series should be used within 6 months, the other series should be used within 12 months. Solderability should be checked if this period is exceeded.

## 2. Storage Conditions

- (1) Storage temperature: -10 to +40°C  
Relative humidity: 15 to 85%  
Avoid sudden changes in temperature and humidity.
- (2) Do not store products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.

## ● Notice (Soldering and Mounting)

## 1. Cleaning

Failure and degradation of a product are caused by the cleaning method. When you clean in conditions that are not in mounting information, please contact Murata engineering.

## 2. Soldering

Reliability decreases with improper soldering methods. Please solder by the standard soldering conditions shown in mounting information.

## 3. Other

Noise suppression levels resulting from Murata's EMI suppression filters EMIFIL® may vary, depending on the circuits and ICs used, type of noise, mounting pattern, mounting location, and other operating conditions. Be sure to check and confirm in advance the noise suppression effect of each filter, in actual circuits, etc. before applying the filter in a commercial-purpose equipment design.

## ● Handling

## 1. Resin Coating (Except for DLW Series.)

Using resin for coating/molding products may affect the products performance. So please pay careful attention in selecting resin. Prior to use, please make the reliability evaluation with the product mounted in your application set.

## 2. Resin Coating (DLW Series)

The impedance value may change due to high cure-stress of resin to be used for coating/molding products. An open circuit issue may occur by mechanical stress caused by the resin, amount/cured shape of resin, or operating condition etc. Some resin contains some impurities or chloride possible to generate chlorine by hydrolysis under some operating condition may cause corrosion of wire of coil, leading to open circuit. So, please pay your careful attention in selecting resin in case of coating/molding the products with the resin. Prior to use the coating resin, please make sure no reliability issue is observed by evaluating products mounted on your board.

## 3. Caution for Use (DLW Series)


When you hold products with a tweezer, please hold by the sides. Sharp materials, such as a pair of tweezers, should not touch the winding portion to prevent breaking the wire. Mechanical shock should not be applied to the products mounted on the board to prevent breaking the core.

## 4. Brushing

When you clean the neighborhood of products such as connector pins, bristles of cleaning brush shall not be touched to the winding portion of this product to prevent the breaking of wire.

## 5. Handling of a Substrate

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate. Excessive mechanical stress may cause cracking in the Product.



⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## ⚠ Caution

## ● Rating

1. Do not use products beyond the rated current and rated voltage as this may create excessive heat and deteriorate the insulation resistance.
2. Be sure to provide an appropriate fail-safe function on your product to prevent a second damage that may be caused by the abnormal function or the failure of our product.

## ● Soldering and Mounting


## 1. Self-heating

Please provide special attention when mounting chip common mode choke coils in close proximity to other products that radiate heat.

The heat generated by other products may deteriorate the insulation resistance and cause excessive heat in this component.

## 2. Mounting Direction

Mount Chip Common Mode Choke Coils in right direction. Wrong direction, which is 90 degrees rotated from right direction, causes not only open or short circuit but also flames or other serious trouble.



## Notice

## ● Storage and Operating Conditions

## &lt;Operating Environment&gt;

Do not use products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.

Do not use products in the environment close to the organic solvent.

## &lt;Storage and Handling Requirements&gt;

## 1. Storage Period

PLT10H series should be used within 12 months.  
Solderability should be checked if this period is exceeded.

## 2. Storage Conditions

- (1) Storage temperature: -10 to +40°C  
Relative humidity: 15 to 85%  
Avoid sudden changes in temperature and humidity.
- (2) Do not store products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.

## ● Notice (Soldering and Mounting)

## 1. Cleaning

Failure and degradation of a product are caused by the cleaning method. When you clean in conditions that are not in mounting information, please contact Murata engineering.

## 2. Soldering

Reliability decreases with improper soldering methods. Please solder by the standard soldering conditions shown in mounting information.

## 3. Other

Noise suppression levels resulting from Murata's EMI suppression filters EMIFIL<sup>®</sup> may vary, depending on the circuits and ICs used, type of noise, mounting pattern, mounting location, and other operating conditions. Be sure to check and confirm in advance the noise suppression effect of each filter, in actual circuits, etc. before applying the filter in a commercial-purpose equipment design.


## ● Handling

## 1. Handling of a Substrate


After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate.

Excessive mechanical stress may cause cracking in the Product.

## Bending



## Twisting






### 1. Standard Land Pattern Dimensions


(in mm)

DLM11S  
 DLM11G  
 DLP0QS  
 DLP0NS  
 DLP11S  
 DLP11R  
 DLP11T  
 DLP1ND  
 DLP2AD  
 DLP31S  
 DLP31D  
 DLW21S  
 DLW21H  
 DLW31SN  
 DLW5A  
 DLW5B

#### ●Reflow and Flow DLP31S




#### DLP31D




#### ●Reflow Soldering


##### DLP0QS




##### DLP0NS




##### DLP11S/DLM11S




##### DLP11R/11T




##### DLP1ND




##### DLP2AD




##### DLM11G



##### DLW21S/21H/31SN



#### DLW5A/5B (Except for DLW5AT\_MQ2)



Series	a	b	c	d
DLW21S/H	0.8	2.6	0.4	1.2
DLW31SN	1.6	3.7	0.4	1.6


\*1: If the pattern is made with wider than 1.2mm (DLW21) / 1.6mm (DLW31S) it may result in components turning around, because melting speed is different. In the worst case, short circuit between lines may occur.

\*2: If the pattern is made with less than 0.4mm, in the worst case, short circuit between lines may occur due to spread of soldering paste or mount placing accuracy.


\*3: If the pattern is made with wider than 0.8mm (DLW21) / 1.6mm (DLW31SN), the bending strength will be reduced. Do not use gild pattern; excess soldering heat may dissolve metal of a copper wire.

#### DLW5AT\_MQ2

#### ●Reflow Soldering Chip Mounting Side DLW5AT\_MQ2



#### ●Flow Soldering Chip Mounting Side DLW5AT\_MQ2




⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



### ● PCB Warping

PCB should be designed so that products are not subjected to the mechanical stress caused by warping the board.

Products should be located in the sideways direction (Length:  $a < b$ ) to the mechanical stress.



## 2. Solder Paste Printing and Adhesive Application

When reflow soldering the chip common mode choke coils, the printing must be conducted in accordance with the following cream solder printing conditions.








If too much solder is applied, the chip will be prone to damage by mechanical and thermal stress from the PCB and may crack.

Standard land dimensions should be used for resist and copper foil patterns.

When flow soldering the chip common mode choke coils, apply the adhesive in accordance with the following conditions.

If too much adhesive is applied, then it may overflow into the land or termination areas and yield poor solderability. In contrast, if insufficient adhesive is applied, or if the adhesive is not sufficiently hardened, then the chip may become detached during flow soldering process.

(in mm)

Series	Solder Paste Printing	Adhesive Application																																			
DLP DLW DLM	<p>● Guideline of solder paste thickness: 80-100μm: DLP0QS 100-150μm: DLW21S/21H/31S, DLP0NS/11S/11R/11T/1ND/2AD/DLM11G 150-200μm: DLP31D/31S, DLW5A/5B</p> <p>*Solderability is subject to reflow conditions and thermal conductivity. Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.</p>	<p>■ DLP31S/DLP31D/DLW5AT_MQ2 Apply 0.3mg of bonding agent at each chip.</p>																																			
	<p>DLP0QS/0NS/11S/11R/11T/31S/DLM11G</p> 	<p>DLP31D</p>  <p>Coating Position of Bonding Agent</p>																																			
	<p>DLW21S/21H/31S</p> 	<p>DLP31S</p>  <p>Coating Position of Bonding Agent</p>																																			
	<table border="1"><thead><tr><th>Series</th><th>a</th><th>b</th><th>c</th><th>d</th></tr></thead><tbody><tr><td>DLP0QS</td><td>0.3</td><td>0.2</td><td>0.23</td><td>0.48</td></tr><tr><td>DLP0NS</td><td>0.3</td><td>0.3</td><td>0.3</td><td>0.5</td></tr><tr><td>DLP11S</td><td>0.7</td><td>0.55</td><td>0.3</td><td>0.55</td></tr><tr><td>DLP11R/T</td><td>0.5</td><td>0.55</td><td>0.3</td><td>0.55</td></tr><tr><td>DLP31S</td><td>1.0</td><td>0.6</td><td>0.7</td><td>2.1</td></tr><tr><td>DLM11G</td><td>0.5</td><td>0.5</td><td>0.4</td><td>0.7</td></tr></tbody></table>	Series	a	b	c	d	DLP0QS	0.3	0.2	0.23	0.48	DLP0NS	0.3	0.3	0.3	0.5	DLP11S	0.7	0.55	0.3	0.55	DLP11R/T	0.5	0.55	0.3	0.55	DLP31S	1.0	0.6	0.7	2.1	DLM11G	0.5	0.5	0.4	0.7	<p>DLW5AT_MQ2</p>  <p>Coating Position of Bonding Agent</p>
	Series	a	b	c	d																																
	DLP0QS	0.3	0.2	0.23	0.48																																
	DLP0NS	0.3	0.3	0.3	0.5																																
	DLP11S	0.7	0.55	0.3	0.55																																
	DLP11R/T	0.5	0.55	0.3	0.55																																
	DLP31S	1.0	0.6	0.7	2.1																																
DLM11G	0.5	0.5	0.4	0.7																																	
<p>DLP1ND/2AD/31D</p> 	<table border="1"><thead><tr><th>Series</th><th>a</th><th>b</th><th>c</th><th>d</th></tr></thead><tbody><tr><td>DLP1ND</td><td>0.3</td><td>0.3</td><td>0.2</td><td>0.4</td></tr><tr><td>DLP2AD</td><td>0.55</td><td>0.4</td><td>0.25</td><td>0.5</td></tr><tr><td>DLP31D</td><td>1.0</td><td>0.8</td><td>0.4</td><td>0.8</td></tr></tbody></table>	Series	a	b	c	d	DLP1ND	0.3	0.3	0.2	0.4	DLP2AD	0.55	0.4	0.25	0.5	DLP31D	1.0	0.8	0.4	0.8																
Series	a	b	c	d																																	
DLP1ND	0.3	0.3	0.2	0.4																																	
DLP2AD	0.55	0.4	0.25	0.5																																	
DLP31D	1.0	0.8	0.4	0.8																																	
<p>DLW5A/5B</p> 																																					

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## 3. Standard Soldering Conditions

## (1) Soldering Methods

Use flow and reflow soldering methods only.

Use standard soldering conditions when soldering chip common mode choke coils.

In cases where several different parts are soldered, each having different soldering conditions, use those conditions requiring the least heat and minimum time.

Solder: Use Sn-3.0Ag-0.5Cu solder. Use of Sn-Zn based solder will deteriorate performance of products.

If using DLP/DLM series with Sn-Zn based solder, please contact Murata in advance.

## Flux:

- Use Rosin-based flux.

In case of DLW21/31 series, use Rosin-based flux with converting chlorine content of 0.06 to 0.1wt%.


In case of using RA type solder, products should be cleaned completely with no residual flux.

- Do not use strong acidic flux (with chlorine content exceeding 0.20wt%)
- Do not use water-soluble flux.

For additional mounting methods, please contact Murata.


## (2) Soldering Profile

- Flow Soldering Profile  
(Sn-3.0Ag-0.5Cu Solder)



Series	Pre-heating		Standard Profile			Limit Profile		
			Heating		Cycle of Flow	Heating		Cycle of Flow
	Temp. (T1)	Time. (t1)	Temp. (T2)	Time. (t2)		Temp. (T3)	Time. (t2)	
DLW5AT_MQ2 DLP31D/31S	150°C	60s min.	250°C	4 to 6s	2 times max.	265±3°C	5s max.	2 times max.

- Reflow Soldering Profile  
(Sn-3.0Ag-0.5Cu Solder)



Series	Standard Profile				Limit Profile			
	Heating		Peak Temperature (T2)	Cycle of Reflow	Heating		Peak Temperature (T4)	Cycle of Reflow
	Temp. (T1)	Time. (t1)			Temp. (T3)	Time. (t2)		
DLM/DLP DLW21/31	220°C min.	30 to 60s	245±3°C	2 times max.	230°C min.	60s max.	260°C/10s	2 times max.
DLW5A/5B	220°C min.	30 to 60s	250±3°C	2 times max.	230°C min.	60s max.	260°C/10s	2 times max.

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## (3) Reworking with Solder Iron

The following conditions must be strictly followed when using a soldering iron.

Pre-heating: 150°C 60s min.

Soldering iron power output / Tip diameter:

30W max. / ø3mm max.

Temperature of soldering iron tip / Soldering time / Times:

350°C max. / 3-4s / 2 times\*<sup>1</sup>

\*<sup>1</sup> DLP0QS, DLP0NS, DLP11S, DLP11T, DLP1ND,  
DLP2AD: 380°C max. / 3-4s / 2 times

Do not allow the tip of the soldering iron to directly contact the chip.

For additional methods of reworking with a soldering iron, please contact Murata engineering.

## 4. Cleaning

Following conditions should be observed when cleaning chip EMI filter.

(1) Cleaning Temperature: 60°C max. (40°C max. for alcohol type cleaner)

(2) Ultrasonic

Output: 20W/liter max.

Duration: 5 minutes max.

Frequency: 28 to 40kHz

(3) Cleaning agent

The following list of cleaning agents have been tested on the individual components. Evaluation of final assembly should be completed prior to production.

Do not clean DLW (Except for DLW21H) series.

Before cleaning, please contact Murata engineering.

(a) Alcohol cleaning agent

Isopropyl alcohol (IPA)

(b) Aqueous cleaning agent

Pine Alpha ST-100S

(4) Ensure that flux residue is completely removed.

Component should be thoroughly dried after aqueous agent has been removed with deionized water.

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




## 1. Standard Land Pattern Dimensions

(in mm)

## PLT10H

## ● Reflow Soldering


Copper Foil Pattern  
 Copper Foil Pattern + Resist  
 Resist



## ● PCB Warping

PCB should be designed so that products are not subjected to the mechanical stress caused by warping the board.

Products should be located in the sideways direction (Length:  $a < b$ ) to the mechanical stress.



## 2. Solder Paste Printing and Adhesive Application

When reflow soldering the chip common mode choke coils, the printing must be conducted in accordance with the following cream solder printing conditions.

If too much solder is applied, the chip will be prone to damage by mechanical and thermal stress from the PCB and may crack.

Standard land dimensions should be used for resist and copper foil patterns.

When flow soldering the chip common mode choke coils, apply the adhesive in accordance with the following conditions.

If too much adhesive is applied, then it may overflow into the land or termination areas and yield poor solderability. In contrast, if insufficient adhesive is applied, or if the adhesive is not sufficiently hardened, then the chip may become detached during flow soldering process.

Series	Solder Paste Printing
PLT10H	<p>● Guideline of solder paste thickness: 150-200<math>\mu</math>m: PLT10H For the solder paste printing pattern, use standard land dimensions.</p> <p>*Solderability is subject to reflow conditions and thermal conductivity. Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.</p>

### 3. Standard Soldering Conditions

#### (1) Soldering Methods

Use reflow soldering methods only.  
Use standard soldering conditions when soldering chip common mode choke coils.  
In cases where several different parts are soldered, each having different soldering conditions, use those conditions requiring the least heat and minimum time.

Solder: Use Sn-3.0Ag-0.5Cu solder. Use of Sn-Zn based solder will deteriorate performance of products.


Flux:

- Use Rosin-based flux.
- Do not use strong acidic flux (with chlorine content exceeding 0.20wt%)
- Do not use water-soluble flux.

For additional mounting methods, please contact Murata.

#### (2) Soldering Profile

##### ● Reflow Soldering Profile (Sn-3.0Ag-0.5Cu Solder)



Series	Standard Profile				Limit Profile			
	Heating		Peak Temperature (T2)	Cycle of Reflow	Heating		Peak Temperature (T4)	Cycle of Reflow
	Temp. (T1)	Time. (t1)			Temp. (T3)	Time. (t2)		
PLT10H	220°C min.	30 to 60s	250±3°C	2 times max.	230°C min.	60s max.	260°C/10s	2 times max.

#### (3) Reworking with Solder Iron

The following conditions must be strictly followed when using a soldering iron.  
Pre-heating: 150°C 60s min.  
Soldering iron power output / Tip diameter:  
80W max. / ø3mm max.  
Temperature of soldering iron tip / Soldering time / Times:  
400°C max. / 5s / 2 times


Do not allow the tip of the soldering iron to directly contact the chip.

For additional methods of reworking with a soldering iron, please contact Murata engineering.

### 4. Cleaning

Do not clean after soldering. If cleaning, please contact us.


## ■ Minimum Quantity and Dimensions of 8mm Width Paper / Embossed Tape



\*1 DLM11G/DLP0QS: 2.0±0.05  
DLP0NS: 2.0±0.1

Dimension of the cavity of embossed tape is measured at the bottom side.

<Embossed>



c: Depth of Cavity  
(Embossed Tape)

<Paper>




c: Total Thickness of Tape  
(Paper Tape)

DLP0QS

Part Number	Dimensions				Minimum Qty. (pcs.)				
					ø180mm Reel		ø330mm Reel		Bulk
	a	b	c	d	Paper Tape	Embossed Tape	Paper Tape	Embossed Tape	
DLM11G	1.45	1.2	0.8 max.	-	10000	-	-	-	1000
DLM11S	1.4	1.15	0.65	0.25	-	4000	-	-	500
DLP0QS	0.73	0.6	0.55 max.	-	15000	-	-	-	500
DLP0NS	0.95	0.75	0.55	0.25	-	10000	-	-	500
DLP11S	1.4	1.2	0.98	0.25	-	3000	-	-	500
DLP11R	1.4	1.15	0.7	0.25	-	4000	-	-	500
DLP11T	1.35	1.1	0.45	0.25	-	5000	-	-	500
DLP1ND	1.7	0.84	0.57	0.25	-	5000	-	-	500
DLP2AD	2.2	1.2	0.98	0.25	-	3000	-	-	500
DLP31D/31S	3.5	1.9	1.3	0.25	-	3000	-	-	500
DLW21S	2.25	1.45	1.4	0.3	-	2000	-	-	500
DLW21H	2.3	1.55	1.1	0.25	-	3000	-	-	500
DLW31S	3.6	2.0	2.1	0.3	-	2000	-	-	500

(in mm)

## ■ Minimum Quantity and Dimensions of 12mm Width Embossed Tape



\*1 DLW5AT: 0.3 c: Depth of Cavity

Dimension of the cavity is measured at the bottom side.

Part Number	Dimensions			Minimum Qty. (pcs.)		
	a	b	c	ø180mm Reel	ø330mm Reel	Bulk
DLW5AH	5.4	4.1	4.4	400	1500	100
DLW5AT	5.4	4.1	2.7	700	2500	100
DLW5BS	5.5	5.4	4.7	400	1500	100
DLW5BT	5.5	5.5	2.7	700	2500	100


(in mm)

"Minimum Quantity" means the number of units of each delivery or order. The quantity should be an integral multiple of the "Minimum Quantity."

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.




## ■ Minimum Quantity and Dimensions of 24mm Width Embossed Tape



Dimension of the cavity is measured at the bottom side.


Part Number	Dimensions				Minimum Qty. (pcs.)		
	a	b	c	d	ø180mm Reel	ø330mm Reel	Bulk
PLT10H	13.5	6.8	9.4	0.5	125	500	50

(in mm)



### ●EKEMDL21P (Chip Common Mode Choke Coils)

No.	Part Number	Quantity (pcs.)	Common Mode Impedance (at 100MHz, 20 degrees C)	Rated Voltage (Vdc)	Rated Current (mA)
1	DLW21HN670SQ2	10	67Ω±25%	50	330
2	DLW21HN900SQ2	10	90Ω±25%	50	330
3	DLW21HN121SQ2	10	120Ω±25%	50	280
4	DLW21HN181SQ2	10	180Ω±25%	50	250
5	DLW21HN670HQ2	10	67Ω±25%	20	240
6	DLW21HN900HQ2	10	90Ω±25%	20	220
7	DLW21HN121HQ2	10	120Ω±25%	20	200
8	DLW21SN501SK2	10	500Ω±25%	50	250
9	DLW21SN670SQ2	10	67Ω±25%	50	400
10	DLW21SN900SQ2	10	90Ω±25%	50	330
11	DLW21SN121SQ2	10	120Ω±25%	50	370
12	DLW21SN181SQ2	10	180Ω±25%	50	330
13	DLW21SN261SQ2	10	260Ω±25%	50	300
14	DLW21SN371SQ2	10	370Ω±25%	50	280
15	DLW21SN670HQ2	10	67Ω±25%	20	320
16	DLW21SN900HQ2	10	90Ω±25%	20	280
17	DLW21SN121HQ2	10	120Ω±25%	20	280
18	DLW21SR670HQ2	10	67Ω±25%	20	400
19	DLP0NSC280HL2	10	28Ω±20%	5	100
20	DLP0NSN350HL2	10	35Ω±10Ω	5	100
21	DLP0NSN670HL2	10	67Ω±20%	5	110
22	DLP0NSN900HL2	10	90Ω±20%	5	100
23	DLP0NSN121HL2	10	120Ω±20%	5	90
24	DLP0NSA070HL2	10	7Ω±2Ω	5	100
25	DLP0NSA150HL2	10	15Ω±5Ω	5	100
26	DLP0QSN600HL2	10	60Ω±25%	5	50
27	DLP0QSA070HL2	10	7Ω±2Ω	5	100
28	DLP0QSA150HL2	10	15Ω±5Ω	5	100
29	DLP0QSA350HL2	10	35Ω±10Ω	5	100
30	DLP1NDN350HL4	10	35Ω±20%	5	100
31	DLP1NDN670HL4	10	67Ω±20%	5	80
32	DLP1NDN900HL4	10	90Ω±20%	5	60
33	DLP11SA350HL2	10	35Ω±20%	5	170
34	DLP11SA670HL2	10	67Ω±20%	5	150
35	DLP11SA900HL2	10	90Ω±20%	5	150
36	DLP11SN670SL2	10	67Ω±20%	5	180
37	DLP11SN121SL2	10	120Ω±20%	5	140
38	DLP11SN161SL2	10	160Ω±20%	5	120
39	DLP11SN900HL2	10	90Ω±20%	5	150
40	DLP11SN201HL2	10	200Ω±20%	5	110
41	DLP11SN241HL2	10	240Ω±20%	5	100
42	DLP11SN281HL2	10	280Ω±20%	5	90
43	DLP11SN331HL2	10	330Ω±20%	5	80
44	DLP11RB150UL2	10	15Ω±5Ω	5	100
45	DLP11RB400UL2	10	40Ω±10Ω	5	100
46	DLP11RN450UL2	10	45Ω±25%	5	100
47	DLP11TB800UL2	10	80Ω±25%	5	100
48	DLP2ADA350HL4	10	35Ω±20%	5	150
49	DLP2ADA670HL4	10	67Ω±20%	5	130
50	DLP2ADA900HL4	10	90Ω±20%	5	120
51	DLP2ADN670HL4	10	67Ω±20%	5	140
52	DLP2ADN900HL4	10	90Ω±20%	5	130
53	DLP2ADN121HL4	10	120Ω±20%	5	120
54	DLP2ADN161HL4	10	160Ω±20%	5	100
55	DLP2ADN201HL4	10	200Ω±20%	5	90

Continued on the following page. 

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

No.	Part Number	Quantity (pcs.)	Common Mode Impedance (at 100MHz, 20 degrees C)	Rated Voltage (Vdc)	Rated Current (mA)
56	DLP2ADN241HL4	10	240Ω±20%	5	80
57	DLP2ADN281HL4	10	280Ω±20%	5	80
58	DLM11SN450HY2	10	45Ω±25%	5	100
59	DLM11SN900HY2	10	90Ω±25%	5	100

●EKEMDCC5E (Chip Common Mode Choke Coils for DC Power Line / SMD Block type EMIFIL<sup>®</sup> for Power Line)

No.	Part Number	Quantity (pcs.)	Common Mode Impedance (at 100MHz, 20 degrees C)	Rated Voltage (Vdc)	Rated Current (mA)
1	DLW5AHN402SQ2	5	4000Ω (Typ.)	50	200
2	DLW5ATN111SQ2	5	110Ω (Typ.)	50	5000
3	DLW5ATN401SQ2	5	400Ω (Typ.)	50	2000
4	DLW5ATN501SQ2	5	500Ω (Typ.)	50	1500
5	DLW5ATN851SQ2	5	850Ω (Typ.)	50	1500
6	DLW5ATN272SQ2	5	2700Ω (Typ.)	50	1000
7	DLW5BSM191SQ2	5	190Ω (Typ.)	50	5000
8	DLW5BSM351SQ2	5	350Ω (Typ.)	50	2000
9	DLW5BSM102SQ2	5	1000Ω (Typ.)	50	1500
10	DLW5BSM152SQ2	5	1500Ω (Typ.)	50	1000
11	DLW5BSM302SQ2	5	3000Ω (Typ.)	50	500
12	DLW5BTM101SQ2	5	100Ω (Typ.)	50	6000
13	DLW5BTM251SQ2	5	250Ω (Typ.)	50	5000
14	DLW5BTM501SQ2	5	500Ω (Typ.)	50	4000
15	DLW5BTM102SQ2	5	1000Ω (Typ.)	50	2000
16	DLW5BTM142SQ2	5	1400Ω (Typ.)	50	1500

●EKEMDL5AA (Chip Common Mode Choke Coils for DC Power Line / SMD Block type EMIFIL<sup>®</sup> for Power Line / 105 degree C available type)

No.	Part Number	Quantity (pcs.)	Common Mode Impedance (at 100MHz, 20 degrees C)	Rated Voltage (Vdc)	Rated Current (mA)
1	DLW5ATN500MQ2	5	50Ω (Typ.)	50	6000
2	DLW5ATN151MQ2	5	150Ω (Typ.)	50	5000
3	DLW5ATN331MQ2	5	330Ω (Typ.)	50	4000
4	DLW5ATN112MQ2	5	1100Ω (Typ.)	50	2000
5	DLW5ATN450TQ2	5	45Ω (Typ.)	50	7000
6	DLW5ATN111TQ2	5	110Ω (Typ.)	50	5000
7	DLW5ATN231TQ2	5	230Ω (Typ.)	50	4000
8	DLW5ATN501TQ2	5	500Ω (Typ.)	50	2000
9	DLW5BTM101TQ2	5	100Ω (Typ.)	50	6000
10	DLW5BTM251TQ2	5	250Ω (Typ.)	50	5000
11	DLW5BTM501TQ2	5	500Ω (Typ.)	50	4000
12	DLW5BTM142TQ2	5	1400Ω (Typ.)	50	2000

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



## ●EKEPBLCKD

No.	Part Number	Quantity (pcs.)	Common Mode Impedance (at 10MHz, 20 degrees C)	Rated Voltage (Vdc)	Rated Current (A)
1	PLT10HH450180PN	2	45Ω (Typ.)	300	18
2	PLT10HH101150PN	2	100Ω (Typ.)	300	15
3	PLT10HH401100PN	2	400Ω (Typ.)	100	10
4	PLT10HH501100PN	2	500Ω (Typ.)	100	10
5	PLT10HH9016R0PN	2	900Ω (Typ.)	100	6
6	PLT10HH1026R0PN	2	1000Ω (Typ.)	100	6

No.	Part Number	Quantity (pcs.)	Insertion Loss	Rated Voltage (Vdc)	Rated Current (A)
7	BNX002-01	1	1MHz to 1GHz : 40dB min.	50	10
8	BNX003-01	1	5MHz to 1GHz : 40dB min.	150	10
9	BNX005-01	1	1MHz to 1GHz : 40dB min.	50	15
10	BNX012-01	1	1MHz to 1GHz : 40dB min.	50	15
11	BNX016-01	1	100kHz to 1GHz : 40dB min.	25	15
12	BNX022-01	2	1MHz to 1GHz : 35dB min.	50	10
13	BNX023-01	2	1MHz to 1GHz : 35dB min.	100	15
14	BNX024H01	2	100kHz to 1GHz : 35dB min.	50	15
15	BNX025H01	2	50kHz to 1GHz : 35dB min.	25	15



## Block Type EMIFIL®

Series Line Up .....	206
Function Example .....	206
Product Detail .....	209
⚠Caution/Notice .....	213
Soldering and Mounting .....	215
Packaging .....	219
Design Kits .....	220

Chip Ferrite Bead

Chip EMIFIL®


Chip Common Mode Choke Coil

Block Type EMIFIL®


Microwave Absorber

Type	Part Number	Thickness (mm)	Rated Voltage	Effective Frequency Range	Rated Current	$K_{it}$	$\geq 3A$	$F_{low}$	$R_{eFlow}$
SMD Type for Power Lines <small>p209</small>	BNX022-01	3.1	50Vdc	1MHz to 1GHz:35dB min.	10A	$K_{it}$	$\geq 3A$		$R_{eFlow}$
	BNX023-01	3.1	100Vdc	1MHz to 1GHz:35dB min.	15A	$K_{it}$	$\geq 3A$		$R_{eFlow}$
	BNX024H01	3.5	50Vdc	100kHz to 1GHz:35dB min.	15A	$K_{it}$	$\geq 3A$		$R_{eFlow}$
	BNX025H01	3.5	25Vdc	50kHz to 1GHz:35dB min.	15A	$K_{it}$	$\geq 3A$		$R_{eFlow}$
Lead Type for Power Lines <small>p211</small>	BNX002-01	18.0	50Vdc	1MHz to 1GHz:40dB min.	10A	$K_{it}$	$\geq 3A$	$F_{low}$	
	BNX003-01	18.0	150Vdc	5MHz to 1GHz:40dB min.	10A	$K_{it}$	$\geq 3A$	$F_{low}$	
	BNX005-01	18.5	50Vdc	1MHz to 1GHz:40dB min.	15A	$K_{it}$	$\geq 3A$	$F_{low}$	
Lead Type Low Profile for Power Lines <small>p212</small>	BNX012-01	8.0	50Vdc	1MHz to 1GHz:40dB min.	15A	$K_{it}$	$\geq 3A$	$F_{low}$	
	BNX016-01	8.0	25Vdc	100kHz to 1GHz:40dB min.	15A	$K_{it}$	$\geq 3A$	$F_{low}$	

## Suppression of Radiation Noise from Power Line Cable




### Test Result






## Impulse Noise Countermeasure




### Without Filter




Applied Impulse Voltage: 4kV/50nS  
Y-AXIS: 1kV/div


### With Filter



BNX002-01




BNX012-01



BNX022-01

## ESD Countermeasure


ESD Waveform Comparison



## Suppression of Ripple Noise of DC Side in the Switching Power Supply



Test Circuit



Type of Filter	EMI Suppression Effect / Description	
Without Filter	<p>+5.0V→ 50μs/div 0.2V/div</p>	There is high frequency noise of 0.5V maximum.
When BNX002-01 is used	<p>+5.0V→ 50μs/div 0.2V/div</p>	BNX002-01 can suppress most of the noise.

## Example of Impulse Noise Suppression

Type of Filter	EMI Suppression Effect	
Without Filter	<p>Impulse Noise 2000V/50ns</p> <p>Y-axis: 500V/div X-axis: 10ns/sec</p>	
When BNX002 is used	<p>Y-axis: 500V/div X-axis: 10ns/sec</p>	

△Note • Please read rating and △CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# BNX02□ Series




SMD package of block type EMIFIL®.


## BNX022/BNX023



### ■ Dimensions



### ■ Equivalent Circuit




### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	400
K	330mm Reel Embossed Tape	1500
B	Bulk(Bag)	100


## BNX024H/BNX025H



### ■ Dimensions



### ■ Equivalent Circuit



### ■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Reel Embossed Tape	400
K	330mm Reel Embossed Tape	1500
B	Bulk(Bag)	100

Refer to pages from p.215 to p.216 for mounting information.


### ■ Rated Value (□: packaging code)

Part Number	Rated Voltage	Withstand Voltage	Rated Current	Insulation Resistance (min.)	Insertion Loss (20 to 25 degrees C line impedance=50 ohm)	
<b>BNX022-01</b> □	50Vdc	125Vdc	10A	500M ohm	1MHz to 1GHz:35dB min.	Kit ≥3A
<b>BNX023-01</b> □	100Vdc	250Vdc	15A	500M ohm	1MHz to 1GHz:35dB min.	Kit ≥3A
<b>BNX024H01</b> □	50Vdc	125Vdc	15A	100M ohm	100kHz to 1GHz:35dB min.	Kit ≥3A
<b>BNX025H01</b> □	25Vdc	62.5Vdc	15A	50M ohm	50kHz to 1GHz:35dB min.	Kit ≥3A


Operating Temperature Range: -40°C to +125°C (BNX022/BNX023), -55°C to +125°C (BNX024H/BNX025H)

### ■ Insertion Loss Characteristics

#### BNX022/023




#### BNX024H01



Continued on the following page. ↗

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


## ■ Insertion Loss Characteristics BNX025H01



## ■ Notice (Rating)


In operating temperature exceeding +85°C, derating of current is necessary for BNX022 series. Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current




In operating temperature exceeding +85°C, derating of current is necessary for BNX023 series. Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current



In operating temperature exceeding +85°C, derating of current is necessary for BNX024H/025H series. Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# BNX00□ Series




Large insertion loss from several hundred kHz to several GHz.


## BNX002/BNX003



### Dimensions



### Equivalent Circuit




### Packaging

Code	Packaging	Minimum Quantity
-	Box	100


## BNX005



### Dimensions



### Equivalent Circuit



### Packaging

Code	Packaging	Minimum Quantity
-	Box	100


Refer to pages from p.217 to p.218 for mounting information.

### Rated Value

Part Number	Rated Voltage	Withstand Voltage	Rated Current	Insulation Resistance (min.)	Insertion Loss (20 to 25 degrees C line impedance=50 ohm)	
BNX002-01	50Vdc	125Vdc	10A	100M ohm	1MHz to 1GHz:40dB min.	Kit $\geq 3A$
BNX003-01	150Vdc	375Vdc	10A	100M ohm	5MHz to 1GHz:40dB min.	Kit $\geq 3A$
BNX005-01	50Vdc	125Vdc	15A	100M ohm	1MHz to 1GHz:40dB min.	Kit $\geq 3A$

Operating Temperature Range: -30°C to +85°C

### Insertion Loss Characteristics



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.


# BNX01□ Series




Low profile version of BNX series.



## ■ Dimensions



## ■ Equivalent Circuit



## ■ Packaging

Code	Packaging	Minimum Quantity
-	Box	150


Refer to pages from p.217 to p.218 for mounting information.

## ■ Rated Value

Part Number	Rated Voltage	Withstand Voltage	Rated Current	Insulation Resistance (min.)	Insertion Loss (20 to 25 degrees C line impedance=50 ohm)	
BNX012-01	50Vdc	125Vdc	15A	500M ohm	1MHz to 1GHz:40dB min.	Kit ≥3A
BNX016-01	25Vdc	62.5Vdc	15A	50M ohm	100kHz to 1GHz:40dB min.	Kit ≥3A

Operating Temperature Range: -40°C to +125°C


## ■ Insertion Loss Characteristics



## ■ Notice (Rating)

In operating temperature exceeding +85°C, derating of current is necessary for BNX01□ series. Please apply the derating curve shown in chart according to the operating temperature.

### Derating of Rated Current



### ● Connecting ± power line

In case of using ± power line, please connect to each terminal as shown.

Power Supply (BNX Input)	BNX	Circuit (BNX Output)
Power Supply +Bias	B CB	Load Circuit +Bias
Power Supply Ground	PSG CG	Load Circuit Ground
Power Supply -Bias	B CB	Load Circuit -Bias
Power Supply Ground	PSG CG	Load Circuit Ground

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



## ⚠ Caution

### ● Rating

Do not use products beyond the rated current and rated voltage as this may create excessive heat and deteriorate the insulation resistance.

## Notice

### ● Storage and Operating Conditions

#### <Operating Environment>

Do not use products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.

Do not use products in the environment close to the organic solvent.

#### <Storage and Handling Requirements>

##### 1. Storage Period

BNX series should be used within 12 months.

Solderability should be checked if this period is exceeded.

##### 2. Storage Conditions

(1) Storage temperature: -10 to +40°C

Relative humidity: 15 to 85%

Avoid sudden changes in temperature and humidity.

(2) Do not store products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.

### ● Notice (Soldering and Mounting)

#### 1. Cleaning

Do not clean BNX series (SMD Type).

Before cleaning, please contact Murata engineering.

#### 2. Soldering

Reliability decreases with improper soldering methods.

Please solder by the standard soldering conditions shown in mounting information.

#### 3. Other

Noise suppression levels resulting from Murata's EMI suppression filters EMIFIL® may vary, depending on the circuits and ICs used, type of noise, mounting pattern, mounting location, and other operating conditions. Be sure to check and confirm in advance the noise suppression effect of each filter, in actual circuits, etc. before applying the filter in a commercial-purpose equipment design.

### ● Handling

#### 1. Resin Coating

Using resin for coating/molding products may affect the products performance.

So please pay careful attention in selecting resin.


Prior to use, please make the reliability evaluation with the product mounted in your application set.

#### 2. Handling of a Substrate (for BNX02□)


After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate.

Excessive mechanical stress may cause cracking in the Product.

Bending



Twisting



## ⚠ Caution

## ● Rating

Do not use products beyond the rated current and rated voltage as this may create excessive heat and deteriorate the insulation resistance.

## Notice

## ● Storage and Operating Conditions

<Operating Environment>

1. Do not use products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.
2. Do not use products near water, oil or organic solvents.

<Storage and Handling Requirements>

1. Storage Period  
BNX Series should be used within 12 months.  
Solderability should be checked if this period is exceeded.
2. Storage Conditions
  - (1) Storage temperature: -10 to +40°C  
Relative humidity: 15 to 85%  
Avoid sudden changes in temperature and humidity.
  - (2) Do not store products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.

## ● Notice (Soldering and Mounting)

1. Cleaning  
Failure and degradation of a product are caused by the cleaning method. When you clean in conditions that are not in mounting information, please contact Murata engineering.
2. Soldering  
Reliability decreases with improper soldering methods. Please solder by the standard soldering conditions shown in mounting information.
3. Other  
Noise suppression levels resulting from Murata's EMI suppression filters "EMIFIL" may vary, depending on the circuits and ICs used, type of noise, mounting pattern, lead wire length, mounting location, and other operating conditions. Be sure to check and confirm in advance the noise suppression effect of each filter, in actual circuits, etc. before applying the filter in a commercial-purpose equipment design.


## ● Notice (Appearance)

Although some part of the product surface seems to be white in some cases, do not care because it is the result of waxing process for humidity resistance improvement. This wax does not make bad affection to mechanical or electrical performance, reliability of the product.

### 1. Standard Land Pattern Dimensions



BNX022  
BNX023  
BNX024  
BNX025




- (1) A double-sided print board (or multilayer board) as shown in the left figure is designed, and please apply a soldering Cu electrode with a product electrode to a "Land Pattern", apply resist to a "Land Pattern + Solder Resist" at Cu electrode.
- (2) This product is designed to meet large current. Please design PCB pattern which is connected to this product not to become too hot by applied large current.
- (3) Please drop CG on a ground electrode on the back layer (the same also in a multilayer case) by the through hole. And a surface to ground electrode layer may also take a large area as much as possible.
- (4) It is recommended to use a double-sided printed circuit board with BNX mounting on one side and the ground pattern on the other in order to maximize filtering performance, multiple feed through holes are required to maximize the BNX's connection to ground.
- (5) The ground pattern should be designed to be as large as possible to achieve maximum filtering performance.

#### ● PCB Warping (for BNX02□)

PCB should be designed so that products are not subjected to the mechanical stress caused by warping the board.


Products should be located in the sideways direction (Length: a<b) to the mechanical stress.



### 2. Solder Paste Printing and Adhesive Application

When reflow soldering the block type EMIFIL®, the printing must be conducted in accordance with the following cream solder printing conditions.  
If too much solder is applied, the chip will be prone to

damage by mechanical and thermal stress from the PCB and may crack.  
Standard land dimensions should be used for resist and copper foil patterns.

Series	Solder Paste Printing	Adhesive Application
BNX022 BNX023 BNX024 BNX025	<p>●Guideline of solder paste thickness: 150-200μm</p> 	

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

### 3. Standard Soldering Conditions

#### (1) Soldering Methods

Use reflow soldering methods only.

Use standard soldering conditions when soldering block type EMIFIL® SMD type.

In cases where several different parts are soldered, each having different soldering conditions, use those conditions requiring the least heat and minimum time.

Solder: Use Sn-3.0Ag-0.5Cu solder. Use of Sn-Zn based solder will deteriorate performance of products.


Flux:

- Use Rosin-based flux.  
In case of using RA type solder, products should be cleaned completely with no residual flux.
- Do not use strong acidic flux (with chlorine content exceeding 0.20wt%)
- Do not use water-soluble flux.

For additional mounting methods, please contact Murata.

#### (2) Soldering Profile

- Reflow Soldering Profile  
(Sn-3.0Ag-0.5Cu solder)



Series	Standard Profile				Limit Profile			
	Heating		Peak Temperature (T2)	Cycle of Reflow	Heating		Peak Temperature (T4)	Cycle of Reflow
	Temp. (T1)	Time. (t1)			Temp. (T3)	Time. (t2)		
BNX022/023/024/025	220°C min.	30 to 60s	250±3°C	2 times max.	230°C min.	60s max.	260°C/10s	2 times max.

#### (3) Reworking with Solder Iron

The following conditions must be strictly followed when using a soldering iron.

Pre-heating: 150°C 60s min.

Soldering iron power output: 100W max.

Temperature of soldering iron tip / Soldering time / Times:  
450°C max. / 5s max. / 2 time

Do not allow the tip of the soldering iron to directly contact the chip.

For additional methods of reworking with a soldering iron, please contact Murata engineering.

### 4. Cleaning


Do not clean BNX022/023/024/025 series. In case of cleaning, please contact Murata engineering.

## 1. Mounting Hole


■ Mounting holes should be designed as specified below.

BNX00□/01□

Component Side



Terminal Layout (Bottom figure)



## 2. Using the Block Type EMIFIL® (Lead Type) Effectively

### (1) How to use effectively

This product effectively prevents undesired radiation and external noise from going out / entering the circuit by grounding the high frequency components which cause noise problems. Therefore, grounding conditions may affect the performance of the filter and attention should be paid to the following for effective use.

- Design maximized grounding area in the P.C. board, and grounding pattern for all the grounding terminals of the product to be connected. (Please follow the specified recommendations.)
- Minimize the distance between ground of the P.C. board and the ground plate of the product. (Recommend using the through hole connection between grounding area both of component side and bottom side.)
- Insert the terminals into the holes on P.C. board completely.
- Don't connect PSG terminal with CG terminal directly. (See the item 1. Terminal Layout)

### (2) Self-heating


Though this product has a large rated current, localized self-heating may be caused depending on soldering conditions. To avoid this, attention should be paid to the following:

- Use P.C. board with our recommendation on hole diameter / land pattern dimensions, mentioned in the right hand drawing, especially for 4 terminals which pass current.
- Solder the terminals to the P.C. board with soldercover area at least 90%. Otherwise, excess self-heating at connection between terminals and P.C. board may lead to smoke and / or fire of the product even when operating at rated current.
- After installing this product in your product, please make sure the self-heating is within the rated current recommended.


### P. C. Board Patterns

Use a bilateral P.C. board. Insert the BNX into the P.C. board until the root of the terminal is secured, then solder.


#### (1) Component Side View



#### (2) Bottom View




### Recommended Land Pattern



⚠ Note • Please read rating and ⚠ CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

### 3. Soldering

- (1) Use Sn-3.0Ag-0.5Cu solder.
- (2) Use Rosin-based flux. Do not use strong acidic flux with halide content exceeding 0.2wt% (chlorine conversion value).
- (3) Products and the leads should not be subjected to any mechanical stress during the soldering process, or while subjected to the equivalent high temperatures.
- (4) Standard flow soldering profile



### 4. Cleaning

Clean the block Type EMIFIL® (Lead Type) in the following conditions.

- (1) Cleaning temperature should be limited to 60°C max. (40°C max for alcohol type cleaner).
- (2) Ultrasonic cleaning should comply with the following conditions, avoiding the resonance phenomenon at the mounted products and P.C.B.  
Power: 20W/liter max.  
Frequency: 28 to 40kHz  
Time: 5 min. max.
- (3) Cleaner
  - (a) Alcohol type cleaner  
Isopropyl alcohol (IPA)
  - (b) Aqueous agent  
Pine Alpha ST-100S


- (4) There should be no residual flux or residual cleaner left after cleaning.

In the case of using aqueous agent, products should be dried completely after rinsing with de-ionized water in order to remove the cleaner.

- (5) The surface of products may become dirty after cleaning, but there is no deterioration on mechanical, electrical characteristics and reliability.
- (6) Other cleaning: Please contact us.




## ■ Minimum Quantity and Dimensions of 24mm Width Embossed Tape



Dimension of the cavity is measured at the bottom side.

Part Number	Dimensions			Minimum Qty. (pcs.)		
	a	b	c	ø180mm Reel	ø330mm Reel	Bulk
BNX022/023	12.4	9.4	3.3	400	1500	100



Dimension of the cavity is measured at the bottom side.

Part Number	Dimensions			Minimum Qty. (pcs.)		
	a	b	c	ø180mm reel	ø330mm reel	Bulk
BNX024/025	12.4	9.4	3.6	400	1500	100

(in mm)

"Minimum Quantity" means the number of units of each delivery or order. The quantity should be an integral multiple of the "Minimum Quantity."

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# BNX Block Type EMIFIL® Design Kits



## ●EKEPBLCKD

No.	Part Number	Quantity (pcs.)	Common Mode Impedance (at 10MHz, 20 degrees C)	Rated Voltage (Vdc)	Rated Current (A)
1	PLT10HH450180PN	2	45Ω (Typ.)	300	18
2	PLT10HH101150PN	2	100Ω (Typ.)	300	15
3	PLT10HH401100PN	2	400Ω (Typ.)	100	10
4	PLT10HH501100PN	2	500Ω (Typ.)	100	10
5	PLT10HH9016R0PN	2	900Ω (Typ.)	100	6
6	PLT10HH1026R0PN	2	1000Ω (Typ.)	100	6

No.	Part Number	Quantity (pcs.)	Insertion Loss	Rated Voltage (Vdc)	Rated Current (A)
7	BNX002-01	1	1MHz to 1GHz : 40dB min.	50	10
8	BNX003-01	1	5MHz to 1GHz : 40dB min.	150	10
9	BNX005-01	1	1MHz to 1GHz : 40dB min.	50	15
10	BNX012-01	1	1MHz to 1GHz : 40dB min.	50	15
11	BNX016-01	1	100kHz to 1GHz : 40dB min.	25	15
12	BNX022-01	2	1MHz to 1GHz : 35dB min.	50	10
13	BNX023-01	2	1MHz to 1GHz : 35dB min.	100	15
14	BNX024H01	2	100kHz to 1GHz : 35dB min.	50	15
15	BNX025H01	2	50kHz to 1GHz : 35dB min.	25	15



## Microwave Absorber

Part Numbering .....	222
Product Detail .....	223
Notice .....	226

Chip Ferrite Bead

Chip EMIFIL®

Chip Common Mode Choke Coil

Block Type EMIFIL®

Microwave Absorber

# EA Microwave Absorber Part Numbering

(Part Number)

<b>EA</b>	<b>1026</b>	<b>A</b>	<b>160</b>	<b>M</b>	<b>200</b>	<b>200</b>
①	②	③	④	⑤	⑥	⑦

## ① Product ID

Product ID	
<b>EA</b>	Microwave Absorber

## ② Sheet Type

Code	Sheet Type
<b>10□□</b>	Iron carbonyl type (UL certified type/Halogen Free type)
<b>2070</b>	Metal Flake Powder (Halogen Free type)
<b>2100</b>	Metal Flake Powder (UL certified type)
<b>3008</b>	Magnetic material (UL certified type/Halogen Free type)

## ③ Adhesive Tape Type

Code	Adhesive Tape Type
<b>A</b>	Standard tape type (Halogen Free type)
<b>B</b>	Thin Adhesive tape type (Halogen Free type)
<b>L</b>	No tape type
<b>U</b>	UL certified type (Halogen Free type)

## ④ Sheet Thickness

Expressed by 3 digits including the second decimal place in mm.

Ex.)

Code	Sheet Thickness
<b>020</b>	0.20mm

## ⑤ Unit of Dimension

One capital letter expresses Unit of Dimension (⑥) and Dimensions Length (⑦).

Code	Unit of Dimension
<b>M</b>	in mm (Standard)
<b>C</b>	in cm (Standard)

Standard shape is a rectangle.

Please contact us for other shapes.

## ⑥ Dimension (Length)

Expressed by 3 digits including the first decimal place.

## ⑦ Dimension (Width)

Expressed by 3 digits including the first decimal place.

Ex.)

Code	Dimension (Length × Width)
<b>M300150</b>	30.0×15.0 mm
<b>C150100</b>	15.0×10.0 cm

# EA10 Series




## ■ Packaging

When inquiring, please contact us with size code, referring to "Part Numbering."

## ■ Rated Value

Part Number	Applicable Frequency (Typ.)	Thickness (Typ.)	Flame Class	Halogen	Operating Temperature Range
EA1026A100	20.0GHz	1.0mm	UL94V-0	Halogen Free	-40°C to +80°C
EA1026A160	11.5GHz	1.6mm	UL94V-0	Halogen Free	-40°C to +80°C
EA1026A180	10.0GHz	1.8mm	UL94V-0	Halogen Free	-40°C to +80°C
EA1046A180	5.8GHz	1.8mm	UL94V-0	Halogen Free	-40°C to +80°C
EA1075A270	2.5GHz	2.7mm	UL94V-0	Halogen Free	-40°C to +80°C

## ■ Reflection Loss (Typ.)



# EA20/EA21 Series




## ■ Packaging

When inquiring, please contact us with size code, referring to "Part Numbering."

## ■ Rated Value

Part Number	Applicable Frequency (Typ.)	Thickness (Typ.)	Flame Class	Halogen	Operating Temperature Range
EA2070A020	0.1 to 3.0GHz	0.20mm	-	Halogen Free	-40°C to +120°C
EA2070A050	0.1 to 3.0GHz	0.50mm	-	Halogen Free	-40°C to +120°C
EA2070A100	0.1 to 3.0GHz	1.00mm	-	Halogen Free	-40°C to +120°C
EA2070B005	0.1 to 3.0GHz	0.05mm	-	Halogen Free	-40°C to +120°C
EA2070B010	0.1 to 3.0GHz	0.10mm	-	Halogen Free	-40°C to +120°C
EA2070B013	0.1 to 3.0GHz	0.13mm	-	Halogen Free	-40°C to +120°C
EA2070B020	0.1 to 3.0GHz	0.20mm	-	Halogen Free	-40°C to +120°C
EA2070B050	0.1 to 3.0GHz	0.50mm	-	Halogen Free	-40°C to +120°C
EA2100A020	0.1 to 3.0GHz	0.20mm	UL94V-0	-	-40°C to +120°C
EA2100A050	0.1 to 3.0GHz	0.50mm	UL94V-0	-	-40°C to +120°C
EA2100A100	0.1 to 3.0GHz	1.00mm	UL94V-0	-	-40°C to +120°C
EA2100B020	0.1 to 3.0GHz	0.20mm	UL94V-0	-	-40°C to +120°C
EA2100B050	0.1 to 3.0GHz	0.50mm	UL94V-0	-	-40°C to +120°C
EA2100B100	0.1 to 3.0GHz	1.00mm	UL94V-0	-	-40°C to +120°C

## ■ Magnetic Permeability-Reluctance





# EA30 Series




## ■ Packaging

When inquiring, please contact us with size code, referring to "Part Numbering."

## ■ Rated Value

Part Number	Applicable Frequency (Typ.)	Thickness (Typ.)	Flame Class	Halogen	Operating Temperature Range
EA3008U025	0.1 to 3.0GHz	0.25mm	UL94V-0	Halogen Free	-40°C to +120°C
EA3008U035	0.1 to 3.0GHz	0.35mm	UL94V-0	Halogen Free	-40°C to +120°C
EA3008U050	0.1 to 3.0GHz	0.50mm	UL94V-0	Halogen Free	-40°C to +120°C
EA3008U100	0.1 to 3.0GHz	1.00mm	UL94V-0	Halogen Free	-40°C to +120°C
EA3008U250	0.1 to 3.0GHz	2.50mm	UL94V-0	Halogen Free	-40°C to +120°C

## ■ Magnetic Permeability-Reluctance




## Notice

## ● Storage and Operating Conditions

## 1. Adhesive Tape Stress

This product is designed to use adhesive tape to hold itself to the object.

And please avoid causing mechanical stress by bending or variation of the object.



## 2. Cleaning

Avoid cleaning this product.

## 3. Handling of the Product

Adhesive tape must be clean to maintain the quality of adhesion.

Please wipe off any dirt, dust and any kind of oil from the surface of the object before use.

## 4. Storage Conditions

## (1) Storage period

Products that were inspected by Murata over 6 months ago should be examined and used. This can be confirmed by the inspection No. marked on the container.

Adhesiveness should be checked if this period is exceeded.

## (2) Storage conditions

· Products should be stored in the warehouse in the following conditions:

Temperature: -10 to +40°C

Humidity: 30 to 70% relative humidity

No rapid change of temperature or humidity

· Products should be stored in the warehouse without heat shock condition, vibration, direct sunlight and so on.

# Product Guide by Size

Which Size? inch (mm)	Inductor Type	Capacitor Type			Common Mode Choke Coils	Block Type L×W×T(mm)
		Simple Capacitor	LC(RC) Combined	T Circuit Filter Feed Through Type		
01005 (0402)	BLM02A <small>p23</small>					12×11×max13 <small>p211</small> BNX002-01 BNX003-01 Lead
0201 (0603)	BLM03AG <small>p30</small> BLM03AX <small>p28</small> BLM03B <small>p32</small> BLM03E <small>p84</small> BLM03P <small>p25</small> BLM03H <small>p82</small>					
025020 (0605)					DLP0QS <small>p176</small>	
03025 (0806)					DLP0NS <small>p177</small>	12×11×max13.5 <small>p211</small> BNX005-01 Lead
0402 (1005)	BLM15AG <small>p40</small> BLM15AX <small>p38</small> BLM15B <small>p42</small> BLM15HD <small>p85</small> BLM15P <small>p34</small> BLM15HB <small>p85</small> BLM15EG <small>p87</small> BLM15GG <small>p88</small> BLM15HG <small>p85</small> BLM15GA <small>p88</small>		NFL15ST <small>p132</small>			
05025 (1506)					DLP1ND <small>p183</small>	
0504 (1210)					DLM11G <small>p174</small> DLM11S <small>p175</small> DLP11S/11R/11T <small>p179</small>	12×11×max8.5 <small>p212</small> BNX012-01 BNX016-01 Lead
0603 (1608)	BLM18A <small>p54</small> BLM18EG <small>p93</small> BLM18T <small>p60</small> BLM18HE <small>p89</small> BLM18B <small>p56</small> BLM18HG <small>p89</small> BLM18R <small>p61</small> BLM18HD <small>p89</small> BLM18P <small>p48</small> BLM18HB <small>p89</small> BLM18K <small>p50</small> BLM18HK <small>p89</small> BLM18S <small>p52</small> BLM18GG <small>p95</small>	NFM18C <small>p127</small> NFM18P <small>p118</small>	NFL18ST <small>p133</small> NFL18SP <small>p134</small>			
Array			NFA18S <small>p137</small> <small>p138</small> <small>p139</small>			
0804 (2010) Array	BLA2AA <small>p77</small> BLA2AB <small>p77</small>				DLP2AD <small>p184</small>	9.1×12.1×max3.3 <small>p209</small> BNX022-01 BNX023-01 SMD
0805 (2012) Array	BLM21A <small>p66</small> BLM21R <small>p71</small> BLM21B <small>p68</small> BLM21P <small>p64</small>	NFM21C <small>p128</small> NFM21P <small>p121</small> <small>p122</small>	NFL21S <small>p136</small> NFR21G <small>p144</small> NFA21S <small>p140</small> <small>p141</small>		DLW21S <small>p187</small> DLW21H <small>p189</small>	
1205 (3212)		NFM3DC <small>p129</small> NFM3DP <small>p123</small>				
1206 (3216) Array	BLM31P <small>p73</small> BLA31A <small>p80</small> BLA31B <small>p80</small>	NFM31P <small>p124</small> NFM31K <small>p125</small>	NFW31S <small>p142</small> NFA31C <small>p131</small> NFA31G <small>p145</small>	NFE31P <small>p116</small>	DLP31S <small>p182</small> DLW31S <small>p190</small> DLP31D <small>p186</small>	9.1×12.1×max3.7 <small>p209</small> BNX024H01 BNX025H01 SMD
1806 (4516)	BLM41P <small>p75</small>	NFM41C <small>p130</small> NFM41P <small>p126</small>				
2014 (5036)					DLW5AH <small>p167</small> DLW5AT <small>p169</small> <small>p171</small>	
2020 (5050)					DLW5BS <small>p167</small> DLW5BT <small>p169</small> <small>p171</small>	
2606 (6816)				NFE61P <small>p117</small>		

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

## Part Number Quick Reference

### BL□ Series

BLA2AA	p77
BLA2AB	p77
BLA31A	p80
BLA31B	p80
BLM02AX	p23
BLM03AG	p30
BLM03AX	p28
BLM03B	p32
BLM03E	p84
BLM03H	p82
BLM03PG	p25
BLM03PX	p26
BLM15AG	p40
BLM15AX	p38
BLM15B	p44
BLM15BX	p42
BLM15EG	p87
BLM15GA	p88
BLM15GG	p88
BLM15HB	p85
BLM15HD	p85
BLM15HG	p85
BLM15PG/PD	p36
BLM15PX	p34
BLM18A	p54
BLM18B	p56
BLM18EG	p93
BLM18GG	p95
BLM18HB	p89
BLM18HD	p89
BLM18HE	p89
BLM18HG	p89
BLM18HK	p89
BLM18K	p50
BLM18P	p48
BLM18R	p61
BLM18S	p52
BLM18T	p60
BLM21A	p66
BLM21B	p68
BLM21P	p64
BLM21R	p71
BLM31P	p73
BLM41P	p75

### NF□ Series

NFA18SD	p139
NFA18SL	p137
NFA21SL	p140
NFA31C	p131
NFA31G	p145
NFE31P	p116
NFE61P	p117
NFL15ST	p132
NFL18SP	p135
NFL18ST	p133
NFL21SP	p136
NFM18C	p127
NFM18PC	p119
NFM18PS	p118
NFM21C	p128
NFM21PC	p122
NFM21PS	p121
NFM31K	p125
NFM31P	p124
NFM3DC	p129
NFM3DP	p123
NFM41C	p130
NFM41P	p126
NFR21G	p144
NFW31S	p142

### DL□ (PL□) Series

DLM11G	p174
DLM11S	p175
DLP0NS	p177
DLP0QS	p176
DLP11S/11R/11T	p179
DLP1ND	p183
DLP2AD	p184
DLP31D	p186
DLP31S	p182
DLW21H	p189
DLW21S	p187
DLW31S	p190
DLW5AH	p167
DLW5AT	p169
DLW5BS	p167
DLW5BT	p169
PLT10H	p191

### BNX Series

BNX002	p211
BNX003	p211
BNX005	p211
BNX012	p212
BNX016	p212
BNX022	p209
BNX023	p209
BNX024	p209
BNX025	p209

### EA Series

EA10	p223
EA20	p224
EA21	p224
EA30	p225

## Alphabetic Product Name Index

3 Terminal Filter	p107	Chip EMIFIL® LC Combined Type Array	p137
Block Type EMIFIL® LC Combined Type	p209	Chip EMIFIL® LC Combined Wire Wound Type	p142
Chip Common Mode Choke Coil Film Type	p176	Chip EMIFIL® RC Combined Type	p144.145
Chip Common Mode Choke Coil Film Type Array	p184	Chip EMIFIL® RC Combined Type Array	p145
Chip Common Mode Choke Coil Multilayer Type	p174	Chip Ferrite Bead	p13
Chip Common Mode Choke Coil Wire Wound Type	p187	Chip Ferrite Bead Array	p77
Chip Common Mode Choke Coil Wire Wound Type For Large Current	p167	Chip Ferrite Bead For GHz Band Noise	p82
Chip EMIFIL® Array	p77.80.131.137.140.145	Chip Ferrite Bead For High-GHz Band Noise	p88
Chip EMIFIL® Capacitor Type	p107	Common Mode Filter	p159
Chip EMIFIL® Capacitor Type Array	p131	EMIFIL®	p13.107.159.205
Chip EMIFIL® Feed Through Type	p116	EMI Suppression Filter	p13.107.159.205
Chip EMIFIL® For Large Current	p25.116.118.167.209	LC Combined L Circuit Array	p137
Chip EMIFIL® Inductor Type	p13	L Circuit Filter	p137
Chip EMIFIL® LC Combined Multilayer Type	p132	Microwave Absorber	p221
Chip EMIFIL® LC Combined T Circuit Type	p116.132	PI Circuit Filter	p135.136.142
Chip EMIFIL® LC Combined Type	p116	T Circuit Filter	p116.132

⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.  
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Please refer to catalogs below for ferrite cores, Microwave Absorber and leaded EMIFIL®.

## Ferrite Core, Microwave Absorber

### Ferrite Core for EMI Suppression Microwave Absorber

Contents	Thin Type Sandwich Core <FSSA> Core for Flat Cables <FSRC> Beads Core <FSRH> Ring Core <FSRB> Microwave Absorber <EA>
----------	---

This Catalog is PDF version only. Please refer to following URL.  
<http://www.murata.com/products/catalog/pdf/o63e.pdf>



## Lead Type EMIFIL®

### EMI Suppression Filters (Lead Type EMIFIL®)

Contents	Ferrite Beads Inductors <BL01/02/03> Disc Type EMIFIL® <DS□6/DS□9> EMIGUARD® (EMIFIL® with Varistor Function) <VF□3/VF□6/VF□9> Common Mode Choke Coils <PLT>
----------	--



# **EMICON-FUN!**

Please check Murata's newsletter!  
 You can learn about electric parts with fun.  
[http://www.murata.com/products/emicon\\_fun/](http://www.murata.com/products/emicon_fun/)


EMICON-FUN! disseminated widely from basics (principles, characteristics, mounting, etc.) of capacitors, EMI suppression filters and inductors to information can practically be used.  
 Updated information is also distributed via the mail magazine.

**Click here to register as reader → <https://fofa.jp/murata/a.p/107/>**

You can register from Murata Manufacturing Web site page TOP.  
<http://www.murata.com/products/>



← This banner is the entrance of register form



**Capacitor Room**

- Why does the electrostatic capacitance increase as the thickness decreases?
- Next-generation characteristics of capacitors and measurement methods
- What are impedance ESR frequency characteristics in capacitors?
- The voltage characteristics of electrostatic capacitance
- The temperature characteristics of electrostatic capacitance

**Noise suppression filter Room**

- How can the mounting area be reduced? - Methods of using low-ESL capacitors -
- Availability of monolithic ferrite bead development: Horizontally wound-type ferrite beads that support GHz frequencies
- The secret story behind the birth of chip ferrite beads (part 1/2)
- The secret story behind the birth of chip ferrite beads (part 2/2)
- What is inrush current?

**Inductor Room**

- Announcement of inductor development [No. 4] Japan's first air-core horizontal non-wound coil
- Announcement of inductor development [No. 3] The LQI series realized super tight tolerance by trimming
- Why second-generation film-type inductors are incredible!
- Announcement of inductor development [No. 2] Birth of the first film-type inductor: the "LQF15A series"
- Inductor Applied Products Chapter 3: What are Dividers and Couplers?

**For the earth**

- Special Feature on the Environment, Part 3 "Toward a Low-carbon Society - Initiatives for Global Warming Prevention"
- Special Feature on the Environment, Part 2 "Murata's Waste Management Systems"
- Environmental Packaging Materials

**Murata Newsletter**  
 EMICON-FUN! also available.  
 Click here to register as reader

email Magazine: Have fun while learning about electronic components  
**EMICON-FUN!**  
 Wide range of information about capacitors, noise suppression filters, and inductors.

Enter keywords to be searched Search

Global Site Select Region

News Products About MURATA Investor Relations

#####  
 email Magazine: Have fun while learning about electronic components  
 The index of June 14 issue  
 - Inductor Room  
 - Product News  
 - Proposal of the Loss Reduction in the RF Circuit  
 - Industry Pickup - Smart Phones  
 Expertly written articles explain the basics of capacitors, inductors and EMI suppression filters.  
 #####  
 Product News  
 #####  
 - Large Current Common Mode Coil for Automotive Available  
 <PLT10H series>  
 1. Meets large current up to 18A max, suitable for power lines.  
 2. Suitable for surface mounting.  
 3. Large common mode impedance up to 1000ohm [at 10mhz] enables good noise suppression effect.  
 4. Wide operating temperature range from -55°C to 125°C.  
 [PLT10HH9016R0 / 401100 / 101150 / 450180]  
<http://newsletter.murata.co.jp/c/p12celnY3hk>



**⚠Note:**

1. Export Control

<For customers outside Japan>

No Murata products should be used or sold, through any channels, for use in the design, development, production, utilization, maintenance or operation of, or otherwise contribution to (1) any weapons (Weapons of Mass Destruction [nuclear, chemical or biological weapons or missiles] or conventional weapons) or (2) goods or systems specially designed or intended for military end-use or utilization by military end-users.

<For customers in Japan>

For products which are controlled items subject to the "Foreign Exchange and Foreign Trade Law" of Japan, the export license specified by the law is required for export.

2. Please contact our sales representatives or product engineers before using the products in this catalog for the applications listed below, which require especially high reliability for the prevention of defects which might directly damage a third party's life, body or property, or when one of our products is intended for use in applications other than those specified in this catalog.

- |                             |  |
|-----------------------------|--|
| ① Aircraft equipment        | ② Aerospace equipment  |
| ③ Undersea equipment        | ④ Power plant equipment  |
| ⑤ Medical equipment         | ⑥ Transportation equipment (vehicles, trains, ships, etc.)   |
| ⑦ Traffic signal equipment  | ⑧ Disaster prevention / crime prevention equipment   |
| ⑨ Data-processing equipment | ⑩ Application of similar complexity and/or reliability requirements to the applications listed above |

3. Product specifications in this catalog are as of March 2013. They are subject to change or our products in it may be discontinued without advance notice.

Please check with our sales representatives or product engineers before ordering. If there are any questions, please contact our sales representatives or product engineers.

4. Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.

5. This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

6. Please note that unless otherwise specified, we shall assume no responsibility whatsoever for any conflict or dispute that may occur in connection with the effect of our and/or a third party's intellectual property rights and other related rights in consideration of your use of our products and/or information described or contained in our catalogs. In this connection, no representation shall be made to the effect that any third parties are authorized to use the rights mentioned above under licenses without our consent.

7. No ozone depleting substances (ODS) under the Montreal Protocol are used in our manufacturing process.



**Murata Manufacturing Co., Ltd.**

<http://www.murata.com/>

**Head Office**

1-10-1, Higashi Kotari, Nagaokakyo-shi, Kyoto 617-8555, Japan  
Phone: 81-75-951-9111

**International Division**

3-29-12, Shibuya, Shibuya-ku, Tokyo 150-0002, Japan  
Phone: 81-3-5469-6123 Fax: 81-3-5469-6155 E-mail: intl@murata.co.jp

**Cat. No. C31E-25**