




All rights strictly reserved. Reproduction or issue in any form without written authority from the proprietor.
Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite du propriétaire.
FCI
© F C I S.A.



All rights strictly reserved. Reproduction or issue in any form without written authority from the proprietor.
Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite du propriétaire.
FCI
© F C I S.A.



PRODUCT NR:	ROW#	CONFIGURATION																								DIM A	PCB THICKNESS
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24		
85869-X20	D	X	X	X	-	-	-	X	X	X	X	-	-	X	X	X	X	X	X	-	-	X	X	X	X	2.90	1.6
	C	X	X	X	-	-	-	X	X	X	X	-	-	X	X	X	X	X	X	-	-	X	X	X	X		
85869-X20LF	B	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	2.90	1.6
	A	X	X	X	-	-	-	X	X	X	X	X	X	X	X	X	X	X	X	-	-	X	X	X	X		
85869-X21	D	X	X	-	X	X	-	X	X	-	-	X	X	-	X	X	X	X	X	X	X	X	X	X	X	2.90	1.6
	C	X	X	-	X	X	-	X	X	-	-	X	X	-	X	X	X	X	X	X	X	X	X	X	X		
85869-X21LF	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	X	2.90	1.6
	A	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X		
85869-X22	D	-	X	-	-	-	-	X	-	-	-	-	-	X	X	X	X	X	X	-	-	X	-	-	X	2.90	1.6
	C	X	-	-	-	X	-	X	-	-	-	-	-	X	X	X	X	X	X	-	-	X	-	-	X		
85869-X22LF	B	-	X	-	-	X	-	X	-	-	-	-	-	X	X	X	X	X	X	-	-	X	-	-	X	2.90	1.6
	A	X	-	X	-	X	-	X	-	-	-	-	-	X	X	X	X	X	X	-	-	X	-	-	X		
85869-X23	D	-	X	-	X	-	-	X	-	-	-	-	-	X	X	X	X	X	X	-	-	X	-	-	X	2.90	1.6
	C	X	-	-	X	-	-	X	-	-	-	-	-	X	X	X	X	X	X	-	-	X	-	-	X		
85869-X23LF	B	-	X	-	X	-	-	X	-	-	-	-	-	X	X	X	X	X	X	-	-	X	-	-	X	2.90	1.6
	A	X	-	X	-	X	-	X	-	-	-	-	-	X	X	X	X	X	X	-	-	X	-	-	X		
85869-X24	D	-	X	-	X	-	-	X	-	-	-	-	-	X	X	X	X	X	X	-	-	X	-	-	X	2.90	1.6
	C	X	-	X	-	X	-	X	-	-	-	-	-	X	X	X	X	X	X	-	-	X	-	-	X		
85869-X24LF	B	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	2.90	1.6
	A	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X		
85869-X25	D	X	X	-	-	X	X	-	-	-	-	-	-	X	X	X	X	X	X	X	X	X	X	X	X	2.90	1.6
	C	X	X	-	-	X	X	-	-	-	-	-	-	X	X	X	X	X	X	X	X	X	X	X	X		
85869-X25LF	B	X	X	-	-	X	X	-	-	-	-	-	-	X	X	X	X	X	X	X	X	X	X	X	X	2.90	1.6
	A	X	X	-	-	X	X	-	-	-	-	-	-	X	X	X	X	X	X	X	X	X	X	X	X		

"-" POSITION NOT LOADED
"X" POSITION LOADED



- NOTES:
- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
 - 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - 3 PLATING SOLDER TAILS 2-8 μ m SnPb 90-97.
OR 2-8 μ m PURE Sn FOR PART NUMBER WITH LF SUFFIX.
 - 4 INDICATED HOLES ARE UNPLATED.
 - 5 PRODUCT MARKING: PART NUMBER & BATCH ID.
 - 6 SET BACK FOR PRESS BLOCK
 - 7 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
 - 8 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
 - 9 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - 10 THE HOUSING WILL WITHSTAND EXPOSURE TO 245 DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

mat'l. code SEE NOTES		tolerances unless otherwise specified		CUSTOMER COPY		FCI www.fciconnection.com	
litr	ecn no	dr	date	linear	projection	title	RA RECEPTACLE
R				angles		product family	SIG48mm PRESS PEG
		dr	H. Mengede	990525	mm	product family METAL (tm)	code
		engr	M. Loman	990525		size dwg no	213
		chr	M. Loman	990525	scale	A2	85869
		app	M. Loman	990525	5:1	sheet	2 of 2
sheet	revision						
Index	sheet						

