

## 97 Crimping Plier for Western Plugs



97 51 12



4-poles 6-poles 8-poles

- ▶ professional tool for cutting and stripping unshielded ribbon telephone cables
- ▶ for crimping 4-, 6- and 8-pole Western plugs type RJ 10 (7.65 mm width), type RJ 11/12 (9.65 mm width) and type RJ 45 (11.68 mm width)
- ▶ exact crimping process due to parallel crimping
- ▶ repetitive, high crimping quality due to integral lock (self-releasing mechanism)

- ▶ optimum transmission of force due to lever action for fatigue-reduced operation
- ▶ with length cutter and dismantling knife for ribbon cables 6 and 12 mm length
- ▶ head burnished, with two-colour dual component handles




Crimping Plier with cutting and dismantling device

| Article-No. | EAN-Code       | Range of Application                                                                               | Capacity                                                                           | Length<br>mm | g   |
|-------------|----------------|----------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|--------------|-----|
| 97 51 12    | 4003773-043188 | Western plugs<br> | RJ 10, (4-poles) 7.65 mm<br>RJ 11/12 (6-poles) 9.65 mm<br>RJ 45 (8-poles) 11.68 mm | 200          | 530 |
| 97 59 06    | 029700         | 4 spare blades for 97 51 04 / 10 / 12                                                              |                                                                                    |              |     |

## 97 Four-Mandrel Crimping Pliers for turned contacts



97 52 64



97 52 65



- ▶ for crimping turned contacts
- ▶ for solder-free electrical connections
- ▶ four-mandrel crimping for exact crimping performance
- ▶ mandrel gauge to check the basic setting
- ▶ locator for positioning the contacts
- ▶ repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- ▶ these tools have been set precisely (calibrated) in the factory
- ▶ optimum transmission of force due to lever action for fatigue-reduced operation
- ▶ high operation comfort thanks to handy shape
- ▶ all stressed parts are made of special steel, oil-hardened and tempered

### Model 97 52 63:

- ▶ fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- ▶ nickel plated head, two-colour dual component handles

### Model 97 52 64:

- ▶ pressure adjustment depending on the conductor's diameter by means of adjusting wheel in 4 different positions
- ▶ nickel plated head, two-colour dual component handles

### Model 97 52 65:

- ▶ fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- ▶ nickel plated head, plastic handles



Four-mandrel squeezing for exact crimping performance

| Article-No. | EAN-Code       | Range of Application                                                                                                                                                                                 | Capacity   | Length<br>mm | g   |
|-------------|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|--------------|-----|
| 97 52 63    | 4003773-050148 |  turned contacts<br>           | 0.08 - 2.5 | 28 - 13      | 180 |
| 97 52 64    | 041481         |  turned contacts<br>           | 0.08 - 2.5 | 28 - 13      | 180 |
| 97 52 65    | 045236         |  turned contacts (Harting)<br> | 0.14 - 6.0 | 26 - 10      | 230 |