

## Network cable - VS-PPC/ME-PPC/ME-93E-LI/5,0 - 1406438

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Assembled Ethernet cable, CAT5e, shielded, 2-pair, AWG 26 stranded (7-wire), RAL 5021 (water blue), RJ45 plug/IP67 push-pull metal housing on RJ45 plug/IP67 push-pull metal housing, line, length 5 m



### Key commercial data

|                      |          |
|----------------------|----------|
| Packing unit         | 1 pc     |
| Custom tariff number | 85444210 |
| Country of origin    | Poland   |

### Technical data

#### Dimensions

|                 |     |
|-----------------|-----|
| Length of cable | 5 m |
|-----------------|-----|

#### Ambient conditions

|                      |      |
|----------------------|------|
| Degree of protection | IP65 |
|                      | IP67 |

#### General data

|                       |                                |
|-----------------------|--------------------------------|
| Number of positions   | 4                              |
| Signal type/category  | Ethernet CAT5 (IEC 11801:2002) |
|                       | Ethernet CAT5e (TIA 568B:2001) |
| Standards/regulations | IEC PAS 61076-3-117            |
| Pollution degree      | 2                              |

#### Characteristics head 1

|                                          |                                     |
|------------------------------------------|-------------------------------------|
| Head type                                | Plug Straight RJ45 Push Pull / IP67 |
| No. of positions (pin connector pattern) | 4                                   |
| Material (component)                     | Metal                               |

#### Characteristics head 2

# Network cable - VS-PPC/ME-PPC/ME-93E-LI/5,0 - 1406438

## Technical data

### Characteristics head 2

|                                          |                                     |
|------------------------------------------|-------------------------------------|
| Head type                                | Plug Straight RJ45 Push Pull / IP67 |
| No. of positions (pin connector pattern) | 4                                   |
| Material (component)                     | Metal                               |

### Cable

|                                               |                                                    |
|-----------------------------------------------|----------------------------------------------------|
| Cable type                                    | PUR ETHERNET 2x2 FLEX                              |
| Cable type (abbreviation)                     | 93E                                                |
| UL AWM style                                  | 20963 (80°C/30 V)                                  |
| Signal type/category                          | Ethernet CAT5 (IEC 11801:2002), 100 Mbps           |
|                                               | Ethernet CAT5e (TIA 568B:2001), 100 Mbps           |
| Cable structure                               | 2x2xAWG26/7; SF/UTP                                |
| Conductor cross section                       | 2x 2x 0.14 mm <sup>2</sup>                         |
| AWG signal line                               | 26                                                 |
| Conductor structure signal line               | 7x 0.16 mm                                         |
| Core diameter including insulation            | 0.98 mm                                            |
| Wire colors                                   | white/orange-orange, white/green-green             |
| Twisted pairs                                 | 2 cores to the pair                                |
| Overall twist                                 | Two pairs with two fillers to the core             |
| Shielding                                     | Aluminum-coated foil, tinned copper braided shield |
| Optical shield covering                       | 70 %                                               |
| External sheath, color                        | water blue RAL 5021                                |
| External cable diameter D                     | 6.4 mm ±0.2 mm                                     |
| Minimum bending radius, fixed installation    | 4 x D                                              |
| Minimum bending radius, flexible installation | 8 x D                                              |
| Tensile strength short-term/long-term         | ≤ 80N                                              |
| Cable weight                                  | 42 kg/km                                           |
| Outer sheath, material                        | PUR                                                |
| Material conductor insulation                 | Foamed PE                                          |
| Conductor material                            | Bare Cu litz wires                                 |
| Insulation resistance                         | ≥ 500 MΩ*km (at 20 °C)                             |
| Conductor resistance                          | ≤ 290000000 Ω/km (at 20 °C)                        |
| Working capacitance                           | 45 nF (At 1 kHz)                                   |
| Wave impedance                                | 100 Ω ±5 Ω (at 100 MHz)                            |
| Signal runtime                                | 5.3 ns/m                                           |
| Nominal voltage, cable                        | ≤ 100 V                                            |
|                                               | 300 V (Outer cable sheath)                         |
| Test voltage Core/Core                        | 700 V (50 Hz, 1 min.)                              |
| Test voltage Core/Shield                      | 700 V (50 Hz, 1 min.)                              |

## Network cable - VS-PPC/ME-PPC/ME-93E-LI/5,0 - 1406438

### Technical data

#### Cable

|                                         |                                                 |
|-----------------------------------------|-------------------------------------------------|
| Flame resistance                        | IEC 60332-1-2                                   |
| Halogen-free                            | According to IEC 60754-1                        |
| Resistance to oil                       | in accordance with DIN EN 60811-2-1             |
| Ambient temperature (operation)         | -40 °C ... 80 °C (cable, fixed installation)    |
|                                         | -20 °C ... 80 °C (cable, flexible installation) |
| Ambient temperature (installation)      | -20 °C ... 80 °C                                |
| Ambient temperature (storage/transport) | -20 °C ... 80 °C                                |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27060307 |
| eCl@ss 6.0 | 27061801 |
| eCl@ss 7.0 | 27061801 |
| eCl@ss 8.0 | 27061801 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000830 |
| ETIM 4.0 | EC002599 |
| ETIM 5.0 | EC000830 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 26121616 |
| UNSPSC 7.0901 | 26121616 |
| UNSPSC 11     | 26121604 |
| UNSPSC 12.01  | 31261501 |
| UNSPSC 13.2   | 26121616 |

### Drawings


## Network cable - VS-PPC/ME-PPC/ME-93E-LI/5,0 - 1406438

Cable cross section




PUR ETHERNET 2x2 FLEX [93E]

Circuit diagram



Dimensioned drawing



Push-pull RJ45 connector IP65/67