







	SUPERSEDED BY 5-147384-9		88 mm	65.28 [2.570]	32.64 [1.285]	67.97 [2.676]	63.91 [2.516]	49	100	147384-9
	SUPERSEDED BY 5-147384-8		72 mm	52.58 [2.070]	26.29 [1.035]	55.27 [2.176]	51.21 [2.016]	39	80	147384-8
			72 mm	46.23 [1.820]	23.11 [.910]	48.92 [1.926]	44.86 [1.766]	34	70	147384-7
	SUPERSEDED BY 5-147384-6		72 mm	39.88 [1.570]	19.94 [.785]	42.57 [1.676]	38.51 [1.516]	29	60	147384-6
			56 mm	33.53 [1.320]	16.76 [.660]	36.22 [1.426]	32.16 [1.266]	24	50	147384-5
			56 mm	27.18 [1.070]	13.59 [.535]	29.87 [1.176]	25.81 [1.016]	19	40	147384-4
			44 mm	20.83 [.820]	10.41 [.410]	23.52 [.926]	19.46 [.766]	14	30	147384-3
			32 mm	14.48 [.570]	7.24 [.285]	17.17 [.676]	13.11 [.516]	9	20	147384-2
	SUPERSEDED BY 5-147384-1		32 mm	8.12 [.320]	4.06 [.160]	10.82 [.426]	6.75 [.266]	4	10	147384-1
		FINISH	TAPE WIDTH	E	D	C	B	A	NO. OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN B. HAYMAKER QWK J. MOSIER APPROV J. MOSIER	28JAN00 28JAN00 28JAN00	 TE Connectivity	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME ASSEMBLY, RECEPTACLE, VERTICAL, DOUBLE ROW, SURFACE MOUNT, AMPMODU 50/50 GRID CONNECTOR	PRODUCT SPEC 108-1332	APPLICATION SPEC 114-7010	SIZE CAGE CODE DRAWING NO A1 00779 C=147384
	0 PLG ± 1 PLG ± 2 PLG ± 3 PLG ± 0.1x[.005] 4 PLG ± ANGLES				
MATERIAL 	FINISH SEE TABLE				
		CUSTOMER DRAWING		SCALE 10:1 SHEET 1 of 1 REV D.3	

RECOMMENDED BOARD LAYOUT

SCALE: 5:1