


ISS.	AMEND	DATE
1	ISSUED	18/06/09
2	MATERIAL TABLE ADD	20/07/12



DESCRIPTION	MATERIAL	FINISH	QTY
CONTACT PIN	BRASS	SILVER PLATE	5
EARTH TERMINAL	PHOSPHOR BRONZE	SILVER PLATE	1
REAR COVER	PBT 30%GF	BLACK	1
HOUSING	PBT 30%GF	BLACK	1


SPECIFICATION

- CURRENT RATING: 100VAC 1A max
12VDC 2A max
- CONTACT RESISTANCE (INITIAL): 30mΩ max @AC100mA(max) 1kHz
- INSULATION RESISTANCE (INITIAL): 100MΩ (MIN) @500V DC
- WITHSTAND VOL TAGE: 500VAC 60HZ FOR 1 MINUTE
- INSERTION FORCE (INITIAL): 4.5kg max
- WITHDRAWAL FORCE: 0.9-3.0Kg
- LIFE TEST: 5000 CYCLES MIN. AFTER TESTING CONTACT RESISTANCE SHALL NOT EXCEED 100mΩ
- RoHS COMPLIANT

ROHS
COMPLIANT

TOLERANCE
NO DEC. PLACE ±
1 DEC. PLACE ±
2 DEC. PLACE ±

HOLE Ø ±
ANGLES ±
UNLESS
OTHERWISE STATED



VIEW FROM UNDERSIDE

PCB LAYOUT

Cliff Electronic Components Ltd.

76 Holmehorpe Avenue, Holmehorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk
THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2009

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.	3rd ANGLE PROJECTION:	DO NOT SCALE
MATERIAL: PBT +30% GF - UL94V-0 / COMPOSITE METAL	TITLE: 5 PIN DIN SOCKET 180°	
FINISH: AS MOULDED / SILVER PLATED		
DRAWN: C.A.M.J.	APPROVED: R.W.T.	FORM: ADDRWGH

FC680805