


P1,P2:	M-Y222E
	M-222D
P3: M-426E	

Date	Rev.	Description



2009		
P1		P2
1	_____	1
2	_____	2
3	_____	3
Σ 1:1		
23	_____	23
24	_____	24
25	_____	25
SHIELD	_____	SHIELD

4	BLACK PVC TUBE $\phi 3.0 \times 30\text{mm}$	2
	ALUMINUM FOIL 33*110mm	2
	MOLDED PE COLOR TRANSPARENT	
	MOLDED PVC BIEGE	
3	NON-UL 25C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 7.0mm, JACKET BEIGE, DRAWING No. EMAL2825C-095	L-10mm
2	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE	4
1	DB25 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	2
No.	DESCRIPTION	Q'TY

Cable Length Unless Other Spec. Tolerances:	
0 ~200mm	±10mm
201~1000mm	±20mm
1001 ~1500mm	±25mm
1501~2100mm	±30mm
2100mm↑	±40mm
UNIT:mm	

DCC. NO.
A4 DRAWING NO.

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.	
		JAMECO NO. 224267	GOLDSUN NO. 2009-6FT-R
DRAWN: Collin		Description CABLE, EXT, F-F, 25 LINE S, 6' DB25F TO DB25F	Rev. 1
VERIFY PEOPLE: Alvin Lin		UNIT: mm	SHEET 1 OF 1
		SCALE:	CAS No: ERN No: