

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

FT

0

D

REVISED PER ECO-10-013614

13OCT10

HMR

CR

MATERIAL:

HOUSING: THERMOPLASTIC, UL94V-0, BLACK.

TERMINALS: BRIGHT TIN OVER COPPER ALLOY.

SCREWS: #6-32 STEEL, ZINC PLATING W/ CLEAR CHROMATE.

ELECTRICAL:

RATED CURRENT UL/CSA:

CLASS C: 20A, 300V.

CLASS D: 5A, 600V.





WIRE RANGE: 12-22 AWG.

MECHANICAL:

RECOMMENDED TORQUE: 7 IN-LB.


OPERATING TEMP.: 105°C MAX.

1 STAINLESS STEEL SCREWS.



RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHESTOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± .01
3 PLC ± .005
4 PLC ± -
ANGLES ± -
FINISH

MATERIAL

-

DWN 9/15/03

S SCHLEGEL

CHK 9/15/03

S. YODER

APVD 9/15/03

S. YODER

PRODUCT SPEC

-

APPLICATION SPEC


-

WEIGHT

-

CUSTOMER DRAWING

9/15/03



Tyco Electronics Corporation

Harrisburg, Pa 17105-3608

NAME

JC6-P207-XX ASSEMBLY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-3-1437665-3

-

SCALE NTS

SHEET

1

OF

1

REV

D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JC6-P207-08](#) [JC6-P207-10](#) [JC6-P207-03](#) [JC6-P207-06](#) [JC6-P207-05](#) [JC6-P207-20](#)