




RF CONNECTORS



✓ Active

TE CONNECTIVITY (TE)

2058 5573 36

Subminiature Coax | SM , SMA

6311167-1

TE Internal Number: 6311167-1

EU RoHS Compliant with Exemptions

EU ELV Compliant with Exemptions

Connector Interface SMA

Connector Style Jack

Mated Outer Diameter (Approximate) 6.35 mm [.25 in]

Impedance (Ω) 50

Operating Frequency (GHz) 18

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

SMA, PANEL MOUNT, JACK RECEPTACLE STRAIGHT TERMINAL (2058-5573-36)

PDF [\(TIFF AVAILABLE\)](#)

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface SMA

Connector Style Jack

Connector & Contact Terminates To Wire & Cable

Electrical Characteristics

Impedance (Ω) 50

Body Features

Cable Connector Orientation Straight

Body Material Brass

Body Plating Material White Bronze

Contact Features

Center Contact Plating Material Gold

Center Contact Material Beryllium Copper

Connector Product Type Connector Assembly

RF Connector Contact Configuration Captivated Contacts

Mechanical Attachment

Connector Mounting Type Panel

Captivation Method Mechanical

Panel Attachment Style Front Mount

Dimensions

Mated Outer Diameter (Approximate) 6.35 mm [.25 in]

Length 13.21 mm [.521 in]

Operation/Application

Operating Frequency (GHz) 18

Other

Dielectric Material TFE Fluorocarbon

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
