

F1T1G - F1T7G

1.0 AMP. Glass Passivated Fast Recovery Rectifiers


TS-1

Features

- ✧ Glass passivated chip junction.
- ✧ High efficiency, Low VF
- ✧ High current capability
- ✧ High reliability
- ✧ High surge current capability
- ✧ Low power loss

Mechanical Data

- ✧ Cases: Molded plastic
- ✧ Epoxy: UL 94V-0 rate flame retardant
- ✧ Lead: Pure tin plated, Lead free., solderable per MIL-STD-202, Method 208 guaranteed
- ✧ Polarity: Color band denotes cathode end
- ✧ High temperature soldering guaranteed: 260 °C /10 seconds/.375", (9.5mm) lead lengths at 5 lbs., (2.3kg) tension
- ✧ Mounting position: Any
- ✧ Weight: 0.20 gram



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	F1T 1G	F1T 2G	F1T 3G	F1T 4G	F1T 5G	F1T 6G	F1T 7G	Units
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current .375"(9.5mm) Lead Length @T _A = 55 °C	I _(AV)	1.0							A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I _{FSM}	30							A
Maximum Instantaneous Forward Voltage @ 1.0A	V _F	1.3							V
Maximum DC Reverse Current @ T _A =25 °C at Rated DC Blocking Voltage @ T _A =125 °C	I _R	5.0 150							uA uA
Maximum Reverse Recovery Time (Note 1)	T _{rr}	150				250	500		nS
Typical Junction Capacitance (Note 2)	C _j	15							pF
Typical Thermal Resistance (Note 3)	R _{θJA}	90							°C/W
Operating Temperature Range T _J	T _J	-65 to +150							°C
Storage Temperature Range T _{STG}	T _{STG}	-65 to +150							°C

- Notes:
- Reverse Recovery Test Conditions: $I_F = 0.5\text{A}$, $I_R = 1.0\text{A}$, $I_{RR} = 0.25\text{A}$
 - Measured at 1 MHz and Applied Reverse Voltage of 4. 0 Volts D.C.
 - Mount on Cu-Pad Size 5mm x 5mm on P.C.B.

RATINGS AND CHARACTERISTIC CURVES (F1T1G THRU F1T7G)

FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.2- TYPICAL REVERSE CHARACTERISTICS PER LEG




FIG.3- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.5- TYPICAL FORWARD CHARACTERISTICS




FIG.4- TYPICAL JUNCTION CAPACITANCE






FIG.6- REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taiwan Semiconductor:](#)

[F1T1G](#) [F1T2G](#) [F1T3G](#) [F1T4G](#) [F1T5G](#) [F1T6G](#) [F1T7G](#)