

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	V	PRODUCTION ISSUE	30JAN2019	PNT	MT





TABLE OF DIMENSIONS

PART NUMBER	H		J		K		P	R	S	T	HW	JW & KW	C	Weight Nom lb/[gms]
	Min a	Max b	Min a	Max b	Min a	Max b	±10% b	±10% b	±10% b	±10% b	±20% b	±20% b	±5% b	
382A012	13.2 [.52]	6.1 [.24]	6.6 [.26]	3.3 [.13]	6.6 [.26]	3.3 [.13]	22.4 [.88]	19.3 [.76]	23.9 [.94]	15.5 [.61]	1.52 [.06]	1.02 [.04]	22 1/2*	1.81 [.004]
382A023	26.9 [1.06]	12.4 [.49]	13.2 [0.52]	6.1 [.24]	13.2 [.52]	6.1 [.24]	38.1 [1.50]	43.2 [1.70]	53.3 [2.10]	33.0 [1.30]	2.54 [.10]	1.52 [.06]	22 1/2*	11.79 [.026]
382A034	38.6 [1.52]	18.0 [.71]	26.9 [1.06]	12.4 [.49]	26.9 [1.06]	12.4 [.49]	65.5 [2.58]	78.7 [3.10]	78.7 [3.10]	55.9 [2.20]	3.05 [.12]	2.54 [.10]	22 1/2*	63.96 [.141]
382A046	55.6 [2.19]	25.9 [1.02]	26.9 [1.06]	12.7 [.50]	26.9 [1.06]	12.7 [.50]	85.1 [3.35]	94.0 [3.70]	111.8 [4.40]	71.1 [2.80]	4.57 [.18]	2.54 [.10]	22 1/2*	112.95 [.249]

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE Connectivity Ltd.

DIMENSIONS:
mm [INCHES]

DWN 30JAN2019
PRAVEEN N T

CHK 30JAN2019
N NAGAR

APVD 30JAN2019
M TAYLOR

MATERIAL

SEE SHEET 2

FINISH

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.50[.1]

2 PLC ± 0.25[.01]

3 PLC ± 0.13[.005]

4 PLC ± -

ANGLES ± 1°

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

NAME

TRANSITION, Y

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-

382A0XX-XX-0

-

CUSTOMER DRAWING

SCALE


DNS

SHEET

1 OF 2

REV

V



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATABILITY CHART

COMPATABILITY CHART				
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
-3	Polyolefin, Semi-rigid	RT-301	/42;/86;/180	S1017;S1048;S1030
-4	Polyolefin, Flexible	RT-1304	/42;/86;/180	S1017;S1048;S1030
-12	Fluoroelastomer, Flexible	RT-1312	N/A	N/A
-25	Elastomer, Fluid Resistant	RW-2070	/42;/86;/225	S1017;S1048;S1206
-100	Polyolefin, semi-flexible Zerohal	RW-2082	/86;/180	S1048; S1030


ORDERING INFORMATION

Diagram illustrating the breakdown of the part number 382A0XX-XX-XX/XX-0 into its components:

- BASE PART NUMBER: 382A0XX
- MATERIAL DASH NUMBER (SEE COMPATABILITY CHART): -XX
- MODIFICATION NUMBER: -XX
- ADHESIVE SLASH NUMBER (IF NECESSARY, SEE COMPATABILITY CHART): /XX
- COLOR DESIGNATOR: -0

NOTES:

1. DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
 - a - AS SUPPLIED
 - b - AFTER UNRESTRICTED RECOVERY
2. COATING IS OPTIONAL. AS SUPPLIED DIMENSIONS APPEARING IN TABLE ARE FOR UNCOATED PARTS. WHEN COATING IS ADDED, ENTRY DIAMETERS WILL BE REDUCED BY 1.5mm[.06] MAX.
3. MOLDING PORTS ARE OPTIONAL. WHEN -00 MODIFICATION NUMBER IS SPECIFIED MOLDING PORTS WILL BE LOCATED AS SHOWN.
4. WEIGHT SHOWN IN TABLE OF DIMENSIONS IS BASED ON POLYOLEFIN PART.

DIMENSIONS:		DWN	30JAN2019	MATERIAL		FINISH					
mm [INCHES]		PRAVEEN N T		-		-					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	30JAN2019	TE Connectivity Ltd.							
		N NAGAR									
		APVD	30JAN2019	NAME							
		M TAYLOR									
0 PLC ± -		PRODUCT SPEC		TRANSITION, Y							
1 PLC ± 0.50[.1]		-									
2 PLC ± 0.25[.01]		APPLICATION SPEC		SIZE							
3 PLC ± 0.13[.005]											
4 PLC ± -		-		CAGE CODE		DRAWING NO					
ANGLES ± 1°		WEIGHT		A4		00779					
		CUSTOMER DRAWING		©		382A0XX-XX-0					
				RESTRICTED TO		-					
				SCALE		DNS	SHEET				
							2	OF	2	REV	V