



Ausführung / DESIGN



Ausführung / DESIGN




Ausführung / DESIGN



NOTES
Bemerkungen

- 1 Datumscode (Woche/Jahr z.B. KW 38/Jahr2009)
und TE-Revision (z.B. Rev. A)
DATE CODE (WEEK/YEAR E.G. WEEK NUMBER 38/YEAR2009)
AND TE REVISION (E.G. REV. A)
- 2 Passend zu Buchsenkontakt siehe Zeichnung 929454
SUITABLE FOR SOCKET CONTACT SEE DRAWING 929454
- 3 Einzelheiten der Ausführung bleiben dem Hersteller überlassen
DETAILS OF DESIGN ARE LEFT TO MANUFACTURER
- 4 Nur für FLR-Leitung nach DIN 72551 Teil 6
FOR FLR-CONDUCTOR ACCORDING TO DIN 72551-6 ONLY
- 5 nicht für Neuanwendung
NOT FOR NEW APPLICATION
- 6 zugverstärkte Leitung nach LV 112-4
REINFORCED WIRE ACCORDING LV 112-4
- 7 Bei doppelt fallenden Werkzeugen wird die erste Überfeder
mit einer Kennzeichnung "-2" versehen
WITH DOUBLE OUT DIES THE FIRST SPRING WILL BE PROVIDED
WITH AN INDICATION "-2"
- 8 Varianten von Design1 werden durch die entsprechenden
Versionen von Design2 ersetzt
VARIANTS OF DESIGN1 ARE SUPERSEDED BY CORRESPONDING
VERSIONS OF DESIGN2



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. Garcia 06JAN1999 CHK R. Jetter 06JAN1999		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.2		NAME APVD M. Bleicher 13AUG2003	
		PRODUCT SPEC 108-18030 APPLICATION SPEC 114-18021 / -18025		MQS Tabellenzzeichnung Stiftkontakt TABLE PIN CONTACT	
MATERIAL -		FINISH -		WEIGHT -	
		CUSTOMER DRAWING		SIZE A1	
		CAGE CODE 00779		DRAWING NO C=929453	
		RESTRICTED TO -		SCALE 10:1	
		SHEET 1 OF 1		REV 33	