



Non-Polar Aluminum Electrolytic Capacitors

NPAL Series



FEATURES

- Non-polarized, suitable for use in circuits whose polarity is sometimes reversed or unknown
- The leakage current and dissipation factor have been improved
- Close tolerance
- Excellent frequency characteristics in the audio range
- RoHS compliant



CHARACTERISTICS

Item	Characteristics								
Operating Temperature Range	-40°C ~ +85°C								
Capacitance Tolerance	±10% at +20°C, 120Hz								
Leakage Current	I = 0.03CWV or 3μA whichever is greater after 2 minutes of applied rated DC working voltage at 20°C Where: C = rated capacitance in μF; WV = rated DC working voltage								
Dissipation Factor (Tan δ, at +20°C 120Hz)	Working voltage (WV)	6.3	10	16	25	35	50	63	100
	Tan δ	0.25	0.22	0.19	0.16	0.14	0.12	0.10	0.09
	For capacitors whose capacitance exceeds 1,000μF, the specification of tan δ is increased by 0.02 for every addition of 1,000μF.								
Surge Voltage	Working voltage (WV)	6.3	10	16	25	35	50	63	100
	Surge voltage (SV)	8	13	20	32	44	63	79	125
Low Temperature Characteristics	Working voltage (WV)	6.3	10	16	25	35	50	63	100
	Impedance ratio	Z-25°C/Z+20°C	4	3	3	2	2	2	2
		Z-40°C/Z+20°C	8	6	6	4	4	3	3
Life Test	When returned to +20°C after 1,000 hours application of working voltage with the polarity inverted every 250 hours at +85°C, the capacitor will meet the following limits: Capacitance change is ≤±20% of initial value; tan δ is < 200% of initial specified value; leakage current is ≤ initial specified value								
Shelf Test	When returned to +20°C after 1,000 hours +85°C with no voltage applied, the capacitor will meet the following limits: Capacitance change is ≤±20% of initial value; tan δ is < 200% of initial specified value; leakage current is ≤ initial specified value								

PART NUMBERING SYSTEM

1 4 0 - N P A L

Prefix

Series

5 0 V

Voltage
Actual Value

2 2 0 - R C

Capacitance (μF)
Actual Value

Suffix
(RoHS
compliant)


Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.



Non-Polar Aluminum Electrolytic Capacitors

NPAL Series

■ DIMENSIONS AND PERMISSIBLE RIPPLE CURRENT



Lead Dimensions (mm)

ϕD	6.3	8	10	13	16	18
ϕd	0.6	0.6	0.6	0.6	0.8	0.8
α	1.5	1.5	2.0	2.0	2.0	2.0
β	0.5	0.5	1.0	1.0	1.0	1.0

Value (μF)	Working Voltage (WV); Dimensions: $\phi D \times L$ (mm); Ripple Current: mA/RMS @ 120Hz, 85°C															
	6.3		10		16		25		35		50		63		100	
	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
0.1											6.3 x 12	5	6.3 x 13	5	6.3 x 12	5
0.22											6.3 x 12	7	6.3 x 13	8	6.3 x 12	8
0.33											6.3 x 12	9	6.3 x 13	10	6.3 x 12	10
0.47											6.3 x 12	10	6.3 x 13	12	6.3 x 12	12
1											6.3 x 12	16	6.3 x 13	18	6.3 x 12	18
2.2											6.3 x 12	23	6.3 x 13	27	6.3 x 12	27
3.3											6.3 x 12	29	6.3 x 12	31	6.3 x 16	35
4.7											6.3 x 12	34	6.3 x 13	40	6.3 x 16	42
10									6.3 X 13	46	6.3 x 12	54	8 x 13	59	8 x 16	69
15											8 x 13	71	8 x 16	97	10 x 26	
22					6.3 x 13	61	6.3 x 12	69	6.3 x 13	74	8 x 16	89	8 x 16	97	10 x 22	120
33			6.3 x 13	71	6.3 x 13	80	8 x 13	85	8 x 16	101	8 x 16	109	10 x 17	139	10 x 24	153
47			6.3 x 12	85	8 X 13	95	8 x 13	113	8 X 16	120	10 x 17	152	10 x 21	174	10 x 30	203
100	6.3 x 16	118	8 x 13	147	8 x 16	155	10 x 17	192	10 x 17	205	10 x 21	232	13 x 22	269	16 x 28	317
220	8 x 16	195	8 x 16	254	10 x 17	268	10 x 21	298	13 x 22	338	10 x 27	381	16 x 27	447	16 x 37	501
330	8 x 16	239	10 x 17	312	10 x 21	344	13 x 22	387	13 X 27	433	16 x 28	500	16 x 33	567		
470	10 x 17	333	10 x 21	389	13 x 22	436	13 x 27	483	16 x 28	552	16 x 33	668	18 x 42	792		
1000	13 x 22	508	13 x 22	603	13 X 27	664	16 x 28	781	16 x 37	857	18 x 42	1054				
2200	13 x 27	836	16 x 28	1000	16 X 36	1121	18 x 42	1355								

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

[140-NPAL50V68-RC](#) [140-NPAL100V3.3-RC](#) [140-NPAL50V33-RC](#) [140-NPAL100V33-RC](#) [140-NPAL100V47-RC](#)
[140-NPAL50V10-RC](#) [140-NPAL100V22-RC](#) [140-NPAL100V10-RC](#) [140-NPAL100V6.8-RC](#) [140-NPAL50V47-RC](#) [140-](#)
[NPAL100V68-RC](#) [140-NPAL50V2.2-RC](#) [140-NPAL50V1.0-RC](#) [140-NPAL50V5.6-RC](#) [140-NPAL100V220-RC](#) [140-](#)
[NPAL100V1.0-RC](#) [140-NPAL50V3.3-RC](#) [140-NPAL50V100-RC](#) [140-NPAL100V2.2-RC](#) [140-NPAL100V15-RC](#) [140-](#)
[NPAL100V4.7-RC](#) [140-NPAL50V22-RC](#) [140-NPAL50V6.8-RC](#) [140-NPAL50V4.7-RC](#) [140-NPAL100V100-RC](#) [140-](#)
[NPAL50V15-RC](#)